

Regulated Power Supply, 100 to 240V AC, 24V, 3.1A, single phase, Optimized

ABLS1A24031

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Modicon Power Supply
Product or Component Type	Power supply
Power supply type	Regulated switch mode
Variant option	Optimized
Enclosure Material	Plastic
Nominal input voltage	100240 V AC single phase 100240 V AC phase to phase 140340 V DC
Kw Rating	75 W
Output voltage	24 V DC
Power supply output current	3.13 A

Complementary

Efficiency at full load	OF 204 V AC without temperature deseting		
Efficiency at full load	85264 V AC without temperature derating		
	120375 V DC without temperature derating		
Nominal network frequency	5060 Hz		
Network system compatibility	TN		
	TT		
	IT		
Maximum leakage current	1 mA 240 V AC		
Input protection type	Integrated fuse (not interchangeable) 5 A		
	External protection (recommended) 20 A Curve C		
	External protection (recommended) 13 A Curve B		
	External protection (recommended) 10 A Curve C		
Inrush current	40.0 A 115 V		
	80.0 A 230 V		
Power factor	0.55 at 115 V AC		
	0.45 at 230 V AC		
Efficiency	88 % 230 V AC		
Output voltage adjustment	21.626.4 V		
Power dissipation in W	15 W		
Current consumption	< 1.8 A 115 V AC		
	< 1 A 230 V AC		
	< 0.8 A 140 V DC		
Turn-on time	< 1.2 s		
Holding time	> 20 ms 115 V AC		
	> 40 ms 230 V AC		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Startup with capacitive loads	5000 μF		
Residual ripple	< 120 mV		
Meantime between failure [MTBF]	700000 h at 77 °F (25 °C), full load conforming to SR 332		
Output protection type	Against overload and short-circuits, protection technology: automatic reset Against over temperature, protection technology: manual reset Against overvoltage, protection technology: manual reset		
Connections - terminals	Screw connection 0.52.5 mm², AWG 20AWG 14) output Screw connection 0.752.5 mm², AWG 18AWG 14) input		
Line and load regulation	< 0.5 % network 0 to 100 % load at 77 °F (25 °C) < 1 % network full voltage range in line at 77 °F (25 °C)		
Status LED	1 LED (Green) output voltage		
Depth	4.02 in (102 mm)		
Height	4.9 in (123.6 mm)		
Width	1.06 in (27 mm)		
Net Weight	0.49 lb(US) (0.22 kg)		
Output coupling	Parallel Serial		
Mounting support	Top hat type TH35-15 rail IEC 60715 Top hat type TH35-7.5 rail IEC 60715 Double-profile DIN rail		
Supply	SELV IEC 60950-1 SELV IEC 60204-1 SELV IEC 60364-4-41		
Dielectric strength	3000 V AC with input to output		
Service life	10 year(s)		
Overvoltage category	П		

Environment

Standards	IEC 62368-1 EN/IEC 61010-1 EN 61010-2-201 EN/IEC 61204-3 IEC 61000-6-1 IEC 61000-6-2 IEC 61000-6-3 IEC 61000-6-4 IEC 61000-3-2 EN 61000-3-3 UL 62368-1 UL 61010-1 UL 61010-2-201 CSA C22.2 No 62368-1 CSA C22.2 No 61010-1 CSA C22.2 No 61010-2-201 EN/IEC 62368-1
Product certifications	CE CUL Listed CUL Recognized RCM CB Scheme EAC KC NEC class 2
Operating altitude	< 5000 m
Shock resistance	150 m/s² 11 ms
IP degree of protection	IP20

Ambient air temperature for operation	-414 °F (-2010 °C) with current derating of 1 % per °C mounting position A < 6561.68 ft (2000 m)		
	14104 °F (-1040 °C) without derating mounting position A 115 V AC < 6561.68 ft (2000 m) 14122 °F (-1050 °C) without derating mounting position A 230 V AC < 6561.68 ft (2000 m)		
	104158 °F (4070 °C) with current derating of 1.67 % per °C mounting position A 115 V AC < 6561.68 ft (2000 m)		
	122158 °F (5070 °C) with current derating of 2.5 % per °C mounting position A 230 V AC < 6561.68 ft (2000 m)		
Electrical shock protection class	Class I		
Pollution degree	2		
Vibration resistance	3 mm (f= 29 Hz) conforming to IEC 60068-2-6		
	10 m/s² (f= 9200 Hz) conforming to IEC 60068-2-6		
Electromagnetic immunity	Immunity to electrostatic discharge - test level: 8 kV (contact discharge) conforming to IEC 61000-4-2		
	Immunity to electrostatic discharge - test level: 15 kV (air discharge) conforming to IEC 61000-4-2		
	Immunity to conducted RF disturbances - test level: 15 V/m (80 MHz2 GHz) conforming to IEC 61000-4-3		
	Immunity to conducted RF disturbances - test level: 5 V/m (22.7 GHz) conforming to IEC 61000-4-3		
	Immunity to conducted RF disturbances - test level: 5 V/m (2.76 GHz) conforming to IEC 61000-4-3		
	Immunity to fast transients - test level: 4 kV (on input-output) conforming to IEC 61000-4-4		
	Surge immunity test - test level: 4 kV (between power supply and earth) conforming to IEC 61000-4-5		
	Surge immunity test - test level: 3 kV (between phases) conforming to IEC 61000-4-5 Immunity to conducted RF disturbances - test level: 15 V (0.1580 MHz) conforming to IEC 61000-4-6		
	Immunity to magnetic fields - test level: 30 A/m (5060 Hz) conforming to IEC 61000-4-8		
	Immunity to voltage dips conforming to IEC 61000-4-11		
	Disturbing field emission conforming to EN 55016-2-3		
	Limits for harmonic current emissions conforming to IEC 61000-3-2 conforming to EN 55016-1-2		
	conforming to EN 55016-2-1		
Electromagnetic emission	Conducted emissions IEC 61000-6-3		
	Radiated emissions IEC 61000-6-4		

Ordering and shipping details

Category	US1CP1222525
Discount Schedule	CP12
GTIN	3606481500205
Returnability	Yes
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.46 in (3.700 cm)
Package 1 Width	5.51 in (14.000 cm)
Package 1 Length	6.30 in (16.000 cm)
Package 1 Weight	11.393 oz (323.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	22
Package 2 Height	11.81 in (30.000 cm)

Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	16.830 lb(US) (7.634 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	176
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	147.710 lb(US) (67.000 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	648
Environmental Disclosure	Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	698d9b2a-7a6a-4b8f-a149-489156f55645
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

ABLS1A24031


Dimensions Drawings

Electrical Safety

- If the unit is use in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.
- For means of disconnection a switch or circuit breaker, located near the product, must be included in the installation. A marking as disconnecting device for the product is required.
- The device has an internal fuse. The unit is tested and approved with branch circuit protective device up to 20A. This circuit breaker can be used as disconnecting device.
- The power supply is only suitable for audio, video, information, communication, industrial and control equipment.

Dimensions


Front and Side Views



Connections and Schema


Connections and Schema

Correct Parallel Connection



(1): Load


Incorrect Parallel Connection



(1): Load ABLx1Axxxxx-1 = ABLx1Axxxxx-2 max 2 x ABLx1Axxxxx L1 = L2 Δ V max 25 mV I_{Load} < 90% 2 x I_{nom}


Output Voltage Balancing

ABLS1A24031



- (1): R_{Load1}
- (2): R_{Load2}
- $R_{Load1} = R_{Load2}$
- $I_1 = I_2 = \sim I_{nom}$

Series Connection



- (1): V_{out1}
- $\textbf{(2)}: \mathsf{V}_{out2}$
- (3) : 2 x Diode, V_{RRM}> 2 x V_{out1/2}, I_F > 2 x I_{nom1/2}
- (4) : V_{Load} = 2 x V_{out}
- (5) : Load

Connections and Schema


	(1)		
	<40°C	<50°C	<70°C
ABLS1A24021	50°C	60°C	75°C
ABLS1A24038	50°C	60°C	75°C
ABLS1A12062	50°C	60°C	80°C
ABLS1A24031	50°C	60°C	80°C
ABLS1A12100	60°C	70°C	90°C
ABLS1A24050	60°C	70°C	90°C
ABLS1A48025	60°C	70°C	90°C
ABLS1A24100	60°C	70°C	90°C
ABLS1A24200	95°C	95°C	90°C

(1): Ambient


Mounting and Clearance


Mounting

Mounting Position A




Mounting Position B






Incorrect Mounting

ABLS1A24031










ABLS1A24031


Performance Curves

Performance Curve

Mounting Position A



Mounting Position B



- X : Surrounding Air Temperature (°C)
- Y: Percentage of Maximum Load (%)
- 1 : Altitude ≤ 2000 m (6561 ft), Input voltage = 230 VAC / 325 VDC
- 2 : Altitude ≤ 2000 m (6561 ft), 115 VAC / 162 VDC
- 3: Altitude \leq 5000 m (16404 ft), Input voltage = 230 VAC / 325 VDC
- **4** : Altitude ≤ 5000 m (16404 ft), 115 VAC / 162 VDC

Image of product / Alternate images

Alternative









15



