

logic controller, Modicon M241, 24 IO, relay, Ethernet CAN master

TM241CEC24R

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Modicon M241
Product or Component Type	Logic controller
[Us] rated supply voltage	100240 V AC
Discrete input number	14, discrete input 8 fast input IEC 61131-2 Type 1
Discrete output type	Transistor Relay
Discrete output number	6 relay 4 transistor 4 fast output
Discrete output voltage	5125 V DC relay output 5250 V AC relay output 24 V DC transistor output
Discrete output current	2 A relay output Q4Q9) 0.1 A fast output (PTO mode) TR0TR3) 0.5 A transistor output TR0TR3)

Complementary

Discrete I/O number	24
Maximum number of I/O expansion module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)
Supply voltage limits	85264 V
Network Frequency	50/60 Hz
Discrete input logic	Sink or source
Discrete input voltage	24 V
Discrete input voltage type	DC
Voltage state 1 guaranteed	>= 15 V input
Voltage state 0 guaranteed	<= 5 V input
Discrete input current	5 mA input
Input impedance	4.7 kOhm input
Response time	50 μs turn-on, I0I13 input
Configurable filtering time	1 µs fast input
Discrete output logic	Positive logic (source)
Output voltage limits	125 V DC relay output 30 V DC transistor output 277 V AC relay output
Maximum output frequency	1 kHz transistor output 20 kHz fast output (PWM mode) 100 kHz fast output (PLS mode)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Accuracy	+/- 0.1 % 0.020.1 kHz fast output +/- 1 % 0.11 kHz fast output	
Protection type	Short-circuit protection transistor output Short-circuit and overload protection with automatic reset transistor output Reverse polarity protection transistor output Without protection relay output	
Reset time	10 ms automatic reset output 12 s automatic reset fast output	
Memory capacity	64 MB system memory RAM	
Data backed up	128 MB built-in flash memory backup of user programs	
Data storage equipment	<= 16 GB SD card optional)	
Battery type	BR2032 lithium non-rechargeable 4 year(s)	
Backup time	2 years 77 °F (25 °C)	
Execution time for 1 KInstruction	0.3 ms event and periodic task 0.7 ms other instruction	
Application structure	4 cyclic master tasks 8 external event tasks 8 event tasks 3 cyclic master tasks + 1 freewheeling task	
Realtime clock	With	
Clock drift	<= 60 s/month 77 °F (25 °C)	
Positioning functions	PTO 4 100 kHz)	
Counting input number	4 fast input (HSC mode) 200 kHz 14 standard input 1 kHz	
Control signal type	A/B 100 kHz fast input (HSC mode) Pulse/direction 200 kHz fast input (HSC mode) Single phase 200 kHz fast input (HSC mode)	
Integrated connection type	Non isolated serial link serial 1 RJ45 RS232/RS485 Non isolated serial link serial 2 removable screw terminal block RS485 USB port mini B USB 2.0 Ethernet RJ45 CANopen J1939 male SUB-D 9	
Supply	Serial 1)serial link supply 5 V, <200 mA	
Transmission rate	1.2115.2 kbit/s (115.2 kbit/s by default) 49.2 ft (15 m) RS485 1.2115.2 kbit/s (115.2 kbit/s by default) 9.8 ft (3 m) RS232 480 Mbit/s 9.8 ft (3 m) USB 10/100 Mbit/s Ethernet 1000 kbit/s 65.6 ft (20 m) CANopen 800 kbit/s 131.2 ft (40 m) CANopen 500 kbit/s 328.08 ft (100 m) CANopen 250 kbit/s 820.2 ft (250 m) CANopen 125 kbit/s 1640.4 ft (500 m) CANopen 50 kbit/s 328.08 ft (1000 m) CANopen	
Communication port protocol	Non isolated serial link Modbus master/slave	
Port Ethernet	10BASE-T/100BASE-TX - 1 copper cable	
ethernet services	SNMP client/server Modbus TCP slave device Modbus TCP server Modbus TCP client IEC VAR ACCESS FTP client/server SQL client DHCP client Ethernet/IP adapter Send and receive email from the controller based on TCP/UDP library Web server (WebVisu & XWeb system) OPC UA server DNS client	

Local signalling	1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (red) for I/O error (I/O) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED (green) for SL1 1 LED (green) for SL2 1 LED (red) for bus fault on TM4 (TM4) 1 LED per channel (green) for I/O state 1 LED (green) for Ethernet port activity 1 LED (green) for CANopen run 1 LED (green) for CANopen error	
Electrical connection	removable screw terminal block for inputs and outputs pitch 5.08 mm) removable screw terminal block for connecting the 24 V DC power supply pitch 5.08 mm)	
Maximum cable distance between devices	Unshielded cable <164.04 ft (50 m) input Shielded cable <32.8 ft (10 m) fast input Unshielded cable <164.04 ft (50 m) output Shielded cable <9.8 ft (3 m) fast output	
Insulation	Between supply and internal logic 500 V AC Non-insulated between supply and ground	
Marking	CE	
Sensor power supply	24 V DC 400 mA supplied by the controller	
Surge withstand	2 kV power lines (AC) common mode IEC 61000-4-5 2 kV relay output common mode IEC 61000-4-5 1 kV shielded cable common mode IEC 61000-4-5 1 kV power lines (AC) differential mode IEC 61000-4-5 1 kV relay output differential mode IEC 61000-4-5 1 kV input common mode IEC 61000-4-5 1 kV transistor output common mode IEC 61000-4-5	
Web services	Web server	
Maximum number of connections	16 Ethernet/IP device 8 Modbus server	
CANopen feature profile	DR 303-1 DS 301 V4.02	
Number of server device(s)	63 CANopen	
Mounting support	Top hat type TH35-15 rail IEC 60715 Top hat type TH35-7.5 rail IEC 60715 plate or panel with fixing kit	
Height	3.5 in (90 mm)	
Depth	3.7 in (95 mm)	
Width	5.9 in (150 mm)	
Net Weight	1.17 lb(US) (0.53 kg)	
Environment		
Standards	ANSI/ISA 12-12-01 CSA C22.2 No 142 CSA C22.2 No 213 IEC 61131-2:2007 Marine specification (LR, ABS, DNV, GL) UL 508	
Product Certifications	RCM cULus CE UKCA DNV-GL ABS LR	

8 kV in air IEC 61000-4-2 4 kV on contact IEC 61000-4-2

Resistance to electrostatic discharge

Resistance to electromagnetic fields	9.1 V/m (10 V/m) 80 MHz1 GHz IEC 61000-4-3
neius	2.7 V/m (3 V/m) 1.4 GHz2 GHz IEC 61000-4-3
	0.9 V/m (1 V/m) 2 GHz3 GHz IEC 61000-4-3
Resistance to fast transients	2 kV IEC 61000-4-4 power lines)
	2 kV IEC 61000-4-4 relay output)
	1 kV IEC 61000-4-4 Ethernet line)
	1 kV IEC 61000-4-4 serial link)
	1 kV IEC 61000-4-4 input)
	1 kV IEC 61000-4-4 transistor output)
Resistance to conducted	10 V 0.1580 MHz IEC 61000-4-6
disturbances	3 V 0.180 MHz Marine specification (LR, ABS, DNV, GL)
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) Marine
	specification (LR, ABS, DNV, GL)
Electromagnetic emission	Conducted emissions 12069 dBµV/m QP power lines)10150 kHz IEC 55011
· ·	Conducted emissions 63 dB _µ V/m QP power lines)1.530 MHz IEC 55011
	Conducted emissions 79 dBµV/m QP/66 dBµV/m AV power lines)0.150.5 MHz IEC
	55011
	Conducted emissions 73 dBµV/m QP/60 dBµV/m AV power lines)0.5300 MHz IEC
	55011
	Radiated emissions 40 dBµV/m QP class A 10 m)30230 MHz IEC 55011
	Conducted emissions 7963 dBµV/m QP power lines)1501500 kHz IEC 55011
	Radiated emissions 47 dBµV/m QP class A 10 m)2301000 MHz IEC 55011
	·
Immunity to microbreaks	10 ms
Ambient air temperature for	14122 °F (-1050 °C) vertical installation)
operation	14131 °F (-1055 °C) horizontal installation)
Ambient Air Temperature for Storage	-13158 °F (-2570 °C)
Relative humidity	1095 %, without condensation in operation)
	1095 %, without condensation in storage)
IP degree of protection	IP20 with protective cover in place
Pollution degree	2
Operating altitude	06561.68 ft (02000 m)
Storage altitude	09842.5 ft (03000 m)
Vibration resistance	3.5 mm 58.4 Hz symmetrical rail
	3 gn 8.4150 Hz symmetrical rail
	3.5 mm 58.4 Hz panel mounting
	3 gn 8.4150 Hz panel mounting
Shock resistance	15 gn 11 ms

Ordering and shipping details

Category	US10MSX22533
Discount Schedule	0MSX
GTIN	3606480648854
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.46 in (11.335 cm)
Package 1 Width	5.19 in (13.188 cm)
Package 1 Length	7.37 in (18.727 cm)
Package 1 Weight	27.5 oz (780.0 g)

Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	15.56 lb(US) (7.06 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	64
Package 3 Height	29.53 in (75.0 cm)
Package 3 Width	15.75 in (40.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	142.9 lb(US) (64.8 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	2278
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	3d1fb974-648d-4978-8c59-b7dcc486f5a5
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again


○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.


Product data sheet

TM241CEC24R

Dimensions Drawings

Dimensions







Product data sheet

TM241CEC24R


Mounting and Clearance

Clearance






Mounting Position




Acceptable Mounting




NOTE: Expansion modules must be mounted above the logic controller.

Incorrect Mounting



Direct Mounting On a Panel Surface


Mounting Hole Layout



Connections and Schema

Digital Inputs


Wiring Diagram (Positive Logic)



(*): Type T fuse

(1): The COM0, COM1 and COM2 terminals are not connected internally.

Wiring Diagram (Negative Logic)




(*): Type T fuse

(1): The COM0, COM1 and COM2 terminals are not connected internally.

Fast Transistor Outputs


Wiring Diagram



(*): 2 A fast-blow fuse


Relay Outputs

Wiring Diagram




- (*): Type T fuse
- (1): The terminals COM1 to COM4 are not connected internally.
- (2): To improve the life time of the contacts, and to protect from potential inductive load damage, you must connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load

USB Mini-B Connection




Ethernet Connection to a PC



15

CANopen Connection

Wiring Diagram



Pin	Signal	Description	Marking	Color of Cable
1	Not used	Reserved	NC	red
2	CAN_H	CAN_H bus line (dominant high)	CAN_H	white
3	CAN_SHLD	Optional CAN shield	Shield	-
4	CAN_L	CAN_L bus line (dominant low)	CAN_L	blue
5	CAN_GND	CAN Ground	GND	black