

3.3V, 2.5 Gbps Any Input-to-LVPECL Dual Translator

Features

- Input Accepts Virtually All Logic Standards:
 - Single-Ended: SSTL, TTL, CMOS
 - Differential: LVDS, HSTL, CML
- Ensured AC Parameters over Temperature:
 - $f_{MAX} > 2.5$ Gbps (2.5 GHz Toggle)
 - $t_r/t_f < 200$ ps
 - Within-Device Skew < 50 ps
 - Propagation Delay < 400 ps
- Low Power: 46 mW/Channel (Typ.)
- 3.0V to 3.6V Power Supply
- 100K LVPECL Outputs
- Flow-Through Pinout and Fully Differential Design
- Two Channels in a 10-Lead (3 mm x 3 mm) MSOP Package


Applications

- High-Speed Logic
- Data Communication Systems
- Wireless Communication Systems
- Telecom Systems


General Description

The SY55857L is a fully differential, high-speed dual translator optimized to accept any logic standard from single-ended TTL/CMOS to differential LVDS, HSTL, or CML and translate it to LVPECL. Translation is ensured for speeds up to 2.5 Gbps (2.5 GHz toggle frequency). The SY55857L does not internally terminate its inputs, as different interfacing standards have different termination requirements.

Package Type



Functional Block Diagram



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

Power Supply Voltage (V_{CC})	–0.5V to +6.0V
Input Voltage (V_{IN})	–0.5V to $V_{CC} + 0.5V$
Continuous Output Current (I_{OUT})	50 mA
Surge Output Current (I_{OUT})	100 mA

Operating Ratings ‡

Power Supply Voltage (V_{CC})	+3.0V to +3.6V
-----------------------------------	----------------

† **Notice:** Stresses above those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

‡ **Notice:** The device is not guaranteed to function outside its operating ratings.

DC ELECTRICAL CHARACTERISTICS

$T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$, unless noted. [Note 1](#)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Power Supply Voltage	V_{CC}	3.0	3.3	3.6	V	—
Power Supply Current	I_{CC}	—	28	45	mA	Inputs/outputs open

Note 1: The specifications shown are valid after thermal equilibrium has been established.

INPUT ELECTRICAL CHARACTERISTICS

$V_{CC} = +3.0V$ to $+3.6V$; $GND = 0V$; $T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$, unless noted. [Note 1](#)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Input Voltage Swing	V_{ID}	100	—	—	mV	See Figure 1-1 , $V_{IN} < 2.4V$
		200	—	—	mV	$V_{IN} < V_{CC} + 0.3V$
Input High Voltage	V_{IH}	—	—	$V_{CC} + 0.3V$	V	—
Input Low Voltage	V_{IL}	–0.3	—	—	V	—

Note 1: The specifications shown are valid after thermal equilibrium has been established.

100K LVPECL OUTPUT CHARACTERISTICS

$V_{CC} = +3.0V$ to $+3.6V$; $GND = 0V$; $T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$; $R_L = 50\Omega$ to $V_{CC} - 2V$, unless otherwise stated. [Note 1](#)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Output Low Voltage Q, /Q	V_{OL}	$V_{CC} - 1.945$	$V_{CC} - 1.820$	$V_{CC} - 1.695$	V	—
Output High Voltage Q, /Q	V_{OH}	$V_{CC} - 1.145$	$V_{CC} - 1.020$	$V_{CC} - 0.895$	V	—
Output Voltage Swing Q, /Q	V_{OUT}	550	800	—	mV	See Figure 1-1
Differential Output Voltage Swing Q, /Q	V_{DIFF_OUT}	1100	1600	—	mV _{PP}	See Figure 1-2

Note 1: 100K circuits are designed to meet the DC specifications shown in the table above after thermal equilibrium has been established.




FIGURE 1-1: Single-Ended Voltage Swing.




FIGURE 1-2: Differential Voltage Swing.

AC ELECTRICAL CHARACTERISTICS

$V_{CC} = 3.3V \pm 10\%$; $R_L = 50\Omega$ to $V_{CC} - 2V$; $T_A = -40^\circ C$ to $+85^\circ C$, unless otherwise stated.

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Maximum Operating Frequency (Note 1)	f_{MAX}	2.5	—	—	Gbps	$V_{IN} < 2.4V$, NRZ Data
		2.5	—	—	GHz	$V_{IN} < 2.4V$, Clock
		1.25	—	—	Gbps	$V_{IN} < V_{CC} + 0.3V$, NRZ Data
		1.25	—	—	GHz	$V_{IN} < V_{CC} + 0.3V$, Clock
Propagation Delay (D-to-Q)	t_{PD}	—	—	400	ps	—
Within-Device Skew (Diff.)	t_{SKEW}	—	—	50	ps	Note 2
Part-to-Part Skew (Diff.)		—	—	200	ps	Note 3
Random Jitter (RJ)	t_{JITTER}	—	—	1	ps _{RMS}	Note 4
Deterministic Jitter (DJ)		—	—	10	ps _{PP}	Note 5
Total Jitter (TJ)		—	1	10	ps _{PP}	Note 6
Output Rise/Fall Time, 20% to 80%	t_r/t_f	—	—	200	ps	At full output swing.

Note 1: Clock frequency is defined as the maximum toggle frequency, and ensured for functionality only. Measured with a 750 mV signal, 50% duty cycle and V_{OUT} swing ≥ 400 mV. High-frequency AC parameters are ensured by design and characterization.

2: Within-device skew is measured between two different outputs under identical transitions.

3: Part-to-part skew is defined for two parts with identical power supply voltages at the same temperature and with no skew of the edges at the respective inputs.

4: Random jitter is measured with a K28.7 comma detect character pattern, measured at 2.5 Gbps.

5: Deterministic jitter is measured at 2.5 Gbps with both K28.5 and $2^{23}-1$ PRBS pattern.

6: Total jitter definition: with an ideal differential clock input of frequency $\leq f_{MAX}$, no more than one output edge in 10^{12} output edges will deviate by more than the specified peak-to-peak jitter value

TEMPERATURE SPECIFICATIONS

Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions
Temperature Ranges						
Storage Temperature Range	T_S	-65	—	+150	$^\circ C$	—
Lead Temperature	T_{LEAD}	—	—	+260	$^\circ C$	Soldering, 20 sec.
Ambient Temperature Range	T_A	-40	—	+85	$^\circ C$	—
Package Thermal Resistances (Note 1)						
Thermal Resistance, MSOP 10-Ld	θ_{JA}	—	113	—	$^\circ C/W$	Still-Air
	θ_{JA}	—	96	—	$^\circ C/W$	500 lpm
	θ_{JC}	—	42	—	$^\circ C/W$	Junction-to-case

Note 1: Package thermal resistance assumes exposed pad is soldered (or equivalent) to the device's most negative potential (GND) on the PCB. θ_{JC} uses 4-layer θ_{JA} in a still air environment, unless otherwise stated.

2.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in [Table 2-1](#).

TABLE 2-1: PIN FUNCTION TABLE

Pin Number	Pin Name	Description
1, 2	D0, /D0	Channel 0 Differential Inputs (clock or data). See Figure 3-1 for input structure. See the Input Interface section for typical interface recommendations.
3, 4	D1, /D1	Channel 1 Differential Inputs (clock or data). See Figure 3-1 for input structure. See the Input Interface section for typical interface recommendations.
9, 8	Q0, /Q0	Channel 0 Differential 100K-compatible LVPECL Outputs. Terminate to $V_{CC} - 2V$. See the LVPECL Output Termination section. Outputs are low impedance, emitter-followers. For AC-coupled applications, a pull-down resistor is required on Q and /Q to ensure a DC current path to GND.
7, 6	Q1, /Q1	Channel 1 Differential 100K-compatible LVPECL Outputs. Terminate to $V_{CC} - 2V$. See the LVPECL Output Termination section. Outputs are low impedance, emitter-followers. For AC-coupled applications, a pull-down resistor is required on Q and /Q to ensure a DC current path to GND.
5	GND	Device Ground. Typically connected to Logic ground.
10	VCC	Supply Voltage. Typically connect to +3.3V $\pm 10\%$ supply. Bypass with 0.01 μF 0.1 μF low ESR capacitors.

3.0 FUNCTIONAL DESCRIPTION

3.1 Establishing Static Logic Inputs

Do not leave unused inputs floating. Tie either the true or complement inputs to ground, but not both. A logic zero is achieved by connecting the complement input to ground with the true input floating. For a TTL input, tie a 2.5 k Ω resistor between the complement input and ground. See the [Input Interface](#) section.

3.2 Input Levels

LVDS, CML, and HSTL differential signals may be connected directly to the D inputs. Depending on the actual worst case voltage seen, performance of SY55857L varies as per the following table:

TABLE 3-1: INPUT VOLTAGE SWINGS

Input Voltage Range	Minimum Voltage Swing	Maximum Translation Speed
0V to 2.4V	100 mV	2.5 Gbps
0V to $V_{CC} + 0.3V$	200 mV	1.25 Gbps

For LVDS applications, only point-to-point interfaces are supported. Due to the current required by the input structure shown in [Figure 3-1](#), multi-drop and multi-point architectures are not supported.




FIGURE 3-1: Simplified Input Structure.

4.0 INPUT INTERFACE




FIGURE 4-1: 3.3V TTL.




FIGURE 4-5: HSTL.




FIGURE 4-2: DC-Coupled CML.




FIGURE 4-6: AC-Coupled CML, Short Lines.




FIGURE 4-3: 2.5V TTL.




FIGURE 4-7: AC-Coupled CML, Long Lines.




FIGURE 4-4: DC-Coupled PECL.




FIGURE 4-8: LVDS.




FIGURE 4-9: SSDL 2.




FIGURE 4-10: SSDL 3.

5.0 LVPECL OUTPUT TERMINATION

LVPECL outputs have very low output impedance (open emitter) and small signal swing that results in low EMI. LVPECL is ideal for driving 50Ω and 100Ω-controlled impedance transmission lines. There are several techniques in terminating the LVPECL output, as shown in Figure 5-1 through Figure 5-3.




FIGURE 5-1: Parallel Termination: Thevenin Equivalent.




FIGURE 5-2: Parallel Termination: Three-Resistor "Y-Termination".




FIGURE 5-3: Terminating Unused I/O.

6.0 PACKAGING INFORMATION

6.1 Package Marking Information

10-Lead MSOP*



Example




Legend:	XX...X	Product code or customer-specific information
	Y	Year code (last digit of calendar year)
	YY	Year code (last 2 digits of calendar year)
	WW	Week code (week of January 1 is week '01')
	NNN	Alphanumeric traceability code
	(e3)	Pb-free JEDEC® designator for Matte Tin (Sn)
	*	This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package.
	•, ▲, ▼	Pin one index is identified by a dot, delta up, or delta down (triangle mark).
Note:	In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.	
	Underbar (_) and/or Overbar (¯) symbol may not be to scale.	

Note: If the full seven-character YYWWNNN code cannot fit on the package, the following truncated codes are used based on the available marking space:
6 Characters = YYWWNNN; 5 Characters = WWNNN; 4 Characters = WNNN; 3 Characters = NNN;
2 Characters = NN; 1 Character = N



10-Lead Plastic Micro Small Outline Package (DQA)- 3x3x1.0 mm Body [MSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



10-Lead Plastic Micro Small Outline Package (DQA)- 3x3x1.0 mm Body [MSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Dimension Limits	Units	MILLIMETERS		
		MIN	NOM	MAX
Number of Terminals	N	10		
Pitch	e	0.50 BSC		
Overall Height	A	0.94	1.02	1.10
Standoff	A1	0.05	0.10	0.15
Molded Package Thickness	A2	0.91	0.92	0.95
Overall Length	D	3.00 BSC		
Molded Package Length	D1	2.23 BSC		
Overall Width	E	4.90 BSC		
Molded Package Width	E1	3.00 BSC		
Terminal Width	b	0.16	0.23	0.30
Terminal Thickness	c	0.13	0.15	0.23
Footprint	L	0.40	0.55	0.70
Terminal Length	L1	0.95 REF		
Lead Bend Radius	R1	0.08	-	-
Lead Bend Radius	R2	0.08	-	0.20
Foot Angle	θ	0°	3°	6°


Notes:

- Pin 1 visual index feature may vary, but must be located within the hatched area.
- Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-01081 Rev A Sheet 2 of 2

10-Lead Plastic Micro Small Outline Package (DQA)- 3x3x1.0 mm Body [MSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Dimension Limits	Units	MILLIMETERS		
		MIN	NOM	MAX
Contact Pitch	E	0.50 BSC		
Contact Pad Spacing	C		4.40	
Overall Width	Z			6.06
Contact Pad Width (X10)	X1	0.28	0.30	0.32
Contact Pad Length (X10)	Y1	1.24	1.26	1.28
Distance Between Pads (X5)	G1	3.00		
Distance Between Pads (X8)	G	0.20		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-03081 Rev A

APPENDIX A: REVISION HISTORY

Revision A (February 2024)

- Converted Micrel document SY55857L to Microchip data sheet template DS20006853A.
- Minor text changes throughout.

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

<u>Part No.</u>	<u>X</u>	<u>X</u>	<u>X</u>	<u>[-XX]</u>	Examples:
Device	Supply Voltage	Package	Temperature Range	Media Type	
Device:	SY55857:	3.3V, 2.5 Gbps Any Input-to-LVPECL Dual Translator			a) SY55857LKG: SY55857, 3.3V Supply Voltage, 10-Lead MSOP, -40°C to +85°C Temperature Range, 100/Tube b) SY55857LKG-TR: SY55857, 3.3V Supply Voltage, 10-Lead MSOP, -40°C to +85°C Temperature Range, 1,000/Reel Note 1: Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.
Supply Voltage:	L	=	3.3V		
Package:	K	=	10-Lead 3 mm x 3 mm MSOP		
Temperature Range:	G	=	-40°C to +85°C		
Media Type:	<blank> TR	= =	100/Tube 1,000/Reel		

NOTES:

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
 - Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
 - Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
 - Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable" Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.
-

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at <https://www.microchip.com/en-us/support/design-help/client-support-services>.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Klear, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricon, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, TimeCesium, TimeHub, TimePictra, TimeProvider, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, Clockstudio, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, EyeOpen, GridTime, IdealBridge, IGaT, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, IntelliMOS, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, MarginLink, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mSiC, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, Power MOS IV, Power MOS 7, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQL, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, Trusted Time, TSHARC, Turing, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2024, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-6683-4036-3

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Worldwide Sales and Service

AMERICAS

Corporate Office
2355 West Chandler Blvd.
Chandler, AZ 85224-6199
Tel: 480-792-7200
Fax: 480-792-7277
Technical Support:
<http://www.microchip.com/support>
Web Address:
www.microchip.com

Atlanta
Duluth, GA
Tel: 678-957-9614
Fax: 678-957-1455

Austin, TX
Tel: 512-257-3370

Boston
Westborough, MA
Tel: 774-760-0087
Fax: 774-760-0088

Chicago
Itasca, IL
Tel: 630-285-0071
Fax: 630-285-0075

Dallas
Addison, TX
Tel: 972-818-7423
Fax: 972-818-2924

Detroit
Novi, MI
Tel: 248-848-4000

Houston, TX
Tel: 281-894-5983

Indianapolis
Noblesville, IN
Tel: 317-773-8323
Fax: 317-773-5453
Tel: 317-536-2380

Los Angeles
Mission Viejo, CA
Tel: 949-462-9523
Fax: 949-462-9608
Tel: 951-273-7800

Raleigh, NC
Tel: 919-844-7510

New York, NY
Tel: 631-435-6000

San Jose, CA
Tel: 408-735-9110
Tel: 408-436-4270

Canada - Toronto
Tel: 905-695-1980
Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733

China - Beijing
Tel: 86-10-8569-7000

China - Chengdu
Tel: 86-28-8665-5511

China - Chongqing
Tel: 86-23-8980-9588

China - Dongguan
Tel: 86-769-8702-9880

China - Guangzhou
Tel: 86-20-8755-8029

China - Hangzhou
Tel: 86-571-8792-8115

China - Hong Kong SAR
Tel: 852-2943-5100

China - Nanjing
Tel: 86-25-8473-2460

China - Qingdao
Tel: 86-532-8502-7355

China - Shanghai
Tel: 86-21-3326-8000

China - Shenyang
Tel: 86-24-2334-2829

China - Shenzhen
Tel: 86-755-8864-2200

China - Suzhou
Tel: 86-186-6233-1526

China - Wuhan
Tel: 86-27-5980-5300

China - Xian
Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444

India - New Delhi
Tel: 91-11-4160-8631

India - Pune
Tel: 91-20-4121-0141

Japan - Osaka
Tel: 81-6-6152-7160

Japan - Tokyo
Tel: 81-3-6880-3770

Korea - Daegu
Tel: 82-53-744-4301

Korea - Seoul
Tel: 82-2-554-7200

Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906

Malaysia - Penang
Tel: 60-4-227-8870

Philippines - Manila
Tel: 63-2-634-9065

Singapore
Tel: 65-6334-8870

Taiwan - Hsin Chu
Tel: 886-3-577-8366

Taiwan - Kaohsiung
Tel: 886-7-213-7830

Taiwan - Taipei
Tel: 886-2-2508-8600

Thailand - Bangkok
Tel: 66-2-694-1351

Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Fax: 43-7242-2244-393

Denmark - Copenhagen
Tel: 45-4485-5910
Fax: 45-4485-2829

Finland - Espoo
Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching
Tel: 49-8931-9700

Germany - Haan
Tel: 49-2129-3766400

Germany - Heilbronn
Tel: 49-7131-72400

Germany - Karlsruhe
Tel: 49-721-625370

Germany - Munich
Tel: 49-89-627-144-0
Fax: 49-89-627-144-44

Germany - Rosenheim
Tel: 49-8031-354-560

Israel - Ra'anana
Tel: 972-9-744-7705

Italy - Milan
Tel: 39-0331-742611
Fax: 39-0331-466781

Italy - Padova
Tel: 39-049-7625286

Netherlands - Drunen
Tel: 31-416-690399
Fax: 31-416-690340

Norway - Trondheim
Tel: 47-7288-4388

Poland - Warsaw
Tel: 48-22-3325737

Romania - Bucharest
Tel: 40-21-407-87-50

Spain - Madrid
Tel: 34-91-708-08-90
Fax: 34-91-708-08-91

Sweden - Gothenberg
Tel: 46-31-704-60-40

Sweden - Stockholm
Tel: 46-8-5090-4654

UK - Wokingham
Tel: 44-118-921-5800
Fax: 44-118-921-5820