

# OSRAM GW VJLPL1.CM

## Datasheet

Published by **ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved




## OSLON® Pure 1414

# GW VJLPL1.CM

The OSLON Pure® 1414, one of the best lumen density, excellent efficiency and color homogeneity.

The OSLON Pure® 1414 come with full color spectrum and color temperature of 1800K to 6500K that enable customer to perform color tuning and tight clustering. It can be use stand alone as well as in cluster together to achieve the spectrum that you need.



### Applications

- Appliances & Tools
- Entertainment
- Factory Automation
- Indoor Lighting
- Medical Lighting
- Outdoor & Industrial Lighting
- Projection & Display
- Robotics

### Features

- Package: chip level conversion
- Typ. Radiation: 120° (Lambertian emitter)
- Color temperature: 1800K - 6500K
- CRI: 90 (min.), 91 (typ.), R9: 50 (min.)
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- Luminous Flux: typ. 122 lm @ 4000 K, 85 °C
- Luminous efficacy: typ. 124 lm/W @ 4000 K, 85 °C

## Ordering Information

| Type                      | Color temperature | Luminous Flux <sup>1)</sup><br>$I_F = 350 \text{ mA}$<br>$\Phi_V$ | Ordering Code |
|---------------------------|-------------------|-------------------------------------------------------------------|---------------|
| GW VJLPL1.CM-JGK2-XX512-1 | 1800 K            | 70 ... 100 lm                                                     | Q65113A7112   |
| GW VJLPL1.CM-LTLV-XX58-1  | 2700 K            | 105 ... 135 lm                                                    | Q65113A7115   |
| GW VJLPL1.CM-LTLV-XX57-1  | 3000 K            | 105 ... 135 lm                                                    | Q65113A7110   |
| GW VJLPL1.CM-K3LX-XX56-1  | 3500 K            | 115 ... 145 lm                                                    | Q65113A7108   |
| GW VJLPL1.CM-K3LX-XX55-1  | 4000 K            | 115 ... 145 lm                                                    | Q65113A7109   |
| GW VJLPL1.CM-K4LY-XX53-1  | 5000 K            | 120 ... 150 lm                                                    | Q65113A7114   |
| GW VJLPL1.CM-K4LW-XX52-1  | 5700 K            | 120 ... 140 lm                                                    | Q65115A0061   |
| GW VJLPL1.CM-K3LX-XX51-1  | 6500 K            | 115 ... 145 lm                                                    | Q65113A7113   |

## Maximum Ratings

| Parameter                                                                            | Symbol    |                                    | Values  |
|--------------------------------------------------------------------------------------|-----------|------------------------------------|---------|
| Operating Temperature                                                                | $T_{op}$  | min.                               | -40 °C  |
|                                                                                      |           | max.                               | 100 °C  |
| Storage Temperature                                                                  | $T_{stg}$ | min.                               | -40 °C  |
|                                                                                      |           | max.                               | 100 °C  |
| Junction Temperature                                                                 | $T_j$     | max.                               | 135 °C  |
| Forward Current<br>$T_j = 85\text{ °C}$                                              | $I_F$     | min.                               | 10 mA   |
|                                                                                      |           | max.                               | 1000 mA |
| Surge Current<br>$t \leq 10\text{ }\mu\text{s}$ ; $D = 0.005$ ; $T_j = 85\text{ °C}$ | $I_{FS}$  | max.                               | 2000 mA |
| Reverse voltage <sup>2)</sup>                                                        | $V_R$     | Not designed for reverse operation |         |
| ESD withstand voltage<br>acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)               | $V_{ESD}$ | 2 kV                               |         |

Note : Maximum Junction Temperature for 1800K CCT is 125°C.

## Characteristics

 $I_F = 350 \text{ mA}$ ;  $T_J = 85 \text{ °C}$ 

| Parameter                                                                                | Symbol                   |      | Values                                   |
|------------------------------------------------------------------------------------------|--------------------------|------|------------------------------------------|
| Viewing angle at 50% $I_V$                                                               | $2\phi$                  | typ. | 120 °                                    |
| Forward Voltage <sup>3)</sup><br>$I_F = 350 \text{ mA}$                                  | $V_F$                    | min. | 2.60 V                                   |
|                                                                                          |                          | typ. | 2.80 V                                   |
|                                                                                          |                          | max. | 3.00 V                                   |
| Reverse current <sup>2)</sup>                                                            | $I_R$                    |      | Not designed<br>for reverse<br>operation |
| Color Rendering Index <sup>4)</sup>                                                      | CRI                      | min. | 90                                       |
|                                                                                          |                          | typ. | 91                                       |
| Color Rendering Index (R9) <sup>4)</sup>                                                 | CRI (R9)                 | min. | 50                                       |
| Electrical thermal resistance junction/solderpoint<br>with efficiency $\eta_e = 40.0 \%$ | $R_{thJS \text{ elec.}}$ | typ. | 5.9 K / W                                |


## Brightness Groups

| Group | Luminous Flux <sup>1)</sup><br>$I_F = 350 \text{ mA}$<br>min.<br>$\Phi_V$ | Luminous Flux <sup>1)</sup><br>$I_F = 350 \text{ mA}$<br>max.<br>$\Phi_V$ |
|-------|---------------------------------------------------------------------------|---------------------------------------------------------------------------|
| JG    | 70 lm                                                                     | 75 lm                                                                     |
| KY    | 75 lm                                                                     | 80 lm                                                                     |
| KZ    | 80 lm                                                                     | 85 lm                                                                     |
| KS    | 85 lm                                                                     | 90 lm                                                                     |
| K1    | 90 lm                                                                     | 95 lm                                                                     |
| K2    | 95 lm                                                                     | 100 lm                                                                    |
| LT    | 105 lm                                                                    | 110 lm                                                                    |
| LU    | 110 lm                                                                    | 115 lm                                                                    |
| K3    | 115 lm                                                                    | 120 lm                                                                    |
| K4    | 120 lm                                                                    | 125 lm                                                                    |
| K5    | 125 lm                                                                    | 130 lm                                                                    |
| LV    | 130 lm                                                                    | 135 lm                                                                    |
| LW    | 135 lm                                                                    | 140 lm                                                                    |
| LX    | 140 lm                                                                    | 145 lm                                                                    |
| LY    | 145 lm                                                                    | 150 lm                                                                    |


## Forward Voltage Groups

| Group | Forward Voltage <sup>3)</sup><br>$I_F = 350 \text{ mA}$<br>min.<br>$V_F$ | Forward Voltage <sup>3)</sup><br>$I_F = 350 \text{ mA}$<br>max.<br>$V_F$ |
|-------|--------------------------------------------------------------------------|--------------------------------------------------------------------------|
| K1    | 2.60 V                                                                   | 2.70 V                                                                   |
| K2    | 2.70 V                                                                   | 2.80 V                                                                   |
| L1    | 2.80 V                                                                   | 2.90 V                                                                   |
| L2    | 2.90 V                                                                   | 3.00 V                                                                   |

## Chromaticity Coordinate Groups <sup>5)</sup>



## Chromaticity Coordinate Groups <sup>5)</sup>



Chromaticity Coordinate Groups

| CCT    | Center<br>Cx | Center<br>Cy | 3step<br>a | 3step<br>b | 5step<br>a | 5step<br>b | Ø    |
|--------|--------------|--------------|------------|------------|------------|------------|------|
| 1800 K | 0.5492       | 0.4082       | 0.0096     | 0.0046     | 0.016      | 0.0077     | 47.3 |
| 2700 K | 0.4577       | 0.4098       | 0.008      | 0.0041     | 0.0133     | 0.0068     | 54.1 |
| 3000 K | 0.4339       | 0.4032       | 0.0086     | 0.0042     | 0.0142     | 0.0069     | 53.7 |
| 3500 K | 0.4077       | 0.3929       | 0.0093     | 0.0042     | 0.0155     | 0.0069     | 53.9 |
| 4000 K | 0.3818       | 0.3796       | 0.0094     | 0.0041     | 0.0157     | 0.0068     | 53.4 |
| 5000 K | 0.3446       | 0.3551       | 0.0081     | 0.0035     | 0.0135     | 0.0059     | 59.8 |
| 5700 K | 0.3287       | 0.3425       | 0.0072     | 0.0032     | 0.0119     | 0.0052     | 58.8 |
| 6500 K | 0.3123       | 0.3282       | 0.0066     | 0.0027     | 0.011      | 0.0045     | 58.1 |

| CCT    | Group | 1      |        | 2      |        | 3      |        | 4      |        | 5      |        |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
|        |       | Cx     | Cy     | Cx     | Cy     | Cx     | Cy     | Cx     | Cy     | Cx     | Cy     |
| 1800 K | E     | 0.5566 | 0.4195 | 0.5427 | 0.4099 | 0.5452 | 0.4091 | 0.5536 | 0.4150 |        |        |
|        | F     | 0.5566 | 0.4195 | 0.5555 | 0.4061 | 0.5529 | 0.4069 | 0.5536 | 0.4150 |        |        |
|        | G     | 0.5555 | 0.4061 | 0.5418 | 0.3969 | 0.5448 | 0.4015 | 0.5529 | 0.4069 |        |        |
|        | H     | 0.5448 | 0.4015 | 0.5452 | 0.4091 | 0.5427 | 0.4099 | 0.5418 | 0.3969 |        |        |
| 2700 K | E     | 0.4637 | 0.4212 | 0.4491 | 0.4081 | 0.4526 | 0.4088 | 0.4613 | 0.4166 |        |        |
|        | F     | 0.4637 | 0.4212 | 0.4663 | 0.4115 | 0.4628 | 0.4108 | 0.4613 | 0.4166 |        |        |
|        | G     | 0.4663 | 0.4115 | 0.4517 | 0.3984 | 0.4541 | 0.4030 | 0.4628 | 0.4108 |        |        |
|        | H     | 0.4541 | 0.4030 | 0.4526 | 0.4088 | 0.4491 | 0.4081 | 0.4517 | 0.3984 |        |        |
| 3000 K | E     | 0.4393 | 0.4153 | 0.4246 | 0.4002 | 0.4283 | 0.4014 | 0.4371 | 0.4105 |        |        |
|        | F     | 0.4393 | 0.4153 | 0.4432 | 0.4062 | 0.4395 | 0.4050 | 0.4371 | 0.4105 |        |        |
|        | G     | 0.4432 | 0.4062 | 0.4285 | 0.3911 | 0.4307 | 0.3960 | 0.4395 | 0.4050 |        |        |
|        | H     | 0.4307 | 0.3960 | 0.4283 | 0.4014 | 0.4246 | 0.4002 | 0.4285 | 0.3911 |        |        |
| 3500 K | E     | 0.4118 | 0.4054 | 0.3977 | 0.3883 | 0.4017 | 0.3902 | 0.4102 | 0.4004 |        |        |
|        | F     | 0.4118 | 0.4054 | 0.4177 | 0.3975 | 0.4137 | 0.3956 | 0.4102 | 0.4004 |        |        |
|        | G     | 0.4177 | 0.3975 | 0.4036 | 0.3804 | 0.4052 | 0.3854 | 0.4137 | 0.3956 |        |        |
|        | H     | 0.4052 | 0.3854 | 0.4017 | 0.3902 | 0.3977 | 0.3883 | 0.4036 | 0.3804 |        |        |
| 4000 K | E     | 0.3845 | 0.3913 | 0.3714 | 0.3737 | 0.3756 | 0.3760 | 0.3834 | 0.3866 |        |        |
|        | F     | 0.3845 | 0.3913 | 0.3922 | 0.3855 | 0.3880 | 0.3832 | 0.3834 | 0.3866 |        |        |
|        | G     | 0.3922 | 0.3855 | 0.3791 | 0.3679 | 0.3802 | 0.3726 | 0.3880 | 0.3832 |        |        |
|        | H     | 0.3802 | 0.3726 | 0.3756 | 0.3760 | 0.3714 | 0.3737 | 0.3791 | 0.3679 |        |        |
| 5000 K | E     | 0.3451 | 0.3648 | 0.3372 | 0.3528 | 0.3371 | 0.3496 | 0.3396 | 0.3514 | 0.3449 | 0.3609 |
|        | F     | 0.3451 | 0.3648 | 0.3530 | 0.3612 | 0.3496 | 0.3588 | 0.3449 | 0.3609 |        |        |
|        | G     | 0.3530 | 0.3612 | 0.3441 | 0.3454 | 0.3443 | 0.3493 | 0.3496 | 0.3588 |        |        |
|        | H     | 0.3443 | 0.3493 | 0.3396 | 0.3514 | 0.3371 | 0.3496 | 0.3369 | 0.3445 | 0.3441 | 0.3454 |
| 5700 K | E     | 0.3283 | 0.3502 | 0.3212 | 0.3373 | 0.3213 | 0.3365 | 0.3242 | 0.3388 | 0.3284 | 0.3471 |
|        | F     | 0.3283 | 0.3502 | 0.3363 | 0.3486 | 0.3332 | 0.3462 | 0.3284 | 0.3471 |        |        |
|        | G     | 0.3363 | 0.3486 | 0.3291 | 0.3348 | 0.3290 | 0.3379 | 0.3332 | 0.3462 |        |        |
|        | H     | 0.3291 | 0.3348 | 0.3215 | 0.3337 | 0.3213 | 0.3365 | 0.3242 | 0.3388 | 0.3290 | 0.3379 |
| 6500 K | E     | 0.3110 | 0.3340 | 0.3054 | 0.3220 | 0.3082 | 0.3245 | 0.3115 | 0.3317 |        |        |
|        | F     | 0.3110 | 0.3340 | 0.3192 | 0.3344 | 0.3165 | 0.3319 | 0.3115 | 0.3317 |        |        |
|        | G     | 0.3192 | 0.3344 | 0.3136 | 0.3224 | 0.3131 | 0.3247 | 0.3165 | 0.3319 |        |        |
|        | H     | 0.3136 | 0.3224 | 0.3054 | 0.3220 | 0.3082 | 0.3245 | 0.3131 | 0.3247 |        |        |


Group Name on Label

Example: JG-35-K1

| Brightness | Color Chromaticity | Forward Voltage |
|------------|--------------------|-----------------|
| JG         | 35                 | K1              |


## Relative Spectral Emission <sup>6)</sup>

$\Phi_{\text{rel}} = f(\lambda); I_F = 350 \text{ mA}; T_J = 85^\circ \text{C}$




## Radiation Characteristics <sup>6)</sup>

$I_{\text{rel}} = f(\varphi); T_J = 85^\circ \text{C}$




## Forward current <sup>6)</sup>

$$I_F = f(V_F); T_J = 85\text{ °C}$$




## Relative Luminous Flux <sup>6), 7)</sup>

$$\Phi_V / \Phi_V(350\text{ mA}) = f(I_F); T_J = 85\text{ °C}$$




## Chromaticity Coordinate Shift <sup>6)</sup>

$$\Delta Cx, \Delta Cy = f(I_F); T_J = 85\text{ °C}$$




## Forward Voltage <sup>6)</sup>

$$\Delta V_F = V_F - V_F(85^\circ\text{C}) = f(T_j); I_F = 350\text{ mA}$$




## Relative Luminous Flux <sup>6)</sup>

$$\Phi_V / \Phi_V(85^\circ\text{C}) = f(T_j); I_F = 350\text{ mA}$$




## Chromaticity Coordinate Shift <sup>6)</sup>

$$\Delta C_x, \Delta C_y = f(T_j); I_F = 350\text{ mA}$$




## Max. Permissible Forward Current <sup>8)</sup>

$$I_F = f(T)$$




## Permissible Pulse Handling Capability

$I_F = f(t_p)$ ; duty cycle  $D = \text{parameter}$ ;  $T_s = 25^\circ\text{C}$





## Permissible Pulse Handling Capability


$I_F = f(t_p)$ ; duty cycle  $D = \text{parameter}$ ;  $T_s = 100^\circ\text{C}$



Dimensional Drawing <sup>9)</sup>



| CRI 90      |      |
|-------------|------|
| CCT         | T    |
| 1800K       | 0.85 |
| 2700K-6500K | 0.75 |



general tolerance  $\pm 0.1$

lead finish Au 


C67062-A0479-A3-01

Further Information:

Approximate Weight: 6.0 mg

Package marking: Cathode

## Recommended Solder Pad <sup>9)</sup>



E067.0346.25-01

For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere, further information can be found in our Application Note : "Handling and Processing Details for Ceramic LEDs". Package not suitable for any kind of wet cleaning or ultrasonic cleaning.

## Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E





| Profile Feature                                                       | Symbol | Pb-Free (SnAgCu) Assembly |                |         | Unit               |
|-----------------------------------------------------------------------|--------|---------------------------|----------------|---------|--------------------|
|                                                                       |        | Minimum                   | Recommendation | Maximum |                    |
| Ramp-up rate to preheat <sup>*)</sup><br>25 °C to 150 °C              |        |                           | 2              | 3       | K/s                |
| Time $t_s$<br>$T_{Smin}$ to $T_{Smax}$                                | $t_s$  | 60                        | 100            | 120     | s                  |
| Ramp-up rate to peak <sup>*)</sup><br>$T_{Smax}$ to $T_p$             |        |                           | 2              | 3       | K/s                |
| Liquidus temperature                                                  | $T_L$  |                           | 217            |         | $^{\circ}\text{C}$ |
| Time above liquidus temperature                                       | $t_L$  |                           | 80             | 100     | s                  |
| Peak temperature                                                      | $T_p$  |                           | 245            | 260     | $^{\circ}\text{C}$ |
| Time within 5 °C of the specified peak temperature $T_p - 5\text{ K}$ | $t_p$  | 10                        | 20             | 30      | s                  |
| Ramp-down rate*<br>$T_p$ to 100 °C                                    |        |                           | 3              | 6       | K/s                |
| Time<br>25 °C to $T_p$                                                |        |                           |                | 480     | s                  |

All temperatures refer to the center of the package, measured on the top of the component


\* slope calculation  $DT/Dt$ :  $Dt$  max. 5 s; fulfillment for the whole T-range

## Taping <sup>9)</sup>



C67062-A0479-B1-01

## Tape and Reel <sup>10)</sup>



## Reel Dimensions

| A      | W                  | N <sub>min</sub> | W <sub>1</sub> | W <sub>2 max</sub> | Pieces per PU |
|--------|--------------------|------------------|----------------|--------------------|---------------|
| 180 mm | 8 + 0.3 / - 0.1 mm | 60 mm            | 8.4 + 2 mm     | 14.4 mm            | 1000          |

|                                                                                    |                |                                                                                    |                                                                                     |
|------------------------------------------------------------------------------------|----------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| <b>OSRAM</b>                                                                       |                | LX XXXX                                                                            | BIN1: XX-XX-X-XXX-X                                                                 |
|                                                                                    |                | RoHS Compliant                                                                     |                                                                                     |
| (6P) BATCH NO: 1234567890                                                          |                |                                                                                    |                                                                                     |
|   |                |  | ML Temp ST<br>X XXX °C X                                                            |
| (1T) LOT NO: 1234567890                                                            | (9D) D/C: 1234 |                                                                                    |  |
|   |                | Pack: RXX<br>DEMY XXX<br>X_X123_1234.1234 X                                        |                                                                                     |
| (X) PROD NO: 123456789                                                             | (Q) QTY: 9999  | (G) GROUP: XX-XX-X-X                                                               |                                                                                     |
|  |                |                                                                                    |                                                                                     |

The diagram illustrates the components of a moisture-sensitive package for a semiconductor device. It shows a large rectangular package and a smaller circular package, both with labels and desiccant indicators.

- Moisture-sensitive label or print:** A label on the large rectangular package.
- Barcode label:** A label on the large rectangular package.
- Humidity indicator:** A small indicator on the circular package.
- Barcode label:** A label on the circular package.
- Desiccant:** A small packet shown next to the large rectangular package.

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

---

## Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **moderate risk (exposure time 0.25 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

This device is designed for specific/recommended applications only. Please consult OSRAM Opto Semiconductors Sales Staff in advance for detailed information on other non-recommended applications (e.g. automotive).

Change management for this component is aligned with the requirements of the lighting market.

For further application related information please visit <https://ams-osram.com/support/application-notes>

---

## Disclaimer

### Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

### Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

### Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

---

## Glossary

- 1) **Brightness:** Brightness values are measured during a current pulse of typically 10 ms, with a tolerance of +/- 7%.
- 2) **Reverse Operation:** Not designed for reverse operation. Continuous reverse operation can cause migration and damage of the device.
- 3) **Forward Voltage:** The Forward voltage is measured during a current pulse duration of typically 1 ms with a tolerance of  $\pm 0.05V$ .
- 4) **Color reproduction index:** Color reproduction index values (CRI-RA) are measured during a current pulse of typically 10 ms and with a tolerance of  $\pm 2$ .
- 5) **Chromaticity coordinate groups:** Chromaticity coordinate groups are measured during a current pulse duration of typically 10ms with a tolerance of  $\pm 0.005$ .
- 6) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 7) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- 8) **Thermal Resistance:**  $R_{th\ max}$  is based on statistic values ( $6\sigma$ ) used for Derating.
- 9) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with  $\pm 0.1$  and dimensions are specified in mm.
- 10) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Revision History

| Version | Date       | Change                                                 |
|---------|------------|--------------------------------------------------------|
| 1.0     | 2023-11-06 | Initial Version                                        |
| 1.1     | 2024-02-05 | Description                                            |
| 1.3     | 2024-04-03 | Certificate Logo<br>Applications<br>Characteristics    |
| 1.4     | 2025-01-16 | Ordering Information<br>Chromaticity Coordinate Groups |



EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求；  
按照中国的相关法规和标准，  
不含有毒有害物质或元素。

**Published by ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved

**am**

**OSRAM**