

BFP450

Surface mount high linearity wideband silicon NPN RF bipolar transistor



Order now



Technical
documents



Simulation



Support

Product description

The BFP450 is a low noise device based on a grounded emitter (SIEGET™) that is part of Infineon's established fourth generation RF bipolar transistor family. Its transition frequency f_T of 24 GHz, collector design and high linearity characteristics make the device suitable for energy efficiency applications up to 3 GHz. It remains cost competitive without compromising on ease of use.



Feature list

- Minimum noise figure $NF_{min} = 1.7$ dB at 1.9 GHz, 3 V, 50 mA
- High gain $G_{ma} = 15.5$ dB at 1.9 GHz, 3 V, 90 mA
- $OIP_3 = 31$ dBm at 1.9 GHz, 3 V, 90 mA

Product validation

Qualified for industrial applications according to the relevant tests of JEDEC JESD47, JESD22, and J-STD-020.
Qualified for industrial applications according to the relevant tests of AEC-Q 101.

Potential applications

- Broadband amplifiers
- Low noise, high linearity amplifiers for sub-1 GHz ISM band applications

Device information

Table 1 Part information

Product name / Ordering code	Package	Pin configuration				Marking	Pieces / Reel
BFP450 / BFP450H6327XTSA1	SOT343	1 = B	2 = E	3 = C	4 = E	ANs	3000
BFP450 / BFP450H6433XTMA1							10000

Attention: *ESD (Electrostatic discharge) sensitive device, observe handling precautions*

Table of contents**Table of contents**

Product description	1
Feature list	1
Product validation	1
Potential applications	1
Device information	1
Table of contents	2
1 Absolute maximum ratings	3
2 Thermal characteristics	4
3 Electrical characteristics	5
3.1 DC characteristics	5
3.2 General AC characteristics	5
3.3 Frequency dependent AC characteristics	6
3.4 Characteristic DC diagrams	9
3.5 Characteristic AC diagrams	12
4 Package information SOT343	19
Revision history	20
Disclaimer	21

Absolute maximum ratings**1 Absolute maximum ratings****Table 2 Absolute maximum ratings at $T_A = 25^\circ\text{C}$ (unless otherwise specified)**

Parameter	Symbol	Values		Unit	Note or test condition
		Min.	Max.		
Collector emitter voltage	V_{CEO}	-	4.5	V	Open base
			4.1		$T_A = -55^\circ\text{C}$, open base
Collector emitter voltage	V_{CES}	15			E-B short circuited
Collector base voltage			15		Open emitter
Emitter base voltage	V_{EBO}	1.5			Open collector
Base current			10		-
Collector current	I_C	170			
Total power dissipation ¹⁾			500		$T_S \leq 90^\circ\text{C}$
Junction temperature	T_J	150		$^\circ\text{C}$	-
Storage temperature			-55		

Attention: *Stresses above the max. values listed here may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Exceeding only one of these values may cause irreversible damage to the integrated circuit.*

¹⁾ T_S is the soldering point temperature. T_S is measured on the emitter lead at the soldering point of the PCB.

Thermal characteristics

2 Thermal characteristics

Table 3 Thermal resistance

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Junction - soldering point	R_{thJS}	–	120	–	K/W	–




Figure 1

Total power dissipation $P_{tot} = f(T_s)$

Electrical characteristics

3 Electrical characteristics

3.1 DC characteristics

Table 4 DC characteristics at $T_A = 25^\circ\text{C}$

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Collector emitter breakdown voltage	$V_{(\text{BR})\text{CEO}}$	4.5	5	-	V	$I_C = 1 \text{ mA}$, $I_B = 0$, open base
Collector emitter leakage current	I_{CES}	-	- 1 30 ²⁾	1 ²⁾ 30 ²⁾	μA nA	$V_{\text{CE}} = 15 \text{ V}$, $V_{\text{BE}} = 0$, $V_{\text{CE}} = 3 \text{ V}$, $V_{\text{BE}} = 0$, E-B short circuited
Collector base leakage current	I_{CBO}		1	30 ²⁾	nA	$V_{\text{CB}} = 3 \text{ V}$, $I_E = 0$, open emitter
Emitter base leakage current	I_{EBO}		0.05	3 ²⁾	μA	$V_{\text{EB}} = 0.5 \text{ V}$, $I_C = 0$, open collector
DC current gain	h_{FE}	60 50	95 85	130 120		$V_{\text{CE}} = 4 \text{ V}$, $I_C = 50 \text{ mA}$, $V_{\text{CE}} = 3 \text{ V}$, $I_C = 90 \text{ mA}$, pulse measured

3.2 General AC characteristics

Table 5 General AC characteristics at $T_A = 25^\circ\text{C}$

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Transition frequency	f_T	18	24	-	GHz	$V_{\text{CE}} = 3 \text{ V}$, $I_C = 90 \text{ mA}$, $f = 1 \text{ GHz}$
Collector base capacitance	C_{CB}	-	0.48	0.8	pF	$V_{\text{CB}} = 3 \text{ V}$, $V_{\text{BE}} = 0$, $f = 1 \text{ MHz}$, emitter grounded
Collector emitter capacitance	C_{CE}		1.2	-		$V_{\text{CE}} = 3 \text{ V}$, $V_{\text{BE}} = 0$, $f = 1 \text{ MHz}$, base grounded
Emitter base capacitance	C_{EB}		1.7			$V_{\text{EB}} = 0.5 \text{ V}$, $V_{\text{CB}} = 0$, $f = 1 \text{ MHz}$, collector grounded

² Maximum values not limited by the device but by the short cycle time of the 100% test.

Electrical characteristics

3.3 Frequency dependent AC characteristics

Measurement setup is a test fixture with Bias-T's in a 50Ω system, $T_A = 25^\circ\text{C}$.




Figure 2 Testing circuit

Table 6 AC characteristics, $V_{CE} = 3 \text{ V}$, $f = 150 \text{ MHz}$

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Power gain	G_{ms} $ S_{21} ^2$	–	35.5 33.5	–	dB	$I_C = 90 \text{ mA}$
• Maximum power gain • Transducer gain						
Noise figure	NF_{min} G_{ass}		1.55 32		dBm	$I_C = 50 \text{ mA}$
• Minimum noise figure • Associated gain						
Linearity	OIP_3 OP_{1dB}		30.5 19		dBm	$Z_S = Z_L = 50 \Omega, I_C = 90 \text{ mA}$
• 3rd order intercept point at output • 1 dB gain compression point at output						

Table 7 AC characteristics, $V_{CE} = 3 \text{ V}$, $f = 450 \text{ MHz}$

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Power gain	G_{ms} $ S_{21} ^2$	–	29 25	–	dB	$I_C = 90 \text{ mA}$
• Maximum power gain • Transducer gain						
Noise figure	NF_{min} G_{ass}		1.55 27.5		dBm	$I_C = 50 \text{ mA}$
• Minimum noise figure • Associated gain						
Linearity	OIP_3 OP_{1dB}		30 19		dBm	$Z_S = Z_L = 50 \Omega, I_C = 90 \text{ mA}$
• 3rd order intercept point at output • 1 dB gain compression point at output						

Electrical characteristics

Table 8 AC characteristics, $V_{CE} = 3$ V, $f = 900$ MHz

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Power gain	G_{ms} $ S_{21} ^2$	-	23.5	-	dB	$I_C = 90$ mA
• Maximum power gain • Transducer gain			19			
Noise figure	NF_{min} G_{ass}		1.6	-	dBm	$I_C = 50$ mA
• Minimum noise figure • Associated gain			23			
Linearity	OIP_3 OP_{1dB}		30.5	-	dBm	$Z_S = Z_L = 50 \Omega, I_C = 90$ mA
• 3rd order intercept point at output • 1 dB gain compression point at output			19			

Table 9 AC characteristics, $V_{CE} = 3$ V, $f = 1.5$ GHz

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Power gain	G_{ma} $ S_{21} ^2$	-	18	-	dB	$I_C = 90$ mA
• Maximum power gain • Transducer gain			14			
Noise figure	NF_{min} G_{ass}		1.65	-	dBm	$I_C = 50$ mA
• Minimum noise figure • Associated gain			17			
Linearity	OIP_3 OP_{1dB}		31	-	dBm	$Z_S = Z_L = 50 \Omega, I_C = 90$ mA
• 3rd order intercept point at output • 1 dB gain compression point at output			19			

Table 10 AC characteristics, $V_{CE} = 3$ V, $f = 1.9$ GHz

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Power gain	G_{ma} $ S_{21} ^2$	-	15.5	-	dB	$I_C = 90$ mA
• Maximum power gain • Transducer gain			11.5			
Noise figure	NF_{min} G_{ass}		1.7	-	dBm	$I_C = 50$ mA
• Minimum noise figure • Associated gain			14			
Linearity	OIP_3 OP_{1dB}		31	-	dBm	$Z_S = Z_L = 50 \Omega, I_C = 90$ mA
• 3rd order intercept point at output • 1 dB gain compression point at output			19			

Electrical characteristics

Table 11 AC characteristics, $V_{CE} = 3$ V, $f = 2.4$ GHz

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Power gain	G_{ma} $ S_{21} ^2$	-	13.5	-	dB	$I_C = 90$ mA
• Maximum power gain • Transducer gain			9.5			
Noise figure	NF_{min} G_{ass}		1.8	-	dBm	$I_C = 50$ mA
• Minimum noise figure • Associated gain			12			
Linearity	OIP_3 OP_{1dB}		30	-	dBm	$Z_S = Z_L = 50 \Omega, I_C = 90$ mA
• 3rd order intercept point at output • 1 dB gain compression point at output			19			

Table 12 AC characteristics, $V_{CE} = 3$ V, $f = 3.5$ GHz

Parameter	Symbol	Values			Unit	Note or test condition
		Min.	Typ.	Max.		
Power gain	G_{ma} $ S_{21} ^2$	-	10	-	dB	$I_C = 90$ mA
• Maximum power gain • Transducer gain			6			
Noise figure	NF_{min} G_{ass}		2.05	-	dBm	$I_C = 50$ mA
• Minimum noise figure • Associated gain			9			
Linearity	OIP_3 OP_{1dB}		29.5	-	dBm	$Z_S = Z_L = 50 \Omega, I_C = 90$ mA
• 3rd order intercept point at output • 1 dB gain compression point at output			18.5			

Note: $G_{ms} = |S_{21}| / S_{12}|I$ for $k < 1$; $G_{ma} = |S_{21}| / S_{12}|I(k - (k^2 - 1)^{1/2})$ for $k > 1$. In order to get the NF_{min} values stated in this chapter, the test fixture losses have been subtracted from all measured results. OIP_3 value depends on termination of all intermodulation frequency components. Termination used for this measurement is 50Ω from 0.1 MHz to 6 GHz.

Electrical characteristics

3.4

Characteristic DC diagrams



Figure 3 Collector current vs. collector emitter voltage $I_C = f(V_{CE})$, $I_B = \text{parameter}$ 

Figure 4

DC current gain $h_{FE} = f(I_C)$, $V_{CE} = 3 \text{ V}$

Electrical characteristics




Figure 5 Collector current vs. base emitter forward voltage $I_C = f(V_{BE})$, $V_{CE} = 2$ V




Figure 6 Base current vs. base emitter forward voltage $I_B = f(V_{BE})$, $V_{CE} = 2$ V

Electrical characteristics




Figure 7

Base current vs. base emitter reverse voltage $I_B = f(V_{EB})$, $V_{CE} = 2$ V

Electrical characteristics

3.5

Characteristic AC diagrams




Figure 8


Transition frequency $f_T = f(I_C)$, $f = 1$ GHz, V_{CE} = parameter

Figure 9

3rd order intercept point $OIP_3 = f(I_C)$, $Z_S = Z_L = 50 \Omega$, V_{CE} , f = parameters

Electrical characteristics




Figure 10




Collector base capacitance $C_{CB} = f(V_{CB})$, $f = 1$ MHz

Figure 11

Gain G_{ma} , G_{ms} , $|S_{21}|^2 = f(f)$, $V_{CE} = 3$ V, $I_C = 90$ mA

Electrical characteristics

Figure 12 Maximum power gain $G_{\max} = f(I_C)$, $V_{CE} = 3$ V, f = parameter in GHzFigure 13 Maximum power gain $G_{\max} = f(V_{CE})$, $I_C = 90$ mA, f = parameter in GHz

Electrical characteristics




Figure 14 **Input reflection coefficient $S_{11} = f(f)$, $V_{CE} = 3\text{ V}$, $I_C = 50 / 90\text{ mA}$**




Figure 15 **Source impedance for minimum noise figure $Z_{S,\text{opt}} = f(f)$, $V_{CE} = 3\text{ V}$, $I_C = 50 / 90\text{ mA}$**

Electrical characteristics




Figure 16


Output reflection coefficient $S_{22} = f(f)$, $V_{CE} = 3$ V, $I_C = 50 / 90$ mA

Figure 17

Noise figure $NF_{\min} = f(f)$, $Z_S = Z_{S,\text{opt}}$, $V_{CE} = 3$ V, $I_C = 50 / 90$ mA

Electrical characteristics




Figure 18


Noise figure $NF_{min} = f(I_c)$, $Z_s = Z_{s,opt}$, $V_{CE} = 3\text{ V}$, $f = \text{parameter in GHz}$ 

Figure 19

Noise figure $NF_{50} = f(I_c)$, $Z_s = 50\Omega$, $V_{CE} = 3\text{ V}$, $f = \text{parameter in GHz}$

Electrical characteristics





Figure 20 **Noise figure $NF_{50} = f(I_c)$, $Z_s = 50 \Omega$, $NF_{min} = f(I_c)$, $Z_s = Z_{s,opt}$, $V_{CE} = 3 \text{ V}$, $f = 1.9 \text{ GHz}$**

Note: The curves shown in this chapter have been generated using typical devices but shall not be considered as a guarantee that all devices have identical characteristic curves. $T_A = 25 \text{ }^\circ\text{C}$.

4

Package information SOT343



MOLD FLASH, PROTRUSION OR GATE BURRS OF 0.2 MM MAXIMUM PER SIDE ARE NOT INCLUDED
ALL DIMENSIONS ARE IN UNITS MM
THE DRAWING IS IN COMPLIANCE WITH ISO 128 & PROJECTION METHOD 1 []

Figure 21 **SOT343 package**

Note: For package information including footprint, packing and assembly recommendation refer to:

<https://www.infineon.com/cms/en/product/packages/PG-SOT343/PG-SOT343-4-1>

Revision history**Revision history**

Document version	Date of release	Description of changes
Revision 2.0	2019-01-25	New datasheet layout.
Revision 3.0	2024-07-01	Updated product validation

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-07-01

Published by

**Infineon Technologies AG
81726 Munich, Germany**

**© 2024 Infineon Technologies AG
All Rights Reserved.**

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

**Document reference
IFX-ehy1521536352893**

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.