### R41T, THB, Class X1/Y2, 300 VAC, 125°C (Automotive Grade)

#### Metallized Polypropylene Film EMI Suppression Capacitors



#### **Overview**

The R41T is constructed of metallized polypropylene film encapsulated with self-extinguishing resin, in a box of material meeting the requirements of UL 94 V-0.

Automotive Grade devices meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.

### **Applications**

For use in electromagnetic interference (EMI) suppression filter in "line-to-ground" and "across-the-line" applications, requiring Y2/X1 safety classification. Suitable for use in situations where failure of the capacitor could lead to danger of electric shock.

#### **Benefits**

• Approvals: ENEC, UL, cUL, CQC

Class X1/Y2 (IEC 60384-14)

 THB Grade IIIB: 85°C, 85% RH, 1,000 hours at 300 V URAC acc. to IEC 60384-14, for details see Environmental Test Data

• Rated voltage: 300 VAC 50/60 Hz

• Capacitance range: 0.001  $\mu F - 1 \mu F$ 

• Lead spacing: 7.5 - 37.5 mm

• Capacitance tolerance: ±20%, ±10%

Climatic category 40/110/56, IEC 60068-1

• Tape and reel in accordance with IEC 60286-2

· RoHS compliant and lead-free terminations

• Operating temperature range of -40°C to +125°C

· Self-healing properties

Automotive (AEC-Q200) grade



# **Part Number System**

R41	3	1	2330	00	T0	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Y2, Metallized Polypropylene	3 = 300	D = 7.5 F = 10.0 I = 15.0 N = 22.5 R = 27.5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	T0 T1	K = ±10% M = ±20%

# **Ordering Options Table**


1 1 0			
Lead Spacing Nominal	Type of Leads and Packaging	Lead Length	Lead and Packaging Code
(mm)		(IIIII)	1 ackaging code
	Standard Lead and Packaging Options		
	Bulk (Bag) – Short Leads	4 +2/-0	00
	Ammo Pack	H <sub>0</sub> = 18.5 ±0.5	DQ
	Other Lead and Packaging Options		
7.5	Tape & Reel (Standard Reel Ø 355 mm)	H <sub>0</sub> = 18.5±0.5	СК
	Bulk (Bag) – Short Leads	2.7 +0.5/-0	JA
	Bulk (Bag) – Short Leads	3.5 +0.5/-0	JB
	Bulk (Bag) – Short Leads	4.0 +0.5/-0	JE
	Bulk (Bag) – Short Leads	3.2 +0.3/-0.2	JH
	Bulk (Bag) – Long Leads	18 ±1	JM
	Standard Lead and Packaging Options		
	Bulk (Bag) - Short Leads	4 +2/-0	00
	Ammo Pack	H <sub>0</sub> = 18.5 ±0.5	DQ
	Other Lead and Packaging Options	U	
10	Tape & Reel (Large Reel)	H <sub>0</sub> = 18.5 ±0.5	СК
15	Tape & Reel (Standard Reel)	H <sub>0</sub> = 18.5 ±0.5	GY
13	Bulk (Bag)² – Short Leads	3.5 +0.5/-0	JB
22.5	Bulk (Bag)² – Short Leads	4.0 +0.5/-0	JE
	Bulk (Bag) <sup>2</sup> – Short Leads	3.2 +0.3/-0.2	JH
	Bulk (Bag) – Long Leads	18 ±1	JM
	Standard Lead and Packaging Options  Bulk (Bag) - Short Leads	30 +5/-0	40
	Bulk (Bag) – Long Leads	Comparison	50
	Standard Lead and Packaging Ontions		
		4 +2/-0	00
			CK <sup>1</sup>
27.5		U	
	Bulk (Tray) – Long Leads	30 +5/-0	40
	Bulk (Tray) – Long Leads	25 +2/-1	50
	Standard Load and Packaging Ontions		
		A +2/-0	00
37.5	, -,	412/10	00
37.0		30 + 5/-0	40
	,		50
	Daik (Tray) Long Leads	20 12/ 1	1 30

<sup>&</sup>lt;sup>1</sup> Not for all sizes, see "Packaging Quantities" table

 $<sup>^2</sup>$  For lead spacing 22.5 case sizes  $\geq$  8.5\*17\*26.5 the parts are packed in a Pizza box 335\*320\*34 mm



# **Dimensions - Millimeters**




	S		Г		1				F
Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance
7.5	±0.4	4	+0.1/-0.5	9	+0.1/-0.5	10	+0.2/-0.5	0.6	±0.05
7.5	±0.4	5	+0.1/-0.5	10.5	+0.1/-0.5	10	+0.2/-0.5	0.6	±0.05
7.5	±0.4	6	+0.1/-0.5	12	+0.1/-0.5	10.5	+0.2/-0.5	0.6	±0.05
10.0	±0.4	4.0	+0.2/-0.5	9.0	+0.1/-0.5	13.0	+0.3/-0.5	0.6	±0.05
10.0	±0.4	5.0	+0.2/-0.5	11.0	+0.1/-0.5	13.0	+0.3/-0.5	0.6	±0.05
10.0	±0.4	6.0	+0.2/-0.5	12.0	+0.1/-0.5	13.0	+0.3/-0.5	0.6	±0.05
15.0	±0.4	5.0	+0.2/-0.5	11.0	+0.1/-0.5	18.0	+0.3/-0.5	0.6	±0.05
15.0	±0.4	6.0	+0.2/-0.5	12.0	+0.1/-0.5	18.0	+0.3/-0.5	0.6	±0.05
15.0	±0.4	7.5	+0.2/-0.5	13.5	+0.1/-0.5	18.0	+0.3/-0.5	0.6	±0.05
15.0	±0.4	8.5	+0.2/-0.5	14.5	+0.1/-0.5	18.0	+0.3/-0.5	0.6	±0.05
15.0	±0.4	10.0	+0.2/-0.5	16.0	+0.1/-0.5	18.0	+0.3/-0.5	0.8	±0.05
15.0	±0.4	11.0	+0.2/-0.5	19.0	+0.1/-0.5	18.0	+0.3/-0.5	0.8	±0.05
22.5	±0.4	6.0	+0.2/-0.5	15.0	+0.1/-0.5	26.5	+0.3/-0.5	0.8	±0.05
22.5	±0.4	7.0	+0.2/-0.5	16.0	+0.1/-0.5	26.5	+0.3/-0.5	0.8	±0.05
22.5	±0.4	8.5	+0.2/-0.5	17.0	+0.1/-0.5	26.5	+0.3/-0.5	0.8	±0.05
22.5	±0.4	10.0	+0.2/-0.5	18.5	+0.1/-0.5	26.5	+0.3/-0.5	0.8	±0.05
22.5	±0.4	11.0	+0.2/-0.5	20.0	+0.1/-0.5	26.5	+0.3/-0.5	0.8	±0.05
22.5	±0.4	13.0	+0.2/-0.5	22.0	+0.1/-0.5	26.5	+0.3/-0.5	0.8	±0.05
27.5	±0.4	13.0	+0.2/-0.7	22.0	+0.1/-0.7	32.0	+0.3/-0.7	0.8	±0.05
27.5	±0.4	14.0	+0.2/-0.7	28.0	+0.1/-0.7	32.0	+0.3/-0.7	0.8	±0.05
27.5	±0.4	18.0	+0.2/-0.7	33.0	+0.1/-0.7	32.0	+0.3/-0.7	0.8	±0.05
37.5	±0.4	13.0	+0.2/-0.7	24.0	+0.1/-0.7	41.5	+0.3/-0.7	1.0	±0.05
37.5	±0.4	16.0	+0.2/-0.7	28.5	+0.1/-0.7	41.5	+0.3/-0.7	1.0	±0.05
37.5	±0.4	20.0	+0.2/-0.7	40.0	+0.1/-0.7	41.5	+0.3/-0.7	1.0	±0.05
		Note: Se	e Ordering O	ptions Tabl	e for lead ler	ngth (LL/H <sub>s</sub> )	options.		_


### **Performance Characteristics**


	D. 1. 61						
Dielectric	Polypropylene film						
Plates	Metal layer deposited by evaporation under vacum						
Winding	Non-inductive type						
Leads	Tinned wire						
Protection	Plastic case, thermosetting	g resin filled. Box material is s	olvent resistant and flame reta	ardant according to UL 94			
Related Documents	IEC 60384-14, EN 60384-	14					
Rated Voltage (V <sub>R</sub> )	300 VAC (50/60 Hz)						
Recommended DC Voltage	1,500 VDC						
Capacitance Range	0.001 - 1.0 μF						
Capacitance Values	E6 series (IEC 60063)						
Capacitance Tolerance	±10%, ±20%						
Operating Temperature Range	-40°C to +125°C						
Rated Temperature	+110°C						
Climatic Category	40/110/56 IEC 60068-1						
Reliability	Operational life at rated v 100,000 hours at 85°C (6	voltage: 0,000 hours for lead spacin	g 7.5 mm parts); 2,000 hour	s at 125°C			
	Storage time: ≤ 24 months from the date marked on the label package						
	Average relative humidity per year ≤ 70%						
Storage Conditions	RH ≤ 85% for 30 days randomly distributed throughout the year						
	Dew is absent						
	Temperature: -40 to 80°C (see "Maximum Humidity in Storage Conditions" graph below)						
Approvals	ENEC, UL, cUL, CQC						
		Maximum Value	s at +25°C ±5°C				
Dissipation Factor (tanδ) at 1 kHz	Pitch = 7.5 mm	Pitch = 10 mm	Pitch = 15 - 27.5 mm	Pitch = 37.5 mm			
4	1.5%	0.8%	0.3% (typical: 0.2%)	0.2%			
H: Dat Tool	Terminal To Terminal	4.0k VDC (Type test 60 s	econds, each ramp 5 secon	ds)			
Hi-Pot Test	Terminal To Case	4.0k VDC (Type test 60 s	econds, each ramp 5 secon	ds)			
		Measured at	t +25°C ±5°C				
		Minimum Values E	Between Terminals				
Insulation Resistance	Voltage Charge	Voltage Charge Time	C ≤ 0.33 µF	C > 0.33 µF			
	100 VDC	1 minute	$\geq 1 \cdot 10^{5} M\Omega$ ( $\geq 5 \cdot 10^{5} M\Omega$ )*	≥ 30,000 MΩ • µF ( ≥ 150,000 MΩ • µF )*			

<sup>\*</sup> Typical value

### **Performance Characteristics cont.**











 $T_h$  is the maximum ambient temperature surrounding the capacitor or hottest contact point (e.g. tracks), whichever is higher, in the worst operation conditions in °C.


# Maximum Voltage ( $V_{rms}$ ) Versus Frequency (Sinusoidal Waveform/Th $\leq 85$ °C)



















# Maximum Current ( $I_{rms}$ ) Versus Frequency (Sinusoidal Waveform/Th $\leq 85$ °C)












# Qualification

Automotive grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. For additional information regarding the Automotive Electronics Council and AEC-Q200, please visit their website at www.aecouncil.com.

# **Impedance Graph**





# **Environmental Test Data**

Test	IEC Publication	Procedure
Endurance	IEC 60384-14	1.7 x V <sub>R</sub> VAC 50 Hz, once every hour increase to 1,000 VAC for 0.1 second, 1,000 hours at upper rated temperature"
Vibration	IEC 60068-2-6 Test Fc	3 directions at 2 hours each 10 – 55 Hz at 0.75 mm or 98m/s²
Bump	IEC 60068-2-29 Test Eb	1,000 bumps at 390 m/s <sup>2</sup>
Temperature Cycling	JESD22-Method JA-104	1,000 cycles (-55°C to 110°C) Note: Measurement at 24±4 hours after test conclusion. 30 minute maximum dwell time at each temperature extreme. 1 minute maximum transition time.
Active Flammability	IEC 60384-14	V <sub>R</sub> +20 surge pulses at 5 kV (pulse every 5 seconds)
Passive Flammability	IEC 60384-14	IEC 60384-1, IEC 60695-11-5 Needle Flame Test
Damp Heat Steady State	IEC 60068-2-78 Test Cab	+40°C and 93% RH, 56 days
THB test1		65°C, 93% RH and 1000 VDC, 1,600 hours Capacitance change (Δ C/C): ≤ 10% for ≥P10 (≤20% for P7.5 parts) Dissipation factor change (Δtanδ): ≤ 150 * $10^{-4}$ (at 1 kHz for Cap > 1 μF) Dissipation factor change (Δtanδ): ≤ 240 * $10^{-4}$ (at 10 kHz for Cap ≤ 1 μF) IR ≥ 50% of initial limit or minimum 200 MΩ
THB test2		85°C, 85% RH and 1,500 VDC, 1,000 hours Capacitance change ( $\Delta$ C/C): $\leq$ 10% for $\geq$ P10 ( $\leq$ 20% for P7.5 parts) Dissipation factor change ( $\Delta$ tanδ): $\leq$ 150 * 10 <sup>-4</sup> (at 1 kHz for Cap > 1 $\mu$ F) Dissipation factor change ( $\Delta$ tanδ): $\leq$ 240 * 10 <sup>-4</sup> (at 10 kHz for Cap $\leq$ 1 $\mu$ F) IR $\geq$ 50% of initial limit or minimum 200 MΩ
THB test3 For P10 (≥ 2.2 nF) and ≥ P15 Parts		85°C, 85% RH and 300 VAC, 1,000 hours Capacitance change (Δ C/C): ≤ 10% Dissipation factor change (Δtanδ): ≤ 150 * 10 <sup>-4</sup> (at 1 kHz for Cap > 1 μF) Dissipation factor change (Δtanδ): ≤ 240 * 10 <sup>-4</sup> (at 10 kHz for Cap ≤ 1 μF) IR ≥ 50% of initial limit or minimum 200 MΩ
THB test4 For P10 (< 2.2 nF) and all P7.5 Parts		85°C, 85% RH and 240 VAC, 1,000 hours Capacitance change ( $\Delta$ C/C): $\leq$ 10% for P10 ( $\leq$ 20% for P7.5 parts) Dissipation factor change ( $\Delta$ tanδ): $\leq$ 150 * 10 <sup>-4</sup> (at 1 kHz for Cap > 1 μF) Dissipation factor change ( $\Delta$ tanδ): $\leq$ 240 * 10 <sup>-4</sup> (at 10 kHz for Cap $\leq$ 1 μF) IR $\geq$ 50% of initial limit or minimum 200 MΩ
THB test5 For P10 (< 2.2 nF) Parts		85°C, 85% RH and 300 VAC, 500 hours Capacitance change ( $\Delta$ C/C): $\leq$ 10% Dissipation factor change ( $\Delta$ tanδ): $\leq$ 150 * 10 <sup>-4</sup> (at 1 kHz for Cap > 1 μF) Dissipation factor change ( $\Delta$ tanδ): $\leq$ 240 * 10 <sup>-4</sup> (at 10 kHz for Cap $\leq$ 1 μF) IR $\geq$ 50% of initial limit or minimum 200 MΩ

# **Approvals**

Certification Body	Mark	Specification	File Number
IMQ S.p.A.		EN/IEC 60384-14	V4160
UL	c FNO US	UL 60384-14 and CAN/CSA E60384-14 (300 VAC)	E97797
CQC	Cec	IEC 60384-14	CQC13001101264 CQC15001128704 CQC19001218777 CQC13001087758



# **Environmental Compliance**

All KEMET EMI capacitors are RoHS Compliant.



# **Table 1 – Ratings & Part Number Reference**

Capacitance	ance Dimensions in mm Lead Spacing dV/dt KEMET		KEMET	Customer			
Value (µF)	Т	Н	L	(S)	(V/µs)	Part Number	Part Number
0.001	4.0	9.0	10.0	7.5	800	413D1100(1)T0(2)	R413D1100(1)T0(2)
0.0015	4.0	9.0	10.0	7.5	800	413D1150(1)T0(2)	R413D1150(1)T0(2)
0.0022	5.0	10.5	10.0	7.5	800	413D1220(1)T0(2)	R413D1220(1)T0(2)
0.0033	6.0	12.0	10.5	7.5	800	413D1330(1)T0(2)	R413D1330(1)T0(2)
0.0047	6.0	12.0	10.5	7.5	800	413D1470(1)T0(2)	R413D1470(1)T0(2)
0.001	4.0	9.0	13.0	10.0	800	413F1100(1)T0(2)	R413F1100(1)T0(2)
0.0015	4.0	9.0	13.0	10.0	800	413F1150(1)T0(2)	R413F1150(1)T0(2)
0.0022	4.0	9.0	13.0	10.0	800	413F1220(1)T0(2)	R413F1220(1)T0(2)
0.0033	5.0	11.0	13.0	10.0	800	413F1330(1)T0(2)	R413F1330(1)T0(2)
0.0047	5.0	11.0	13.0	10.0	800	413F1470(1)T1(2)	R413F1470(1)T1(2)
0.0047	6.0	12.0	13.0	10.0	800	413F1470(1)T0(2)	R413F1470(1)T0(2)
0.0068	6.0	12.0	13.0	10.0	800	413F1680(1)T0(2)	R413F1680(1)T0(2)
0.0047	5.0	11.0	18.0	15.0	600	413I1470(1)T0(2)	R413I1470(1)T0(2)
0.0068	5.0	11.0	18.0	15.0	600	413I1680(1)T0(2)	R413I1680(1)T0(2)
0.010	5.0	11.0	18.0	15.0	600	413I2100(1)T0(2)	R413I2100(1)T0(2)
0.015	5.0	11.0	18.0	15.0	600	413I2150(1)T1(2)	R413I2150(1)T1(2)
0.015	6.0	12.0	18.0	15.0	600	413I2150(1)T0(2)	R413I2150(1)T0(2)
0.022	6.0	12.0	18.0	15.0	600	413I2220(1)T1(2)	R413I2220(1)T1(2)
0.022	7.5	13.5	18.0	15.0	600	413I2220(1)T0(2)	R413I2220(1)T0(2)
0.033	7.5	13.5	18.0	15.0	600	413I2330(1)T1(2)	R413I2330(1)T1(2)
0.033	8.5	14.5	18.0	15.0	600	413I2330(1)T0(2)	R413I2330(1)T0(2)
0.047	10.0	16.0	18.0	15.0	600	413I2470(1)T0(2)	R413I2470(1)T0(2)
0.068	11.0	19.0	18.0	15.0	600	413I2680(1)T0(2)	R413I2680(1)T0(2)
0.047	6.0	15.0	26.5	22.5	500	413N2470(1)T0(2)	R413N2470(1)T0(2)
0.068	7.0	16.0	26.5	22.5	500	413N2680(1)T0(2)	R413N2680(1)T0(2)
0.10	8.5	17.0	26.5	22.5	500	413N3100(1)T1(2)	R413N3100(1)T1(2)
0.10	10.0	18.5	26.5	22.5	500	413N3100(1)T0(2)	R413N3100(1)T0(2)
0.15	10.0	18.5	26.5	22.5	500	413N3150(1)T1(2)	R413N3150(1)T1(2)
0.15	11.0	20.0	26.5	22.5	500	413N3150(1)T0(2)	R413N3150(1)T0(2)
0.22	13.0	22.0	26.5	22.5	500	413N3220(1)T0(2)	R413N3220(1)T0(2)
0.22	13.0	22.0	32.0	27.5	400	413R3220(1)T0(2)	R413R3220(1)T0(2)
0.33	14.0	28.0	32.0	27.5	400	413R3330(1)T0(2)	R413R3330(1)T0(2)
0.47	18.0	33.0	32.0	27.5	400	413R3470(1)T0(2)	R413R3470(1)T0(2)
0.68	18.0	33.0	32.0	27.5	400	413R3680(1)T0(2)	R413R3680(1)T0(2)
0.47	13.0	24.0	41.5	37.5	300	413W3470(1)T0(2)	R413W3470(1)T0(2)
0.68	16.0	28.5	41.5	37.5	300	413W3680(1)T0(2)	R413W3680(1)T0(2)
1.0	20.0	40.0	41.5	37.5	300	413W4100(1)T0(2)	R413W4100(1)T0(2)
Capacitance Value (µF)	T (mm)	H (mm)	L (mm)	Lead Spacing (S)	dV/dt (V/µs)	KEMET Part Number	Customer Part Number

<sup>(1)</sup> Insert lead and packaging code. See Ordering Options Table for available options.



<sup>(2)</sup>  $M = \pm 20\%$ ,  $K = \pm 10\%$ 

<sup>(3)</sup> M = ±20% (only available tolerance).

## **Soldering Process**

The implementation of the RoHS directive has resulted in the selection of SnAgCu (SAC) alloys or SnCu alloys as primary solder. This has increased the liquidus temperature from that of 183°C for SnPb eutectic alloy to 217 - 221°C for the new alloys. As a result, the heat stress to the components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (the melting point of polypropylene is 160 – 170°C). Wave soldering can be destructive, especially for mechanically small polypropylene capacitors (with lead spacing of 5 mm to 15 mm), and great care has to be taken during soldering. The recommended solder profiles from KEMET should be used. Please consult KEMET with any questions. In general, the wave soldering curve from IEC Publication 61760-1 Edition 2 serves as a solid guideline for successful soldering. Please see Figure 1.


Reflow soldering is not recommended for through-hole film capacitors. Exposing capacitors to a soldering profile in excess of the above the recommended limits may result to degradation or permanent damage to the capacitors.

Do not place the polypropylene capacitor through an adhesive curing oven to cure resin for surface mount components. Insert through-hole parts after the curing of surface mount parts. Consult KEMET to discuss the actual temperature profile in the oven, if through-hole components must pass through the adhesive curing process. A maximum two soldering cycles is recommended. Please allow time for the capacitor surface temperature to return to a normal temperature before the second soldering cycle.

#### **Manual Soldering Recommendations**


The following is the recommendation for manual soldering with a soldering iron.

#### **Recommended Soldering Temperature**



The soldering iron tip temperature should be set at 350°C (+10°C maximum) with the soldering duration not to exceed more than 3 seconds.

#### **Wave Soldering Recommendations**





## **Soldering Process cont.**

#### **Wave Soldering Recommendations cont.**


1. The table indicates the maximum set-up temperature of the soldering process Figure 1

Dielectric	Pre	mum heat erature	Maximum Peak Soldering Temperature		
Film Material	Capacitor Pitch ≤ 15 mm	Capacitor Pitch > 15 mm	Capacitor Pitch ≤ 15 mm	Capacitor Pitch > 15 mm	
Polyester	130°C	130°C	270°C	270°C	
Polypropylene	125°C	130°C	260°C	270°C	
Paper	130°C	140°C	270°C	270°C	
Polyphenylene Sulphide	150°C	160°C	270°C	270°C	

2. The maximum temperature measured inside the capacitor:

Set the temperature so that inside the element the maximum temperature is below the limit:

Dielectric Film Material	Maximum temperature measured inside the element
Polyester	160°C
Polypropylene	125°C
Paper	160°C
Polyphenylene sulphide	160°C



Temperature monitored inside the capacitor.

#### **Selective Soldering Recommendations**

Selective dip soldering is a variation of reflow soldering. In this method, the printed circuit board with through-hole components to be soldered is preheated and transported over the solder bath as in normal flow soldering without touching the solder. When the board is over the bath, it is stopped and pre-designed solder pots are lifted from the bath with molten solder only at the places of the selected components, and pressed against the lower surface of the board to solder the components.

The temperature profile for selective soldering is similar to the double wave flow soldering outlined in this document, however, instead of two baths, there is only one bath with a time from 3 to 10 seconds. In selective soldering, the risk of overheating is greater than in double wave flow soldering, and great care must be taken so that the parts are not overheated.



# **Mounting**


#### **Resistance to Vibration and Mechanical Shock**

AEC-0200 Rev. E Mechanical Stress Tests:


ALO Q200 NCV. L IVICCITATI		
Mechanical Shock	MIL-SDT-202 Method 213	Figure 1 of Method 213  • THT: Condition C  • SMD: Condition C  • Tested per the Supplier's recommended mounting method
Vibration	MIL-SDT-202 Method 204	• 5 g for 20 minutes, 12 cycles each of 3 orientations  • Tested per the Supplier's recommended mounting method  • Verification of transfer load: during setup, verify that with the selected PCB design (size, thickness and secure points), or an alternative mount, that the transferred load onto the component corresponds to the requested load. This verification can be achieved using a laser vibrometer or other adequate measuring device  • Test from 10 Hz – 2,000 Hz.

The capacitors are designed for PCB mounting. The stand-off pipes must be in good contact with the printed circuit board. The capacitors with pitch ≤ 22.5 mm can be mechanically fixed by the leads, for pitch > 22.5 mm, the capacitor body has to be properly fixed (e.g. clamped or glued).

### Construction



#### **Winding Scheme**







#### Metallized Polypropylene Film EMI Suppression Capacitors

### **Marking**


#### Lead Spacing 7.5 mm






NOTE: Hot imprinting with or without color or ink jet or laser marking

#### Lead Spacing 7.5 mm (alternatives\*)





NOTE: Hot imprinting with or without color or ink jet or laser marking

Slight change in the layout can be possible but this does not affect the content of the information of the current marking.


This change will be achieved without impact to product form, fit or function, as the products are equivalent with respect to physical, mechanical, quality and reliability characteristics.


<sup>\*</sup> Differences caused by technology (clichee, laser or ink jet) and production line

#### Metallized Polypropylene Film EMI Suppression Capacitors

### Marking cont.


Lead Spacing 10 mm






NOTE: Hot imprinting with or without color or ink jet or laser marking

Lead Spacing ≥ 15 mm, 22.5 mm (small case sizes)





NOTE: Hot imprinting with or without

color or ink jet or laser marking

Slight change in the layout can be possible but this does not affect the content of the information of the current marking.


This change will be achieved without impact to product form, fit or function, as the products are equivalent with respect to physical, mechanical, quality and reliability characteristics.

<sup>\*</sup> Differences caused by technology (clichee, laser or ink jet) and production line

#### Metallized Polypropylene Film EMI Suppression Capacitors

# Marking cont.

Lead Spacing 22.5 and 27.5 mm (alternatives\*) and 37.5 mm



<sup>\*</sup> Differences caused by technology (clichee, laser or ink jet) and production line

Slight change in the layout can be possible but this does not affect the content of the information of the current marking.

This change will be achieved without impact to product form, fit or function, as the products are equivalent with respect to physical, mechanical, quality and reliability characteristics.


	Manufacturing Date Code (IEC 60062)									
Year	Code	Year	Code	Year	Code	Month	Code	Month	Code	
2020	М	2027	V	2034	E	January	1	July	7	
2021	N	2028	W	2035	F	February	2	August	8	
2022	Р	2029	X	2036	Н	March	3	September	9	
2023	R	2030	Α	2037	J	April	4	October	0	
2024	S	2031	В	2038	K	May	5	November	N	
2025	T	2032	С	2039	L	June	6	December	D	
2026	U	2033	D	2040	М					

# **Packaging Quantities**

Lead Spacing (mm)	Thickness (mm)	Height (mm)	Length (mm)	Bulk Short Leads	Bulk Long Leads		Standard Reel ø 355 mm	Large Reel ø 500 mm	Ammo Taped
Lea	nd and Packagi	ng Code:		00 - JA - JB JE - JH	40 - 50	JM	GY - CK <sup>1</sup>	СК	DQ
	4.0	9.0	10.0	2,000	-	1,500	1,500	-	2,100
7.5	5.0	10.5	10.0	1,500	-	1,000	1,200	-	1,600
	6.0	12.0	10.5	1,000	-	800	1,000	-	1,350
	4.0		10.0		1 000	0.000	750	4.500	1.000
40	4.0	9.0	13.0	2,000	1,800	2,200	750	1,500	1,000
10	5.0	11.0	13.0	1,300	1,500	2,000	600	1,250	800
	6.0	12.0	13.0	1,000	1,200	1,800	500	1,000	680
	5.0	11.0	18.0	2,000	1,000	1,250	600	1,250	800
	6.0	12.0	18.0	1,750	900	1,000	500	1,000	680
_	7.5	13.5	18.0	1,000	700	800	350	800	500
15	8.5	14.5	18.0	1,000	500	650	300	700	440
	10.0	16.0	18.0	750	500	550	270	600	380
	11.0	19.0	18.0	450	350	400	270	500	340
	-								
	6.0	15.0	26.5	805	500	450	300	700	464
	7.0	16.0	26.5	700	500	450	250	550	380
22.5	8.5	17.0	26.5	468	300	350	250	450	280
22.5	10.0	18.5	26.5	396	300	350	160	350	235
	11.0	20.0	26.5	360	250	200	160	350	217
	13.0	22.0	26.5	300	200	150	130	300	-
	12.0	22.0	32.0	480	288	288	Ī	300	
27.5	13.0 14.0	22.0 28.0	32.0	352	176	176	-	300	-
27.5			32.0	256			-	-	
	18.0	33.0	32.0	<u> </u> 250	128	128	_	-	-
	13.0	24.0	41.5	360	216	216	-	-	-
37.5	16.0	28.5	41.5	216	108	108	-	-	-
	20.0	40.0	41.5	126	84	84	-	-	-

<sup>1</sup> Only for 7.5 mm lead spacing

# Lead Taping & Packaging (IEC 60286-2)



# **Taping Specification**

Description	Symbol	Dimensions (mm)					
		Lead Spacing					Talawanaa
		7.5	10.0	15.0	22.5	27.5	Tolerance
Lead wire diameter	d	0.5 - 0.6	0.6	0.6 - 0.8	8.0	0.8	±0.05
Taping lead space	Р	12.7	25.4	25.4	38.1	38.1	±1
Feed hole lead space *	P <sub>0</sub>	12.7	12.7	12.7	12.7	12.7	±0.2 **
Centering of the lead wire	P <sub>1</sub>	2.6	7.7	5.2	7.8	5.3	±0.7
Centering of the body	P <sub>2</sub>	6.35	12.7	12.7	19.05	19.05	±1.3
Lead spacing ***	F	7.5	10.0	15.0	22.5	27.5	+0.6/-0.1
Component alignment	Δh	0	0	0	0	0	±2
Component deviation	Δр	0	0	0	0	0	±1
Height of component from tape center	H <sub>0</sub> ****	18.5	18.5	18.5	18.5	18.5	±0.5
Carrier tape width	W	18	18	18	18	18	+1/-0.5
Hold down tape width	W <sub>o</sub>	6	9	10	10	10	Minimum
Hole position	W <sub>1</sub>	9	9	9	9	9	±0.5
Hold down tape position	W <sub>2</sub>	3	3	3	3	3	Maximum
Feed hole diameter	D <sub>0</sub>	4	4	4	4	4	±0.2
Total Tape thickness	t	0.7	0.7	0.7	0.7	0.7	±0.2

<sup>\*</sup> Available also 15 mm.



<sup>\*\*</sup> Maximum 1 mm on 20 lead spacing.


<sup>\*\*\* 15</sup> mm and 10 mm taped to 7.5 mm (crimped leads) available upon request.

<sup>\*\*\*\*</sup>  $H_0$  = 16.5 mm is available upon request.

# Lead Taping & Packaging (IEC 60286-2) cont.


# **Ammo Specifications**


Dimensions (mm)						
Н	W	Т				
360	340	59				



# **Reel Specifications**

Reel Size	Dimensions (mm)				
Reel Size	D	Н	W		
Standard	355	30	55 Maximum		
Large	500	25			





### R41T, THB, Class X1/Y2, 300 VAC, 125°C (Automotive Grade)

#### Metallized Polypropylene Film EMI Suppression Capacitors

### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit https://www.yaqeogroup.com/SalesResources/SalesOffices

#### **Disclaimer**

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

Additional information about production site flexibility can be found < here >

