

Polypropylene (PP) Capacitors for Pulse Applications with Double-Sided Metallized Electrodes in PCM 7.5 mm to 52.5 mm. Capacitances from 1000 pF to 47 μF. Rated Voltages from 100 VDC to 3000 VDC.

Special Features

- Pulse duty construction
- Self-healing
- Very low dissipation factor
- Negative capacitance change versus temperature
- AEC-Q200 qualified
- According to RoHS 2015/863/EU

Typical Applications

For pulse applications e.g.

- Switch mode power supplies
- TV and monitor sets
- Lighting
- Audio/video equipment


Construction

Dielectric: Polypropylene (PP) film

Capacitor electrodes:

Double-sided metallized plastic film

Internal construction:



Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

Terminations: Tinned wire.

Marking: Colour: Red.

Marking: Black.

Electrical Data

Capacitance range:

1000 pF to 47 μF

Rated voltages: 100VDC, 250VDC, 400VDC, 630VDC, 850VDC, 1000VDC, 1600VDC, 2000VDC, 2500VDC, 3000 VDC

Capacitance tolerances:

±20%, ±10%, ±5%

Operating temperature range:

-55° C to +105° C

Insulation resistance at +20° C:

$C \leq 0.33 \mu\text{F}: \geq 1 \times 10^5 \text{ M}\Omega$

$C > 0.33 \mu\text{F}: \geq 30000 \text{ sec} (\text{M}\Omega \times \mu\text{F})$

Measuring voltage: 100 V/1 min.

Test voltage: 2 sec.

L	≤2000VDC	2500VDC	≥3000VDC
< 41.5	1.6 U _r	1.4 U _r	1.2 U _r
41.5	1.4 U _r	1.4 U _r	1.2 U _r
57	1.2 U _r	1.2 U _r	1.2 U _r

Climatic test category:

55/100/56 in accordance with IEC

Dielectric absorption: 0.05%

Voltage derating:

A voltage derating factor of 1.35 % per K must be applied from +85° C for DC voltages and from +75° C for AC voltages.

Reliability:

Operational life > 300000 hours

Failure rate < 1 fit (0.5 x U_r and 40° C)

Specific dissipation:

Box size* WxHxL in mm	Specific dissipation in Watts per K above the ambient temperature
35 x 50 x 57	0.132
45 x 55 x 57	0.164
45 x 65 x 57	0.184

* other box sizes see page 10.

Dissipation factors at + 20° C: tan δ

at f	C ≤ 0.1 μF	0.1 μF < C ≤ 1.0 μF	C > 1.0 μF
1 kHz	≤ 6 x 10 ⁻⁴	≤ 6 x 10 ⁻⁴	≤ 6 x 10 ⁻⁴
10 kHz	≤ 6 x 10 ⁻⁴	≤ 6 x 10 ⁻⁴	-
100 kHz	≤ 15 x 10 ⁻⁴	-	-

Maximum pulse rise time:

Capacitance pF/μF	max. pulse rise time V/μsec at T _A < 40° C									
	100VDC	250VDC	400VDC	630VDC	850VDC	1000VDC	1600VDC	2000VDC	2500VDC	3000VDC
1000 ... 2200	1250	2300	2300	2300	3500	3500	7000	11500	11500	-
3300 ... 6800	1150	1500	1500	1500	3500	3500	7000	11500	11500	-
0.01 ... 0.022	900	1400	1500	1500	2700	2700	3800	4400	11500	-
0.033 ... 0.068	500	1000	1150	1400	2700	2700	2700	2700	2700	2700
0.1 ... 0.22	250	650	650	1150	1800	1800	1800	1800	1800	1800
0.33 ... 0.68	130	390	500	900	1150	1150	1150	1150	1150	1150
1.0 ... 2.2	90	250	250	500	500	500	650	650	650	500
3.3 ... 4.7	65	100	130	190	230	230	330	-	-	-
6.8 ... 15	45	65	90	160	-	-	-	-	-	-
22 ... 47	30	45	45	-	-	-	-	-	-	-

Mechanical Tests

Pull test on pins:

d ≤ 0.8 Ø: 10 N in direction of pins

d > 0.8 Ø: 20 N in direction of pins

according to IEC 60068-2-21

Vibration: 6 hours at 10... 2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6

Low air density: 1kPa = 10 mbar in accordance with IEC 60068-2-13

Bump test: 4000 bumps at 390 m/sec² in accordance with IEC 60068-2-29

Packing

Available taped and reeled up to and including case size 15 x 26 x 31.5 / PCM 27.5 mm.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

Continuation

General Data

Capacitance	100 VDC/63 VAC					250 VDC/180 VAC				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 µF	4	9	10	7.5	MKP1D021002C	4	9	10	7.5	MKP1F021002C
0.015 "	4	9	10	7.5	MKP1D021502C	4	9	13	10	MKP1F021003C
0.022 "	4	9	10	7.5	MKP1D022202C	4	9	10	7.5	MKP1F021502C
0.033 "	4	9	13	10	MKP1D023303C	4	9	13	10	MKP1F021503C
0.047 "	5	10.5	10.3	7.5	MKP1D023302E	4	9	10	7.5	MKP1F022202C
0.068 "	4	9	13	10	MKP1D024702E	4	9	13	10	MKP1F022203C
	5	10.5	10.3	7.5	MKP1D024703C	5	10.5	10.3	7.5	MKP1F023302E
	4	9	13	10	MKP1D026803F	4	9	13	10	MKP1F023303C
	5	11	13	10	MKP1D026804B	5	11	13	10	MKP1F024702E
	5	11	18	15	MKP1F026804B	5	11	18	15	MKP1F024703C
0.1 µF	6	12	13	10	MKP1D031003G	6	12	13	10	MKP1F031003G
0.12 "	6	12.5	18	15	MKP1D031204C	5	11	18	15	MKP1F031004B
0.15 "	6	12.5	18	15	MKP1D031504C	6	12.5	18	15	MKP1F031204C
0.18 "	7	14	18	15	MKP1D031804D	6	12.5	18	15	MKP1F031504C
0.22 "	7	14	18	15	MKP1D032204D	6	15	26.5	22.5	MKP1F031505B
0.27 "	8	15	18	15	MKP1D032704F	7	14	18	15	MKP1F031804D
0.33 "	8	15	18	15	MKP1D033304F	7	14	18	15	MKP1F032204D
0.39 "	9	16	18	15	MKP1D033904J	6	15	26.5	22.5	MKP1F032205B
0.47 "	9	16	18	15	MKP1D034704J	8	15	18	15	MKP1F032704F
0.56 "	7	16.5	26.5	22.5	MKP1D034705D	8	15	18	15	MKP1F033304F
0.68 "	8.5	18.5	26.5	22.5	MKP1D035605F	6	15	26.5	22.5	MKP1F033305B
0.82 "	8.5	18.5	26.5	22.5	MKP1D036805F	9	16	18	15	MKP1F033904J
	10.5	19	26.5	22.5	MKP1D038205G	9	16	18	15	MKP1F034704J
	11	21	26.5	22.5	MKP1F038205I	9	16	18	15	MKP1F034705D
1.0 µF	10.5	19	26.5	22.5	MKP1D041005G	7	16.5	26.5	22.5	MKP1F034705D
1.2 "	11	21	31.5	27.5	MKP1D041206B	8.5	18.5	26.5	22.5	MKP1F035605F
1.5 "	11	21	31.5	27.5	MKP1D041506B	8.5	18.5	26.5	22.5	MKP1F036805F
1.8 "	13	24	31.5	27.5	MKP1D041806D	9	19	31.5	27.5	MKP1F036806A
2.2 "	13	24	31.5	27.5	MKP1D042206D	11	21	26.5	22.5	MKP1F038205I
2.7 "	17	29	31.5	27.5	MKP1D042706G	11	21	31.5	27.5	MKP1F041005I
3.3 "	17	29	31.5	27.5	MKP1D043306G	11	21	31.5	27.5	MKP1F041006B
3.9 "	20	39.5	31.5	27.5	MKP1D043906J	13	24	31.5	27.5	MKP1F041206D
4.7 "	20	39.5	31.5	27.5	MKP1D044706J	13	24	31.5	27.5	MKP1F041506D
5.6 "	17	29	41.5	37.5	MKP1D044707E	15	26	31.5	27.5	MKP1F041806F
6.8 "	19	32	41.5	37.5	MKP1D045607F	15	26	31.5	27.5	MKP1F042206F
8.2 "	20	39.5	41.5	37.5	MKP1D046807F	13	24	41.5	37.5	MKP1F042207C
	20	39.5	41.5	37.5	MKP1D048207G	17	34.5	31.5	27.5	MKP1F042706I
						17	34.5	31.5	27.5	MKP1F043306I
						17	29	41.5	37.5	MKP1F043307E
						20	39.5	31.5	27.5	MKP1F043906J
						20	39.5	31.5	27.5	MKP1F044706J
						19	32	41.5	37.5	MKP1F044707F
						20	39.5	41.5	37.5	MKP1F045607G
						20	39.5	41.5	37.5	MKP1F046807G
						24	45.5	41.5	37.5	MKP1F048207H

* AC voltage: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_{\text{r}}$

** PCM = Printed circuit module = pin spacing

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:

Version code: 2-pin = 00
 4-pin = D4
 Tolerance: 20 % = M
 10 % = K
 5 % = J
 Packing: bulk = S
 Pin length: 6-2 = SD

Taped version see page 133.

Rights reserved to amend design data without prior notification.



Continuation

General Data

Capacitance	100 VDC/63 VAC*					250 VDC/180 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
10 µF	20	39.5	41.5	37.5	MKP1D051007G	24	45.5	41.5	37.5	MKP1F051007H
12 "	24	45.5	41.5	37.5	MKP1D051207H	28	38	41.5	37.5	MKP1F051007L
15 "	24	45.5	41.5	37.5	MKP1D051507H	35	50	41.5	37.5	MKP1F051207J
18 "	28	38	41.5	37.5	MKP1D051507L	35	50	41.5	37.5	MKP1F051507J
22 "	35	50	41.5	37.5	MKP1D051807J	35	50	57	52.5	MKP1F051509F
27 "	35	50	41.5	37.5	MKP1D052207J	35	50	57	52.5	MKP1F051809F
33 "	40	55	41.5	37.5	MKP1D052707K	35	50	57	52.5	MKP1F052209F
39 "	40	55	41.5	37.5	MKP1D053307K	45	65	57	52.5	MKP1F052709J
47 "	35	50	57	52.5	MKP1D053309F	45	65	57	52.5	MKP1F053309J
	45	65	57	52.5	MKP1D053909J					
	45	65	57	52.5	MKP1D054709J					

Capacitance	400 VDC/250 VAC*					630 VDC/400 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	4	9	10	7.5	MKP1G011002C	4	9	10	7.5*	MKP1J011002C
1200 "	4	9	10	7.5	MKP1G011202C	4	9	10	7.5*	MKP1J011202C
1500 "	4	9	10	7.5	MKP1G011502C	4	9	10	7.5*	MKP1J011502C
1800 "	4	9	10	7.5	MKP1G011802C	4	9	10	7.5*	MKP1J011802C
2200 "	4	9	10	7.5	MKP1G012202C	4	9	10	7.5*	MKP1J012202C
2700 "	4	9	10	7.5	MKP1G012702C	4	9	10	7.5*	MKP1J012702C
3300 "	4	9	10	7.5	MKP1G013302C	4	9	10	7.5*	MKP1J013302C
3900 "	4	9	10	7.5	MKP1G013902C	4	9	10	7.5*	MKP1J013902C
4700 "	4	9	10	7.5	MKP1G014702C	4	9	10	7.5*	MKP1J014702C
5600 "	4	9	10	7.5	MKP1G015602C	4	9	10	7.5*	MKP1J015602C
6800 "	4	9	10	7.5	MKP1G016802C	4	9	10	7.5*	MKP1J016802C
8200 "	4	9	10	7.5	MKP1G018202C	4	9	13	10	MKP1J016803C
						5	10.5	10.3	7.5*	MKP1J018202E
0.01 µF	4	9	10	7.5	MKP1G021002C	5	10.5	10.3	7.5*	MKP1J021002E
	4	9	13	10	MKP1G021003C	4	9	13	10	MKP1J021003C
0.012 "	5	10.5	10.3	7.5	MKP1G021202E	5	11	13	10	MKP1J021203F
0.015 "	5	10.5	10.3	7.5	MKP1G021502E	5	11	13	10	MKP1J021503F
	4	9	13	10	MKP1G021503C	5	11	18	15	MKP1J021504B
0.018 "	5	10.5	10.3	7.5	MKP1G021802E	5	11	13	10	MKP1J021803F
0.022 "	5	10.5	10.3	7.5	MKP1G022202E	5	11	13	10	MKP1J022203F
	4	9	13	10	MKP1G022203C	5	11	18	15	MKP1J022204B
0.027 "	5.7	12.5	10.3	7.5	MKP1G022702F	6	12	13	10	MKP1J022703G
0.033 "	5.7	12.5	10.3	7.5	MKP1G023302F	6	12	13	10	MKP1J023303G
	5	11	13	10	MKP1G023303F	5	11	18	15	MKP1J023304B
0.039 "	6	12	13	10	MKP1G023903G	6	12.5	18	15	MKP1J023904C
0.047 "	6	12	13	10	MKP1G024703G	6	12.5	18	15	MKP1J024704C
	5	11	18	15	MKP1G024704B	6	15	26.5	22.5	MKP1J024705B
0.056 "	6	12.5	18	15	MKP1G025604C	7	14	18	15	MKP1J025604D
0.068 "	6	12.5	18	15	MKP1G026804C	7	14	18	15	MKP1J026804D
	6	15	26.5	22.5	MKP1G026805B	6	15	26.5	22.5	MKP1J026805B
0.082 "	7	14	18	15	MKP1G028204D	9	16	18	15	MKP1J028204J

* AC voltage: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

** PCM = Printed circuit module = pin spacing

* Admissible AC voltage 280 VAC.

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:	
Version code:	2-pin = 00
	4-pin = D4
Tolerance:	20 % = M
	10 % = K
	5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 133.	

Rights reserved to amend design data without prior notification.

Continuation

General Data

Capacitance	400 VDC/250 VAC*					630 VDC/400 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.1 μ F	7	14	18	15	MKP1G031004D	9	16	18	15	MKP1J031004J
	6	15	26.5	22.5	MKP1G031005B	7	16.5	26.5	22.5	MKP1J031005D
0.12 "	8	15	18	15	MKP1G031204F	8.5	18.5	26.5	22.5	MKP1J031205F
0.15 "	8	15	18	15	MKP1G031504F	8.5	18.5	26.5	22.5	MKP1J031505F
	6	15	26.5	22.5	MKP1G031505B	9	19	31.5	27.5	MKP1J031506A
0.18 "	9	16	18	15	MKP1G031804J	8.5	18.5	26.5	22.5	MKP1J031805F
0.22 "	9	16	18	15	MKP1G032204J	8.5	18.5	26.5	22.5	MKP1J032205F
	7	16.5	26.5	22.5	MKP1G032205D	9	19	31.5	27.5	MKP1J032206A
0.27 "	8.5	18.5	26.5	22.5	MKP1G032705F	11	21	26.5	22.5	MKP1J032705I
0.33 "	8.5	18.5	26.5	22.5	MKP1G033305F	11	21	26.5	22.5	MKP1J033305I
	9	19	31.5	27.5	MKP1G033306A	11	21	31.5	27.5	MKP1J033306B
0.39 "	10.5	19	26.5	22.5	MKP1G033905G	11	21	31.5	27.5	MKP1J033906B
0.47 "	10.5	19	26.5	22.5	MKP1G034705G	11	21	31.5	27.5	MKP1J034706B
	9	19	31.5	27.5	MKP1G034706A					
0.56 "	11	21	26.5	22.5	MKP1G035605I	15	26	31.5	27.5	MKP1J035606F
0.68 "	11	21	26.5	22.5	MKP1G036805I	15	26	31.5	27.5	MKP1J036806F
	11	21	31.5	27.5	MKP1G036806B	13	24	41.5	37.5	MKP1J036807C
0.82 "	13	24	31.5	27.5	MKP1G038206D	17	29	31.5	27.5	MKP1J038206G
1.0 μ F	13	24	31.5	27.5	MKP1G041006D	17	29	31.5	27.5	MKP1J041006G
						15	26	41.5	37.5	MKP1J041007D
1.2 "	17	29	31.5	27.5	MKP1G041206G	20	39.5	31.5	27.5	MKP1J041206J
1.5 "	17	29	31.5	27.5	MKP1G041506G	20	39.5	31.5	27.5	MKP1J041506J
	13	24	41.5	37.5	MKP1G041507C	19	32	41.5	37.5	MKP1J041507F
1.8 "	20	39.5	31.5	27.5	MKP1G041806J	20	39.5	41.5	37.5	MKP1J041807G
2.2 "	20	39.5	31.5	27.5	MKP1G042206J	20	39.5	41.5	37.5	MKP1J042207G
	17	29	41.5	37.5	MKP1G042207E					
2.7 "	20	39.5	41.5	37.5	MKP1G042707G	24	45.5	41.5	37.5	MKP1J042707H
3.3 "	20	39.5	41.5	37.5	MKP1G043307G	24	45.5	41.5	37.5	MKP1J043307H
						28	38	41.5	37.5	MKP1J043307L
3.9 "	20	39.5	41.5	37.5	MKP1G043907G	35	50	41.5	37.5	MKP1J043907J
4.7 "	20	39.5	41.5	37.5	MKP1G044707G	35	50	41.5	37.5	MKP1J044707J
5.6 "	24	45.5	41.5	37.5	MKP1G045607H	40	55	41.5	37.5	MKP1J045607K
6.8 "	24	45.5	41.5	37.5	MKP1G046807H	40	55	41.5	37.5	MKP1J046807K
	28	38	41.5	37.5	MKP1G046807L	35	50	57	52.5	MKP1J046809F
8.2 "	35	50	41.5	37.5	MKP1G048207J	45	55	57	52.5	MKP1J048209H
10 μ F	35	50	41.5	37.5	MKP1G051007J	45	55	57	52.5	MKP1J051009H
	35	50	57	52.5	MKP1G051009F					
12 "	40	55	41.5	37.5	MKP1G051207K					
15 "	40	55	41.5	37.5	MKP1G051507K					
18 "	35	50	57	52.5	MKP1G051509F					
22 "	45	65	57	52.5	MKP1G051809J					
	45	65	57	52.5	MKP1G052209J					

* AC voltage: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_{\text{r}}$

** PCM = Printed circuit module = pin spacing

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:

Version code:	2-pin	= 00
	4-pin	= D4
Tolerance:	20 %	= M
	10 %	= K
	5 %	= J
Packing:	bulk	= S
Pin length:	6-2	= SD
Taped version see page 133.		

Rights reserved to amend design data without prior notification.

Continuation page 56



Continuation

General Data

Capacitance	850 VDC/450 VAC*					1000 VDC/600 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	4	9	10	7.5	MKP1M011002C	4	9	10	7.5	MKP1O111002C
	4	9	13	10	MKP1M011003C	4	9	13	10	MKP1O111003C
1200 "	4	9	10	7.5	MKP1M011202C	4	9	10	7.5	MKP1O111202C
1500 "	4	9	10	7.5	MKP1M011502C	4	9	10	7.5	MKP1O111502C
	4	9	13	10	MKP1M011503C	4	9	13	10	MKP1O111503C
1800 "	4	9	10	7.5	MKP1M011802C	4	9	10	7.5	MKP1O111802C
2200 "	4	9	10	7.5	MKP1M012202C	4	9	10	7.5	MKP1O112202C
	4	9	13	10	MKP1M012203C	4	9	13	10	MKP1O112203C
2700 "	4	9	10	7.5	MKP1M012702C	4	9	10	7.5	MKP1O112702C
3300 "	4	9	10	7.5	MKP1M013302C	4	9	10	7.5	MKP1O113302C
	4	9	13	10	MKP1M013303C	4	9	13	10	MKP1O113303C
3900 "	4.5	9.5	10.3	7.5	MKP1M013902D	4.5	9.5	10.3	7.5	MKP1O113902D
4700 "	4.5	9.5	10.3	7.5	MKP1M014702D	4.5	9.5	10.3	7.5	MKP1O114702D
	4	9	13	10	MKP1M014703C	4	9	13	10	MKP1O114703C
5600 "	5.7	12.5	10.3	7.5	MKP1M015602F	5.7	12.5	10.3	7.5	MKP1O115602F
6800 "	5.7	12.5	10.3	7.5	MKP1M016802F	5.7	12.5	10.3	7.5	MKP1O116802F
	5	11	13	10	MKP1M016803F	5	11	13	10	MKP1O116803F
8200 "	5	11	13	10	MKP1M018203F	5	11	13	10	MKP1O118203F
0.01 µF	5	11	13	10	MKP1M021003F	5	11	13	10	MKP1O121003F
	5	11	18	15	MKP1M021004B	5	11	18	15	MKP1O121004B
0.012 "	6	12	13	10	MKP1M021203G	6	12	13	10	MKP1O121203G
0.015 "	6	12	13	10	MKP1M021503G	6	12	13	10	MKP1O121503G
	5	11	18	15	MKP1M021504B	5	11	18	15	MKP1O121504B
0.018 "	6	12.5	18	15	MKP1M021804C	6	12.5	18	15	MKP1O121804C
0.022 "	6	12.5	18	15	MKP1M022204C	6	12.5	18	15	MKP1O122204C
	6	15	26.5	22.5	MKP1M022205B	6	15	26.5	22.5	MKP1O122205B
0.027 "	7	14	18	15	MKP1M022704D	7	14	18	15	MKP1O122704D
0.033 "	7	14	18	15	MKP1M023304D	7	14	18	15	MKP1O123304D
	6	15	26.5	22.5	MKP1M023305B	6	15	26.5	22.5	MKP1O123305B
0.039 "	8	15	18	15	MKP1M023904F	8	15	18	15	MKP1O123904F
0.047 "	8	15	18	15	MKP1M024704F	8	15	18	15	MKP1O124704F
	6	15	26.5	22.5	MKP1M024705B	6	15	26.5	22.5	MKP1O124705B
0.056 "	7	16.5	26.5	22.5	MKP1M025605D	7	16.5	26.5	22.5	MKP1O125605D
0.068 "	7	16.5	26.5	22.5	MKP1M026805D	7	16.5	26.5	22.5	MKP1O126805D
0.08 "	7	16.5	26.5	22.5	MKP1M028205D	8.5	18.5	26.5	22.5	MKP1O128205F
0.1 µF	7	16.5	26.5	22.5	MKP1M031005D	8.5	18.5	26.5	22.5	MKP1O131005F
	11	21	31.5	27.5	MKP1M031006B	11	21	31.5	27.5	MKP1O131006B
0.12 "	8.5	18.5	26.5	22.5	MKP1M031205F	11	21	26.5	22.5	MKP1O131205I
0.15 "	8.5	18.5	26.5	22.5	MKP1M031505F	11	21	26.5	22.5	MKP1O131505I
	11	21	31.5	27.5	MKP1M031506B	11	21	31.5	27.5	MKP1O131506B
0.18 "	11	21	26.5	22.5	MKP1M031805I	11	21	31.5	27.5	MKP1O131806B
0.22 "	11	21	26.5	22.5	MKP1M032205I	11	21	31.5	27.5	MKP1O132206B
	11	21	31.5	27.5	MKP1M032206B					
0.27 "	11	21	31.5	27.5	MKP1M033306B	15	26	31.5	27.5	MKP1O132706F
0.33 "	15	26	31.5	27.5	MKP1M033306F	15	26	31.5	27.5	MKP1O133306F
	13	24	41.5	37.5	MKP1M033307C	13	24	41.5	37.5	MKP1O133307C
0.39 "	17	29	31.5	27.5	MKP1M033906G	17	29	31.5	27.5	MKP1O133906G
0.47 "	17	29	31.5	27.5	MKP1M034706G	17	29	31.5	27.5	MKP1O134706G
	13	24	41.5	37.5	MKP1M034707C	13	24	41.5	37.5	MKP1O134707C
0.56 "	17	29	41.5	37.5	MKP1M035607E	20	39.5	31.5	27.5	MKP1O135606J
0.68 "	20	39.5	31.5	27.5	MKP1M036806J	20	39.5	31.5	27.5	MKP1O136806J
	17	29	41.5	37.5	MKP1M036807E	17	29	41.5	37.5	MKP1O136807E
0.82 "	19	32	41.5	37.5	MKP1M038207F	20	39.5	41.5	37.5	MKP1O138207G

* AC voltage: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_{\text{r}}$

** PCM = Printed circuit module = pin spacing

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Rights reserved to amend design data without prior notification.



Continuation

General Data

Capacitance	1600 VDC/650 VAC*					2000 VDC/700 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.1 μ F	11	21	26.5	22.5	MKP1T031005L	13	24	31.5	27.5	MKP1U031006D
	11	21	31.5	27.5	MKP1T031006B					
0.12 "	13	24	31.5	27.5	MKP1T031206D	15	26	31.5	27.5	MKP1U031206F
0.15 "	13	24	31.5	27.5	MKP1T031506D	15	26	31.5	27.5	MKP1U031506F
						13	24	41.5	37.5	MKP1U031507C
0.18 "	15	26	31.5	27.5	MKP1T031806F	17	34.5	31.5	27.5	MKP1U031806L
0.22 "	15	26	31.5	27.5	MKP1T032206F	17	34.5	31.5	27.5	MKP1U032206L
						17	29	41.5	37.5	MKP1U032207E
0.27 "	17	34.5	31.5	27.5	MKP1T032706L	19	32	41.5	37.5	MKP1U032707F
0.33 "	17	34.5	31.5	27.5	MKP1T033306L	19	32	41.5	37.5	MKP1U033307F
0.39 "	20	39.5	31.5	27.5	MKP1T033906J	20	39.5	41.5	37.5	MKP1U033907G
0.47 "	20	39.5	31.5	27.5	MKP1T034706J	20	39.5	41.5	37.5	MKP1U034707G
0.56 "	20	39.5	41.5	37.5	MKP1T035607G	24	45.5	41.5	37.5	MKP1U035607H
0.68 "	20	39.5	41.5	37.5	MKP1T036807G	24	45.5	41.5	37.5	MKP1U036807H
						28	38	41.5	37.5	MKP1U036807L
						35	50	41.5	37.5	MKP1U038207J
1.0 μ F	24	45.5	41.5	37.5	MKP1T041007H	35	50	41.5	37.5	MKP1U041007J
	28	38	41.5	37.5	MKP1T041007L					
1.2 "	31	46	41.5	37.5	MKP1T041207L	40	55	41.5	37.5	MKP1U041207K
1.5 "	31	46	41.5	37.5	MKP1T041507L	40	55	41.5	37.5	MKP1U041507K
						35	50	57	52.5	MKP1U041509F
1.8 "	40	55	41.5	37.5	MKP1T041807K	45	55	57	52.5	MKP1U041809H
2.2 "	40	55	41.5	37.5	MKP1T042207K	45	55	57	52.5	MKP1U042209H
2.7 "	45	65	57	52.5	MKP1T042709J					
3.3 "	45	65	57	52.5	MKP1T043309J					

Capacitance	2500 VDC/700 VAC*				
	W	H	L	PCM**	Part number
1000 pF	5	11	18	15	MKP1V011004B
	6	15	26.5	22.5	MKP1V011005B
1200 "	5	11	18	15	MKP1V011204B
1500 "	5	11	18	15	MKP1V011504B
1800 "	5	11	18	15	MKP1V011804B
2200 "	5	11	18	15	MKP1V012204B
2700 "	5	11	18	15	MKP1V012704B
3300 "	5	11	18	15	MKP1V013304B
3900 "	6	12.5	18	15	MKP1V013904C
4700 "	6	12.5	18	15	MKP1V014704C
5600 "	7	14	18	15	MKP1V015604D
6800 "	7	14	18	15	MKP1V016804D
8200 "	8.5	18.5	26.5	22.5	MKP1V018205F

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:	
Version code:	2-pin = 00 4-pin = D4
Tolerance:	20 % = M 10 % = K 5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 133.	

* AC voltage: $f \leq 1000$ Hz; $1.4 \times U_{rms} + UDC \leq U_r$

** PCM = Printed circuit module = pin spacing

Rights reserved to amend design data without prior notification.

Continuation page 59

Continuation

General Data

Capacitance	2500 VDC/700 VAC*					3000 VDC/700 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 µF	8.5	18.5	26.5	22.5	MKP1V021005F	8.5	18.5	26.5	22.5	MKP1W021005F
0.012 "	10.5	19	26.5	22.5	MKP1V021205G	10.5	19	26.5	22.5	MKP1W021205G
0.015 "	10.5	19	26.5	22.5	MKP1V021505G	10.5	19	26.5	22.5	MKP1W021505G
0.018 "	11	21	26.5	22.5	MKP1V021805L	11	21	26.5	22.5	MKP1W021805L
0.022 "	11	21	26.5	22.5	MKP1V022205I	11	21	26.5	22.5	MKP1W022205I
0.027 "	11	21	26.5	22.5	MKP1V022705I	11	21	26.5	22.5	MKP1W022705I
0.033 "	11	21	26.5	22.5	MKP1V023305L	11	21	26.5	22.5	MKP1W023305L
	9	19	31.5	27.5	MKP1V023306A	9	19	31.5	27.5	MKP1W023306A
0.039 "	11	21	31.5	27.5	MKP1V023906B	11	21	31.5	27.5	MKP1W023906B
0.047 "	11	21	31.5	27.5	MKP1V024706B	11	21	31.5	27.5	MKP1W024706B
0.056 "	13	24	31.5	27.5	MKP1V025606D	13	24	31.5	27.5	MKP1W025606D
0.068 "	13	24	31.5	27.5	MKP1V026806D	13	24	31.5	27.5	MKP1W026806D
0.082 "	15	26	31.5	27.5	MKP1V028206F	15	26	31.5	27.5	MKP1W028206F
0.1 µF	15	26	31.5	27.5	MKP1V031006F	15	26	31.5	27.5	MKP1W031006F
	13	24	41.5	37.5	MKP1V031007C	13	24	41.5	37.5	MKP1W031007C
0.12 "	17	34.5	31.5	27.5	MKP1V031206L	17	34.5	31.5	27.5	MKP1W031206L
0.15 "	17	34.5	31.5	27.5	MKP1V031506I	17	34.5	31.5	27.5	MKP1W031506I
	15	26	41.5	37.5	MKP1V031507D	15	26	41.5	37.5	MKP1W031507D
0.18 "	19	32	41.5	37.5	MKP1V031807F	19	32	41.5	37.5	MKP1W031807F
0.22 "	19	32	41.5	37.5	MKP1V032207F	19	32	41.5	37.5	MKP1W032207F
0.27 "	24	45.5	41.5	37.5	MKP1V032707H	24	45.5	41.5	37.5	MKP1W032707H
0.33 "	24	45.5	41.5	37.5	MKP1V033307H	24	45.5	41.5	37.5	MKP1W033307H
	28	38	41.5	37.5	MKP1V033307L	28	38	41.5	37.5	MKP1W033307L
0.39 "	31	46	41.5	37.5	MKP1V033907I	31	46	41.5	37.5	MKP1W033907I
0.47 "	31	46	41.5	37.5	MKP1V034707L	31	46	41.5	37.5	MKP1W034707L
0.56 "	35	50	41.5	37.5	MKP1V035607J	35	50	41.5	37.5	MKP1W035607J
0.68 "	35	50	41.5	37.5	MKP1V036807J	35	50	41.5	37.5	MKP1W036807J
0.82 "	40	55	41.5	37.5	MKP1V038207K	40	55	41.5	37.5	MKP1W038207K
1.0 µF	40	55	41.5	37.5	MKP1V041007K	40	55	41.5	37.5	MKP1W041007K
	35	50	57	52.5	MKP1V041009F	35	50	57	52.5	MKP1W041009F
1.2 "	45	55	57	52.5	MKP1V041209H	45	55	57	52.5	MKP1W041209H
1.5 "	45	55	57	52.5	MKP1V041509H	45	55	57	52.5	MKP1W041509H

* AC voltage: $f \leq 1000 \text{ Hz}$; $1.4 \times U_{\text{rms}} + \text{UDC} \leq U_r$


** PCM = Printed circuit module = pin spacing

Dims. in mm.


Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Part number completion:	
Version code:	2-pin = 00 4-pin = D4
Tolerance:	20 % = M 10 % = K 5 % = J
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 133.	

2-pin version



4-pin version










Rights reserved to amend design data without prior notification.

Continuation page 60

Continuation










Impedance change with frequency
(general guide).



Continuation

Permissible AC voltage in relation to frequency till 15° C internal temperature rise (general guide).

The information behind the cross bar denote the PCM of the measured value.














Continuation

Permissible AC current in relation to frequency till 15° C internal temperature rise (general guide).

The information behind the cross bar denote the PCM of the measured value.



Recommendation for Processing and Application of Through-Hole Capacitors

Soldering Process

Internal temperature of the capacitor must be kept as follows:

Polyester: preheating: $T_{max.} \leq 125^{\circ} C$
soldering: $T_{max.} \leq 135^{\circ} C$

Polypropylene: preheating: $T_{max.} \leq 100^{\circ} C$
soldering: $T_{max.} \leq 110^{\circ} C$

Single wave soldering

Soldering bath temperature: $T < 260^{\circ} C$


Dwell time: $t < 5 \text{ sec}$

Double wave soldering

Soldering bath temperature: $T < 260^{\circ} C$

Dwell time: $\sum t < 5 \text{ sec}$

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



WIMA Quality and Environmental Philosophy

ISO 9001:2015 Certification

ISO 9001:2015 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2015 of our factories certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- Testing as per customer requirements

WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- Lead
- PCB
- CFC
- Hydrocarbon chloride
- Chromium 6+
- PBB/PBDE
- Arsenic
- Cadmium
- Mercury
- etc.

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- adhesive tapes made of plastic
- metal clips

RoHS Compliance

According to the RoHS Directive 2015/863/EU as amended from time to time certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has re-frained from using such substances since years already.



WIMA Kondensatoren sind bleifrei konform RoHS 2015/863/EU

WIMA capacitors are lead free in accordance with RoHS 2015/863/EU

Tape for lead-free WIMA capacitors

DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

Typical Dimensions for Taping Configuration




Diagram 1:
PCM 2.5/5/7.5mm

Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5*mm

*PCM 27.5 tapping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 tapping	PCM 5 tapping	PCM 7.5 tapping	PCM 10 tapping*	PCM 15 tapping*	PCM 22.5 tapping	PCM 27.5 tapping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W ₀	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W ₁	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W ₂	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D ₀	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	*38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P ₀	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch	12.7 ±0.3 error max. 1.0 mm/20 pitch
Feed hole centre to pin	P ₁	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P ₂	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H _▲	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H ₁	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 24.5 to 31.5	H+H _{component} < H ₁ 25.0 to 31.5	H+H _{component} < H ₁ 26.0 to 37.0	H+H _{component} < H ₁ 30.0 to 43.0	H+H _{component} < H ₁ 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 ^{+0.8} _{-0.2}	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	*0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	*0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2
Package (see also page 134)	▲	ROLL/AMMO			AMMO			
		REEL Ø 360 max. Ø 30 ±1	B 52 ±2 58 ±2	depending on comp. dimensions	REEL Ø 360 max. Ø 30 ±1	B 52 ±2 58 ±2 66 ±2	or REEL Ø 500 max. Ø 25 ±1	B 54 ±2 60 ±2 68 ±2
Unit		see details page 135.						

▲ When ordering please specify dimension H and required packaging type.

Dims in mm.

• Diameter of pins see General Data.


Please clarify customer-specific deviations with the manufacturer.

* PCM 10 and PCM 15 can be crimped to PCM 7.5.


Position of components according to PCM 7.5 (sketch 1). P₀ = 12.7 or 15.0 is possible

Types of Tape Packaging of Capacitors for Automatic Radial Insertion


■ ROLL Packaging



■ AMMO Packaging



■ REEL Packaging



BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumeric Bar Code

- WIMA supplier number
- Date code
- Customer's P/O number
- P/O line
- Customer's part number
- WIMA part number
- Quantity
- WIMA confirmation number
- Country of origin
- Customer name
- Handling unit number
- Week of delivery.

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- technical note
- capacitance tolerance
- packing
- connecting information

WIMA Best Capacitors Made in Germany	
Werk Aurich	
Supplier-ID: LIEF.NR.	Date Code: 20210419
Purchase Order No. (P/O): Bestellung xyz	P/O line: 100
Customer Part No.: KUNDENTEILENUMMER	
WIMA Part No.: MKP1F041006B00KSSD	Quantity: 459
WIMA Confirmation No.: 0001105072000100	
Customer No.: 0000100002	RoHS 2011/65/EU
Gross Weight [g]: 4557	COO: DE
WIMA – MKP 10 WIMA Part No.: MKP1F041006B00KSSD	
MKP 10 1.0 µF 250 VDC 11x21x31.5 RM27.5	
Standard 10% Lose – Standard Drähte 6–2	
Vorlage Debitor Inland	
	0001105072000100
1002021443	QTY: 459 Week 19/2021

BARCODE PDF417
BARCODE 2D Datamatrix

Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm



PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
	W	H	L	Codes		S	N	O	Ø 360		Ø 500		340 x 340		490 x 370
								F	I	H	J	A	C	B	D
2.5 mm	2.5	7	4.6	0B	5000		2200	2500		-		2800		-	
	3	7.5	4.6	0C	5000		2000	2300		-		2300		-	
	3.8	8.5	4.6	0D	5000		1500	1800		-		1800		-	
	4.6	9	4.6	0E	5000		1200	1500		-		1500		-	
	5.5	10	4.6	0F	5000		900	1200		-		1200		-	
5 mm	2.5	6.5	7.2	1A	5000		2200	2500		-		2800		-	
	3	7.5	7.2	1B	5000		2000	2300		-		2300		-	
	3.5	8.5	7.2	1C	5000		1600	2000		-		2000		-	
	4.5	6	7.2	1D	6000		1300	1500		-		1500		-	
	4.5	9.5	7.2	1E	4000		1300	1500		-		1500		-	
	5	10	7.2	1F	3500		1100	1400		-		1400		-	
	5.5	7	7.2	1G	4000		1000	1200		-		1200		-	
	5.5	11.5	7.2	1H	2500		1000	1200		-		1200		-	
	6.5	8	7.2	1I	2500		800	1000		-		1000		-	
	7.2	8.5	7.2	1J	2500		700	1000		-		1000		-	
	7.2	13	7.2	1K	2000		700	950		-		1000		-	
	8.5	10	7.2	1L	2000		600	800		-		800		-	
	8.5	14	7.2	1M	1500		600	800		-		800		-	
11	16	7.2	1N	1000		500	600		-		640		-		
11	18	7.2	1O	1000		500	600		-		640		-		
7.5 mm	2.5	7	10	2A	5000		-	2500		4400		2500		-	
	3	8.5	10	2B	5000		-	2200		4300		2300		4150	
	4	9	10	2C	4000		-	1700		3200		1700		3000	
	4.5	9.5	10.3	2D	3500		-	1500		2900		1400		2700	
	5	10.5	10.3	2E	3000		-	1300		2500		1300		-	
	5.7	12.5	10.3	2F	2000		-	1000		2200		1100		-	
	7.2	12.5	10.3	2G	1500		-	900		1800		1000		-	
10 mm	4	9	13	3C	3000		-	900		1600		-		1450	
	4	9.5	13	3D	3000		-	900		1600		-		1400	
	5	11	13	3F	3000		-	700		1300		-		1100	
	6	12	13	3G	2400		-	550		1100		-		1000	
	6	12.5	13	3H	2400		-	550		1100		-		1000	
	8	12	13	3I	2000		-	400		800		-		740	
15 mm	5	11	18	4B	2400		-	600		1200		-		1150	
	6	12.5	18	4C	2000		-	500		1000		-		1000	
	7	14	18	4D	1600		-	450		900		-		850	
	8	15	18	4F	1200		-	400		800		-		740	
	9	14	18	4H	1200		-	350		700		-		650	
	9	16	18	4J	900		-	350		700		-		650	
	11	14	18	4M	1000		-	300		600		-		540	
22.5 mm	5	14	26.5	5A	1200		-	-		800		-		770	
	6	15	26.5	5B	1000		-	-		700		-		640	
	7	16.5	26.5	5D	760		-	-		600		-		550	
	8.5	18.5	26.5	5F	500		-	-		480		-		450	
	10.5	19	26.5	5G	594*		-	-		400		-		360	
	10.5	20.5	26.5	5H	594*		-	-		400		-		360	
	11	21	26.5	5I	561*		-	-		380		-		350	

* for 2-inch transport pitches.

* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

Rights reserved to amend design data without prior notification.



Packing Quantities for Capacitors with Radial Pins in PCM 27.5 mm to 52.5 mm

PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
	W	H	L	Codes		S	H16.5	H18.5	Ø 360		Ø 500		340 x 340		490 x 370
					N	O	F	I	H	J	A	C	B	D	
27.5 mm	9	19	31.5	6A	567*	-	-	-	-	460/340*	-	-	-	-	
	11	21	31.5	6B	459*	-	-	-	-	380/280*	-	-	-	-	
	13	24	31.5	6D	378*	-	-	-	-	300	-	-	-	-	
	15	26	31.5	6F	324*	-	-	-	-	270	-	-	-	-	
	17	29	31.5	6G	198*	-	-	-	-	-	-	-	-	-	
	17	34.5	31.5	6I	198*	-	-	-	-	-	-	-	-	-	
	20	39.5	31.5	6J	162*	-	-	-	-	-	-	-	-	-	
37.5 mm**	9	19	41.5	7A	441*	-	-	-	-	-	-	-	-		
	11	22	41.5	7B	357*	-	-	-	-	-	-	-	-		
	13	24	41.5	7C	294*	-	-	-	-	-	-	-	-		
	15	26	41.5	7D	252*	-	-	-	-	-	-	-	-		
	17	29	41.5	7E	154*	-	-	-	-	-	-	-	-		
	19	32	41.5	7F	140*	-	-	-	-	-	-	-	-		
	20	39.5	41.5	7G	126*	-	-	-	-	-	-	-	-		
	24	45.5	41.5	7H	112*	-	-	-	-	-	-	-	-		
	28	38	41.5	7L	84*	-	-	-	-	-	-	-	-		
	31	46	41.5	7I	84*	-	-	-	-	-	-	-	-		
	35	50	41.5	7J	35*	-	-	-	-	-	-	-	-		
40	55	41.5	7K	28*	-	-	-	-	-	-	-	-			
48.5 mm**	19	31	56	8D	120*	-	-	-	-	-	-	-	-		
	23	34	56	8E	80*	-	-	-	-	-	-	-	-		
	27	37.5	56	8H	84*	-	-	-	-	-	-	-	-		
	33	48	56	8J	25*	-	-	-	-	-	-	-	-		
	37	54	56	8L	25*	-	-	-	-	-	-	-	-		
52.5 mm	25	45	57	9D	70*	-	-	-	-	-	-	-	-		
	30	45	57	9E	60*	-	-	-	-	-	-	-	-		
	35	50	57	9F	25*	-	-	-	-	-	-	-	-		
	45	55	57	9H	20*	-	-	-	-	-	-	-	-		
	45	65	57	9J	20*	-	-	-	-	-	-	-	-		

* TPS (Tray-Packing-System). Plate versions may have different packing units.

Rights reserved to amend design data without prior notification.

**For Snubber capacitors in 2-pin version the PCM is changing to 38.5 respective 49.5 mm. Samples and pre-production needs on request.

Updated data on www.wima.com



A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 -10: Capacitance
- Field 11 -12: Size and PCM
- Field 13 -14: Version code (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 -18: Pin length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
M	K	S	2	C	0	2	1	0	0	1	A	0	0	M	S	S	D
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2			-		20%	bulk	6 -2	

<p>Type description:</p> <p>SMD-PET = SMDT SMD-PPS = SMDI MKS 02 = MKS0 FKS 2 = FKS2 FKP 2 = FKP2 MKS 2 = MKS2 MKP 2 = MKP2 MKS 4 = MKS4 MKP 4 = MKP4 MKP 10 = MKP1 FKP 1 = FKP1 MKP-X2 = MKX2 MKP-X1 R = MKX1 MKP-Y2 = MKY2 Snubber MKP = SNMP Snubber FKP = SNFP GTO MKP = GTOM DC-LINK MKP 4 = DCP4 DC-LINK MKP 6 = DCP6 DC-LINK HC = DCHC</p>	<p>Rated voltage:</p> <p>63 VDC = C0 100 VDC = D0 250 VDC = F0 400 VDC = G0 450 VDC = H0 520 VDC = H2 600 VDC = I0 630 VDC = J0 700 VDC = K0 800 VDC = L0 850 VDC = M0 900 VDC = N0 1000 VDC = O1 1100 VDC = P0 1200 VDC = Q0 1250 VDC = R0 1500 VDC = S0 1600 VDC = T0 1700 VDC = TA 2000 VDC = U0 2500 VDC = V0 3000 VDC = W0 4000 VDC = X0 6000 VDC = Y0 230 VAC = 3Y 275 VAC = 1W 300 VAC = 2W 305 VAC = AW 350 VAC = BW 440 VAC = 4W ...</p>	<p>Capacitance:</p> <p>22 pF = 0022 47 pF = 0047 100 pF = 0100 150 pF = 0150 220 pF = 0220 330 pF = 0330 470 pF = 0470 680 pF = 0680 1000 pF = 1100 1500 pF = 1150 2200 pF = 1220 3300 pF = 1330 4700 pF = 1470 6800 pF = 1680 0.01 µF = 2100 0.022 µF = 2220 0.047 µF = 2470 0.1 µF = 3100 0.22 µF = 3220 0.47 µF = 3470 1 µF = 4100 2.2 µF = 4220 4.7 µF = 4470 10 µF = 5100 22 µF = 5220 47 µF = 5470 100 µF = 6100 220 µF = 6220 1000 µF = 7100 1500 µF = 7150 ...</p>	<p>Size:</p> <p>4.8x3.3x3 Size 1812 = KA 4.8x3.3x4 Size 1812 = KB 5.7x5.1x3.5 Size 2220 = QA 5.7x5.1x4.5 Size 2220 = QB 7.2x6.1x3 Size 2824 = TA 7.2x6.1x5 Size 2824 = TB 10.2x7.6x5 Size 4030 = VA 12.7x10.2x6 Size 5040 = XA 15.3x13.7x7 Size 6054 = YA 2.5x7x4.6 PCM2.5 = 0B 3x7.5x4.6 PCM2.5 = 0C 2.5x6.5x7.2 PCM5 = 1A 3x7.5x7.2 PCM5 = 1B 2.5x7x10 PCM7.5 = 2A 3x8.5x10 PCM7.5 = 2B 3x9x13 PCM10 = 3A 4x9x13 PCM10 = 3C 5x11x18 PCM15 = 4B 6x12.5x18 PCM15 = 4C 5x14x26.5 PCM22.5 = 5A 6x15x26.5 PCM22.5 = 5B 9x19x31.5 PCM27.5 = 6A 11x21x31.5 PCM27.5 = 6B 9x19x41.5 PCM37.5 = 7A 11x22x41.5 PCM37.5 = 7B 19x31x56 PCM 48.5 = 8D 25x45x57 PCM 52.5 = 9D ...</p> <p>Version code:</p> <p>Standard = 00 Version A1 = 1A Version A1.1.1 = 1B Version A2 = 2A ...</p>	<p>Tolerance:</p> <p>±20% = M ±10% = K ±5% = J ±2.5% = H ±1% = E ...</p> <p>Packing:</p> <p>AMMO H16.5 340x340 = A AMMO H16.5 490x370 = B AMMO H18.5 340x340 = C AMMO H18.5 490x370 = D REEL H16.5 360 = F REEL H16.5 500 = H REEL H18.5 360 = I REEL H18.5 500 = J ROLL H16.5 = N ROLL H18.5 = O BLISTER W12 180 = P BLISTER W12 330 = Q BLISTER W16 330 = R BLISTER W24 330 = T Bulk/TPS Standard = S ...</p> <p>Pin length (untaped)</p> <p>3.5 ±0.5 = C9 6 -2 = SD 16 ±1 = P1 ...</p> <p>Pin length (taped)</p> <p>none = 00</p>
---	--	---	--	---

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.