


Final datasheet

HybridPACK™ Drive G2 module

Features

- Electrical features
 - $V_{CES} = 750 \text{ V}$
 - $I_{CN} = 1150 \text{ A} / I_{CRM} = 2300 \text{ A}$
 - Low $V_{CE,sat}$
 - Low switching losses
 - Low Q_g and C_{rss}
 - Low inductive design
 - $T_{vj,op} = 175^\circ\text{C}$
 - Integrated on-chip temperature sensor
 - Short-time extended operation temperature $T_{vj,op} = 185^\circ\text{C}$
- Mechanical features
 - 4.25 kV DC 1 second insulation
 - High creepage and clearance distances
 - Direct-cooled PinFin base plate
 - Guiding elements for PCB and cooler assembly
 - PressFIT contact technology
 - RoHS compliant, lead-free
 - UL 94 V0 module frame
 - High-performance Si_3N_4 ceramic
 - High power and thermal cycling capability



Potential applications

- Automotive applications
- (Hybrid) electrical vehicles (H)EV

Product validation

- Qualified according to AQC 324, release no.: 03.1/2021

Description

The HybridPACK™ Drive is a very compact six-pack module (750V/1150A) optimized for hybrid and electric vehicles.




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	4
3	Diode, Inverter	6
4	Temperature sensor	7
5	Characteristics diagrams	8
6	Circuit diagram	13
7	Package outlines	14
8	Module label code	17
	Revision history	18
	Disclaimer	19

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 0$ Hz, $t = 1$ sec	4.25	kV
Material of module baseplate			Cu+Ni ¹⁾	
Internal isolation		basic insulation (class 1, IEC 61140)	Si_3N_4	
Creepage distance	d_{creep}	terminal to heatsink	10.6	mm
Creepage distance	d_{creep}	terminal to terminal	10.6	mm
Clearance	d_{clear}	terminal to heatsink	4.5	mm
Clearance	d_{clear}	terminal to terminal	4.5	mm
Comparative tracking index	CTI		> 175	

1) Ni plated Cu baseplate.

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Maximum RMS module terminal current	$I_{t,rms}$	$T_{Ct} = 125$ °C	900			A
Heat-staking dome temperature ¹⁾	T_{HS}	$t_{steking} < 10$ s			280	°C

1) Heat-staking according to application note AN-G2-ASSEMBLY.

Table 3 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Pressure drop in cooling circuit	Δp	50% water / 50% ethylene glycol, $\Delta V / \Delta t = 10$ dm ³ /min, $T_f = 65$ °C		76 ¹⁾		mbar
Maximum pressure in cooling circuit	p	$T_{baseplate} < 40$ °C (relative pressure)			3.0	bar
		$T_{baseplate} \geq 40$ °C (relative pressure)			2.5	
Stray inductance module	$L_{s,CE}$			8.0		nH
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_f = 25$ °C, per switch		0.73		mΩ
Storage temperature	T_{stg}		-40		125	°C
Mounting torque for module mounting ²⁾	M	Screw M4 baseplate to heatsink	1.8	2.0	2.2	Nm
		Screw EJOT Delta PCB to frame	0.45	0.5	0.55	
Weight	G			760		g

1) Cooler design and flow direction according to application note AN-G2-ASSEMBLY.

2) Screw types and torque according to application note AN-G2-ASSEMBLY.

2 IGBT, Inverter

Table 4 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Collector-emitter voltage	V_{CES}	$T_{vj} = 25\text{ °C}$	750	V
Implemented collector current	I_{CN}		1150	A
Continuous DC collector current	$I_{C,nom}$	$T_f = 65\text{ °C}$, $T_{vj,max} = 175\text{ °C}$	600 ¹⁾	A
Repetitive peak collector current	I_{CRM}	verified by design, t_p limited by $T_{vj,max}$	2300	A
Total power dissipation	P_{tot}	$T_f = 65\text{ °C}$, $T_{vj,max} = 175\text{ °C}$	1000 ¹⁾	W
Gate-emitter peak voltage	V_{GES}		±20	V

1) Verified by characterization / design, not by test.

Table 5 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE,sat}$	$I_C = 600\text{ A}$, $V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$	1.08	1.21	V
			$T_{vj} = 175\text{ °C}$	1.09		
Collector-emitter saturation voltage	$V_{CE,sat}$	$I_C = 1000\text{ A}$, $V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$	1.22		V
			$T_{vj} = 175\text{ °C}$	1.32		
Gate threshold voltage	$V_{GE,th}$	$I_C = 10.3\text{ mA}$, $V_{CE} = V_{GE}$	$T_{vj} = 25\text{ °C}$	4.9	5.8	V
			$T_{vj} = 175\text{ °C}$	4		
Gate charge	Q_G	$V_{CE} = 400\text{ V}$, $V_{GE} = -8...15\text{ V}$		2.65		μC
Internal gate resistor	$R_{G,int}$	$T_{vj} = 25\text{ °C}$		1.0		Ω
Input capacitance	C_{ies}	$f = 0.1\text{ MHz}$, $V_{CE} = 50\text{ V}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$	60.8		nF
Output capacitance	C_{oes}	$f = 0.1\text{ MHz}$, $V_{CE} = 50\text{ V}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$	2.1		nF
Reverse transfer capacitance	C_{res}	$f = 0.1\text{ MHz}$, $V_{CE} = 50\text{ V}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$	0.27		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 750\text{ V}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		1.0	mA
			$T_{vj} = 175\text{ °C}$	15.0		
			$T_{vj} = 185\text{ °C}$	28.0		
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\text{ V}$, $V_{GE} = 20\text{ V}$	$T_{vj} = 25\text{ °C}$		400	nA

(table continues...)

Table 5 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Turn-on delay time, inductive load	$t_{d,on}$	$I_C = 600\text{ A}$, $V_{CE} = 400\text{ V}$, $V_{GE} = -8/15\text{ V}$, $R_{G,on} = 2.4\ \Omega$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		222		ns
			$T_{vj} = 175\text{ }^{\circ}\text{C}$		255		
Rise time, inductive load	t_r	$I_C = 600\text{ A}$, $V_{CE} = 400\text{ V}$, $V_{GE} = -8/15\text{ V}$, $R_{G,on} = 2.4\ \Omega$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		50.0		ns
			$T_{vj} = 175\text{ }^{\circ}\text{C}$		55.0		
Turn-off delay time, inductive load	$t_{d,off}$	$I_C = 600\text{ A}$, $V_{CE} = 400\text{ V}$, $V_{GE} = -8/15\text{ V}$, $R_{G,off} = 7.5\ \Omega$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		929		ns
			$T_{vj} = 175\text{ }^{\circ}\text{C}$		1060		
Fall time, inductive load	t_f	$I_C = 600\text{ A}$, $V_{CE} = 400\text{ V}$, $V_{GE} = -8/15\text{ V}$, $R_{G,off} = 7.5\ \Omega$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		91.0		ns
			$T_{vj} = 175\text{ }^{\circ}\text{C}$		199		
Turn-on energy loss per pulse	E_{on}	$I_C = 600\text{ A}$, $V_{CE} = 400\text{ V}$, $L_{\sigma} = 7\text{ nH}$, $V_{GE} = -8/15\text{ V}$, $R_{G,on} = 2.4\ \Omega$	$T_{vj} = 25\text{ }^{\circ}\text{C}$, $di/dt = 9.60\text{ A/ns}$		4.5		mJ
			$T_{vj} = 175\text{ }^{\circ}\text{C}$, $di/dt = 8.70\text{ A/ns}$		10.7		
Turn-off energy loss per pulse	E_{off}	$I_C = 600\text{ A}$, $V_{CE} = 400\text{ V}$, $L_{\sigma} = 7\text{ nH}$, $V_{GE} = -8/15\text{ V}$, $R_{G,off} = 7.5\ \Omega$	$T_{vj} = 25\text{ }^{\circ}\text{C}$, $dv/dt = 4.00\text{ V/ns}$		31.1		mJ
			$T_{vj} = 175\text{ }^{\circ}\text{C}$, $dv/dt = 2.70\text{ V/ns}$		43.0		
SC data	I_{SC}	$V_{CC} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $V_{CEmax} = V_{CES} - L_{s,CE} \cdot di/dt$	$T_{vj} = 25\text{ }^{\circ}\text{C}$, $t_p = 3.0\ \mu\text{s}$		8500		A
			$T_{vj} = 175\text{ }^{\circ}\text{C}$, $t_p = 3.0\ \mu\text{s}$		6700		
			$T_{vj} = 185\text{ }^{\circ}\text{C}$, $t_p = 2.5\ \mu\text{s}$		6600		
Thermal resistance, junction to cooling fluid ¹⁾	$R_{th,j-f}$	50% water / 50% ethylene glycol, $\Delta V/\Delta t = 10\text{ dm}^3/\text{min}$, $T_f = 65\text{ }^{\circ}\text{C}$			0.100		K/W
Variance of thermal resistance, junction to cooling fluid ¹⁾	$\sigma_{Rth,j-f}$	50% water / 50% ethylene glycol, $\Delta V/\Delta t = 10\text{ dm}^3/\text{min}$, $T_f = 65\text{ }^{\circ}\text{C}$			0.0022		K/W
Temperature under switching conditions	$T_{vj,op}$		continuous operation	-40		175	$^{\circ}\text{C}$
			extended operation			185 ²⁾	

- 1) Cooler design and flow direction according to application note AN-G2-ASSEMBLY. EoL criteria see AQG324, verified by characterization.
2) For limitation see QPAC documentation.

3 Diode, Inverter

Table 6 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25\text{ °C}$		750	V
Implemented forward current	I_{FN}			1150	A
Continuous DC forward current	$I_{F,nom}$			600	A
Repetitive peak forward current	I_{FRM}	verified by design, t_p limited by $T_{vj,max}$		2300	A
I^2t - value	I^2t	$V_R = 0\text{ V}$, $t_p = 10\text{ ms}$	$T_{vj} = 175\text{ °C}$	31250	A ² s

Table 7 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 600\text{ A}$	$T_{vj} = 25\text{ °C}$		1.76	2.08	V
			$T_{vj} = 175\text{ °C}$		1.57		
Forward voltage	V_F	$I_F = 1000\text{ A}$	$T_{vj} = 25\text{ °C}$		2.09		V
			$T_{vj} = 175\text{ °C}$		1.95		
Peak reverse recovery current	I_{rm}	$I_F = 600\text{ A}$, $V_{GE} = -8\text{ V}$, $V_R = 400\text{ V}$	$T_{vj} = 25\text{ °C}$		351		A
			$T_{vj} = 175\text{ °C}$		526		
Recovered charge	Q_r	$I_F = 600\text{ A}$, $V_R = 400\text{ V}$, $V_{GE} = -8\text{ V}$	$T_{vj} = 25\text{ °C}$		14.4		μC
			$T_{vj} = 175\text{ °C}$		43.1		
Reverse recovery energy	E_{rec}	$I_F = 600\text{ A}$, $V_{GE} = -8\text{ V}$, $V_R = 400\text{ V}$	$T_{vj} = 25\text{ °C}$, $-di_F/dt = 16.2\text{ A/ns}$		4.90		mJ
			$T_{vj} = 175\text{ °C}$, $-di_F/dt = 13.4\text{ A/ns}$		13.40		
Thermal resistance, junction to cooling fluid ¹⁾	$R_{th,j-f}$	50% water / 50% ethylene glycol, $\Delta V/\Delta t = 10\text{ dm}^3/\text{min}$, $T_f = 65\text{ °C}$			0.129		K/W
Variance of thermal resistance, junction to cooling fluid ¹⁾	$\sigma_{Rth,j-f}$	50% water / 50% ethylene glycol, $\Delta V/\Delta t = 10\text{ dm}^3/\text{min}$, $T_f = 65\text{ °C}$			0.0029		K/W
Temperature under switching conditions	$T_{vj,op}$		continuous operation	-40		175	°C
			extended operation			185 ²⁾	

1) Cooler design and flow direction according to application note AN-G2-ASSEMBLY. EoL criteria see AQG324, verified by characterization.

2) For limitation see QPAC documentation.

4 Temperature sensor

Table 8 Characteristic values


Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Transient sense current	I_{TS}					10	mA
Continuous sense current	I_{TS}					1	mA
Forward voltage	V_{TS}		$I_{TS} = 0.2\text{ mA},$ $T_{vj} = 25\text{ °C}$		2.280		V
Temperature coefficient (TCR)	TC_{TS}	$I_{TS} = 0.2\text{ mA}$			-5.50		mV/K

5 Characteristics diagrams

Pressure drop in cooling circuit (typical), Package

$\Delta p = f(\Delta V/\Delta t)$


50% water / 50% ethylene glycol , $T_f = 65\text{ }^{\circ}\text{C}$



Maximum collector-emitter voltage, IGBT, Inverter

$V_{CES} = f(T_{vj})$


Verified by characterization / design, not by test



Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 25\text{ }^{\circ}\text{C}$



5 Characteristics diagrams


Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$
 $V_{CE} = 20\text{ V}$




Gate charge characteristic (typical), IGBT, Inverter

$V_{GE} = f(Q_G)$
 $T_{vj} = 25^\circ\text{C}, V_{CE} = 400\text{ V}, I_C = 600\text{ A}$




Capacity characteristic (typical), IGBT, Inverter

$C = f(V_{CE})$
 $V_{GE} = 0\text{ V}, T_{vj} = 25^\circ\text{C}, f = 0.1\text{ MHz}$



Switching losses (typical), IGBT, Inverter


$E = f(I_C)$
 $V_{GE} = -8/15\text{ V}, R_{G,off} = 7.5\ \Omega, R_{G,on} = 2.4\ \Omega, V_{CE} = 400\text{ V}$



5 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $V_{GE} = -8/15\text{ V}$, $V_{CE} = 400\text{ V}$, $I_C = 600\text{ A}$




Reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$
 $T_{vj} = 175\text{ °C}$, $V_{GE} = -8/15\text{ V}$, $R_{G,off} = 7.5\ \Omega$




Transient thermal impedance (typical), IGBT, Inverter

$Z_{th} = f(t)$
 $\Delta V/\Delta t = 10\text{ dm}^3/\text{min}$, 50% water / 50% ethylene glycol, $T_f = 65\text{ °C}$



Thermal impedance (typical), IGBT, Inverter


$R_{th,JF} = f(\Delta V/\Delta t)$
 $T_f = 65\text{ °C}$, 50% water / 50% ethylene glycol



5 Characteristics diagrams

Forward characteristic (typical), Diode, Inverter


$I_F = f(V_F)$



Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$


$V_{CE} = 400\text{ V}, V_{GE} = -8\text{ V}, R_G = 2.4\ \Omega$



Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$


$V_{CE} = 400\text{ V}, I_F = 600\text{ A}$



Transient thermal impedance (typical), Diode, Inverter

$Z_{th} = f(t)$

$\Delta V/\Delta t = 10\text{ dm}^3/\text{min}, 50\%\text{ water} / 50\%\text{ ethylene glycol}, T_f = 65^\circ\text{C}$




5 Characteristics diagrams

Thermal impedance (typical), Diode, Inverter


$R_{thJF} = f(\Delta V/\Delta t)$

$T_f = 65\text{ }^{\circ}\text{C}$, 50% water / 50% ethylene glycol



Temperature characteristic (typical), Temperature sensor

$V_{TS} = f(T_{vj})$



6 Circuit diagram




Figure 1



7 Package outlines




Figure 3

7 Package outlines




Figure 4

8 Module label code

Module label code				
Code format	Data Matrix		Barcode Code128	
Encoding	ASCII text		Code Set A	
Symbol size	16x16		23 digits	
Standard	IEC24720 and IEC16022		IEC8859-1	
Code content	<i>Content</i> Module serial number Module material number Production order number Date code (production year) Date code (production week)	<i>Digit</i> 1 – 5 6 - 11 12 - 19 20 – 21 22 – 23	<i>Example</i> 71549 142846 55054991 15 30	
Example	 7154914284655054991153071549142846550549911530			

Packing label code				
Code format	Barcode Code128			
Encoding	Code Set A			
Symbol size	34 digits			
Standard	IEC8859-1			
Code content	<i>Content</i> Backend Construction Number Production Lot Number Serial Number Date code Box Quantity	<i>Identifier</i> X 1T S 9D Q	<i>Digit</i> 2 – 9 12 – 19 21 – 25 28 – 31 33 – 34	<i>Example</i> 95056609 2X0003E0 754389 1139 15
Example	 X950566091T2X0003E0S754389D1139Q15			

Figure 5



Revision history

Revision history

Document revision	Date of release	Description of changes
0.10	2024-10-30	Initial version
1.00	2025-07-04	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-07-04

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2025 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABL308-002

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.