Inductive proximity sensors XS extensive range

Catalogue









Inductive proximity sensors XS extensive range

Selection guide, standard sensorspage
Selection guide, basic sensors
■ General
Flush mountability using teach mode:
Simplicity through innovation
XS range, general purpose sensors
Cylindrical type
□ Standard range, flush mountable
□ Increased range, flush mountable
□ Increased range, non-flush mountablepage 4
■ Block type, flat format
□ Standard range, flush mountable
□ Increased range, flush mountable using teach modepage 5
■ Cubic type
40 x 40 x 70 mm format, flush or non-flush mountable page 5
□ 40 x 40 x 117 mm format, flush or non-flush mountable page 5
Multivoltage sensors with short-circuit protectionpage 6
Sensors with 2 complementary outputs
□ Solid-state PNP or NPN, NO + NC outputs
□ Solid-state PNP + NPN, NO or NC programmable outputs page 6
Plastic case sensors
(also for chemical processing, marine applications)
Quasi-flush mountable sensors, increased range
Miniature sensorspage 7
XS range, basic sensors
■ Standard range, flush or non flush mountable
■ Increased range, flush mountable
XS range, applicative sensors
Adjustable range sensorspage 8
Sensors for rotation monitoring, slip and shaft overload detection page 8
Sensors with analogue output
Sensors for food & beverage and pharmaceutical applications
□ Cubic, plastic
□ Cylindrical, stainless steel
□ Cylindrical, plastic
 Sensors for assembly, packaging and light material handling applications 80 x 80 x 40 mm format
Sensors for welding machine applications
XS range, Fail Safe sensors
Cylindrical typepage 12
□ Standard range
Cubic type
□ 40 x 40 x 70 mm format
XS range
■ Accessories
■ Detection curves
Substitution table page 13
Product reference index page 14

XS range General purpose

Cylindrical type

Standard range

Flush mountable











Sensing distance Sn (mm)				
Diameter				
Short case	Supply 3-wire (PNP/NPN)			
	2-wire 			
Long case	Supply 3-wire (PNP/NPN) 2-wire 2-wire			
Function	NO NC			
Connection	Pre-cabled (L = 2 m) (1) M8 connector, 3-pin (3-wire) M12 connector 1/2"-20UNF connector Remote connector			
Degree of protect	ction			
Special temperatures	- 40 °C, + 70 °C - 25 °C, + 85 °C			
Type reference)			

1.5	2	5	10
Ø 6.5 plain and M8	M12	M18	M30
Page 26			
Page 30			
Page 27			
Page 31			
-	Page 34		
•	•	•	•
•	•	•	•
•	•	•	•
•	-	-	-
•	•	•	•
•	•	•	

 $M8, M12, M18, screw\ terminal, 7/8", DIN: please\ consult\ our\ Customer\ Care\ Centre$

IP 65 and IP 67, IP 68 for pre-cabled version, IP 69K for diameters 12 to 30 (2)

Add the suffix TF to the end of the reference (3)

Add the suffix TT to the end of the reference (3)

XS506	XS508	XS512	XS518	XS530

26 to 35

- (1) Also available in lengths of 5 and 10 m, depending on model (2) For M12 connector version
- (3) Product availability depending on model: please consult our Customer Care Centre.

Pages

Increased range

Flush mountable

Non-flush mountable



















2.5	4	8	15	4	7	8	12	16	22	30
Ø 6.5 plain and M8	M12	M18	M30	M8	M12		M18		M30	
Pages 36 and	137			_	-	Page 46	-	Page 46	-	-
Page 40				-	-	-	-	-	-	-
Page 38				Page 44	Page 44	_	Page 44	_	_	Page 44
Page 40				_	_	_	_	_	_	_
-	Page 42			_	_	_	Page 48	-	Page 48	_
•	•	•	•	•	•	•	•	•	•	•
•	•	•	•	•	•	•	•	•	•	•
•	•	•	•	•	•	•	•	•	•	•
•	-	-	_	•	_	-	_	-	_	-
•	•	•	•	_	•	•	•	•	•	•
_	•	•	•	_	_	_	•	_	•	_

Remote connectors available: M8, M12, M18, screw terminal, 7/8", DIN: please consult our Customer Care Centre

IP 65 and IP 67, IP 68 for pre-cabled version, IP 69K for diameters 12 to 30 (2)

Add the suffix TF to the end of the reference (3)

Add the suffix TT to the end of the reference (3)

XS106 XS606 XS108 XS608	XS112 XS612	XS118 XS618	XS130 XS630	XS608	XS612	XS212	XS618	XS218	XS630
36 to 43				44 to 49					

XS range General purpose

Block type (flat format) and cubic type

Standard range

Flush mountable












Sensing distance Sn (mm)						
Dimensions (W >	Dimensions (W x H x D)					
Supply	3-wire == (PNP/NPN)					
	2-wire ===					
	≂					
Function	NO					
	NC					
	NO + NC					
	NO/NC					
Connection	Pre-cabled (L = 2 m) (1)					
	M8 connector, 3-pin (3-wire ===)					
	M12 connector					
	1/2"-20UNF connector					
	Screw terminals					
	Remote connector	M8				
		M12				
		1/2"-20 UNF				
	Other remote connectors a	vailable				
Degree of protect	tion					
Special	- 40 °C, + 70 °C					
temperatures	- 25 °C, + 85 °C					
Type reference						
Pages						

2.5	5	10	15	40
8 x 22 x 8	15 x 32 x 8	26 x 26 x 13	40 x 40 x 15	80 x 80 x 26
Page 50	Page 50	Page 52	Page 52	Page 52
Page 50	Page 50	Page 52	Page 52	Page 52
-	-	-	-	-
•	•	•	•	•
•	•	•	•	•
•	•	•	-	-
•	•	•	-	-
•	•	•	•	•
-	_	•	•	-
_	•	•	_	•
_	•	•	_	-
_	•	•	_	-
•	•	•	-	_
_	_	•	•	-
_	-	-	-	-
M18, screw tern	ninal, 7/8", DIN: p	lease consult ou	r Customer Care	Centre
IP 67	IP 67 or IP 68, d	epending on mo	del	
Add the suffix T	F to the end of the	e reference (2)		
Add the suffix T	T to the end of the	e reference (2)		
XS7J	XS7F	XS7E	XS7C	XS7D
Page 50		Page 52		

(1) Also available in lengths of 5 and 10 m, depending on model. (2) Product availability depending on model: please consult our Customer Care Centre.

Standard and increased ranges

Flush mountable











15	20	40
40 x 40 x 70 and 40 x 40 x 117		
Pages 56 and 58		
Pages 56 and 58		
Pages 56 and 58		
•	•	•
•	•	•
•	•	•
•	•	•
-	-	-
-	-	-
•	•	•
•	•	•
•	•	•
-	-	-
_	-	-
-	-	-
-		
IP 65, IP 67 and IP 69K		
Add the suffix TF to the end of the reference (2)		


Add the suffix TT to the end of the reference (2)

XS7C2, XS7C4, XS8C2 and XS8C4

56 and 58

XS range General purpose

Sensor type: flush and non-flush mountable



Sensing	Flush mountable
distance Sn	Quasi flush mountable
(mm)	Non-flush mountable
Diameter	
Case material	
Supply	=
	$\overline{\sim}$
	$\overline{\sim}$
Function	NO
	NC
	NO + NC
	NO/NC
Connection	Pre-cabled (L = 2 m) (1)
	M8 connector, 3-pin (3-wire ==)
	M12 connector
	1/2"-20UNF connector
	Remote connector
Degree of protec	tion
Special	- 40 °C, + 70 °C
temperatures	- 25 °C, + 85 °C
Type reference	
Pages	

2 10	1.5 15	2 10
-	-	-
4 15	2.515	4 15
Threaded: M12, M18, M30	Plain: Ø 6.5 Threaded: M8, M12, M18, M30	Threaded: M12, M18, M30
Nickel plated brass	Nickel plated brass or stainless steel or plastic	Nickel plated brass or plastic
-	•	•
-	-	-
•	-	-
•	_	-
•	_	-
-	•	-
-	-	 programmable
•	•	•
-	_	-
-	•	•
•	-	-
Remote connectors available: M8, M12, M18, screw terminal,	, 7/8", DIN: please consult our Cust	tomer Care Centre
IP 67, IP 68 or IP 69K dependir	ng on model	
Add the suffix TF to the end of t	the reference (2)	
Add the suffix TT to the end of t	the reference (2)	
XS1M XS2M	XS1••••C410 XS4P•••C410 XS1••B3PC•	XS1MeeKP340 XS2MeeKP340 XS4PeeKP340
60	62 and 66	68

(1) Also available in lengths of 5 and 10 m, depending on model.
(2) Product availability depending on model: please consult our Customer Care Centre.

Plastic case sensors	Almost flush mountable sensors	Miniature sensors
For chemical processing, marine applications	For repetitive machines	For robotic, transfer machine, assembly line applications







-	-	-		
-	-	0 0.65	0 1.21	
2.5 15	2.5 20	-		
Threaded: M8, M12, M18, M30	Threaded: M8, M12, M18, M30	XS●●4: Ø 4 Threaded: M5		
Plastic	Nickel plated brass	Stainless steel		
•	•	•		
-	-	-		
•	-	-		
-	•	•		
•	•	•		
-	-	-		
-	-	-		
•	•	•		
-	•	•		
-	•	-		
•	_	-		
Remote connectors available: M8, M12, M18, screw terminal, 7/8", D	IN: please consult our Customer Care Ce	ntre		
IP 67 or IP 68 depending on model	IP 67 or IP 68 IP 69K depending on model	IP 67		
Add the suffix TF to the end of the refe	rence (2)	-		
Add the suffix TT to the end of the refe	rence (2)	-		
XS4P	XS1N●●349	XS504••••, XS505••••	XS604••••, XS605••••	
70	72	76		

XS range Applications

Applications



Conveying

Sensor type: flush and non-flush mountable

Developed in accordance with the needs expressed by our customers, these sensors provide a complete solution for specific application functions: rotation monitoring, selective detection, analogue control, etc.



Adjustable range sensors



3...11 (1)



15





Sensing dist.	Flush mountable					
Sn (mm)	Non-flush mountable					
Form	Cylindrical					
	Block (W x H x D) dimensions in mm					
Case material						
Supply	=					
	\sim					
	≂					
Function	NO					
	NC					
	NO + NC					
	NO/NC					
Connection	Pre-cabled (L = 2 m) (2)					
	M8 connector, 3-pin (== 3-wire)					
	M12 connector					
	M12 connector 1/2"-20UNF connector					
	1/2"-20UNF connector					
Degree of protec	1/2"-20UNF connector Remote connector Screw terminals					
Special	1/2"-20UNF connector Remote connector Screw terminals tion -40 °C, +70 °C					
	1/2"-20UNF connector Remote connector Screw terminals					
Special	1/2"-20UNF connector Remote connector Screw terminals tion -40 °C, +70 °C -25 °C, +85 °C					

- ()						
518 (1)	-	-	-			
M12 x 54 M18 x 67 M30 x 71	_	-	-			
-	26 x 26 x 13	40 x 40 x15	80 x 80 x 26			
Nickel plated brass	PBT	PBT	PBT			
•	•	•	•			
-	-	_	-			
-	•	•	•			
•	•	•	•			
•	•	•	•			
-	-	-	-			
-	-	-	-			
-	•	•	•			
-	•	•	-			
-	-	_	•			
-	-	-	•			
•	•	•	•			
-	-	-	-			
IP 67	IP 67 or IP 68, depend	ding on model.				
Add the suffix TF to the end of the reference (4)						
Add the suffix TT to the	end of the reference (4	4)				
XS612B2 XS618 B2 XS630 B2	XS8E	XS8C	XS8D			
88	54					

- (1) Depending on model.

- (2) Also available in lengths of 5 and 10 m, depending on model.
 (3) For M12 connector version
 (4) Product availability depending on model: please consult our Customer Care Centre.





Detection of underspeed, shaft overload

Position, displacement and deformation control/monitoring

Machine with stainless steel housing

Sensors for rotation monitoring

Sensors with analogue output 0 ... 10 V or 4 ... 20 mA

Sensors for food/beverage and pharmaceutical applications

Cylindrical, stainless steel 316 L Cylindrical, plastic

















10	1015 (1)	0.210 (1)	540 (1)	-	-	6,10 or 20 (1)	-	-
10	1015 (1)	0.415 (1)	540 (1)	225	225	10, 20 or 40 (1)	722 (1)	722 (1)
M30 x 81	-	Threaded: M12, M18, M30	-	-	-	Threaded: M12, M18, M30	Plain: Ø 18 Threaded: M12, M18, M30	Threaded: M12, M18, M30
-	26 x 26 x 13 40 x 40 x 15	-	32 x 15 x 8 26 x 26 x 13 40 x 40 x 15 80 x 80 x 26	40 x 40 x 70	40 x 40 x 117	-	-	-
Metal	PBT	Metal or plastic	PBT	PBT	PBT	Stainless steel, 316 L	Stainless steel, 316 L	Plastic, PPS
•	•	•	•	•	•	•	•	•
_	-	-	-	-	-	_	-	_
•	•	_	-	-	-	-	•	•
-	-	-	-	-	-	•	•	•
•	•	-	-	_	-	-	_	-
_	_	-	-	_	-	-	-	-
_	-	_	-	_	-	_	-	_
•	-	•	•	-	-	-	•	•
_	-	-	-	_	-	-	-	-
_	-	-	•	•	-	•	•	•
_	-	_	-	_	-	-	•	•
-	•	_	•	_	_	_	_	_
-	_	_	-	_	•	_	-	-
IP 67	IP 67	IP 67	IP 67 or IP 68 (pre-cabled version)	IP 65, IP 67 IP 69K	IP 65, IP 67 IP 69K	IP 68, IP 69K	IP 68 (pre-cable IP 69K conform DIN 40050 (3)	

Add the suffix TF to the end of the reference (4)
Add the suffix TT to the end of the reference (4)

XSAV		XS1MeeeAB1 XS4PeeAB1	XS9•••A	XS9C2	XS9C4	XS9••S•	XS2∙∙SA	XS2∙∙AA
87	89	91	95 and 97	98	98	100	102 and 104	106 and 108

XS range Applications

Applications








Conveying

Robotics

Sensor type: flush and non-flush mountable						

Developed in accordance with the needs expressed by our customers, these sensors provide a complete solution for specific application functions: rotation monitoring, selective detection, analogue control, etc.









Sensing dist.	Flush mountable
Sn (mm)	Non-flush mountable
Form	Cylindrical
	Block (W x H x D) dimensions in mm
Case material	
Supply	=
	\sim
	≂
Function	NO
	NC
	NO + NC
	NO/NC
Connection	Pre-cabled (L = 2 m) <i>(2)</i>
	M8 connector, 3-pin (== 3-wire)
	M12 connector
	1/2"-20UNF connector
	Remote connector
	Screw terminals
Degree of protec	tion
Special	- 40 °C, + 70 °C
temperatures	- 25 °C, + 85 °C
	- 40 °C, + 85 °C (storage)
Type reference	
Pages	

3, 6, 10 or 20 (1)	50	6 or 10 (1)
6, 10, 20 or 40 (1)	42	-
Threaded: M8, M12, M18, M30	-	Threaded: M12, M18
-	80 x 80 x 40	-
Stainless steel 303	PBT	Stainless steel 303
•	•	•
-	_	_
-	-	-
•	•	•
-	-	-
-	-	-
-	-	-
_	_	_
-	-	_
•	•	•
-	-	-
-	-	-
_	_	_
IP 67 and IP 69K	IP 67	IP 68 and IP 69K
Add the suffix TF to the end of t	he reference (3)	
Add the suffix TT to the end of t	he reference (3)	
-		
XS9••R•	XS7D	XS9••RW

- (1) Depending on model.

112

(2) Also available in lengths of 5 and 10 m, depending on model.
(3) Product availability depending on model: please consult our Customer Care Centre





Assembly machines, conveyor systems, material handling

Factor 1 (Fe/Nfe) sensors for ferrous and non ferrous materials		Selective detection sensors for ferrous materials only or non ferrous materials	Fail Safe				
Cylindrical	Cubic	Rectangular	only Cylindrical	Cylindrical	Cylindrical, increased range	Cubic	Rectangular
	Manager International Internat			Townson Market M		INCOME OF THE PARTY OF THE PART	The second of th

5, 10 or 15 (1)	20	20	5	2, 5 or 10 (1)	4, 8 or 15 (1)	20	20
_	-	-	-	-	-	40	40
Threaded: M18, M30	-	-	Threaded: M18	Threaded: M12, M18, M30	Threaded: M12, M18, M30	-	-
_	40 x 40 x 70	40 x 40 x 117	-	-	-	40 x 40 x 70	40 x 40 x 117
Metal	PBT	PBT	Metal	Nickel plated brass/PPS	Nickel plated brass	PBT	PBT
•	•	•	•	•	•	•	•
_	-	-	_	-	_	-	-
_	-	-	-	-	-	-	-
-	-	-	•	-	-	-	-
_	-	-	-	-	-	-	-
_	•	•	-	•	•	•	•
•	-	-	-	-	-	-	-
•	-	-	•	•	•	-	-
_	-	_	_	_	_	-	-
•	•	_	-	•	•	•	-
_	-	_	-	-	_	-	-
•	-	_	_	_	_	-	-
_	-	•	-	-	-	-	•
IP 68	IP 65, IP 67 and IP	69K	IP 68	IP 65, IP 67, and IF IP 65 and IP 68 for		IP 65, IP 67, and IF	P 69K
Add the suffix TT to	the end of the refere	ence (3)		•	•	•	•
Add the suffix TT to	the end of the refere	ence (3)					
_				•	•	•	•
XS1M•••KP	XS9C2	XS9C4	XS1M18PA	XS5••BSPD	XS1••BSPD	XS8C2A•PD	XS8C4A•PD
114	116	116	118	120	122	124	126

XS range Basic sensors

Cylindrical, metal



Sensing distance Sn (mm)					
Diameter					
Power supply					
Function					
Output					
Length (mm) for	pre-cabled versions				
Connection	Pre-cabled (L = 2 m) (2)				
	M8 connector, 3-pin				
	M12 connector, 4-pin				
Operating temperature	erature				
Degree of protect	ction				
Type reference					
Pages					

2.5	4	8	15
M8	M12	M18	M30
3-wire, 1224 V			
NO or NC			
PNP or NPN			
42	49	53	57
•	•	•	•
•	-	-	-
•	•	•	•
-25+70 °C			
IP 65 and IP 67			
XS108BH•••	XS112BH•••	XS118BH•••	XS130BH•••
82			


⁽¹⁾ Sensors with an increased range are sold individually or are available in bulk packs on request. Please contact our Customer Care Centre

⁽²⁾ Available in lengths of 3, 5 and 7 m, depending on model. Please contact our Customer Care Centre.

-							
Standard range							
Flush mountable				Non flush mour	ntable		
	C XXIII		The Control of the Co		551	Training and the second	meani ne XS
1.5	2	5	10	2.5	4	8	15
M8	M12	M18	M30	M8	M12	M18	M30
== 3-wire, 1224 V				3-wire, 1224 V			
NO or NC				NO or NC			
PNP or NPN				PNP or NPN			
42	44	53	57	42	44	53	57
•	•	•	•	•	•	•	•
•	-	-	-	•	-	-	-
•	•	•	•	•	•	•	•
-25+70 °C			-25+70 °C				
IP 65 and IP 67			IP 65 and IP 67				
XS108BL•••	XS112BL•••	XS118BL•••	XS130BL•••	XS208BL•••	XS212BL•••	XS218BL•••	XS230BL•••
78 and 79				78 and 79			

XS range

Standards and certifications Parameters related to the environment



Temperature °C – ■ – Humidity as %

Recommendations

The sensors detailed in this catalogue are designed for use in standard industrial applications relating to presence detection.

These sensors do not incorporate the required redundant electrical circuit enabling their usage

For safety applications, please consult our website: www.telemecaniquesensors.com

Quality control

Our inductive proximity sensors are subject to special precautions in order to guarantee their reliability in the most arduous industrial environments.

- ☐ The product characteristics stated in this catalogue are subject to a qualification procedure carried out in our laboratories.
- □ In particular, the products are subjected to **climatic cycle** tests for 3000 hours whilst powered-up to verify their ability to maintain their characteristics over time

■ Production

- □ The electrical characteristics and sensing distances at both ambient temperature and extreme temperatures are 100% checked.
- □ Products are randomly selected during the course of production and subjected to monitoring tests relating to all their qualified characteristics.

Customer returns

If, in spite of all these precautions, defective products are returned to us, they are subject to systematic analysis and corrective actions are implemented to eliminate the risks of the fault recurring.

Conformity to standards

All Telemecanique Sensors brand inductive proximity sensors conform to and are tested in accordance with the recommendations of standard IEC 60947-5-2.

The sensors are tested in accordance with standard IEC 60068-2-27, 50 gn, duration 11 ms.

Vibration resistance

The sensors are tested in accordance with standard IEC 60068-2-6, amplitude ± 2 mm, f = 10...55 Hz, 25 gn at 55 Hz.

Resistance to the environment

- Please refer to the characteristics pages for the various sensors.
- IP 67: protection against the effects of immersion. Test conforming to IEC 60529: sensor immersed for 30 minutes in 1 m of water. No deterioration in either operating or insulation characteristics is permitted.
- IP 68: protection against prolonged immersion. Sensor immersed for 336 hours in 40 metres of water at 50 °C.
 - No deterioration in either operating or insulation characteristics is permitted. Telemecanique Sensors with an IP 68 degree of protection are ideal for use in the most arduous conditions, such as machine tools, automatic car washers.
- IP 69K: protection against the effects of high pressure cleaning. Adherence to standard DIN 40050 which stipulates that the product must withstand a water jet at a pressure of 90 bar and temperature of +80 °C for 3 minutes.

No deterioration in either operating or insulation characteristics is permitted

Resistance to electromagnetic interference

■ Electrostatic discharges

■ Emission =, \sim , and \sim

- Radiated electromagnetic fields (electromagnetic waves)
- Fast transients (motor start/stop interference)
- Conducted electromagnetic fields
- \sim and \sim versions: 4 kV CD/8 kV AD immunity. IEC 61000-4-2
- and

 versions: 3 V/m or 10 V/m immunity. IEC 61000-4-3
- == version: > 1 kV immunity
- \sim and \sim versions: 2 kV immunity except Ø 8 mm model. IEC 61000-4-4
- -, and ≂ versions: > 3 kV immunity. IEC 61000-4-6

Resistance to chemicals in the environment

- Owing to the very wide range of chemicals encountered in industry, it is very difficult to give general guidelines common to all sensors.
- To ensure lasting efficient operation, it is essential that any chemicals coming into contact with the sensors will not affect their casing and, in doing so, prevent their reliable operation.
- Cylindrical and flat plastic case sensors offer excellent overall resistance to:
- □ chemical products such as salts, aliphatic and aromatic oils, petroleum, acids and diluted bases. For alcohols, ketones and phenols, preliminary tests should be made relating to the nature and concentration of the liquid.
- □ food and beverage industry products such as animal or vegetable based products (vegetable oils, animal fat, fruit juice, dairy proteins, etc.). In all cases, the materials selected (see product characteristics) provide satisfactory

compatibility in most industrial environments (for further information, please consult our Customer Care Centre).

Insulation

Class 2 devices

Electrical insulation conforming to standards IEC 61140 and NF C 20-030 relating to means of protection against electric shock.


XS range


Principle of inductive detection



- Oscillator
- Output driver
- Output stage

Composition of an inductive proximity sensor





Detection of a metal object

Operating principle

An inductive proximity sensor is solely for the detection of metal objects

It basically comprises an oscillator whose windings constitute the sensing face. An alternating magnetic field is generated in front of these windings.

■ When a metal object is placed within the magnetic field generated by the sensor, the resulting currents induced form an additional load and the oscillations cease

This causes the output driver to operate and, depending on the sensor type, a normally open (NO) or normally closed (NC) output signal is produced.

Inductive proximity detection

- Inductive proximity sensors enable the detection, without physical contact, of metal objects.
- Their range of applications is very extensive and includes
- monitoring the position of machine parts (cams, end stops, etc.),
- □ counting the presence of metal objects, etc.

Advantages of inductive detection


- No physical contact with the object to be detected, thus avoiding wear and enabling detection of fragile objects, freshly painted objects, etc.
- High operating rates. Fast response.
- Excellent resistance to industrial environments (robust products, fully encapsulated in resin).
- Solid-state technology: no moving parts, therefore service life of sensor not related to number of operating cycles.

Flush mountable using teach mode sensors


The flush mountable sensors using teach mode are suitable for all metal environments (flush mountable or non-flush mountable) since they ensure a maximum sensing distance, even if there is a metal background. Precise detection of the position of the object can be obtained using the teach mode. For further information, see page 24.




The flush mountable sensors using teach mode are fitted with a green LED that indicates "Power on" and also assists the user during setting-up (teach mode).



Mounting sensors on a metal support





Flush mountable in metal


- No side clearance required.
- All flush mountable sensors using teach mode also enable detection of an object against a metal background. For further information, see pages 24 and 25.

Sensors not suitable for flush mounting in metal

- Side clearance required.
- Sensing distance greater than that for a standard flush mountable model.
- Flush mountable sensors using teach mode eliminate the need for side clearance. For further information, see pages 24 and 25.

XS range


Mounting sensors on a metal support




Mounting using fixing clamp

- Standard flush mountable models: e = 0, h = 0
- Standard non-flush mountable models
- \square Ø 6.5 / 8 / 12 mm: e = 0, h = 0
- □ Ø 18 mm: if h = 0, e \geq 5; e = 0, h \geq 3. □ Ø 30 mm: if h = 0, e \geq 8; e = 0, h \geq 4.
- Flush mountable sensors using teach mode: e = 0, h = 0

Mounting distance between sensors





Standard sensors

If 2 standard sensors are mounted too close to each other they are likely to lock in the "detection state" due to interference between their respective oscillating frequencies. To avoid this condition, the minimum mounting distances stated for the sensors should be

adhered to or, alternatively, sensors with staggered oscillating frequencies should be used.

Staggered frequency sensors

For applications where the minimum recommended mounting distances for standard sensors cannot be achieved, it is possible to overcome this restraint by using staggered frequency sensors. Please consult our Customer Care Centre.

In this case, a staggered frequency sensor is mounted adjacent to or opposite each standard sensor.


Tightening torque for cylindrical type sensors





Maximum tig	htening	torque for t	he variou	s sensor ca	se materi	als
	Metal		Stainl	ess steel	Plasti	С
	XS1ee		XS1ee		XS2ee	
	XS2ee		XS2ee XS9ee		XS4P•	
	XS600 XSAV0 XS1N0 XS1M0 XS2M0	B•	XS9••			
Diameter of sensor	Maxim	um tightening	gtorque			
	Maxim N.m	um tightening lb-in	y torque N.m	lb-in	N.m	lb-in
of sensor			· .	lb-in –	N.m –	lb-in –
of sensor mm	N.m	lb-in	N.m			
of sensor mm Ø 5	N.m 1.6	Ib-in 14.16	N.m –	- -	-	_
of sensor mm Ø 5 Ø 8	N.m 1.6	Ib-in 14.16 44.25	N.m - 9	79.65	1	8.85

XS range

Sensing distance









- Forbidden zone
- Enable zone Transition zone
- Transition 2016
 Disable zone
 Standard metal target plate according to IEC 947-5-2 at an ambient temperature of 20°C

Terminology



E = pick-up point, the object is detected PR = drop-out point, the object is no longer detected



- Detection threshold curves
- "Object detected" LED

Definitions

In order to ensure that customers can make reliable product comparisons and selection, the standard IEC 60947-5-2 defines various sensing distances, such as:

■ Nominal sensing distance (Sn)

The rated operating distance for which the sensor is designed. It does not take into account any variations (manufacturing tolerances, temperature, voltage).

Effective sensing distance (Sr)

The effective sensing distance is measured at the rated voltage (Un) and the rated ambient temperature (Tn).

It must be between 90% and 110% of the nominal sensing distance (Sn): $0.9 \text{ Sn} \leq \text{Sr} \leq 1.1 \text{ Sn}$.

Usable sensing distance (Su)

The usable sensing distance is measured at the limits of the permissible variations in the ambient temperature (Ta) and the supply voltage (Ub). It must be between 90% and 110% of the effective sensing distance: $0.9 \, \text{Sr} \le \text{Su} \le 1.1 \, \text{Sr}$.

Assured operating distance (Sa).

This is the operating zone of the sensor. The assured sensing distance is between 0 and 81% of the nominal sensing distance (Sn): 0 ≤ Sa ≤ 0.9 x 0.9 x Sn.

Standard metal target

The standard IEC 60947-5-2 defines the standard metal target as a square mild steel (Fe 360) plate, 1 mm thick

The side dimension of the plate is either equal to the diameter of the circle engraved on the sensing face of the sensor or 3 times the nominal sensing distance (Sn).

Fail Safe

■ Forbidden zone (1)

This zone ensures that it will not be possible to defeat the solution with simple elements or standard tools (ie: glue a coin on the front face). It is a minimum distance maintaining safe condition in all aspects. In this zone, both sensor outputs are opened.

Assured operating distance (Sao)

When the target approaches the sensor, the contacts will change state no later than Sao max and remain in the same state as the target continues to approach the switch. At distances beyond the Sao min, the contacts enter in the forbidden zone, not maintaining a closed condition in all aspects.

Assured release distance (Sar)

Minimum distance from the sensor that the target must move to assure the reset of the

Standard metal target plate (5) According to IEC 947-5-2 at an ambient temperature of 20°C.

Differential travel

The differential travel (H), or hysteresis, is the distance between the operating point, as the standard metal target moves towards the sensor, and the release point, as it moves away. This hysteresis is essential for the stable operation of the sensor.

The repeat accuracy (R) is the repeatability of the sensing distance between successive operations. Readings are taken over a period of time whilst the sensor is subjected to voltage and temperature variations: 8 hours, 10 to 30 °C, Un ± 5 %.

It is expressed as a percentage of the effective sensing distance Sr.

For all XS sensors, the repeat accuracy is 3 %.

Detection zone and precision adjustment zone

■ Flush mountable sensors using teach mode, due to adjustment of sensitivity whilst teaching, enable the position of an object to be detected as it approaches from the front or side. The teach mode can be used when the object is located in the zone known as the "precision adjustment zone". When the object approaches from the front, the detection zone of the object ranges from the stored position down to zero.

Operating zone

The operating zone relates to the area in front of the sensing face in which the detection of a metal object is certain.

The values stated in the characteristics relating to the various types of sensor are for steel objects of a size equal to the sensing face of the sensor.

For objects of a different nature (smaller than the sensing face of the sensor, other metals, etc.), it is necessary to apply a correction coefficient.

XS range

Correction coefficients to apply to the assured operating distance

Assured operating distance of a sensor


In practice, most objects to be detected are generally made of steel and are of a size equal to, or greater, than the sensing face of the sensor.

For the calculation of the assured operating distance for different operating conditions, one must take into account the correction coefficients that influence it.

The curves indicated are purely representative of typical curves. They are only given as a guide to the approximate usable sensing distance of a proximity sensor for a given application.

Influence of ambient temperature

Apply a correction coefficient Kq, determined from the curve shown opposite.



Material of object to be detected

Apply a correction coefficient Km, determined from the diagram shown opposite.

The fixed sensing distance models for ferrous/non ferrous (Fe/NFe) materials enable the detection of different objects at a fixed distance, irrespective of the type of material.




Steel Brass

Special case of a very thin object made of a non ferrous material.

Typical curve for a copper object used with a Ø 18 mm cylindrical sensor

Stainless steel



Typical curve for a steel object used with a cylindrical

Size of object to be detected

Apply a correction coefficient Kd, determined from the curve shown opposite. When calculating the sensing distance for the selection of a sensor, make the assumption that Kd = 1.

Calculation examples

Variation of supply voltage

In all cases, apply the correction coefficient Kt = 0.9.

Correction of the sensing distance of a sensor

Sensor with nominal sensing distance Sn = 15 mm. Ambient temperature variation 0 to + 20 °C Object material and size: steel, 30 x 30 x 1 mm thick. The assured sensing distance Sa is determined using the formula: Sa = Sn x Kq x Km x Kd x Kt = $15 \times 0.98 \times 1 \times 0.95 \times 0.9$

i.e. Sa = 12.5 mm.

Selecting a sensor for a given application

Application characteristics:


- object material and size: iron (Km = 0.9), 30 x 30 mm, temperature: 0 to 20 °C ($K\theta$ = 0.98),
- object detection distance: 3 mm ± 1.5 mm, i.e. Sa max. = 4.5 mm,
- assume Kd = 1.


A sensor must be selected for which $\operatorname{Sn} \geqslant \frac{\operatorname{Sa}}{\operatorname{Kq} \times \operatorname{Km} \times \operatorname{Kd} \times \operatorname{Kt}} = \frac{4.5}{0.98 \times 0.9 \times 1 \times 0.9}$


i.e. Sn ≥ 5.7 mm

XS range

Specific aspects of electronic sensors







Supply

Terminology

- Residual current (Ir)
- The residual current (Ir) corresponds to the current flowing through the sensor when in the "open" state
- ☐ Characteristic of 2-wire type proximity sensors.
- The voltage drop (Ud) corresponds to the voltage drop at the sensor's terminals when in the "closed" state (value measured at nominal current rating of sensor).
- First-up delay
- The first-up delay corresponds to the time (t) between the connection of the power supply to the sensor and its fully operational state.
- Supply voltage U on
- Sensor operational at state 1
- Sensor at state 0
- Response time
- Response time (Ra): the time delay between the object to be detected entering the sensor's operating zone and the subsequent change of output state. This parameter limits the speed and size of the object
- ☐ Recovery time (Rr): the time delay between an object to be detected leaving the sensor's operating zone and the subsequent change of output state. This parameter limits the interval

Sensors for AC circuits (\sim and \sim models)

Check that the voltage limits of the sensor are compatible with the nominal voltage of the AC supply used.

Sensors for DC circuits

- DC source: check that the voltage limits of the sensor and the acceptable level of ripple are compatible with the supply used.
- AC source (comprising transformer, rectifier, smoothing capacitor): the supply voltage must be within the operating limits specified for the sensor.

Where the voltage is derived from a single-phase AC supply, the voltage must be rectified and smoothed to ensure that:

- the peak voltage of the DC supply is lower than the maximum voltage rating of the sensor. Peak voltage = nominal voltage x $\sqrt{2}$
- the minimum voltage of the supply is greater than the minimum voltage rating of the sensor, given that:

 $\Delta V = (I \times t) / C$

 $\Delta V = \text{max. ripple: } 10 \% (V),$

I = anticipated load current (mA),

t = period of 1 cycle (10 ms full-wave rectified for a 50 Hz supply frequency),

C = capacitance (µF)

As a general rule, use a transformer with a lower secondary voltage (Ue) than the required DC voltage (U).

Example:

 \sim 18 $\dot{ extsf{V}}$ to obtain = 24 V,

 \sim 36 V to obtain = 48 V.

Outputs



Output signal (contact logic)

■ Normally open (NO)

Corresponds to a sensor whose output changes to the closed state when an object is present in the operating zone.

■ Normally closed (NC)


Corresponds to a sensor whose output changes to the open state when an object is present in the operating zone.


■ Complementary outputs (NO + NC)


Corresponds to a sensor with a normally closed output and a normally open output.

XS range

Outputs (continued)







2-wire --- type, non polarised NO or NC output

■ Specific aspects

These sensors are wired in series with the load to be switched.

As a consequence, they are subject to:


- □ a residual current in the open state (current flowing through the sensor in the "open" state),
- $\ \square$ A voltage drop in the closed state (voltage drop across the sensor's terminals in the "closed"

■ Advantages


- □ Only 2 leads to be wired: these sensors can be wired in series in the same way as mechanical limit switches
- ☐ They can be connected to either positive (PNP) or negative (NPN) logic PLC inputs,
- □ No risk of incorrect connections.

■ Operating precautions

- ☐ Check the possible effects of residual current and voltage drop on the actuator or input
- ☐ For sensors that do not have overload and short-circuit protection (AC or AC/DC symbol), it is essential to connect a 0.4 A "quick-blow" fuse in series with the load.



NO output



3-wire = type, NO or NC output, PNP or NPN

■ Specific aspects

- These sensors comprise 2 wires for the DC supply and a 3rd wire for the output signal,
- □ PNP type: switching the positive side to the load,
- □ NPN type: switching the negative side to the load.

Advantages


- ☐ Protection against supply reverse polarity,
- ☐ Protection against overload and short-circuit,
- ☐ No residual current, low voltage drop.

BN/1 BK/4 (NO) NPN BK/4 (NO) WH/2 (NC) Φ

4-wire = type, complementary NO and NC outputs, PNP or NPN

Advantages


- □ Protection against supply reverse polarity (+/-).
- □ Protection against overload and short-circuit.




4-wire ... type, multifunction, programmable NO or NC output, PNP or NPN

■ Advantages

- □ Protection against supply reverse polarity (+/-).
- □ Protection against overload and short-circuit.





Specific output signals, analogue type

- These sensors convert the approach of a metal object towards the sensing face into an output current variation which is proportional to the distance between the object and the sensing
- Two models available:
- 0...10 V (0...10 mA) output for 3-wire connection,
- 4-20 mA output for 2-wire connection.

3-wire connection

XS range

Features of the various models

















Types of case

- Cylindrical case
- Fast installation and setting-up.
- ☐ Short case and long case, 2-wire = and 3-wire = versions available.
- $\hfill\Box$ Pre-cabled (moulded cable) and various integral connector (M8, M12, 7/8", M18) and remote connector (on flying lead) versions available.
 Small size facilitates mounting in locations with restricted access.
- □ Interchangeability, provided by indexed fixing clamp: when assembled, becomes similar to

■ Flat case

- Reduced size (sensor volume divided by 8).
- ☐ Fast installation by mounting on clip-on brackets.
- □ Precision detection with the flush mountable sensors using teach mode (see page 24).

Electrical connection













Connection methods

- 1 Pre-cabled: factory fitted moulded cable, good protection against splashing liquids (IP 68). Example: machine tool.
- 2 Connector: easy installation and maintenance (IP 67).
- 3 Remote connector: easy installation and maintenance (IP 68 at sensor level and IP 67 at remote connector level).

Wiring advice


- Length of cable
- $\,\square\,$ No limitation up to 200 m or up to a line capacitance of < 100 nF (characteristics of sensor remain unaffected).
- ☐ In this case, it is important to take into account the voltage drop on the line.


Separation of control and power circuit wiring

- The sensors are immune to electrical interference encountered in normal industrial conditions.
- Where extreme conditions of electrical "noise" could occur (large motors, spot welders, etc.), it is advisable to protect against transients in the normal way:
- suppress interference at source,
- separate power and control wiring from each other,
- smooth the supply,
- limit the length of cable.
- Connect the sensor with supply switched off.


XS range


Setting-up precautions

























Connection in series

2-wire type sensors

- The following points should be taken into account:
- ☐ Series wiring is only possible using sensors with wide voltage limits.
- Based on the assumption that each sensor has the same residual current value, each sensor, in the open state, will share the supply voltage, i.e.

U sensor = U (supply)

n sensors

- U sensor and U supply must remain within the sensor's voltage limits.
- ☐ If only one sensor in the circuit is in the open state, it will be supplied at a voltage almost equal to the supply voltage.
- □ When in the closed state, a small voltage drop is present across each sensor. The resultant loss of voltage at the load will be the sum of the individual voltage drops and therefore, the load voltage should be selected accordingly.

3-wire type sensors

This connection method is not recommended.

- Correct operation of the sensors cannot be assured and, if this method is used, tests should be made before installation.
 - The following points should be taken into account:
- □ Sensor 1 carries the load current in addition to the no-load current consumption values of the other sensors connected in series. For certain models, this connection method is not possible unless a current limiting resistor is used.
- When in the closed state, a small voltage drop is present across each sensor. The load should therefore be selected accordingly.
- ☐ As sensor 1 closes, sensor 2 does not operate until a certain time (t) has elapsed (corresponding to the first-up delay) and likewise for the following sensors in the sequence.
- ☐ The use of "flywheel" diodes is recommended when an inductive load is being switched.

Sensors and devices in series with an external mechanical contact

2 and 3-wire type sensors

- The following points should be taken into account:
- ☐ When the mechanical contact is open, the sensor is not supplied.
- When the contact closes, the sensor does not operate until a certain time (t) has elapsed (corresponding to the first-up delay).

Connection in parallel

2-wire type sensors

This connection method is not recommended.

- Should one of the sensors be in the closed state, the sensor in parallel will be "shorted-out" and no longer supplied.
 - As the first sensor passes into the open state, the second sensor will become energised and will be subject to its first-up delay.
- This configuration is only permissible where the sensors will be working alternately
- This method of connection can lead to irreversible damage of the units.

3-wire type sensors

No specific restrictions. The use of "flywheel" diodes is recommended when an inductive load (relay) is being switched.

AC supply

- 2-wire type sensors cannot be connected directly to an AC supply.
- ☐ This would result in immediate destruction of the sensor and considerable danger to the user.
- An appropriate load (refer to the instruction sheet supplied with the sensor) must always be connected in series with the sensor.

Capacitive load (C > 0.1 μ F)

- On power-up, it is necessary to limit (by resistor) the charging current of the capacitive load C.
- ☐ The voltage drop in the sensor can also be taken into account by subtracting it from the supply voltage for the calculation of R.

Load comprising an incandescent lamp

- If the load comprises an incandescent lamp, the cold state resistance can be 10 times lower than the hot state resistance. This can cause very high current levels on switching. Fit a pre-heat resistor in parallel with the sensor.
- $R = \frac{U^2}{P} \times 10$, U = supply voltage and P = lamp power

Inductive proximity sensors XS range

Fast trouble shooting guide		
Problem	Possible causes	Remedy
The sensor's output will not change state when a metal object enters the detection zone	On a flush mountable sensor using teach mode: setting-up or programming error.	After a RESET, follow the environment teach mode procedure. Refer to instruction sheet supplied with sensor.
	Output stage faulty or complete failure of the sensor or the short-circuit protection has tripped.	 Check that the sensor is compatible with the supply being used. Check the load current characteristics: if load current I ≥ maximum switching capacity, an auxiliary relay, of the CAD N type for example, should be interposed between the sensor and the load, if I ≤ maximum switching capacity, check for wiring faults (short-circuit). In all cases, a 0.4 A "quick-blow" fuse should be fitted in series with the sensor.
	Wiring error	Check that the wiring conforms to the wiring shown on the sensor label or instruction sheet.
	Supply fault	 Check that the sensor is compatible with the supply (~ or). Check that the supply voltage is within the voltage limits of the sensor. Remember that with a rectified, smoothed supply, U peak = U nominal x √2 with a ripple voltage ≤ 10 %.
False or erratic operation, with or without the presence of a metal object in the detection zone	On flush mountable sensor using teach mode: setting-up or programming error.	After a RESET, follow the environment teach mode procedure. Refer to instruction sheet supplied with sensor.
	Influence of background or metal environment	Refer to the instruction sheet supplied with the sensor. For sensors with adjustable sensitivity, reduce the sensing distance.
	Sensing distance poorly defined for the object to be detected	Apply the correction coefficients.Realign the system or run the teach mode again.
	Influence of transient interference on the supply lines	 ■ Ensure that any DC supplies, when derived from rectified AC, are correctly smoothed (C > 400 µF). ■ Separate AC power cables from low-level DC cables (24 V low level). ■ Where very long distances are involved, use suitable cable: screened and twisted pairs of the correct cross-sectional area.
	Equipment prone to emitting electromagnetic interference	Position the sensors as far away as possible from any sources of interference.
	Response time of the sensor too slow for the particular object being detected	 Check the suitability of the sensor for the position or size of the object to be detected. If necessary, select a sensor with a higher switching frequency.
	Influence of high temperature	 Eliminate sources of radiated heat or protect the sensor casing with a heat shield. Realign, having adjusted the temperature around the fixing support.
No detection following a period of service	Vibration, shock	Realign the system.Replace the support or protect the sensor.

XS range


Flush mountability using teach mode: simplicity through innovation

Max. sensing distance Max. sensing distance GR Max. sensing distance

Operating principle

In proposing flush mountable sensors using teach mode, Telemecanique Sensors offers simplicity through innovation.

- A single product enables flush mounting using teach mode and meets all the requirements for inductive detection of metal objects.
- By simply pressing the "Teach mode" button, the sensor automatically acquires optimum configuration for all detection, flush mountability and environment requirements
- Other advantages of flush mountable sensors using teach mode
- □ Increased performance:
- sensing distance guaranteed and optimised irrespective of the mounting method, object, environment or background,
 - suitable for all metal environments.
- ☐ Simplified use provided by:
- the flush mountability using teach mode technology, associated with the availability of the flattest and most compact sensors on the market, ensures full integration in the machine and limits the risks of mechanical damage,
 - mechanical adjustments no longer necessary due to teach mode.
- □ Lower costs due to:
 - the elimination of adjustment times and complex supports
- the elimination of flush mountable and non-flush mountable versions, which halves the number of references.
 - much easier and much quicker product selection.




Max. sensing distance

Precision position detection All flush mountable inductive proximity:

All flush mountable inductive proximity sensors using teach mode benefit from ultra precise adjustment, which is very quick irrespective of the metal environment.

- Precision side approach detection makes it possible to accurately define the distance at which the object will be detected as it passes the sensor. On the flush mountable sensors using teach mode, the desired detection position can be stored in memory by simply pressing the teach button.
- Precision frontal approach detection makes it possible to accurately define the distance at which the object will be detected as it approaches the sensor. On the flush mountable sensors using teach mode, the desired detection position can be stored in memory by simply pressing the teach button.





Mounting accessories

Telemecanique Sensors offers a complete, inexpensive range of mounting accessories (clamps, plates, brackets, etc.) that provide solutions for all installation problems.

- Fixing kits for quick installation or replacement of sensors
- No adjustment required. Simple clipping-in enables the sensor to be fixed in position and ready for operation.

XS range

Flush mountability using teach mode: simplicity through innovation



Cylindrical type				
Dimensions (mm)		12	18	30
Sensing distance (mm)	Flush mounted use	03.4	06	011
	Non-flush mounted use	05	09	018
Sensor type		XS612B2	XS618B2	XS630B2
Page		84		




Block type				
Dimensions (mm)		26 x 26 x 13	40 x 40 x 15	80 x 80 x 26
Sensing distance	Flush mounted use	010	015	040
(mm)	Non-flush mounted use	015	025	060
Sensor type		XS8E1A1	XS8C1A1	XS8D1A1
Page		54		

XS range, general purpose Cylindrical, standard range, flush mountable Three-wire DC, solid-state output

Sensors, 3-wire == 12...24 V, short case model













Ø 6.5, plain					
1.5	NO	PNP	Pre-cabled (L = 2 m) (1)	XS506B1PAL2	0.035
			M8 connector	XS506B1PAM8	0.025
			M12 connector	XS506B1PAM12	0.025
		NPN	Pre-cabled (L = 2 m) (1)	XS506B1NAL2	0.035
			M8 connector	XS506B1NAM8	0.025
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS506B1PBL2	0.035
			M8 connector	XS506B1PBM8	0.025
		NPN	Pre-cabled (L = 2 m) (1)	XS506B1NBL2	0.035
			M8 connector	XS506B1NBM8	0.025
Ø 8, threaded M	2 v 1				
1.5	NO	PNP	Pre-cabled (L = 2 m) (1)	XS508B1PAL2	0.035
			M8 connector	XS508B1PAM8	0.025
			M12 connector	XS508B1PAM12	0.025
		NPN	Pre-cabled (L = 2 m) (1)		0.025
			M8 connector	XS508B1NAM8	0.025
	NC	PNP	Pre-cabled (L = 2 m) (1)		0.035
			M8 connector	XS508B1PBM8	0.025
			M12 connector	XS508B1PBM12	0.025
Ø 12, threaded I					
2	NO	PNP	Pre-cabled (L = 2 m) (1)		0.075
			M12 connector	XS512B1PAM12	0.035
		NPN	Pre-cabled (L = 2 m) (1)		0.075
			M12 connector	XS512B1NAM12	0.035
	NC	PNP	Pre-cabled (L = 2 m) (1)		0.075
			M12 connector	XS512B1PBM12	0.035
Ø 18, threaded	M18 x 1				
5	NO	PNP	Pre-cabled (L = 2 m) (1)	XS518B1PAL2	0.120
			M12 connector	XS518B1PAM12	0.060
		NPN	Pre-cabled (L = 2 m) (1)	XS518B1NAL2	0.120
			M12 connector	XS518B1NAM12	0.060
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS518B1PBL2	0.120
			M12 connector	XS518B1PBM12	0.060
Ø 20 throaded I	//20 v 4 E				
Ø 30, threaded N	NO	PNP	Pre-cabled (L = 2 m) (1)	YS530R4DAL2	0.205
10	INO	LINC	M12 connector	XS530B1PAL2 XS530B1PAM12	0.205
		NPN	Pre-cabled (L = 2 m) (1)		0.145
		INFIN	M12 connector	XS530B1NAM12	0.205
	NC	PNP	Pre-cabled (L = 2 m) (1)		0.145
	INC	LINC	M12 connector	XS530B1PBL2 XS530B1PBM12	0.205
			IVI 12 CONTIECTO	ASSUDTPDIVITZ	0.145



Accessories (2)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 6.5 (plain)	XSZB165	0.005
	Ø8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m cable replace L2 by L5; for a 10 m cable replace L2 by L10. Please consult our Customer Care Center for availability.

Example: XS508B1PAL2 becomes XS508B1PAL5 with a 5 m cable.

⁽²⁾ For more information, see page 128.

XS range, general purpose Cylindrical, standard range, flush mountable Three-wire DC, solid-state output


Sensors, 3-wire = 12...24 V, long case model

Function Output Connection

Reference

Weight





Sensing





Sensors, 3-	-wire 1	248 \	/, long case mod	del	
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Ø 12, threaded	V12 x 1				
2	NO	PNP	Pre-cabled (L = 2 m) (1)	XS512BLPAL2	0.075
			M12 connector	XS512BLPAM12	0.035
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS512BLPBL2	0.075
Ø 18, threaded N	V18 x 1				
5	NO	PNP	Pre-cabled (L = 2 m) (1)	XS518BLPAL2	0.120
			M12 connector	XS518BLPAM12	0.060
		NPN	Pre-cabled (L = 2 m) (1)	XS518BLNAL2	0.120
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS518BLPBL2	0.120
			M12 connector	XS518BLPBM12	0.060
Ø 30, threaded N	M30 x 1.5				
10	NO	PNP	Pre-cabled (L = 2 m) (1)	XS530BLPAL2	0.205
			M12 connector	XS530BLPAM12	0.145
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS530BLPBL2	0.205



Accessories (2))		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 6.5 (plain)	XSZB165	0.005
9	Ø 8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m cable replace L2 by L5; for a 10 m cable replace L2 by L10. Please consult our Customer Care Center for availability.

Example: XS508BLPAL2 becomes XS508BLPAL5 with a 5 m cable.

⁽²⁾ For more information, see page 128.

Inductive proximity sensors
XS range, general purpose
Cylindrical, standard range, flush mountable
Three-wire DC, solid-state output

Characteristics			VCE - D4 - M0 VCE - D4 - M40	V05B4L2	
Sensor type			XS5••B1••M8, XS5••B1••M12 XS5••BL••M8, XS5••BL••M12	XS5••B1••L2 XS5••BL••L2	
Product certifications			cULus, C€, UKCA, E2		
Connection	Connector		M8 on Ø 6.5 and Ø 8, M12 on Ø 8, Ø 12, Ø 18 and Ø 30	-	
	Pre-cabled		_	Length: 2 m	
Operating zone	Ø 6.5 and Ø 8	mm	01.2		
	Ø 12	mm	01.6		
	Ø 18	mm	04		
	Ø 30	mm	08		
Differential travel		%	115 of effective sensing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67	IP 65 and IP 68 (except Ø 6.5 and Ø 8: IP 67)	
	Conforming to DIN 40050		IP 69K for Ø 12 to Ø 30	-	
Storage temperature		°C	-40+85		
Operating temperature		°C	-25+70		
Materials Case			Nickel plated brass (except XS506 and XS508: stainless steel, grade 303)		
	Sensing face		PPS		
	Cable		-	PVC 3 x 0.34 mm ² except XS506 and XS508 : 3 x 0.11 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 50 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED: 4 viewing ports at 90°	Yellow LED: annular	
Rated supply voltage		V	= 1248 for XS5●BL (Ø 12, 18, and 30 = 1224 for XS5●B1, XS508BL with protection against reverse polarity		
Voltage limits (including r	ipple)	٧	1058 for XS5●●BL (Ø 12, 18, and 30) 1036 for XS5●●B1, XS508BL		
Insulation class			M12: M8: III	0	
Switching capacity		mA	≤ 200 with overload and short-circuit prote	ection	
Voltage drop, closed state	•	٧	€2		
Current consumption, no-	-load	mA	≤ 10		
Maximum switching	XS506, XS508, XS512	Hz	5000		
frequency	XS518	Hz	2000		
	XS530	Hz	1000		
Delays	First-up	ms	≤ 10		
	Response	ms	≤ 0.1: XS506, XS508 and XS512 ≤ 0.15: XS518 ≤ 0.3: XS530		
	Recovery	ms	≤ 0.1: XS506, XS508 and XS512 ≤ 0.35: XS518 ≤ 0.7: XS530		


XS range, general purpose Cylindrical, standard range, flush mountable Three-wire DC, solid-state output


Wiring schemes Connector Pre-cabled NPN M8 BN/1 BN/1 + BK/4 (NO) BU: Blue PNP BK/4 (NO) NPN BN: Brown BK: Black \Diamond \Diamond BK/2 (NC) BU/3


For M8 connector, NO and NC outputs on terminal 4

Setting-up

Minimum mounting distances (mm)







Flush mountable				
sensors				
Ø 6.5				
Ø8				
Ø 12				
Ø 18				
Ø 30				

Ø 30


XS530BL

62

	Side by side
6	e≥3
6	e≥3
6	e≥4
6	e ≥ 10
6	e≥20

Face to face
e ≥ 18
e ≥ 18
e ≥ 24
e ≥ 60
e ≥ 120

Facing a metal object
e≥4.5
e≥4.5
e≥6
e≥15
e≥30



(1)	I	FD	
''	_	$ \nu$	

Sensors			Pre-cabled (mm)		M8 connector (mm)		M12 connector (mm)	
Short case model			b	а	b	а	b	
Ø 6.5	XS506B1	34	_	42	_	45	_	
Ø8	XS508B1	34	25	42	27	45	23	
Ø 12	XS512B1	37	25		_	50	30	
Ø 18	XS518B1	39	28		_	50	28	
Ø 30	XS530B1	43	32		_	54	32	
Sensors		Pre-c	abled (mm)	M12 c	onnector (mm)			
Long case model		а	b	а	b			
Ø8	XS508BL	51	42	61	40			
Ø 12	XS512BL	53	42	61	42			
Ø 18	XS518BL	62	52	74	52			

52


74

52

XS range, general purpose Cylindrical, standard range, flush mountable Two-wire DC









Accessories (3)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m cable replace L2 by L5; for a 10 m cable replace L2 by L10. Please consult our Customer Care Center for availability. Example: XS508BSCBL2 becomes XS508BSCBL5 with a 5 m cable.

Example: XS508BSCBL2 becomes **XS508BSCBL5** with a 5 m cable. (2) The NO output is connected to terminals 1 and 4 of the M12 connector.

⁽³⁾ For more information, see page 128.

Inductive proximity sensors
XS range, general purpose
Cylindrical, standard range, flush mountable Two-wire DC

Sensors, 2-wire == 12...48 V, long case model



XS512BS••L2



XS5••BS••M12



XS5••B1••L01C

Sensing distance (Sn) mm		Connection	Reference	Weight (kg)
Ø 8, thre	aded M8 x 1			
1.5	NO	Pre-cabled (L = 2 m) (1)	XS508B1DAL2	0.035
		M12 connector	XS508B1DAM12	0.025
	NO terminals 1 & 4 (2)	Remote M12 connector	XS508B1CAL08M12	0.050
Ø 12, thr	eaded M12 x 1			
2	NO	Pre-cabled (L = 2 m) (1)	XS512B1DAL2	0.075
		M12 connector	XS512B1DAM12	0.035
	NO terminals	M12 connector	XS512B1CAM12	0.035
	1 & 4 (2)	Remote M12 connector	XS512B1CAL08M12	0.060
	NC	Pre-cabled (L = 2 m) (1)	XS512B1DBL2	0.075
Ø 18, thr	eaded M18 x 1			
5	NO	Pre-cabled (L = 2 m) (1)	XS518B1DAL2	0.120
		Remote EN 175301-803-A connector	XS518B1DAL01C	0.085
		M12 connector	XS518B1DAM12	0.060
	NO terminals	M12 connector	XS518B1CAM12	0.060
	1 & 4 (2)	Remote M12 connector	XS518B1CAL08M12	0.085
	NC	Pre-cabled (L = 2 m) (1)	XS518B1DBL2	0.120
		M12 connector	XS518B1DBM12	0.060
Ø 30, thr	eaded M30 x 1.	5		
10	NO	Pre-cabled (L = 2 m) (1)	XS530B1DAL2	0.205
		M12 connector	XS530B1DAM12	0.145
	NO terminals 1 & 4 (2)	M12 connector	XS530B1CAM12	0.145
	NC	Pre-cabled (L = 2 m) (1)	XS530B1DBL2	0.205



XSZB1●●

Accessories	(3)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m cable replace L2 by L5; for a 10 m cable replace L2 by L10. Please consult our Customer Care Center for availability.

Example: XS508B1DAL2 becomes XS508B1DAL5 with a 5 m cable.

⁽²⁾ The NO output is connected to terminals 1 and 4 of the M12 connector.


⁽³⁾ For more information, see page 128.

Inductive proximity sensors
XS range, general purpose
Cylindrical, standard range, flush mountable
Two-wire DC

Sensor type			XS5eeB1eeM12, XS5eeBSeeM12	XS5eeB1DeL2, XS5eeBSeeL2
Product certifications			cULus, CE, UKCA	, A00002 12022, A000020022
Connection	Connector		M12	_
	Pre-cabled		_	Length: 2 m
	Remote connector		M12 (L01M12), EN 175301-803-A (L010 M12 (L08M12) connectors on 0.80 m fly	C) and
Operating zone	Ø8	mm	01.2	
	Ø 12	mm	01.6	
	Ø 18	mm	04	
	Ø 30	mm	08	
Differential travel		%	115 of effective sensing distance (Sr)	
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67	IP 65 and IP 68 (except Ø 8: IP 67)
Storage temperature		°C	-40+85	
Operating temperature		°C	-25+70; TF products: -40+70	
Materials	Case		Nickel plated brass (except XS506 and XS508B1: stainless steel, grade 303)	
	Sensing face		PPS	
	Cable		-	PVC 2 x 0.34 mm ² (except XS508: 2 x 0.11 mm ²) PUR available <i>(1)</i>
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz	2)
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms	
Output state indication			Yellow LED: 4 viewing ports at 90°	Yellow LED: annular
Rated supply voltage		V	1248 non polarised for XS5●B1● 1224 non polarised for XS5●BS (except Ø 8 short: polarised) with protection against reverse polarity	
Voltage limits (including	g ripple)	V	1058 for XS5••B1• 1036 for XS5••BS	
Insulation class				
Switching capacity		mA	1.5100 with overload and short-circuit	protection
Voltage drop, closed sta	nte	V	≤4.2	
Residual current, open	state	mA	≤ 0.5	
Maximum switching	XS508	Hz	1000 for XS5●●BS, 1400 for XS5●●B1●	
frequency	XS512	Hz	1000	
	XS518	Hz	1200	
	XS530	Hz	1300	
Delays	First-up	ms	≤ 10	
	Response	ms	≤ 0.5: XS508 and XS512 ≤ 0.6: XS518 ≤ 0.6: XS530	
	Recovery	ms	≤ 0.2 (except XS530 ≤ 0.4)	

⁽¹⁾ For PUR cable, replace the letter L in the reference by P. Example: XS508BSCAL2 becomes XS508BSCAP2 with a PUR cable.

XS range, general purpose Cylindrical, standard range, flush mountable Two-wire DC



Remote connectors L01B, L01C, L01G, U78 Screw terminal (L01B)

The terminal numbering differs according to the version (2-wire ==, 3-wire ==, 2-wire ≂).





The NO or NC outputs are connected to terminal 2.

M18 (L01G)



7/8" (U78)





Terminal 1: not connected Terminal 2: +/-Terminal 3: +/-

Setting-up

Minimum mounting distances (mm)







Ø8	
Ø 12	
Ø 18	
Ø 30	

Sensors


Side by side	
e≥3	
e ≥ 4	
e ≥ 10	
0 > 20	

Face to face	
e ≥ 18	
e ≥ 24	
e ≥ 60	
e ≥ 120	

Pre-cabled (mm) M8 connector (mm) M12 connector (mm)

Facing a metal object	
e ≥ 4.5	
e ≥ 6	
e ≥ 15	
e ≥ 30	

Dimensions




(1) LED

e model	а	b	а	b	а	b
XS508BS	33	25	42	26	45	24
XS512BS	35	25		_	50	30
XS518BS	40	28		_	50	28
XS530BS	44	32		_	55	32
	Pre-ca	abled (mm)	M12 c	onnector (mm)		
e model	а	b	а	b		
XS508B1	51	42	62	40		
XS512B1	54	42	61	42		
XS518B1	56	44	64	44		
XS530B1	<u>54</u>	42	72	41		
	XS508BS XS512BS XS518BS XS530BS e model XS508B1 XS512B1 XS518B1	XS508BS 33	XS508BS 33 25	XS508BS 33 25 42	XS508BS 33 25 42 26	XS508BS 33 25 42 26 45

XS range, general purpose Cylindrical, standard range, flush mountable Two-wire AC or DC (1)



 $XS5 \bullet \bullet B1M \bullet L2$





XS5	D 1	A 1 -	1100

Ø 18, threaded M18	3 x 1			
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
5	NO	Pre-cabled (L = 2 m) <i>(2)</i>	XS518B1MAL2	0.100
		1/2"-20 UNF connector	XS518B1MAU20	0.060
	NC	Pre-cabled (L = 2 m) (2)	XS518B1MBL2	0.100
		1/2"-20 UNF connector	XS518B1MBU20	0.060



XS530B1••L2

Ø 30, threaded	M30 x 1.5			
Sensing distan (Sn) mm	ce Function	Connection	Reference	Weight (kg)
10	NO	Pre-cabled (L = 2 m) (2)	XS530B1MAL2	0.205
		1/2"-20 UNF connector	XS530B1MAU20	0.145
	NC	Pre-cabled (L = 2 m) (2)	XS530B1MBL2	0.205



Accessorie	S (3)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ \emptyset 8 plastic, double insulation version available (see page 70).

⁽²⁾ For a 5 m cable replace L2 by L5; for a 10 m cable replace L2 by L10. Please consult our Customer Care Center for availability.

Example: XS512B1MAL2 becomes XS512B1MAL5 with a 5 m cable.

⁽³⁾ For more information, see page 128.

Inductive proximity sensors

XS range, general purpose Cylindrical, standard range, flush mountable Two-wire AC or DC

Sensor type			XS5eeB1MeU20	XS5eeB1MeL2		
Product certifications			cULus, CE, UKCA	•		
Connection	Connector		1/2"-20 UNF	_		
	Pre-cabled		-	Length: 2 m		
Operating zone	Ø 12	mm	01.6			
	Ø 18	mm	04	04		
	Ø 30	mm	08			
Differential travel		%	115 of effective sensing distance (Sr)			
Degree of protection Conforming to IEC 60529			IP 65 and IP 67	IP 65 and IP 68		
	Conforming to DIN 40050		IP 69K	-		
Storage temperature		°C	-40+85			
Operating temperature			-25+70			
Materials	Materials Case		Nickel plated brass			
	Sensing face		PPS			
	Cable		_	PVC 2 x 0.34 mm ²		
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)			
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			
Output state indication			Yellow LED: 4 viewing ports at 90°	Yellow LED: annular		
Rated supply voltage		V	∼ or == 24240 (∼ 50/60 Hz)			
Voltage limits (including	ripple)	٧	∼ or == 20264			
Insulation class			1	I		
Switching capacity	XS512B1M•••	mA	5200 (1)	5200 (1)		
	XS518B1Meee, XS530B1Meee	mA	∼5300 or == 5200 (1)			
Voltage drop, closed sta	te	V	≤ 5.5			
Residual current, open	state	mA	≤0.8			
Maximum switching	XS512B1•••, XS518B1M•••	Hz	~ 25 or == 1000			
frequency	XS530B1M●●●	Hz	\sim 25 or $=$ 500			
Delays	First-up	ms	≤ 20 XS512B1M••• ≤ 25 XS518B1M••• and XS530B1M•••			
	Response	ms	≤ 0.5			
	Recovery	ms	<pre>< 0.2 XS512B1M●●● < 0.5 XS518B1M●●● < 2 XS518B1M●●●</pre>			

(1) It is essential to connect a 0.4 A "quick-blow" fuse in series with the load.

Wiring schemes


Connector NF

<u></u>‡։ 1

Pre-cabled

BU: Blue BN: Brown

2-wire \sim or =NO or NC output





±: on connector models only


Setting-up

Minimum mounting distances (mm)










Sens	sor
Ø 12	
Ø 18	
Ø 30	

Side by side	
e≥8	
e ≥ 16	
e ≥ 30	

Face to face e ≥ 48 e ≥ 100 e ≥ 180

Facing a metal object e ≥ 12 e ≥ 25 e ≥ 45

Dimensions



Senso	r
XS512E	31M
XS518E	31M
XS530E	81M

2	XS6		
1	Pre-cabled	(mm)	
	a	b	
5	3	42	
6	2	52	
6	2	52	
5	2	42 52	

Connector	(mm)	
а	b	
62	42	
73	52	
73	52	

(1) LED

XS range, general purpose Cylindrical, increased range, flush mountable Three-wire DC, solid-state output









XS112B3••L2

Senso	rs, 3-wi	re 1	224 V, short ca	ase m	odel	
Sensing distance (Sn) mm	Function	Output	Connection	Sold in lots of		Weight (kg)
Ø 6.5, pla	iin					
2.5	NO	PNP	Pre-cabled (L = 2 m) (1)	1	XS106B3PAL2	0.060
			M8 connector	1	XS106B3PAM8	0.030
			M12 connector	1	XS106B3PAM12	0.050
	NC	PNP	Pre-cabled (L = 2 m) (1)	1	XS106B3PBL2	0.060
			M8 connector	1	XS106B3PBM8	0.030
Ø 8, threa	aded M8 x	1				
2.5	NO	PNP	Pre-cabled (L = 2 m) (1)	1	XS108B3PAL2	0.070
			M8 connector	1	XS108B3PAM8	0.030
			M12 connector	1	XS108B3PAM12	0.060
		NPN	Pre-cabled (L = 2 m) (1)	1	XS108B3NAL2	0.070
			M8 connector	1	XS108B3NAM8	0.030
			M12 connector	1	XS108B3NAM12	0.060
	NC	PNP	Pre-cabled (L = 2 m) (1)	1	XS108B3PBL2	0.070
			M8 connector	1	XS108B3PBM8	0.030
			M12 connector	1	XS108B3PBM12	0.060
		NPN	M8 connector	1	XS108B3NBM8	0.030
Ø 12, thre	eaded M12	x 1				
4	NO	PNP	Pre-cabled (L = 2 m) (1)	1	XS112B3PAL2	0.090
			M12 connector	1	XS112B3PAM12	0.030
		NPN	Pre-cabled (L = 2 m) (1)	1	XS112B3NAL2	0.090
			M12 connector	1	XS112B3NAM12	0.030
	NC	PNP	Pre-cabled (L = 2 m) (1)	1	XS112B3PBL2	0.090
			M12 connector	1	XS112B3PBM12	0.030

⁽¹⁾ For a 5 m long cable replace L2 by **L5**. Please consult our Customer Care Center for availability. Example: XS106B3PAL2 becomes **XS106B3PAL5** with a 5 m cable.


XS range, general purpose Cylindrical, increased range, flush mountable Three-wire DC, solid-state output



XS118B3●•M12



XS118B3•••L2





Ø 30, t	hreaded N	130 x 1.5				
15	NO	PNP	Pre-cabled (L = 2 m) (1)	1	XS130B3PAL2	0.180
			M12 connector	1	XS130B3PAM12	0.130
		NPN	Pre-cabled (L = 2 m) (1)	1	XS130B3NAL2	0.180
			M12 connector	1	XS130B3NAM12	0.130
	NC	PNP	Pre-cabled (L = 2 m) (1)	1	XS130B3PBL2	0.180
			M12 connector	1	XS130B3PBM12	0.130



Accessories (2	2)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 6.5 (plain)	XSZB165	0.005
	Ø 8 (M8 x1)	XSZB108	0.006
	Ø 12 (M12 x1)	XSZB112	0.006
	Ø 18 (M18 x1)	XSZB118	0.010
	Ø 30 (M30 x 1.5)	XSZB130	0.020


⁽¹⁾ For a 5 m cable, replace L2 by L5. Please consult our Customer Care Center for availability. Example: XS118B3PAL2 becomes XS118B3PAL5 with a 5 m cable.

37

⁽²⁾ For more information, see page 128.

XS range, general purpose Cylindrical, increased range, flush mountable Three-wire DC, solid-state output







XS6••E	310	•M	1	2
--------	-----	----	---	---

Sens	ors, 3-wir	e == 12	248 V, long case model		
Sensir distan (Sn) m	ce	Outpu	t Connection	Reference	Weight (kg)
Ø 12, t	hreaded M12	2 x 1			
4	NO	PNP	Pre-cabled (L = 2 m) (1)	XS612B1PAL2	0.075
			M12 connector	XS612B1PAM12	0.020
		NPN	Pre-cabled (L = 2 m) (1)	XS612B1NAL2	0.075
			M12 connector	XS612B1NAM12	0.020
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS612B1PBL2	0.075
			M12 connector	XS612B1PBM12	0.020
		NPN	Pre-cabled (L = 2 m) (1)	XS612B1NBL2	0.075
			M12 connector	XS612B1NBM12	0.020
Ø 18, t	hreaded M18	3 x 1			
8	NO	PNP	Pre-cabled (L = 2 m) (1)	XS618B1PAL2	0.100
			M12 connector	XS618B1PAM12	0.040
			Remote EN 175301-803-A connector	XS618B1PAL01C	0.100
		NPN	Pre-cabled (L = 2 m) (1)	XS618B1NAL2	0.100
			M12 connector	XS618B1NAM12	0.040
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS618B1PBL2	0.100
			M12 connector	XS618B1PBM12	0.040
		NPN	Pre-cabled (L = 2 m) (1)	XS618B1NBL2	0.100
			M12 connector	XS618B1NBM12	0.040
Ø 30, t	hreaded M30	x 1.5			
15	NO	PNP	Pre-cabled (L = 2 m) (1)	XS630B1PAL2	0.205
			M12 connector	XS630B1PAM12	0.145
			Remote EN 175301-803-A connector	XS630B1PAL01C	0.205
		NPN	Pre-cabled (L = 2 m) (1)	XS630B1NAL2	0.205
			M12 connector	XS630B1NAM12	0.145
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS630B1PBL2	0.205
			M12 connector	XS630B1PBM12	0.145
		NPN	Pre-cabled (L = 2 m) (1)	XS630B1NBL2	0.205



Accessorie	S (2)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Please consult our Customer Care Center for availability. Example: XS608B1PAL2 becomes **XS608B1PAL5** with a 5 m cable.

⁽²⁾ For more information, see page 128.

Inductive proximity sensors

XS range, general purpose Cylindrical, increased range, flush mountable Three-wire DC, solid-state output

Characteristics						
Sensor type			XS1/XS6eeBeeeM8	XS1/XS6eeBeeeM12	XS1/XS6eeBeeeL2	
Product certifications	Ø 6.5 and Ø 8		cULus, C€, UKCA	'	•	
	Ø 12, 18 and 30		cULus, C€, UKCA, E2			
Connection	Connector		M8	M12	_	
	Pre-cabled		-	-	Length 2 m	
	Remote connector		Screw terminal (L01B), EN 0.15 m flying lead	I 175301-803-A (L01C) and	d M18 (L01G) remote connectors o	
Operating zone (1)	Ø 6.5 and Ø 8	mm	0 2			
	Ø 12	mm	03.2			
	Ø 18	mm	06.4			
	Ø 30	mm	012			
Differential travel		%	115 of effective sensing	distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67		IP 65 and IP 68 except Ø 6.5 and Ø 8: IP 67	
	Conforming to DIN 40050		_	IP 69K	_	
Storage temperature		°C	-40+85		•	
Operating temperature		°C	-25+70			
Materials Case Sensing fa	Case		Nickel plated brass (except Ø 6.5 and Ø 8: stainless steel, grade 303)			
	Sensing face		PPS			
	Cable		-		PVC 3 x 0.34 mm ² except Ø 6.5 and 8: 3 x 0.11 mm	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f	f = 10 to 55 Hz)	'	
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms	,		
Output state indication			Yellow LED, 4 viewing port	ts at 90°	Yellow LED, annular	
Rated supply voltage		٧	XS1, XS608: 1224 wi XS6: 1248 with protect			
Voltage limits (including ripple)		٧	XS1, XS608: 1036; X	S6: 1058 (Ø 12, 18, 3	30)	
Insulation class			III			
Switching capacity		mA	≤ 200 with overload and sh	nort-circuit protection		
Voltage drop, closed state		٧	≤2			
Current consumption, no-load		mA	≤ 10			
Maximum switching frequency	Ø 6.5, Ø 8 and Ø 12	Hz	2500			
	Ø 18	Hz	1000			
	Ø 30	Hz	500			
Delays	First-up	ms	≤ 10			
	Response	ms	≤ 0.2 for Ø 6.5, Ø 8 and Ø	12, ≤ 0.3 for Ø 18, ≤ 0.6 for	Ø 30	
	Recovery	ms	≤ 0.2 for Ø 6.5, Ø 8 and Ø	12, ≤ 0.7 for Ø 18, ≤ 1.4 for	Ø 30	

(1) Detection curves, see page 136.

Wiring schemes

Connector (1)


M8

Pre-cabled

BU: Blue BN: Brown BK: Black

Setting-up

Minimum mounting distances (mm)







PNP	
BN/1	
PNP	BK/4 (NO)
\Diamond	BK/2 (NC)
BU/3	<u> </u>



Sensors	Side by side	Face to face	Facing a metal object
Ø 6.5	e≥5	e ≥ 30	e ≥ 8
Ø8	e≥5	e ≥ 30	e ≥ 8
Ø 12	e≥8	e ≥ 48	e ≥ 12
Ø 18	e ≥ 16	e ≥ 100	e≥25
Ø 30	e ≥ 30	e ≥ 180	e ≥ 45

(1) For pin arrangement of remote connectors L01B, L01C and L01G, see page 33.

Dimensions									
(1)	Sensors			Pre-ca	abled (mm)	М8 со	nnector (mm)	M12 co	nnector (mm)
<u></u>	Short case	e model		а	b	а	b	а	b
		Ø 6.5	XS106B3	34	_	42	-	45	_
		Ø8	XS108B3	34	25	42	27	45	23
		Ø 12	XS112B3	35	25		_	50	30
a →		Ø 18	XS118B3	39	28		_	50	28
		Ø 30	XS130B3	43	32		_	55	32
(1) LED	Sensors	Sensors			Pre-cabled (mm)		nnector (mm)	M12 connector (mm)	
	Long case	model		а	b	а	b	а	b
		Ø8	XS608B1	51	42	58	43	61	40
		Ø 12	XS612B1	53	42		_	61	42
		Ø 18	XS618B1	62	52		_	74	52
		Ø 30	XS630B1	62	52		_	74	52

XS range, general purpose Cylindrical, increased range, flush mountable Two-wire DC, solid-state output















XSZB1●●

Sensors.	2-wire 1	224 V, short case	model	
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
Ø 6.5, plain				
2.5	NO	Pre-cabled (L = 2 m) (1)	XS606B3CAL2	0.060
	NC	Pre-cabled (L = 2 m) (1)	XS606B3CBL2	0.060
Ø 8, threade	ed M8 x 1			
2.5	NO	Pre-cabled (L = 2 m) (1)	XS608B3CAL2	0.070
Ø 12, thread	led M12 x 1			
4	NO	Pre-cabled (L = 2 m) (1)	XS612B3DAL2	0.090
		M12 connector	XS612B3DAM12	0.030
	NC	Pre-cabled (L = 2 m) (1)	XS612B3DBL2	0.090
		M12 connector	XS612B3DBM12	0.030
Ø 18, thread	led M18 x 1			
8	NO	Pre-cabled (L = 2 m) (1)	XS618B3DAL2	0.110
		M12 connector	XS618B3DAM12	0.060
	NC	Pre-cabled (L = 2 m) (1)	XS618B3DBL2	0.110
		M12 connector	XS618B3DBM12	0.060
Ø 30, thread	led M30 x 1.5			
15	NO	Pre-cabled (L = 2 m) (1)	XS630B3DAL2	0.180
		M12 connector	XS630B3DAM12	0.130

Sensors,	2-wire == 1	248 V, long case r	model	
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
Ø 6.5, plain				
2.5	NC	Pre-cabled (L = 2 m) (1)	XS606B1DBL2	0.060
Ø 8, threade	ed M8 x 1			
2.5	NO	Pre-cabled (L = 2 m) (1)	XS608B1DAL2	0.035
		M12 connector	XS608B1DAM12	0.015
	NC	Pre-cabled (L = 2 m) (1)	XS608B1DBL2	0.035
Ø 12, thread	ded M12 x 1			
4	NO	Pre-cabled (L = 2 m) (1)	XS612B1DAL2	0.180
		M12 connector	XS612B1DAM12	0.020
	NC	M12 connector	XS612B1DBM12	0.020
Ø 18, thread	ded M18 x 1			
8	NO	Pre-cabled (L = 2 m) (1)	XS618B1DAL2	0.100
		M12 connector	XS618B1DAM12	0.040
	NC	Pre-cabled (L = 2 m) (1)	XS618B1DBL2	0.100
		M12 connector	XS618B1DBM12	0.040
Ø 30, thread	ded M30 x 1.5			
15	NO	Pre-cabled (L = 2 m) (1)	XS630B1DAL2	0.205
		M12 connector	XS630B1DAM12	0.145
	NC	M12 connector	XS630B1DBM12	0.145

Accessories (2)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 6.5 (plain)	XSZB165	0.005
	Ø 8 (M8 x1)	XSZB108	0.006
	Ø 12 (M12 x1)	XSZB112	0.006
	Ø 18 (M18 x1)	XSZB118	0.010
	Ø 30 (M30 x 1.5)	XSZB130	0.020

⁽¹⁾ For a 5 m cable, replace L2 by L5. Please consult our Customer Care Center for availability. Example: XS606B3CAL2 becomes XS606B3CAL5 with a 5 m cable.

⁽²⁾ For more information, see page 128.

Inductive proximity sensors

XS range, general purpose Cylindrical, increased range, flush mountable Two-wire DC, solid-state output

Concortino			XS6eeB3eeM12	XS6eeB3eeL2	
Sensor type			XS600B1D0M12	XS6eeB1DeL2	
Product certifications			cULus, C€, UKCA,		
Connection	Connector		M12 or remote M12 connector (L01M12) on	0.15 m flying lead	
	Pre-cabled		Length 2 m		
Operating zone (1)	Ø 6.5 and Ø 8	mm	0 2		
	Ø 12	mm	03.2		
	Ø 18	mm	06.4		
	Ø 30	mm	012		
Differential travel		%	115 of effective sensing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67	IP 65 and IP 68	
				(except Ø 6.5 and Ø 8: IP 67)	
	Conforming to DIN 40050		IP 69K	-	
Storage temperature		°C	-40+85		
Operating temperature		°C	-25+70		
Materials	Case		Nickel plated brass (except XS606B1D or XS	S608B1D: stainless steel, grade 303)	
	Sensing face		PPS		
	Cable		PVC 2 x 0.34 mm ² except Ø 6.5 and Ø 8: 2 x 0.11 mm ²		
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED, 4 viewing ports at 90°		
Rated supply voltage		٧	== 1248 non polarised for XS6••B1D		
				ept \emptyset 6.5 short and \emptyset 8 short: polarised), with	
			protection against reverse polarity		
Voltage limits (including ripple)		٧	1058 for XS6••B1D		
11.0			1036 for XS6●●B3●		
Insulation class		A			
Switching capacity		mA V		on	
Voltage drop, closed state		-	≤4.2		
Residual current, open state	OCE OO		≤ 0.5 mA		
Maximum switching frequency	Ø 6.5, Ø 8 Ø 12	Hz	1400 for XS6••B1D, 1100 for XS6••B3•		
		Hz	1300		
	Ø 18 Ø 30	Hz	1500		
Deleve		Hz	800		
Delays	First-up	ms	≤10		
elays	Response	ms	≤0.5		

(1) Detection curves, see page 136.

Wiring schemes

2 wire - non nelarised

M12 connector Pre-cabled



BU: Blue BN: Brown

Setting-up

Minimum mounting distances (mm)







2-wire non polarised	
NO output	NC output
BN/3 +/- BU/4 -/+	NC BU/2 -/+
2-wire polarised	
XS6••B3CA	XS6eeB3CB
BN/1 +	BN/1 + BU/2

Sensors	Side by side	Face to face	Facing a metal object
Ø 6.5	e≥5	e≥30	e ≥ 8
Ø8	e≥5	e≥30	e ≥ 8
Ø 12	e ≥ 8	e ≥ 48	e ≥ 12
Ø 18	e ≥ 16	e ≥ 100	e ≥ 25
Ø 30	e ≥ 30	e ≥ 180	e ≥ 45

Dimensions
<u>(1)</u>
b
a
(1) LED

Sensor	s		Pre-ca	abled (mm)	M12 co	onnector (mm)	
Short c	ase model		а	b	а	b	
	Ø 6.5	XS606B3C	33	_	_	_	
	Ø8	XS608B3C	33	25		24	
	Ø 12	XS612B3D	35	25	50	30	
	Ø 18	XS618B3D	40	28	50	28	
	Ø 30	XS630B3D	44	32	55	32	
Long ca	ase model		а	b	а	b	
	Ø 6.5	XS606B1D	50	-	_	_	
	Ø8	XS608B1D	51	42	62	40	
	Ø 12	XS612B1D	53	42	61	42	
	Ø 18	XS618B1D	62	52	74	52	
	Ø 30	XS630B1D	62	52	74	52	

XS range, general purpose Cylindrical, increased range, flush mountable Two-wire AC or DC (1)





XS6••B1••U20



XS6••B1••L01B (3)



XS6••B1••L01C



XS6••B1••L01U78



XSZB1●●

Concorr	2 mina	-24 240 V Jana 2002 m	a a da l	
	•	\sim 24-240 V, long case n		
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
Ø 12, threa	ded M12 x 1			
4	NO	Pre-cabled (L = 2 m) (2)	XS612B1MAL2	0.075
		1/2"-20 UNF connector	XS612B1MAU20	0.025
	NC	Pre-cabled (L = 2 m) (2)	XS612B1MBL2	0.075
		1/2"-20 UNF connector	XS612B1MBU20	0.025
Ø 18, threa	ded M18 x 1			
8	NO	Pre-cabled (L = 2 m) (2)	XS618B1MAL2	0.100
		1/2"-20 UNF connector	XS618B1MAU20	0.060
		Remote screw terminal connector	XS618B1MAL01B (3)	0.100
		Remote EN 175301-803-A connector	XS618B1MAL01C	0.100
		Remote 7/8" connector	XS618B1MAL01U78	0.100
	NC	Pre-cabled (L = 2 m) (2)	XS618B1MBL2	0.100
		1/2"-20 UNF connector	XS618B1MBU20	0.060
Ø 30, threa	ded M30 x 1.	5		
15	NO	Pre-cabled (L = 2 m) (2)	XS630B1MAL2	0.205
		1/2"-20 UNF connector	XS630B1MAU20	0.145
		Remote screw terminal connector	XS630B1MAL01B (3)	0.205
		Remote EN 175301-803-A connector	XS630B1MAL01C	0.205
		Remote 7/8" connector	XS630B1MAL01U78	0.205
	NC	Pre-cabled (L = 2 m) (2)	XS630B1MBL2	0.205
		1/2"-20 UNF connector	XS630B1MBU20	0.145
		Remote screw terminal connector	XS630B1MBL01B (3)	0.205

Accessories	(4)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ Ø8 plastic, double insulation version available (see page 70).

⁽²⁾ For a 5 m cable replace L2 by L5; for a 10 m cable replace L2 by L10. Please consult our Customer Care Center for availability.

Example: XS612B1MAL2 becomes XS612B1MAL5 with a 5 m cable.

⁽³⁾ Protective cable gland included with sensor.

⁽⁴⁾ For more information, see page 128.

Inductive proximity sensors

XS range, general purpose Cylindrical, increased range, flush mountable Two-wire AC or DC

Sensor type			XS6eeB1MeU20	XS6eeB1MeLe
Product certifications			cULus, C€, UKCA	
Connection	Connector		1/2" - 20 UNF	_
	Pre-cabled		-	Length 2 m
	Remote connector		Screw terminal (L01B), EN 175301-803-A (L 0.15 m flying lead	.01C) and M18 (L01G) remote connectors or
Operating zone (1)	Ø 12	mm	0 3.2	
	Ø 18	mm	0 6.4	
	Ø 30	mm	012	
Differential travel		%	115 of effective sensing distance (Sr)	
Degree of protection	Conforming to IEC 60529		IP 65, IP 67	IP 65 and IP 68
	Conforming to DIN 40050		IP 69K	-
Storage temperature		°C	-40+85	
Operating temperature		°C	-25+70	
Materials	Case		Nickel plated brass	
	Sensing face		PPS	
	Cable		PVC 2 x 0.34 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)	
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms	
Output state indication			Yellow LED: annular on pre-cabled version Yellow LED with 4 viewing ports at 90° on co	nnector version
Rated supply voltage		٧	≂ 24240 (~ 50/60 Hz)	
Voltage limits (including ripple)		٧	≂20264	
Insulation class			I	1
Switching capacity	XS612B1M•••	mΑ	5200 (2)	
	XS618B1M••• XS630B1M•••	mA	∼5300 or 5200 <i>(2)</i>	
Voltage drop, closed state		٧	≤ 5.5	
Residual current, open state		mΑ	≤ 0.8	
Maximum switching frequency	Ø 12	Hz	 1000 / ∼ 25	
(DC/AC)	Ø 18	Hz	 1000 / ∼ 25	
	Ø 30	Hz	 500 / ∼ 25	
Delays	First-up	ms	≤ 25 for Ø 18 and Ø 30; ≤ 20 for Ø 12	
	Response	ms	≤ 0.5	
	Recovery	ms	≤ 0.2 for Ø 12; ≤ 0.5 for Ø 18; ≤ 2 for Ø 30	

⁽¹⁾ Detection curves, see page 136.

(2) It is essential to connect a 0.4 A "quick-blow" fuse in series with the load.

Wiring schemes


Connector (1)





Pre-cabled

BU: Blue BN: Brown



2-wire \sim or =

NO or NC output

±: on 1/2"-20UNF connector models only

(1) For pin arrangement of remote connectors L01B, L01C and L01G, see page 33.

Setting-up

Minimum mounting distances (mm)








Sensors	Side by side	Face to face	Facing a metal object
Ø 12	e ≥ 8	e ≥ 48	e ≥ 12
Ø 18	e ≥ 16	e ≥ 100	e ≥ 25
Ø 30	e≥30	 e ≥ 180	 e≥45

Dimensions



ors
XS612B1M●
XS618B1M●
XS630B1M●

Pre-cabled (mm)		Connec	ctor (mm)
а	b	а	b
53	42	61	42
62	52	73	52
62	52	73	52

XS range, general purpose Cylindrical, increased range, non-flush mountable Three-wire DC, solid-state output



Sensors, 3		1224	V, long case mod	lel	
Ø 8, threaded	M8 x 1				
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
4	NO	PNP	Pre-cabled (L = 2 m)	XS608B4PAL2	0.035
			M8 connector	XS608B4PAM8	0.015
			M12 connector	XS608B4PAM12	0.015
		NPN	Pre-cabled (L = 2 m)	XS608B4NAL2	0.035
			M8 connector	XS608B4NAM8	0.015
			M12 connector	XS608B4NAM12	0.015
	NC	PNP	Pre-cabled (L = 2 m)	XS608B4PBL2	0.035
			M8 connector	XS608B4PBM8	0.015
			M12 connector	XS608B4PBM12	0.015
		NPN	Pre-cabled (L = 2 m)	XS608B4NBL2	0.035
			M8 connector	XS608B4NBM8	0.015
			M12 connector	XS608B4NBM12	0.015

Sensors,	3-wire == '	1248	V, long case mode	el	
Ø 12, thread	ed M12 x 1				
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
7	NO	PNP	Pre-cabled (L = 2 m) (1)	XS612B4PAL2	0.075
			M12 connector	XS612B4PAM12	0.020
		NPN	Pre-cabled (L = 2 m) (1)	XS612B4NAL2	0.075
			M12 connector	XS612B4NAM12	0.020
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS612B4PBL2	0.075
			M12 connector	XS612B4PBM12	0.020
		NPN	Pre-cabled (L = 2 m) (1)	XS612B4NBL2	0.075

Ø 18, thread	led M18 x 1				
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
12	NO	PNP	Pre-cabled (L = 2 m) (1)	XS618B4PAL2	0.100
			M12 connector	XS618B4PAM12	0.040
		NPN	Pre-cabled (L = 2 m) (1)	XS618B4NAL2	0.100
			M12 connector	XS618B4NAM12	0.040
	NC	PNP	Pre-cabled (L = 2 m) (1)	XS618B4PBL2	0.100
			M12 connector	XS618B4PBM12	0.040
		NPN	Pre-cabled (L = 2 m) (1)	XS618B4NBL2	0.100

Ø 30, thread	ded M30 x 1.5	5			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
30	NO	PNP	Pre-cabled (L = 2 m) (1)	XS630B5PAL2	0.205
			M12 connector	XS630B5PAM12	0.145
		NPN	Pre-cabled (L = 2 m) (1)	XS630B5NAL2	0.205
	NC	PNP	M12 connector	XS630B5PBM12	0.145



XS618B4••M12

XS630B5●•M12

Accessories (2)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 8	XSZB108	0.004
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Please consult our Customer Care Center for availability. Example: XS612B4PAL2 becomes XS612B4PAL5 with a 5 m cable.

⁽²⁾ For more information, see page 128.


Inductive proximity sensors


XS range, general purpose Cylindrical, increased range, non-flush mountable Three-wire DC, solid-state output


Sensor type			XS6eeB4eeeM8	XS6eeB4eeeM12	XS6eeB4eeeL2	
Product certifications	Ø 8		cULus, C€, UKCA		100000	
	Ø 12, 18 and 30		cULus, C€, UKCA, E2			
Connection	Connector		M8	M12	1_	
Connection	Pre-cabled		IVIO	IVITZ	Length: 2 m	
Operating zone	Ø 8	mm	03.2		Lengur. 2 m	
Operating zone	Ø 12	mm	05.6			
	Ø 12 Ø 18	mm	09.6			
	Ø 30	mm	024			
Differential travel	Ø 30	%	115 of effective sensing distance (Sr)			
Degree of protection	Conforming to IEC 60529	/0	IP 65 and IP 67	Tig distance (Si)	IP 65 and IP 68	
Degree of protection				IP 69K	IF 65 and IF 66	
Conforming to DIN 40050		°C	-40+85	IF 09K		
Storage temperature			-40+03 -25+70			
Operating temperature Materials	Case	°C		cept Ø 8: stainless steel, grade	202)	
Wateriais	Sensing face		PPS	cept Ø 6. stalliless steel, grade	: 303)	
Cable			-	PVC 3 x 0.34 mm ² except for Ø 8: 3 x 0.11 mm ²		
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mr	m (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			
Output state indication			Yellow LED: 4 viewing p	ports at 90°	Yellow LED: annular	
Rated supply voltage				on against reverse polarity (Ø 8 on against reverse polarity (Ø 9		
Voltage limits (including	ripple)	V	1036 (Ø 8) 1058 (Ø 12, 18, 30)			
Insulation class			III			
Switching capacity		mA	≤ 200 with overload and	d short-circuit protection		
Voltage drop, closed sta	te	٧	≤2			
Current consumption, n	o-load	mA	≤10			
Maximum switching	XS608B4•••• and XS612B4••••	Hz	2500			
frequency	XS618B4•••	Hz	1000			
	XS630B5••••	Hz	500			
Delays	First-up	ms	≤ 10 for Ø 8, Ø 12 and Ø	Ø 18; ≤ 15 for Ø 30		
•	Response	ms	≤ 0.2 for Ø 8 and Ø 12;	≤ 0.3 for Ø 18; ≤ 0.6 for Ø 30		
Recovery			≤ 0.2 for Ø 8 and Ø12; ≤ 0.7 for Ø 18; ≤ 1.4 for Ø 30			
Wiring schemes						
Connector	Pre-cabled	PNP		NPN		
M8 M12	BU: Blue BN: Brown BK: Black	BN/1 PNP	BK/4 (NO) BK/2 (NC)	BN/1 + NPN BK/4 (NO) BU/3 -		

Setting-up

Minimum mounting distances (mm)







d d	-
ح ا	

	Side by side	
Ø8	e ≥ 24	
Ø 12	e ≥ 48	
Ø 18	e ≥ 72	
Ø 30	e ≥ 300	

	Face to face
(e≥40
(e ≥ 84
(e ≥ 144
	≥≥300

Facing a metal object
e ≥ 12
e≥21
e ≥ 36
e ≥ 90

Mounted in a me support	Mounted in a metal support				
d ≥ 24, h ≥ 8					
d ≥ 36, h ≥ 12					
d ≥ 54, h ≥ 18					
d≥90, h≥35					

(1) b + C a (1) LED

Dimensions

XS6
Ø8
Ø 12
Ø 18
Ø 30

Pre-cab	iea (mm)		M8 Connector (mm)		
a	b	С	а	b	С
51	38	4	58	39	4
54	42	5	-	-	-
60	44	8	-	-	-
66	41	13	_	_	_

M12 C	M12 Connector (mm)				
а	b	С			
61	36	4			
66	42	5			
72	44	8			
74	41	13			


Sensors, 3-wire == 12-24 V, short case model

Ø 12, threaded M12 x 1

XS range, general purpose Cylindrical, increased range, non-flush mountable Three-wire DC, solid-state output



XS212B4eel e



(kg)

0.086

0.160

0.032

0.086

0.032

0.086

0.032

0.086



	XS21	8B4	•• <i>N</i>	112
--	------	-----	-------------	-----

distance (Sn) mm					(kg)
16	NO	PNP	Pre-cabled (L = 2 m)	XS218B4PAL2	0.105
			M12 connector	XS218B4PAM12	0.052
		NPN	Pre-cabled (L = 2 m)	XS218B4NAL2	0.105
			M12 connector	XS218B4NAM12	0.052
	NC	PNP	Pre-cabled (L = 2 m)	XS218B4PBL2	0.105
			M12 connector	XS218B4PBM12	0.052



Accessories (1)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010

(1) For further information, see page 120.

Inductive proximity sensors

XS range, general purpose Cylindrical, increased range, non-flush mountable Three-wire DC, solid-state output

Sensor type			XS21•B4••M12	XS21eB4eeLe	
Product certifications			cULus, C€, UKCA, E2	'	
Connection	Connector		M12	_	
	Pre-cabled		-	Length: 2 or 5 m	
Operating zone	Ø 12	mm	06.4		
	Ø 18	mm	012.8		
Differential travel		%	115 of effective sensing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67		
	Conforming to DIN 40050		IP 69K	_	
Storage temperature		°C	- 40+ 85		
Operating temperature		°C	- 25+ 70		
Materials	Case		Brass		
	Sensing face		PPS		
	Cable		-	PvR 3 x 0.34 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED, 4 viewing ports at 90°	Yellow LED, annular	
Rated supply voltage		٧	== 1224 with protection against reverse polarity		
Voltage limits (including ri	pple)	٧	 1036		
Insulation class					
Switching capacity		mA	≤ 200 with overload and short-circuit protection		
Voltage drop, closed state		٧	≤2		
Current consumption, no-	oad	mA	≤10		
Maximum switching	XS212B4••••	Hz	2000		
frequency	XS218B4•••	Hz	1000		
Delays	First-up	ms	≤ 15		
	Response	ms	≤ 0.2 for Ø 12 ≤ 0.3 for Ø 18		
	Recovery	ms	≤ 0.2 for Ø 12 ≤ 0.7 for Ø 18		

wiring schemes


 Connector
 Pre-cabled
 PNP


 M12
 BN/1 + PNP
 + PNP

 4 3
 BU: Blue
 BK/4 (NO)

BN: Brown


BK: Black








Setting-up

Minimum mounting distances (mm)










	Side by side
Ø 12	e ≥ 100
Ø 18	e ≥ 120

Face to face	Facing a metal object
≥ 120	e≥24
≥ 200	e ≥ 48

Mounted in a metal support				
d≥36,	h ≥ 15			
$d \ge 54$	h ≥ 18			

Dimensions



Ø	12	
Ø	18	

e

Pre-	cabled (m	nm)	M12 co	nnector (mm)	
а	b	С	а	b	С
37	20	5	51	26	5
41	21	8	51	21	8

(1) LED

Inductive proximity sensors
XS range, general purpose
Cylindrical, increased range, non flush mountable
Two-wire AC or DC



 $XS6 \bullet \bullet B4M \bullet L2$

Sensors, 2-w	ire \sim 24 24	10 V, long case m	odel	
Ø 18, threaded M	l18 x 1			
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
12	NO	Pre-cabled (L = 2 m) (1)	XS618B4MAL2	0.120
		1/2"-20 UNF connector	XS618B4MAU20	0.060
	NC	Pre-cabled (L = 2 m) (1)	XS618B4MBL2	0.120
		1/2"-20 UNF connector	XS618B4MBU20	0.060



Ø 30, th	readed N	130 x 1.5				
Sensing (Sn) mm		Function	C	Connection	Reference	Weight (kg)
22		NO	F	Pre-cabled (L = 2 m) (1)	XS630B4MAL2	0.205
			1	/2"-20 UNF connector	XS630B4MAU20	0.145
		NC	F	Pre-cabled (L = 2 m) (1)	XS630B4MBL2	0.205



XSZB	1	•	•
XSZB	1	•	•

Accessories (2))		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m cable replace L2 by **L5**; for a 10 m cable replace L2 by **L10**. Example: XS618B4MAL2 becomes **XS618B4MAL5** with a 5 m cable.

⁽²⁾ For more information, see page 120.

Inductive proximity sensors
XS range, general purpose Cylindrical, increased range, non flush mountable Two-wire AC or DC

Sensor type			XS6eeB4MeU20	XS6eeB4MeL2	
Product certifications			cULus, C€,UKCA	7.00002 1.11022	
Connection	Connector		1/2"-20 UNF	_	
	1/2"-20 UNFPre-cabled		_	Length: 2 m	
Operating zone	Ø 18	mm	09.6		
	Ø 30	mm	017.6		
Differential travel		%	115 of effective sensing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67	IP 65 and IP 68	
Storage temperature		°C	-40+85		
Operating temperature		°C	-25+70		
Materials	Case		Nickel plated brass		
	Sensing face		PPS		
	Cable		_	PvR 2 x 0.34 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED: 4 viewing ports at 90°	Yellow LED: annular	
Rated supply voltage		V	\sim or == 24240 (\sim 50/60 Hz)		
Voltage limits (including	ripple)	V	∼ or == 20264		
Insulation class			1	1	
Switching capacity		mA	∼5300 or 5200 (1)		
Voltage drop, closed sta	te	V	≤5.5		
Residual current, open	state	mA	≤ 0.8		
Maximum switching	XS618B4M●●●	Hz	∼ 25 or 1000		
frequency	XS630B4M●●●	Hz	\sim 25 or $=$ 300		
Delays	First-up	ms	≤ 30 XS618B4M●●● and XS630B4M●●	•	
	Response	ms	≤ 0.5		
	Recovery	ms	≤ 0.5 XS618B4M•••, ≤ 2 XS630B4M•••		

⁽¹⁾ It is essential to connect a 0.4 A "quick-blow" fuse in series with the load.

Wiring schemes


Connector

1/2"-20 UNF



Pre-cabled

BU: Blue BN: Brown




2-wire \sim or =

NO or NC output


±: on connector models only

Setting-up


Minimum mounting distances (mm)








Face to face	
e ≥ 144	
e ≥ 264	




Facing a metal object
e≥36
e ≥ 66



Mounted in a metal support	
d ≥ 54, h ≥ 18	
d≥90, h≥30	

Dimensions



	Pre-c	abled (mr	n)
	а	b	С
Ø 18	60	44	8
Ø 30	63	41	13

Connec	ctor (mm)		
а	b	С	
72	44	8	
74	41	13	

(1) LED

References

Inductive proximity sensors

Flat, 8 x 22 x 8 mm format (1) (2)

Three-wire ---


XS range, general purpose, standard range Flat format, flush mountable Two-wire DC Three-wire DC, solid-state output



XS7.J1A1eel 2



XS7F1A1●●L2



riat, 13 x 32 x 6 mm format (1)					
Three-wire ==					
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
5	NO	PNP	Pre-cabled $(L=2 m) (3)$	XS7F1A1PAL2	0.065
			Remote M8 connector on 0.15 m flying lead	XS7F1A1PAL01M8	0.045
		NPN	Pre-cabled (L = 2 m) (3)	XS7F1A1NAL2	0.065
	NC	PNP	Pre-cabled $(L=2 m)$ (3)	XS7F1A1PBL2	0.065
			Remote M8 connector on 0.15 m flying lead	XS7F1A1PBL01M8	0.045
		NPN	Pre-cabled $(L=2 m)$ (3)	XS7F1A1NBL2	0.065
Two-wire ===					
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
5	NO		Pre-cabled $(L=2 m)$ (3)	XS7F1A1DAL2	0.055
	NC		Pre-cabled (L=2m) (3)	XS7F1A1DBL2	0.055
			Remote M8 connector on 0.15 m flying lead	XS7F1A1DBL01M8	0.045



XS7F1A1●●L01M8

⁽¹⁾ For accessories, see page 120.

⁽²⁾ Sensors **XS7J** include a fixing clamp with screw.

⁽³⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Example: XS7J1A1PAL2 becomes XS7J1A1PAL5 with a 5 m long cable.

Inductive proximity sensors
XS range, general purpose, standard range
Flat format, flush mountable Two-wire DC Three-wire DC, solid-state output

Characteristics			V071- 104140	V07E	V07 !	1.2 VOZE 1.2
Sensor type Product certifications				XS7F•••••L01M8 cULus, (€, UKCA	XS/Jeeeee	L2, X5/F00000L2
Product certifications Connection	Connector		Remote M8 connector	<u> </u>		
connection	Pre-cabled		Remote Mo connector	on o. 15 m nying lead	Length: 2 m	
Operating zone	XS7J	mm	02		Lengin. 2 m	
operating zone	XS7F	mm	04			
Differential travel	ASTE	%	115 of effective sens	ing distance (Cr)		
	Conforming to IEC 60520	70				
Degree of protection	Conforming to IEC 60529	°C	IP 67 (XS7J), IP 68 (X 3 - 40+ 85	5/F)		
Storage temperature		°C				
Operating temperature		٠.	- 25+ 70			
Materials	Case		PBT	0.44 2.0075 0	0 004	2)
	Cable		PvR 3 x 0.11 mm ² or 2		or 3 x 0.34 mm	<u>1²)</u>
/ibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 m	m (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			
Output state indication			Yellow LED			
Rated supply voltage		٧	== 1224 with protect	ion against reverse p	olarity	
/oltage limits (including ripple)		٧	 1036			
nsulation class				III		
Current consumption, no-load	3-wire	mA	≤ 10			
Residual current, open state	2-wire	mA	≤ 0.5			
Switching capacity	3-wire	mA	100 with overload and	short-circuit protection	n	
	2-wire	mA	1.5100 with overload	and short-circuit pro	tection	
/oltage drop, closed state	3-wire	٧	≤2			
	2-wire	٧	≤4			
Maximum switching frequency	3-wire	kHz	2			
	2-wire	kHz	4 for XS7J, 5 for XS7F			
Delays	First-up	ms	Three-wire: 5			
,-		ms	Two-wire: 10 XS7J , 5	XS7F		
	Response	ms	Three-wire: 0,1			
	rtosponeo	ms	Two-wire: 0,5 XS7J , 5	XS7F		
Recovery		ms	Three-wire: 0,1	X011		
	recovery	ms	Two-wire: 1 XS7J, 5 X	C7E		
Miring a alaamaa		1113	Two-wite. Txoro, 5 x	0/1		
Wiring schemes						
Connector	Pre-cabled	PNP	NO or NC	NPN NO or NC		2-wire NO
M8		BN/1		BN/1	+	BN/3 +/-
	BU: Blue	PNP	BK/4	NPN \		_
1// 1/2	BN: Brown BK: Black	\Diamond		BK/4		NO BU/4
11 11 1	DIX. DIACK	BU/3		BU/3		80/4 □ =/∓
						2 wire NC
						2-wire NC
						2-wire NC BN/1 +/-
						BN/1 +/-
						BN/1 +/-
						BN/1 +/-
						BN/1 +/-
		Minir	mum mounting dista	ances (mm)		BN/1 +/-
		Minir	mum mounting dista	ances (mm)		BN/1 +/-
		Minir	<u> </u>	ances (mm)		BN/1 +/-
		_	<u> </u>	пп		BN/1 +/-
		_	<u> </u>	пп		BN/1 +/-
		_	<u> </u>	пп		BN/1 +/-
Setting-up		e		пп		BN/1 +/-
	XS7.J	e	by side	e l		BN/1 +/-
	XS7J XS7F	e Side k e ≥ 7.5	by side	e de la companya de l		BN/1 +/- BU/3 -/+ Facing a metal object e ≥ 7.5
Setting-up	XS7J XS7F	e Side k	by side	Face to face e ≥ 20		BN/1 +/- BU/3 -/+ Facing a metal object
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	ti Ti by side	Face to face e ≥ 20		BN/1 +/- NC BU/3 -/+ Facing a metal object e ≥ 7.5 e ≥ 15
Setting-up		e e e e e e e e e e e e e e e e e e e	by side	Face to face e ≥ 20	XS7J	BN/1 +/- NC BU/3 -/+ Facing a metal object e ≥ 7.5 e ≥ 15
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face e ≥ 20		BN/1 +/- NC BU/3 -/+ Facing a metal object $e \ge 7.5$ $e \ge 15$
		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face e ≥ 20		BN/1 +/- NC BU/3 -/+ Facing a metal object e ≥ 7.5 e ≥ 15
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face e ≥ 20		BN/1 +/- NC BU/3 -/+ Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face e ≥ 20		Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face e ≥ 20		BN/1 +/- NC BU/3 -/+ Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face e ≥ 20		Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face e ≥ 20		Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face $e \ge 20$ $e \ge 40$		Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face $e \ge 20$ $e \ge 40$		Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face $e \ge 20$ $e \ge 40$	XS7J	BN/1 +/- NC BU/3 -/+ Facing a metal object $e \ge 7.5$ $e \ge 15$
Setting-up		Side k $e \ge 7.5$ $e \ge 15$	by side	Face to face $e \ge 20$ $e \ge 40$	XS7J	BN/1 +/- NC BU/3 -/+ Facing a metal object $e \ge 7.5$ $e \ge 15$

ECXLAB certified

Inductive proximity sensors

XS range, general purpose, standard range Flat format. flush mountable Two-wire DC

Three-wire DC, solid-state output









XS7•1A1•L0•M12





XS7C1A1 • M8







XS7D1A1••M12





Sens. dist. Func-Connection Reference Weight (Sn) mm tion (kg) Flat, 26 x 26 x 13 mm format (1) Three-wire ... 10 PNP Pre-cabled (L = 2 m) (3) XS7E1A1PAL2 0.075 M8 connector XS7E1A1PAM8 0.040 XS7E1A1PAL01M12 0.040 Remote M12 connector NPN XS7E1A1NAL2 0.075 Pre-cabled (L = 2 m) (3) NC PNP XS7E1A1PBL2 0.075 Pre-cabled (L = 2 m) (3) XS7E1A1PBM8 0.040 M8 connector Remote M12 connector XS7E1A1PBL01M12 0.040 NPN Pre-cabled (L = 2 m) (3) XS7E1A1NBL2 0.075 Two-wire ... 10 Pre-cabled (L = 2 m) (3) XS7E1A1DAL2 0.070 Remote M12 connector XS7E1A1DAL01M12 0.040 NO terminals 1 and 4 (2) Remote M12 connector XS7E1A1CAL01M12 0.040

Fla	t, 40 x 4	40 x 15 m	m format (1)		
Thre	ee-wire =				
15	NO	PNP	Pre-cabled (L = 2 m) (3)	XS7C1A1PAL2	0.095
			M8 connector	XS7C1A1PAM8	0.060
			Remote M12 connector	XS7C1A1PAL01M12	0.060
	NC	PNP	Pre-cabled (L = 2 m) (3)	XS7C1A1PBL2	0.095
			M8 connector	XS7C1A1PBM8	0.060
		NPN	Pre-cabled (L = 2 m) (3)	XS7C1A1NBL2	0.095
			M8 connector	XS7C1A1NBM8	0.060
Two	-wire ==				
15	NO		Pre-cabled (L = 2 m) (3)	XS7C1A1DAL2	0.090
			M8 connector	XS7C1A1DAM8	0.060
	NC		Remote M12 connector	XS7C1A1DBL01M12	0.060

Flat	t, 80 x 8	0 x 26 m	m format (1)		
Thre	e-wire				
40	NO	PNP	Pre-cabled (L = 2 m) (3)	XS7D1A1PAL2 (4)	0.340
			M12 connector	XS7D1A1PAM12 (4)	0.290
		NPN	Pre-cabled (L = 2 m) (3)	XS7D1A1NAL2 (4)	0.340
	NC	PNP	M12 connector	XS7D1A1PBM12 (4)	0.290
Two-	-wire				
40	NO		Pre-cabled (L = 2 m) (3)	XS7D1A1DAL2 (4)	0.340
			M12 connector	XS7D1A1DAM12 (4)	0.290
	NC		Pre-cabled (L = 2 m) (3)	XS7D1A1DBL2 (4)	0.340

⁽¹⁾ For accessories, see page 120.

⁽²⁾ The NO output is connected to terminals 1 and 4 of the M12 connector.

⁽³⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Example: S7 J1A1PAL2 becomes XS7J1A1PAL5 with a 5 m long cable

⁽⁴⁾ For clipping onto 35 mm omega rail or 80 x 80 x 40 mm format, add DIN to the end of the reference. Example: XS7D1A1PAL2 becomes XS7D1A1PAL2DIN.

Inductive proximity sensors
XS range, general purpose, standard range
Flat format, flush mountable Two-wire DC Three-wire DC, solid-state output

Sensor type				YS7FaacaM9	Y97E	01M12	XS7EeeeeL2,
				XS7E••••M8, XS7C••••M8, XS7D••••M12	XS7E••••L XS7C•••••L		XS7EeeeeL2, XS7CeeeeL2, XS7DeeeeL2
Product certifications				cULus, C€, UKCA, EC	DLAB		
Connection	Connector			M8 except M12 on XS7DeeeeM	M12 on 0.15 n for XS7		-
	Pre-cabled			-	-		Length: 2 m
Operating zone	XS7E		mm	08	·		
	XS7C		mm	012			
	XS7D		mm	032			
Differential travel			%	115 of effective sens	ing distance (Sr)		
Degree of protection	Conforming to IEC	60529		IP 67	,		IP 68
Storage temperature			°C	- 40+ 85			
Operating temperature		-	°C	- 25+ 70			
Materials	Case			PBT			
	Cable			-	PvR 3 x 0.34 n	nm ² or 2 x 0.34 m	ım²
Vibration resistance	Conforming to IEC	60068-2-6		25 gn, amplitude ± 2 m	m (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC			50 gn, duration 11 ms	(
Output state indication				Yellow LED			
Rated supply voltage			٧		against reverse polarity		
Voltage limits (including ripple))		٧	1036	0 points)		
Insulation class	<u>, </u>			M8 connector: III			
				M12 connector:			
Current consumption, no-load	3-wire		mA	≤ 10			
Residual current, open state	2-wire		mA	≤ 0.5			
Switching capacity	3-wire		mA	≤ 100 with overload an	d short-circuit protection		
	2-wire		mA	1.5100 with overload	and short-circuit protection	n	
Voltage drop, closed state	3-wire		٧	≤2			
	2-wire		٧	≤4			
Maximum switching frequency	XS7E, XS7C		kHz	1			
	XS7D		Hz	100			
Delays	First-up	3-wire	ms	10 XS7E and XS7C, 3	XS7D		
		2-wire	ms	5 XS7E and XS7D, 10	XS7D		
	Response	3-wire	ms	2 XS7E and XS7C, 5 X	S7D		
		2-wire	ms	0,3 XS7E and XS7D , 1	0 XS7D		
	Recovery 3-wire		ms	6 XS7E, 5 XS7C, 35 X	S7D		
		2-wire	ms	0,7 XS7E and XS7D , 1	0 XS7D		
Wiring schemes							
Connector	Pre-cabled		PNP	(1)	2-wire NO/M12 or I	//8 2-wir	e NC/M12 or M8
M12 M8	BU: Blue		FINE	(1)	2-WITE NO/WITE OF I	710 Z-WII	
IVI IZ IVIO	BN: Brown		BN/1		BN/3 +/		BN/1 +
4 0 4			PNP	BK/4 (NO)	♦ NO IT	♦	
4 3 4	BK: Black	DK. Diack		BK/2 (NC)			
4 3 1 4 3	BK: Black		\Diamond	BK/2 (NC)	BU/4/-	<u> </u>	NC BU/2 (M12)
4 1 3	BK: Black		⊕ BU/3 □	<u> </u>	BU/4 LJ _/-	F	BU/2 (M12), BU/3 (M8)
4 1 3 1 3	BK: Black		\Diamond	<u> </u>	2-wire NO/M12 XS	70000CA000	−−BU/2 (M12)
4 1 3 1 3	BK: Black		BU/3 L	<u> </u>	2-wire NO/M12 XS		−−BU/2 (M12)
4 1 3 1 3	BK: Black		BU/3 L NPN BN/1	<u> </u>	BU/4 LJ _/-		−−BU/2 (M12)
4 1 3 1 3	BK: Black		BU/3 NPN BN/1 NPN	(1) + BK/4 (NO)	2-wire NO/M12 XS	<u>'-</u>	BU/2 (M12) LJ =, BU/3 (M8)
4 1 3 1 3	BK: Black		BU/3 NPN BN/1 NPN	<u> </u>	2-wire NO/M12 XS	'- - - (1) For	BU/2 (M12) L =, BU/3 (M8)
1 3	BK: Black		BU/3 L NPN BN/1 NPN ONE NPN BU/3 L	(1) + BK/4 (NO) BK/2 (NC)	2-wire NO/M12 XS	'- - - (1) For	BU/2 (M12) LJ =, BU/3 (M8)
Setting-up			BU/3 L NPN BN/1 NPN Dim	(1) BK/4 (NO) BK/2 (NC) ensions	2-wire NO/M12 XS BN/1 + NO BU/4 -/	/- - - (1) For + and NO	BU/3 (M8) - M8 connector, NO Coutputs on termina
1 3			BU/3 L NPN BN/1 NPN ONE NPN BU/3 L	(1) BK/4 (NO) BK/2 (NC) ensions	2-wire NO/M12 XS BN/1 + NO BU/4 -/	'- - - (1) For	BU/3 (M8) - M8 connector, NO Coutputs on termina
Setting-up	ices (mm)		BU/3 NPN BN/1 NPN BU/3 Dim XS70	(1) BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +/	/- - - (1) For + and NO	BU/3 (M8) - M8 connector, NO Coutputs on termina
Setting-up Minimum mounting distan Side by side	ices (mm) × XS7E XS7C		BU/3 NPN BN/1 NPN Dim XS70	(1) BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +/	/- - - (1) For + and NO	BU/3 (M8) - M8 connector, NO Coutputs on termina
Setting-up Minimum mounting distan Side by side e ≥	ices (mm) × XS7E XS7C	XS7D	BU/3 NPN BN/1 NPN BU/3 Dim XS70	(1) BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	/- - - (1) For + and NO	BU/3 (M8) M8 connector, NO Coutputs on termina
Setting-up Minimum mounting distan Side by side	ices (mm) × XS7E XS7C	XS7D	BU/3 NPN BN/1 NPN Dim XS70	(1) BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +/	/- - - (1) For + and NO	BU/3 (M8) - M8 connector, NO Coutputs on termina
Setting-up Minimum mounting distan Side by side	ices (mm) × XS7E XS7C	XS7D	BU/3 NPN BN/1 NPN Dim XS70	(1) BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	/- - - (1) For + and NO	BU/3 (M8) M8 connector, NO Coutputs on termina
Setting-up Minimum mounting distan Side by side e >	ces (mm) XS7E XS7C 30 45	XS7D 120	BU/3 NPN BN/1 NPN Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	/- - - (1) For + and NO	BU/3 (M8) M8 connector, NO Coutputs on termina
Setting-up Minimum mounting distan Side by side	ces (mm) XS7E XS7C 30 45	XS7D 120	BU/3 NPN BN/1 NPN Dim XS70	(1) BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	/- - - (1) For + and NO	BU/3 (M8) M8 connector, NO Coutputs on termina
Setting-up Minimum mounting distan Side by side e >	ces (mm) XS7E XS7C 30 45	XS7D 120	BU/3 NPN BN/1 NPN Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	(1) For and NO	BU/2 (M12) U =, BU/3 (M8) M8 connector, NO C outputs on termina
Setting-up Minimum mounting distan Side by side Face to face e >	ces (mm) XS7E XS7C 30 45	XS7D 120	BU/3 NPN BN/1 NPN Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +/ NO BU/4 -/	/- - - (1) For + and NO	BU/2 (M12) U =, BU/3 (M8) M8 connector, NO C outputs on termina
Setting-up Minimum mounting distan Side by side Face to face e >	ces (mm) XS7E XS7C 30 45	XS7D 120	BU/3 NPN BN/1 NPN Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	(1) For and NO	BU/2 (M12) U =, BU/3 (M8) M8 connector, NO C outputs on termina
Setting-up Minimum mounting distan Side by side Face to face e >	XS7E XS7C 30 45 45 45 45 45 45 45 4	XS7D 120 XS7D 300	Dim Dim	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	(1) For and NO	BU/2 (M12) SU/3 (M8) M8 connector, NO Coutputs on termina E (1) F (2)
Setting-up Minimum mounting distan Side by side Face to face e >	XS7E XS7C 30 45 45 45 45 45 45 45 4	XS7D 120 XS7D 300	BU/3 NPN BN/1 NPN Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 + NO BU/4 -/	(1) For and NO	BU/2 (M12) L =, BU/3 (M8) M8 connector, NO C outputs on termina E (1) F (2)
Setting-up Minimum mounting distan Side by side Face to face e > Facing a metal object e >	XS7E XS7C 30 45 45 45 45 45 45 45 4	XS7D 120 XS7D 300	Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +, BN/1 +, BN/1 +, Color (1)	(1) For and NO	BU/2 (M12) BU/3 (M8) M8 connector, NO C outputs on termina E (1) F (2) F (2) F (2)
Setting-up Minimum mounting distan Side by side e > Face to face e >	XS7E XS7C 30 45 45 45 45 45 45 45 4	XS7D 120 XS7D 300 XS7D 120	BU/3 NPN BN/1 NPN BN/3 Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +, BN/1 +, BN/1 +, A (connector) B	(1) For and NO	BU/2 (M12) BU/3 (M8) M8 connector, NO C outputs on termina E (1) F (2) F (2) F (2) F (2) F (2)
Setting-up Minimum mounting distan Side by side Face to face e > Facing a metal object e >	XS7E XS7C 30 45 45 45 45 45 45 45 4	XS7D 120 XS7D 300 XS7D 120	BU/3 NPN BN/1 NPN BU/3 Dim XS70 Senso XS7E	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +, BN/1 +, BN/1 +, A (connector) B 11 26	(1) For and NO XS7 XS7 (2) F C D 13 8.8	ED F (2) F (3.5)
Setting-up Minimum mounting distan Side by side Face to face e > Facing a metal object e >	XS7E XS7C 30 45 45 45 45 45 45 45 4	XS7D 120 XS7D 300 XS7D 120	BU/3 NPN BN/1 NPN BN/3 Dim XS70	BK/4 (NO) BK/2 (NC) ensions C/D/E XS7C/I	2-wire NO/M12 XS BN/1 +, BN/1 +, BN/1 +, A (connector) B	(1) For and NO	BU/2 (M12) BU/3 (M8) M8 connector, NO C outputs on termina E (1) F (2) F (2) F (2) F (2) F (2)

ECXLAB certified

Inductive proximity sensorsXS range, general purpose with increased range

Flat, 26 x 26 x 13 mm format (2) Sensing Function Output Connection

Flat, flush mountable using teach mode (1) Two-wire AC or DC Three-wire DC, solid-state output





XS8E1A1••L2



XS8E1A1●●M8







XS8C1A1••L2



(Sn) m					(Ng)
		with over	rload and short-circuit pro	otection	
15	NO	PNP	Pre-cabled (L = 2 m) (3)	XS8E1A1PAL2	0.075
			M8 connector	XS8E1A1PAM8	0.040
			Remote M12 connector	XS8E1A1PAL01M12	0.040
		NPN	Pre-cabled (L = 2 m) (3)	XS8E1A1NAL2	0.075
	NC	PNP	Pre-cabled (L = 2 m) (3)	XS8E1A1PBL2	0.075
			M8 connector	XS8E1A1PBM8	0.040
		NPN	Pre-cabled (L = 2 m) (3)	XS8E1A1NBL2	0.075
			M8 connector	XS8E1A1NBM8	0.040
Two-v	vire \sim or	unpro	otected (4)		
15	NO	_	Pre-cabled (L = 2 m) (3)	XS8E1A1MAL2	0.070
			Remote 1/2"-20UNF connec	ctor XS8E1A1MAL01U20	0.040
	NC	_	Pre-cabled (L = 2 m) (3)	XS8E1A1MBL2	0.070
			Remote 1/2"-20UNF connec	ctor XS8E1A1MBL01U20	0.040
Flat	40 x 40	x 15 m	m format (2)		

Reference

Weight

	riat, 40 x 40 x 15 iii			n iormat (2)		
	Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
	Three-w	ire wit	h overlo	oad and short-circuit prote	ection	
2	25	NO	PNP	Pre-cabled (L = 2 m) (3)	XS8C1A1PAL2	0.095
				M8 connector	XS8C1A1PAM8	0.060
				Remote M12 connector	XS8C1A1PAL01M12	0.060
			NPN	Pre-cabled (L = 2 m) (3)	XS8C1A1NAL2	0.095
		NC	PNP	Pre-cabled (L = 2 m) (3)	XS8C1A1PBL2	0.095
				M8 connector	XS8C1A1PBM8	0.060
	Two-wire	\sim or $=$	unprot	ected (4)		
2	25	NO	_	Pre-cabled (L = 2 m) (3)	XS8C1A1MAL2	0.090
				Remote 1/2"-20UNF connector	XS8C1A1MAL01U20	0.060
		NC	_	Pre-cabled (L = 2 m) (3)	XS8C1A1MBL2	0.090





XS8D1A1••L2DIN

103784	Enterocanique Servon	
	(#) Telemecan Seriors	



XS8D1A1●•M12DIN

			Remote 1/2"-20UNF connecto	r XS8C1A1MBL01U20	0.060
Flat, 80	x 80 x	26 mr	n format (2)		
Sensing distance (Sn) mm	Function Output		Connection	Reference	Weight (kg)
Three-w	ire == wit	h overl	oad and short-circuit prote	ection	
60	NO	PNP	Pre-cabled (L = 2 m) (3)	XS8D1A1PAL2 (5)	0.390
			M12 connector	XS8D1A1PAM12 (5)	0.340
		NPN	Pre-cabled (L = 2 m) (3)	XS8D1A1NAL2 (5)	0.390
	NC	PNP	Pre-cabled (L = 2 m) (3)	XS8D1A1PBL2 (5)	0.390
			M12 connector	XS8D1A1PBM12 (5)	0.340
Two-wire	e \sim or $=$	unprot	ected (4)		
60	NO	-	Pre-cabled (L = 2 m) (3)	XS8D1A1MAL2 (5)	0.390
			1/2"-20UNF connector	XS8D1A1MAU20 (5)	0.340
	NC	_	Pre-cabled (L = 2 m) (3)	XS8D1A1MBL2 (5)	0.390
			1/2"-20UNF connector	XS8D1A1MBU20 (5)	0.340

⁽¹⁾ For further information on flush or non-flush mountable sensors using teach mode, see page

⁽²⁾ For accessories, see page 120.

⁽³⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10.
(4) It is essential to connect a 0.4 A "quick-blow" fuse in series with the load.

⁽⁵⁾ For clipping onto 35 mm omega rail or 80 x 80 x 40 mm format, add DIN to the end of the reference. Example: XS8D1A1PAL2DIN.

Inductive proximity sensorsXS range, general purpose with increased range Flat, flush mountable using teach mode (1) Two-wire AC or DC Three-wire DC, solid-state output

Sensor type					XS8E••••M8, XS8C••••M8, XS8D••••M12, XS8D•••••U20		XS8E••••L01M1 XS8E••••L01U2 XS8C••••L01M1 XS8C••••L01U2	0, 2,	XS8E••••Li XS8C••••Li XS8D••••Li
Product certifications					cULus, C€, UKCA, EC	COLAB			
Connection	Connect Pre-cabl				M8 except XS8•••••M12: M1 XS8•••••U20: 1/2'		Remote on 0.15 m f XS8•••••L01M1: XS8•••••L01U20	2: M12	Length: 2 m
Sensing distance	XS8E	Nominal	sensing dist. Sn	mm	015 not flush moun	ted / 010 f	lush mounted		<u> </u>
and adjustment zone			ustment zone		515 not flush moun	ted / 510 f	lush mounted		
	XS8C		sensing dist. Sn	_	025 not flush moun				
			ustment zone		825 not flush moun				
	XS8D		sensing dist. Sn		060 not flush moun				
	7,502		ustment zone		2060 not flush mou				
Differential travel		i ilic auj	usuneni zone	%	115 of effective sen				
Degree of protection	Conform	ing to IEC	3052 <u>0</u>	70	IP 67	oning distanto	(31)		IP 68
Storage temperature	Comon	ing to ILC	00020	°C	- 40+85				11 00
Storage temperature Operating temperature				°C	- 40+85 - 25+70				
Operating temperature Materials	Casa			U	-25+70 PBT				
viatefidis	Case						DvD 2 0 24 2	= and D: D 0	0.24 ====2
file and in a constant	Cable	i	20000 2 2			/5 10:	PvR 3 x 0.34 mm ² =	and PVR 2 x (J.34 mm⁴ ≂
/ibration resistance		ing to IEC			25 gn, amplitude ± 2 r		55 HZ)		
Shock resistance			60068-2-27		50 gn, duration 11 ms				
ndicators	Output s				Yellow LED				
		n and teac	h mode		Green LED				
Rated supply	3-wire			٧	1224 with protectio	n against rev	erse polarity		
roltage	2-wire			٧	\sim or == 24240 (\sim 5	50/60 Hz)			
oltage limits	3-wire			V	1036				
including ripple)	2-wire			٧	∼ or == 20264				
nsulation class					, except M8 connec	tor: III			
Current consumption, no-	load 3-wire			mA	≤10				
Residual current, open st				mA	≤ 1.5				
Switching capacity	3-wire			mA	≤ 100 XS8E , ≤ 200 X	S8C and XS	RD with overload and	short-circuit n	rotection
ountoining oupdoing	2-wire			mA	5200 ₹ XS8E , 5				
laltaga dran alagad atat				V	≤2	300 ° X30C	and AGOD , 5200 -	XOOO and X	300
Voltage drop, closed state	2-wire			V					
Mandan and Albin a form					≤5.5				
Maximum switching frequ				Hz	2000 XS8E, 1000 XS8C, 150 XS8D				
Delays	First-up			ms	≤ 10 XS8E, XS8C and XS8D (3-wire), ≤ 10 XS8E and XS8C, ≤ 15 XS8D (2-wire)				
	Respons			ms	≤ 0.3				
	Recover	У		ms	≤ 0.8 XS8E and XS80	C, ≤ 6 XS8D			
Wiring schemes									
Connector	Pre-	cabled		PNP	/M12 or M8	NPN/N	112 or M8	2-wire 1/	/2"-20UNF
M8 M12 1/2"-20L								2 11110 11	
22	BN: Br			BN/1	+ +	BN/1	¬ 占 +		BN/2
* 4 3 C	BK: Bla			PNP	BK/4 (NO) BK/2 (NC)	NPN	BK/4 (NO)		
((**)) ³ ((**)) ((**)	ኦ)			\bigcirc		\bigcirc	BK/2 (NC)	\bigcirc	J _{BU/3}
	J_3			BU/3		BU/3			20,0 —
					3 connector, NO and NO	outputs on	terminal 4		
Setting-up				Dim	ensions				
Minimum mounting d	stances (mr	n)		XS80	C/D/E	XS8C/D		XS8E	
	e≽ XS8I		XS8D	C		. В		(1)	
•	Flush 40	60	200				<u> </u>		
	nounted				•	-	-		
	Not flush 150 mounted	125	600			(1)		F(<u>(3)</u>
Face to face	^> V00	- V000	VCOD		_			_₹	
	e≽ XS8I		XS8D			_		⊸B⊸	
	Flush 80 nounted	120	400			79	70		
4 -	Not flush 300	250	not		F(3)	/ $\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \$	√		
		200		\Box	<u>' (0)</u>	´ \	<u> </u>		
	nounted		recom-						
	nounted		recom- mended	Ш		ш	·	(1) LED	
	nounted e ≽ XS8I	E XS8C		Ш		7		. ,	node button

6.6

13.6

G

6.8

8.3

8.8

9.8

14

<u>14</u>

A (cable) A (connector) B

40

11

18

Sensor

XS8E

XS8C

XS8D

XS8DeeDIN

Inductive proximity sensors XS range, general purpose Cubic case, 40 x 40 x 70 mm, M12 or 1/2"-20UNF connector 5-position turret head

Sensor type Flush mountable in metal Non-flush mountable in metal



Nominal sensing distance	(Sn)		mm	15	20	40	
References	•						
4-wire	PNP	NO+NC		I_	XS8C2A1PCM12	XS8C2A4PCM12	1_
4-Wire	NPN	NO+NC		_			
					XS8C2A1NCM12	XS8C2A4NCM12	_
3-wire	PNP	NO		XS7C2A1PAM12	-		-
	NPN	NO		XS7C2A1NAM12	-	-	
	PNP NPN	NC NC		XS7C2A1PBM12	-		
2-wire	NO NO	INC		XS7C2A1NBM12 XS7C2A1DAM12	XS8C2A1DAM12	XS8C2A4DAM12	XS8C2A4CAM12 (3)
2-wire	NC NC			XS7C2A1DAW12	A30CZATDAWITZ	ASSCZA4DAWITZ	ASSCZA4CAWIIZ (3)
2-wire (~/==) unprotected				_	XS8C2A1MAU20	XS8C2A4MAU20	
2-wire (5/) disprotected	NC			_	XS8C2A1MBU20	XS8C2A4MBU20	
Weight			kg	0.149	0.149	0.149	0.149
Characteristics							
Operating zone			mm	012	016	032	
Product certifications				cULus, C€, UKCA, E2	(3-wire and 4-wire)		
Conformity to standards				IEC 60947-5-2			
Connection				M12 connector for === v	versions		
				1/2 "-20UNF connecto			
Differential travel			%	315 of Sr			
Degree of protection	Conforming and DIN 400	to IEC 60529		IP 65, IP 67 and IP 69h	<		
Temperature	Storage	-	°C	- 40+ 85			
	Operation (2	')	°C	- 25+ 70			
Material		,		Case: PBT			
Vibration resistance	Conforming	to IEC 60068-2-6		25 gn, amplitude ± 2 m	nm (f = 1055 Hz)		
Shock resistance	Conforming	to IEC 60068-2-27		50 gn for 11 ms			
Indicators	Output state			Yellow LED			
	Power on			Green LED, for 4-wire			
Rated supply voltage		4-wire	٧	1248 with protection		<u> </u>	
		3-wire ===	٧	1224 with protection		<u></u>	
		2-wire	V	1248 with protection	against reverse polar	ity	
		2-wire <i></i> ∼/ 	V	24240 (~50/60 Hz)			
Voltage limits		4-wire ===	٧	1058			
(including ripple)		3-wire ===	٧	1036			
		2-wire ===	٧	1058			
		2-wire ∼/===	٧	20264			
Insulation class		==:					
		~/==		1			
Current consumption,		3-wire and	mA	< 15			
no-load		4-wire ===					
Residual current, open sta	te	2-wire ===	mA	< 0.6			
		2-wire ∼/	mA	1.5			
Switching capacity		3-wire and	mA	< 200 with overload an	nd short-circuit protecti	on	
- · ·		4-wire ===					
		2-wire	mA	< 100 with overload an	nd short-circuit protecti	on	
		2-wire <i></i> ∼/ 	mA	~: 5300 <i>(1)</i>			
William I and the state of the		0	.,	==: 5200 mA (1)			
Voltage drop, closed state		3-wire and	٧	< 2			
		4-wire === 2-wire ===	٧	< 4.2			
		2-wire/∼	٧	< 5.5			
Maximum switching freque	ency		kHz	Flush mountable: == 3			
Deleve	First			Non-flush mountable:		uira —/a	
Delays	First-up		ms	7 (3-wire and 4-wire ==	/		
	Response		ms	Flush mountable: ≤ 1.2			
	Recovery		ms	Flush mountable: ≤ 1.8	s. Non-flush mountable	e: ≤ 3.5	
(1) Sensor must be protecte	d by a 0.4 A g	uick-blow fuse con	nected	in series with the load.			

⁽¹⁾ Sensor must be protected by a 0.4 A quick-blow fuse connected in series with the load.
(2) Sensors are available for very low temperatures (suffix **TF**: - 40°C, + 70°C) or very high temperatures (suffix **TT**: - 25°C, + 85°C). Please consult our Customer


⁽³⁾ NO terminal 1 & 4 - the NO output is connected to terminal 1 and 4 of M12 connectors.


XS range, general purpose Cubic case, 40 x 40 x 70 mm, M12 or 1/2"-20UNF connector 5-position turret head

Setting-up precautions Minimum mounting distances (mm) Side by side Face to face Facing a metal object Sensors flush mountable in metal XS7C2A1 • • e ≥ 60 e ≥ 120 e ≥ 45 XS8C2A1ee e ≥ 60 e≥80 e ≥ 160 Sensors non-flush mountable in metal XS8C2A4ee e ≥ 120 e ≥ 160 e ≥ 320 Wiring schemes 2-wire, 1/2"- 20UNF 4-wire ---, NO + NC outputs 3-wire, PNP 3-wire, NPN Quick blow fuse 4 (NO) PNP 04 (NO) 2 (NC) NPN PNP NPN \Diamond 2₀(NC) 2 (NC) \Diamond \Diamond $| \diamondsuit |$ 30 2-wire ..., NO output 2-wire ..., NC output M12 connector 1/2"-20UNF connector 2-wire ..., NO output (M12 connector) (M12 connector) + V: 1 NC: 2 - V: 3 NO 4 NO NO 40 NO: 4

Accessory references				
Description	Type	Length	Reference	Weight
		(m)		(kg)
Pre-wired M12 connectors	Straight	2	XZCP1141L2	0.090
Female, 4-pin, zinc die-cast, nickel plated clamping ring		5	XZCP1141L5	0.190
		10	XZCP1141L10	0.370
	Elbowed	2	XZCP1241L2	0.090
		5	XZCP1241L5	0.190
		10	XZCP1241L10	0.370
Pre-wired 1/2"-20UNF connectors	Straight	5	XZCP1865L5	0.180
Female, 3-pin, zinc die-cast, nickel plated clamping ring		10	XZCP1865L10	0.350
	Elbowed	5	XZCP1965L5	0.180
		10	XZCP1965L10	0.350

Dimensions





Head positions











Nominal sensing distance (Sn)

Connection type

Inductive proximity sensors

XS range, general purpose Plastic case, 40 x 40 x 117 mm, plug-in 5-position turret head

20

40

Cable entry

M12 connector

Flush mountable in metal Non-flush mountable in metal Sensor type



15

mm

	-	XS8C4A1PCP20	XS8C4A4PCP20	XS8C4A4PCM12		
	_	XS8C4A1NCP20	XS8C4A4NCP20			
	XS7C4A1DPP20	XS8C4A1DPP20	XS8C4A4DPP20			
	XS7C4A1MPP20	XS8C4A1MPP20	XS8C4A4MPP20			
kg	0.244	0.244	0.244	0.244		
	entry (e.g. XS8C4A4P	CG13) or a 1/2" NPT ca				
mm	012	016	032			
	cULus, CE, UKCA, E2 (4-wire)				
	IEC 60947-5-2					
	Screw terminals, clamp	oing capacity: 2 or 4 x 1.	5 mm2 / 2 or 4 x 16 AW	G (2)		
%	315 of Sr					
	IP 65, IP 67 and IP 69k					
	- 40+ 85					
°C						
		m (f = 10 55 Hz)				
7	<u> </u>	III (I – 1033 HZ)				
		and 2-wire ∼/ vers	ions			
V	1248 with protection	against reverse polarity	1			
٧	1248 with protection against reverse polarity					
V	24240 (~ 50/60 Hz)					
V	1058					
V	1058					
V	20264					
	: □ / ~: I					
mA	< 15					
mA	< 0.6					
mA	1.5					
mA						
mA		d short-circuit protection	ו			
mA	==: 5200 (1)					
V	<2					
V	< 4.2					
V	< 5.5					
	mm % °C °C °C V V V V V V V V V V V V V	XS7C4A1DPP20	Note: These sensors have an M20 cable entry entry (e.g. XS8C4A1MPP20	Name		

Hz

Ηz

ms

Flush mountable: == 300, ~ 25

Non-flush mountable: == 150, \sim 25

7 ms (3-wire and 4-wire ==), 20 ms (2-wire == and 2-wire ==/ \sim)

Flush mountable: ≤ 1.2. Non-flush mountable: ≤ 1.4

Flush mountable: ≤ 1.8 ms. Non-flush mountable: ≤ 3.5

Delays

Maximum switching frequency

First-up

Response

Recovery

⁽¹⁾ Sensor must be protected by a 0.4 A quick-blow fuse connected in series with the load.

⁽²⁾ These sensors are supplied without a cable gland. An adaptable PG 13.5 cable gland is available (reference XSZPE13). Accessories are available for

connection to an M12 or 7/8"-16UN connector which can be added to the PG 13.5 sensor. Please consult our Customer Care Centre.

(3) Sensors are available for very low temperatures (suffix TF: -40°C, +70°C) or very high temperatures (suffix TT: -25°C, +85°C). Please consult our Customer Care Centre.

XS range, general purpose Plastic case, 40 x 40 x 117 mm, plug-in 5-position turret head

Setting-up precautions Minimum mounting distances (mm) Side by side Facing a metal object Face to face XS7C4A1 e ≥ 60 e ≥ 45 Sensors flush mountable in metal e ≥ 120 XS8C4A1 e≥80 e ≥ 160 e ≥ 60 Sensors non-flush mountable in metal XS8C4A4ee e ≥ 160 e ≥ 320 e ≥ 120 Wiring schemes NO + NC outputs NO or NC outputs, depending on position of link 2-wire == (non polarised) 4-wire ... 2-wire \sim or \dots (programmable) 5 Quick blow fuse NO • • • 4 (NO) 4 (NO) PNF NPN \Diamond 2 (NC) 2 (NC) $| \diamondsuit |$ $| \diamondsuit |$ **Dimensions Head positions** 4 Ø5,45 15,9

(1) 2 elongated holes Ø 5.3 x 7 cm.

41,3

Tightening torque of cover fixing screws and clamp screws: < 1.2 N.m/< 10.62 lb-in

References

Inductive proximity sensors XS range, general purpose

XS range, general purpose Multivoltage sensor, cylindrical, Flush mountable and non-flush mountable Two-wire AC or DC, short-circuit protection



XS1M•••250





XS1M••••250K



XS2M•••250K

Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
Ø 18, thr	eaded M18 x	1		
Flush mou	ıntable			
5	NO	Pre-cabled (L = 2 m) (1)	XS1M18MA250	0.120
		1/2"-20UNF connector	XS1M18MA250K	0.060
	NC	Pre-cabled (L = 2 m) (1)	XS1M18MB250	0.120
		1/2"-20UNF connector	XS1M18MB250K	0.060
Non flush	mountable			
8	NO	Pre-cabled (L = 2 m) (1)	XS2M18MA250	0.120
		1/2"-20UNF connector	XS2M18MA250K	0.060
	NC	Pre-cabled (L = 2 m) (1)	XS2M18MB250	0.120
		1/2"-20UNF connector	XS2M18MB250K	0.060
Ø 30, thr	eaded M30 x	1.5		
Flush mou	ıntable			
10	NO	Pre-cabled (L = 2 m) (1)	XS1M30MA250	0.205
		1/2"-20UNF connector	XS1M30MA250K	0.145
	NC	Pre-cabled (L = 2 m) (1)	XS1M30MB250	0.205
		1/2"-20UNF connector	XS1M30MB250K	0.145
Non flush	mountable			
15	NO	Pre-cabled (L = 2 m) (1)	XS2M30MA250	0.205
		1/2"-20UNF connector	XS2M30MA250K	0.145
	NC	Pre-cabled (L = 2 m) (1)	XS2M30MB250	0.205
		1/2"-20UNF connector	XS2M30MB250K	0.145



Accessories (2)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m long cable add L1 to the reference; for a 10 m long cable add L2 to the reference. Example: XS1M18MA250 becomes XS1M18MA250L1 with a 5 m long cable.


⁽²⁾ For further information, see page 120.


Inductive proximity sensors

XS range, general purpose Multivoltage sensor, cylindrical, Flush mountable and non-flush mountable Two-wire AC or DC, short-circuit protection

Sensor type			XSeMeeMe250K	XSeMeeMe250			
roduct certifications			cULus, CE, UKCA	•			
onnection			1/2"-20UNF connector	Pre-cabled, length: 2 m			
perating zone	Ø 18 flush mountable	mm	04				
	Ø 18 non-flush mountable	mm	06.4				
	Ø 30 flush mountable	mm	08				
	Ø 30 non-flush mountable	mm	012				
ifferential travel		%	115 of effective sensing distance (Sr)				
egree of protection	Conforming to IEC 60529		IP 67	IP 68			
torage temperature		°C	- 40+ 85				
perating temperature		°C	- 25+ 70				
laterials	Case		Nickel plated brass				
	Cable		-	PvR 2 x 0.34 mm ²			
ibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)				
hock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms				
ndicators	Output state		Yellow LED, 4 viewing ports at 90°	Yellow LED			
	Supply on		-	Green LED			
ated supply voltage		٧	~ 24240 (50/60 Hz) or 24210				
oltage limits (including ripple	9)	٧	∼ or == 20264				
nsulation class			I				
witching capacity		mA	\sim 5300 or == 5200 (except Ø 12: \sim or == 5200) with overload and short-circuit protection				
oltage drop, closed state		٧	≤ 5.5				
urrent consumption, no-load	l .	mA	-				
lesidual current, open state		mA	≤1.5				
laximum switching frequency	y Ø 18	Hz	\sim 25 or == 2000				
	Ø 30 flush mountable	Hz	\sim 25 or == 2000				
	Ø 30 non-flush mountable	Hz	\sim 25 or == 1000				
elays	First-up	ms	≤70				
	Response	ms	≤ 2 for Ø 18 and Ø 30				
	Recovery	ms	≤ 4 for Ø 18, ≤ 5 for Ø 30 flush mountable, ≤	≤ 10 for Ø 30 non-flush mountable			
Wiring schemes							
1/2»-20UNF connector	Pre-cabled	2-wire	e ~ or				
1	BU: Blue	NO or	NC output				
+/-:2 ±:1	BN: Brown	_	BN/2 ≂				

±: on connector model only





References

Inductive proximity sensors

XS range, general purpose Cylindrical, metal and plastic, Flush mountable and non-flush mountable Four-wire DC, solid-state NO + NC output



XS1L06•C410







Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Ø 6.5 plair	า				
Stainless ste	el case, fl	ush mou	ntable		
1.5	NO + NC	PNP	Pre-cabled (L = 2 m)	XS1L06PC410	0.025
Ø 8, threa	ded M8 x	(1			
Stainless ste	el case, fl	ush mou	ntable		
1.5	NO + NC	PNP (3)	Pre-cabled (L = 2 m)	XS1M08PC410	0.035
			M12 connector	XS1M08PC410D	0.025
Stainless ste	el case, n	on-flush	mountable		
2.5	NO + NC	PNP (3)	Pre-cabled (L = 2 m)	XS2M08PC410	0.035
			M12 connector	XS2M08PC410D	0.025
Plastic case	, non-flush	mounta	ble		
2.5	NO + NC	PNP (3)	Pre-cabled (L = 2 m) (1)	XS4P08PC410	0.035
Ø 12, threa	aded M1	2 x 1			
Brass case,	flush mou	ntable			
2	NO + NC	PNP	Pre-cabled (L = 2 m) (1) (2)	XS1N12PC410	0.070
			M12 connector	XS1N12PC410D	0.020
		NPN	Pre-cabled (L = 2 m) (1)	XS1N12NC410	0.070
			M12 connector	XS1N12NC410D	0.020
Brass case,	non-flush	mountal	ole		
4	NO + NC	PNP (3)	Pre-cabled (L = 2 m) (1)	XS2N12PC140	0.070
Plastic case	non-flush	mounta	ble		
4	NO + NC	PNP (3)	Pre-cabled (L = 2 m) (1)	XS4P12PC410	0.070
			M12 connector	XS4P12PC410D	0.020

⁽¹⁾ For a 5 m long cable add L1 to the reference. Example: XS1N12PC410 becomes XS1N12PC410L1 with a 5 m long cable.

⁽²⁾ For a 10 m long cable add L2 to the reference. Example: XS1N12PC410 becomes XS1N12PC410L2 with a 10 m long cable.


(3) These sensors can be supplied in NPN versions. Please contact our Customer Care Centre.

References (continued)

Inductive proximity sensors

XS range, general purpose Cylindrical, metal and plastic, Flush mountable and non-flush mountable Four-wire DC, solid-state NO + NC output







103177	- 1000 K. 200 km	E X51N30NC410		
		E		

//LEOL	# 351M30NC410 and 10 miles	
	11	

XS1N•••C410

Brass case,	flush mou	ntable			
10	NO + NC	PNP	Pre-cabled (L = 2 m) (1) (2)	XS1N30PC410	0.160
			M12 connector	XS1N30PC410D	0.100
Plastic case	, non-flust	n mounta	ıble		
15	NO + NC	PNP (3)	Pre-cabled (L = 2 m)	XS4P30PC410	0.160
			M12 connector	XS4P30PC410D	0.100



Accessories (4)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For a 5 m long cable add L1 to the reference. Example: XS1N18PC410 becomes

XS1N18PC410L1 with a 5 m long cable.

(2) For a 10 m long cable add L2 to the reference. Example: XS1N18PC410 becomes XS1N18PC410L2 with a 10 m long cable.

⁽³⁾ These sensors can be supplied in NPN versions. Please contact our Customer Care Centre.

⁽⁴⁾ For further information, see page 120.

XS range, general purpose Cylindrical, metal and plastic Flush mountable and non-flush mountable Four-wire DC, solid-state NO + NC output

0			VO BOLLER	V0 110115	VO DC 112	V0 110111
Sensor type			XSeeePC410D	XSeeeNC410D	XSeeePC410	XSeeeNC410
Product certifications			cULus, C€, UKCA, E2 (1)	cULus, C€, UKCA	cULus, C€, UKCA, E2	cULus, CE, UKCA
Connection			M12 connector Pre-cabled, length: 2 m			n
Operating zone	Ø 6.5 and Ø 8 flush mountable	mm	01.2			
	Ø 8 non-flush mountable	mm	02			
	Ø 12 flush mountable	mm	01.6			
	Ø 12 non-flush mountable	mm	03.2			
	Ø 18 flush mountable	mm	04			
	Ø 18 non-flush mountable	mm	06.4			
	Ø 30 flush mountable	mm	08			
	Ø 30 non-flush mountable	mm	012			
Differential travel		%	115 of effective sens	sing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67	IP 67	IP 67 (Ø 6.5 and Ø 8) IP 68 (Ø 12, Ø 18 and 9	Ø 30)
	Conforming to DIN 40050		IP 69K (Ø 12, Ø 18 and Ø 30)	_	_	
Storage temperature		°C	- 40+ 85			
Operating temperature		°C	- 25+ 70 (2)			
Materials Case			Nickel plated brass for XS1N•••. Stainless steel 303 for XS1M08••• and XS2M08•••. Plastic, PPS, for XS4P•••.			
	Cable		-		PvR 4 x 0.08 mm ² (Ø 6.9 PvR 4 x 0.22 mm ² (Ø 12	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 m	nm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			
Output state indication			Yellow LED, 4 viewing ports at 90° Yellow LED, annular			
Rated supply voltage		٧	== 1224 with protect	ion against reverse	polarity	
Voltage limits (including ripple)		V	936 (1036 for XS4P•••)	1036	936 (1036 for XS4P18•••)	 1036
Insulation class	<u> </u>					
Switching capacity		mA	≤ 200 with overload and short-circuit protection			
Voltage drop, closed state		٧	≤2			
Current consumption, no-load		mA	≤ 10			
Maximum switching frequency	Ø 6.5, Ø 8 and Ø 12	Hz	5000			
	Ø 18	Hz	2000			
	Ø 30	Hz	1000			
Delays	First-up	ms	≤ 5			
	Response	ms	≤ 0.1 for Ø 8 and Ø 12	, ≤ 0.15 for Ø 18, ≤ 0	.3 for Ø 30	
Recovery		ms	≤ 0.1 for Ø 8 and Ø 12, ≤ 0.35 for Ø 18, ≤ 0.7 for Ø 30			

⁽¹⁾ Except **XS4P•••**: UL, CSA and C€.

⁽²⁾ Sensors are available for very low temperatures (suffix **TF**: -40°C, +70°C) or very high temperatures (suffix **TT**: -25°C, +85°C). Please consult our Customer Care Centre.

XS range, general purpose Cylindrical, metal and plastic Flush mountable and non-flush mountable Four-wire DC, solid-state NO + NC output

Wiring schemes

M12 connector




Pre-cabled


BU: Blue BN: Brown BK: Black WH: White

PNP 4-wire

Face to face



NPN 4-wire



Setting-up

Sensor	
Ø 6.5 flush mountable	XS1L06
Ø 8 flush mountable	XS1M08
Ø 8 non-flush mountable	XS4P08
Ø 12 flush mountable	XS1N12
Ø 12 non-flush mountable	XS4P12
Ø 18 flush mountable	XS1N18
Ø 18 non-flush mountable	XS4P18
Ø 30 flush mountable	XS1N30
Ø 30 non-flush mountable	XS4P30


Minimum mounting distances (mm)



Pre-cabled (mm)

Pre-cabled (mm)

Facing a metal object




e ≥ 45

Mounted in a metal support

+ I	d≥6.5 h≥0
	d≥8h≥0
	d ≥ 24 h ≥ 5
	d ≥ 12 h ≥ 0
	d≥36 h≥8
	d ≥ 18 h ≥ 0
	d ≥ 54 h ≥ 16
	d≥30 h≥0
	d > 90 h > 30

Dimensions



Flush mountable in metal

Sensor	
Ø 6.5 stainless steel	XS1L06
Ø 8 stainless steel	XS1M08
Ø 12 brass	XS1N12
Ø 18 brass	XS1N18
Ø 30 brass	XS1N30

r re-cabled (IIIII)	re-cabled (IIIII)				
а	b				
50	-				
51	42				
37	25				
41	29				
45	33				

M12 conne	ector (mm)	
а	b	
_	_	
62	40	
50	31	
51	28	
54	33	

Non-flush mountable in metal

Sensor	
Ø 8	XS2M08
stainless steel	
Ø8	XS4P08
plastic	
Ø 12	XS4P12
plastic	
Ø 18	XS4P18
plastic	
Ø 30	XS4P30
plastic	

a b	
u b	
54 42	
34 25	
37 25	
41 29	
45 33	

M12 conne	M12 connector (mm)				
а	b				
65	40				
_	-				
50	31				
51	28				
54	33				


References

Inductive proximity sensors

XS range, general purpose Cylindrical, metal, increased range, flush mountable Four-wire DC, solid-state NO + NC output



XS1●B3PCL2





XS112B3PCM12

Sensors, 4-wire == 1224 V, long case model					
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Ø 12, threa	ded M12 x 1				
4	NO + NC	PNP	Pre-cabled (L = 2 m)	XS112B3PCL2	0.070
			M12 connector	XS112B3PCM12	0.020
Ø 18, threa	ided M18 x 1				
8	NO + NC	PNP	Pre-cabled (L = 2 m)	XS118B3PCL2	0.100
			M12 connector	XS118B3PCM12	0.040
Ø 30, threa	ded M30 x 1.	5			
15	NO + NC	PNP	Pre-cabled (L = 2 m)	XS130B3PCL2	0.160
			M12 connector	XS130B3PCM12	0.100



XSZB1●●

Accessories	(1)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For further information, see page 120.

Inductive proximity sensors

XS range, general purpose Cylindrical, metal, increased range, flush mountable Four-wire DC, solid-state NO + NC output

Sensor type Product certifications			XS100B3	PCM12 / XS608B1PC	18440				
Product certifications			XO I CODO	PCIVITZ/ ASSUSBIPC	,IVI12	XS1••B3PC	L2 / XS608B	IPCL2	
	Product certifications Ø 8		cULus, C€	, UKCA					
	Ø 12, 18 and 30		cULus, C€	, UKCA, E2					
Connection	Connector		M12			-			
	Pre-cabled		-	– Length 2 m					
Operating zone (1)	Ø 8	mm	02						
	Ø 12		03.2						
	Ø 18	mm	06.4						
	Ø 30	mm	012						
Differential travel		%	115 of e	ffective sensing dista	nce (Sr)	_			
egree of protection	Conforming to IEC 60529		IP 65 and	IP 65 and IP 67					
	Conforming to DIN 40050		IP 69K	IP 69K –					
torage temperature		°C	- 40+ 85	5					
perating temperature		°C	- 25+ 70	0 (2)					
laterials	Case		Nickel plat	ted brass for Ø 12 to 9	Ø 30, stainle	ss steel grade 3	303 for Ø 8		
	Sensing face		PPS						
	Cable		_			PvR 4 x 0.22	mm² except @	ð 8: 4 x 0.08 m	
ibration resistance	Conforming to IEC 60068-2-6		25 gn. am	plitude ± 2 mm (f = 10	to 55 Hz)	1			
hock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			,			
	30110111111g to 120 00000-2-27				no°	Vellow I ED, appular			
Output state indication				Yellow LED, 4 viewing ports at 90° Yellow LED, annular					
Rated supply voltage		٧	== 1224 polarity	(XS1, XS608), == 12) 12, 18, 30), wi	2, 18, 30), with protection against reverse			
Voltage limits (including ripple)		٧	== 936				KS6 Ø 12, 18,		
Insulation class									
Switching capacity		mA	< 200 with	overload and short-o	ricuit protec	tion			
				TOVETION ATTO STIOIT-C	ircuit protec				
Voltage drop, closed state		٧	≤2						
Current consumption, no-load		mA	≤10						
laximum switching frequenc	y Ø 8 and Ø 12	Hz	2500						
	Ø 18	Hz	1000						
	Ø 30	Hz	500						
)elays	First-up	ms	≤10						
•	Response	ms	≤ 0.2 for Ø 8 and Ø 12, ≤ 0.3 for Ø 18, ≤ 0.6 for Ø 30						
	Recovery	ms	ļ						
	Recovery								
Wiring schemes			tting-up						
M12 connector	Pre-cabled	Mini	imum moui	nting distances (mn					
3	BU: Blue BN: Brown				amAnAm.	e M	_^_		
$((\bullet,\bullet))$	BK: Black			e e	amAnAm	1. 1000	a	9	
2	WH: White						-0-0		
PNP 4-wire		Sen	sors	Side by side	Face	to face	Facing a	a metal object	
BN/1		Ø8		e≥5	e ≥ 30		e≥8		
PNP BK/4 (NO)		Ø 12		e ≥ 8	e ≥ 50	e ≥ 50		e ≥ 12	
WH/2 (NC)		Ø 18			e≥ 100 e≥ 12 e≥ 25				
		Ø 30				e ≥ 180			
Dimensions		50			5 / 100		e≥45		
					D	ablad (mars)	M40	nooter (====)	
3)		0	oorc .			abled (mm)		nector (mm)	
		Ø8	sors		a	b 42	a	b	
<u> </u>					51	42	61	40	
b		Ø 12			37	25	50	31	
 		Ø 18			41	29	51	28	
a		Ø 30			45	33	54	33	

⁽¹⁾ Detection curves, see page 128.

⁽²⁾ Sensors are available for very low temperatures (suffix **TF**: -40°C, + 70°C) or very high temperatures (suffix **TT**: - 25°C, + 85°C). Please consult our Customer Care Centre.

⁽³⁾ LED.

References

Inductive proximity sensors

XS range, general purpose

Cylindrical, metal and plastic, flush and non-flush mountable Four-wire DC, solid-state PNP + NPN NO/NC programmable output



XS1M**●•**KP340



XS4P••KP340



XS2M**●•**KP340



XS4P••KP340D







Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)			
Ø 12, thre	eaded M12	x 1						
Metal case	, flush mounta	able						
2	NO/NC	PNP + NPN	Pre-cabled (L = 2 m) (1)	XS1M12KP340	0.075			
	programmable		M12 connector	XS1M12KP340D	0.025			
Metal case, non-flush mountable								
4	NO/NC	PNP + NPN	Pre-cabled (L = 2 m) (1)	XS2M12KP340	0.075			
	programmable		M12 connector	XS2M12KP340D	0.025			
Plastic cas	e, non-flush n	nountable						
4	NO/NC		Pre-cabled (L = 2 m) (1)	XS4P12KP340	0.075			
	programmable		M12 connector	XS4P12KP340D	0.025			
Ø 18, thre	eaded M18	x 1						
Metal case	, flush mounta	able						
	NO/NC	PNP + NPN	Pre-cabled (L = 2 m) (1)	XS1M18KP340	0.120			
programmable			M12 connector	XS1M18KP340D	0.060			
Metal case, non-flush mountable								
8	NO/NC		Pre-cabled (L = 2 m) (1)	XS2M18KP340	0.120			
programmable			M12 connector	XS2M18KP340D	0.060			
Plastic case, non-flush mountable								
8	NO/NC		Pre-cabled (L = 2 m) (1)	XS4P18KP340	0.120			
	programmable		M12 connector	XS4P18KP340D	0.060			
Ø 30, thre	eaded M30	x 1.5						
	, flush mounta							
10	NO/NC	PNP + NPN	Pre-cabled (L = 2 m) (1)	XS1M30KP340	0.205			
programmable			M12 connector	XS1M30KP340D	0.145			
Metal case	, non-flush me	ountable						
15	NO/NC	PNP + NPN	Pre-cabled (L = 2 m) (1)	XS2M30KP340	0.205			
	programmable		M12 connector	XS2M30KP340D	0.145			
Plastic cas	e, non-flush n	nountable						
15	NO/NC		Pre-cabled (L = 2 m) (1)	XS4P30KP340	0.205			
	programmable		M12 connector	XS4P30KP340D	0 145			

Accessories (2)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

M12 connector

XS4P30KP340D

⁽¹⁾ For a 5 m long cable add **L1** to the reference; for a 10 m long cable add **L2** to the reference. Example: **XS1M12KP340** becomes **XS1M12KP340L1** with a 5 m long cable.

⁽²⁾ For further information, see page 120.

Inductive proximity sensors

XS range, general purpose

Cylindrical, metal and plastic, flush and non-flush mountable Four-wire DC, solid-state PNP + NPN NO/NC programmable output

Sensor type			XSeMeeKP340D	XSeMeeKP340	
Product certifications			cULus, CE, UKCA		
Connection			M12 connector	Pre-cabled, length: 2 m	
Operating zone	Ø 12 flush mountable	mm	01.6		
	Ø 12 non-flush mountable	mm	03.2		
	Ø 18 flush mountable	mm	04		
	Ø 18 non-flush mountable	mm	06.4		
	Ø 30 flush mountable	mm	08		
	Ø 30 non-flush mountable	mm	012		
Differential travel		%	115 of effective sensing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 67	IP 68	
Storage temperature		°C	- 40+ 85		
Operating temperature		°C	-25+70		
Materials	Case		Nickel plated brass for XS1M and XS2M, PPS for XS4P		
	Cable		_	PvR 4 x 0.34 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED, 4 viewing ports at 90°	Yellow LED, annular	
Rated supply voltage		٧	== 1224 with protection against reverse polarity		
Voltage limits (including ripple)		٧	 1036		
Insulation class					
Switching capacity		mΑ	≤ 200 with overload and short-circuit pro	tection	
Voltage drop, closed state		٧	≤ 2.6		
Current consumption, no-load		mΑ	≤ 10		
Maximum switching frequency	Ø 12	Hz	5000		
	Ø 18	Hz	2000		
	Ø 30 flush mountable	Hz	1000		
	Ø 30 non-flush mountable	Hz	1000		
Delays	First-up	ms	≤5		
	Response	ms	≤ 0.1 for Ø 12, ≤ 0.15 for Ø 18, ≤ 0.3 for Ø 30		
	Recovery	ms	≤ 0.1 for Ø 12, ≤ 0.35 for Ø 18, ≤ 0.7 for Ø 30		

Wiring schemes

M12 connector




Pre-cabled

BU: Blue BN: Brown BK: Black WH: White

PNP + NPN

4-wire programmable, NO or NC output



Setting-up

Ø 12 flush mountable XS1M12

Ø 12 non-flush mountable XS2M12 and XS4P12

Ø 18 flush mountable XS1M18

Ø 18 non-flush mountable XS2M18 and XS4P18

Ø 30 flush mountable **XS1M30**

Ø 30 non-flush mountable XS2M30 and XS4P30

Minimum mounting distances (mm) Side by side e ≥ 16

e ≥ 10

e ≥ 16

e ≥ 20

e ≥ 60







e ≥ 120

e ≥ 180



Facing a metal object e ≥ 6 e ≥ 12

e ≥ 15 e ≥ 24

e ≥ 30

e ≥ 45




Mounted in a metal support $d \ge 12 h \ge 0$ d≥36 h≥8

> d≥18h≥0 d ≥ 54 h ≥ 16

d ≥ 30 h ≥ 0 d ≥ 90 h ≥ 30

Dimensions



	Flush mountable in metal				
Sensor	Pre-c	Pre-cabled		ector	
	а	b	а	b	
Ø 12 metal	54	42	61	42	
Ø 12 plastic	-	_	_	_	
Ø 18 metal	60	51	72	51	
Ø 18 plastic	_	_	_	_	
Ø 30 metal	60	51	72	51	
Ø 30 plastic	_	-	-	-	

Non	Non-flush mountable in metal							
Pre-	Pre-cabled		ector					
а	b	а	b	С				
55	42	66	42	5				
54	42	61	43	0				
60	44	72	44	8				
60	51	70	51	0				
63	41	75	41	13				
60	51	70	51	0				

References

ECELAB

Inductive proximity sensors XS range, general purpose

Plastic, cylindrical, non-flush mountable Two-wire AC or DC Three-wire DC, solid-state output











XS4P•••340D XS4P•••370D XS4P•••230K

Canaina diat	Function	Outmost	Connection	Deference	Wainbt
Sensing dist. (Sn) mm		Output	Connection	Reference	Weight (kg)
Ø 8, threade					
Three-wire		DND	Dec	VC4D00D4040	0.005
2.5	NO	PNP	Pre-cabled (L = 2 m) (1) (2)	XS4P08PA340	0.025
	NO.	NPN	Pre-cabled (L = 2 m) (1) (2)	XS4P08NA340	0.025
	NC	PNP	Pre-cabled (L = 2 m) (1) (2)	XS4P08PB340	0.025
		NPN	Pre-cabled (L = 2 m) (1) (2)	XS4P08NB340	0.025
Two-wire \sim c	or == 24-240) V			
2.5	NO		Pre-cabled (L = 2 m) (1)	XS4P08MA230	0.030
	NC		Pre-cabled (L = 2 m) (1)	XS4P08MB230	0.030
Ø 12, thread	ded M12 x	:1			
Three-wire					
4	NO	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P12PA340	0.060
		NPN	Pre-cabled (L = 2 m) (1) (3)	XS4P12NA340	0.060
	NC	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P12PB340	0.060
		NPN	Pre-cabled (L = 2 m) (1) (3)	XS4P12NB340	0.060
Three wire -	- 12 /0 \/				
Three-wire ====	12-48 V NO	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P12PA370	0.065
7	NO	NPN	Pre-cabled (L = 2 m) (1) (3)	XS4P12NA370	0.065
	NC	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P12PB370	0.065
	NO	1 141	1 16-cabled (L = 2 III) (1) (3)	X041 121 B370	0.003
Two-wire \sim 0	or == 24-240) V			
4	NO		Pre-cabled (L = 2 m) (1)	XS4P12MA230	0.065
			1/2"-20UNF connector	XS4P12MA230K	0.030
	NC		Pre-cabled (L = 2 m) (1)	XS4P12MB230	0.065
Ø 18, thread	ded M18 x	1			
Three-wire					
8	NO	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P18PA340	0.090
		NPN	Pre-cabled (L = 2 m) (1) (3)	XS4P18NA340	0.090
	NC	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P18PB340	0.090
Three-wire	- 12 /0 \/				
8	NO	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P18PA370	0.100
		NPN	Pre-cabled (L = 2 m) (1) (3)	XS4P18NA370	0.100
	NC	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P18PB370	0.100
Two-wire \sim 0) V	D 11 1/1 0 \(\frac{1}{2}\)	V0.17.1011.1000	0.400
8	NO		Pre-cabled (L = 2 m) (1)	XS4P18MA230	0.100
	NO		1/2"-20UNF connector	XS4P18MA230K	0.040
	NC		Pre-cabled (L = 2 m) (1)	XS4P18MB230	0.100
			1/2"-20UNF connector	XS4P18MB230K	0.040
Ø 30, thread	ded M30 x	1.5			
Three-wire	12-24 V				
15	NO	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P30PA340	0.120
		NPN	Pre-cabled (L = 2 m) (1) (3)	XS4P30NA340	0.120
	NC	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P30PB340	0.120
Three-wire	12-48 V				
15	NO	PNP	Pre-cabled (L = 2 m) (1) (3)	XS4P30PA370	0.140
	NC	PNP	Pre-cabled (L = 2 m) (3)	XS4P30PB370	0.140
Torre of the co					
Two-wire \sim 0	no NO		Pre-cabled (I = 2 m) (1)	ACADSUMVSSO	0.140
10	INO		Pre-cabled (L = 2 m) (1) 1/2"-20UNF connector	XS4P30MA230	
	NC			XS4P30MA230K	0.080
	INC		Pre-cabled (L = 2 m) (1)	XS4P30MB230	0.140
			1/2"-20UNF connector	XS4P30MB230K	0.080

⁽¹⁾ For a 5 m long cable add L1 to the reference; for a 10 m long cable add L2 to the reference. Example: XS4P08PA340 becomes XS4P08PA340L1 with a 5 m long cable.

⁽²⁾ For an M8 connector, add S to the reference. Example: XS4P08PA340 becomes XS4P08PA340S with an M8 connector.

⁽³⁾ For an M12 connector, add D to the reference. Example: XS4P12PA370 becomes XS4P12PA370D with an M12 connector.


Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range, general purpose Plastic, cylindrical, non-flush mountable Two-wire AC or DC Three-wire DC, solid-state output

Characteristics Sensor type			XS4Peeee340e	XS4P••••370•	XS4PeeMe230e	
Product certifications			cULus, C€, UKCA, ECOLAB		XO-11 COMOZOGO	
Connection	Pre-cabled		Length: 2 m			
	Connector		M8 on Ø 8	M8 on Ø 8 1/2"-20UNF		
	-		M12 on Ø 12, Ø 18 and Ø 30	M12 on Ø 12, Ø 18 and Ø 30		
Operating zone	Ø8	mm	02	02		
	Ø 12	mm	03.2			
	Ø 18	mm	06.4			
	Ø 30	mm	012			
Differential travel		%	115 of effective sensing di			
Degree of protection	Conforming to IEC 60529		IP 68 for pre-cabled version IP 67 for connector version	(except Ø 8: IP 67)		
Storage temperature		°C	- 40+ 85			
Operating temperature		°C	- 25+ 70			
Materials	Case		PPS			
	Cable		PvR 3 x 0.34 mm ² except Ø	8: 3 x 0.11 mm ²	PvR 2 x 0.34 mm ² except Ø 8: 2 x 0.11 mm	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f =	= 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			
Output state indication		Yellow LED: annular on pre-cabled version Yellow LED: 4 viewing ports at 90° on connector version				
Rated supply voltage		V	== 1224 with protection against reverse polarity	== 1248 with protection against reverse polarity	∼ or 24240 (50/60 Hz)	
Voltage limits (including ripple)		٧	 1036	 1058	∼ or 20264	
Insulation class					1	
Switching capacity	Ø 8	mΑ	≤ 200 with overload and sho	5100		
	Ø 12				5200	
	Ø 18 and 30				5200 and 5300 ↑	
Voltage drop, closed state		٧	≤ 2		≤ 5.5	
Residual current, open stat		mA	-	-		
Current consumption, no-lo		mA	1.0		-	
Maximum switching freque		Hz	5000		 3000, ∼ 25	
	Ø 18	Hz	2000		== 2000, ∼ 25	
	Ø 30	Hz	1000		== 1000, ∼ 25	
Delays	First-up	ms	≤ 10		≤ 40	
	Response	ms	≤ 0.1 for Ø 8 and Ø 12, ≤ 0.1		≤ 0.2	
	Recovery	ms	≤ 0.1 for Ø 8 and Ø 12, ≤ 0.3	35 for Ø 18, ≤ 0.7 for Ø 30	≤ 0.2 for Ø 8, Ø 12 and Ø 18, ≤ 0.4 for Ø 30	
Wiring schemes						
Connector	Pre-cabled	PNP	NP	N	2-wire \sim or $=$	
M8 M12 4 1 3	BK: Black	BN/1 PNP	+ BN/1 BK/4 (NO) NPN BK/2 (NC) ↓	BK/4 (NO) BK/2 (NC)	BU/3 \square \square	
1/2"-20UNF ¬: 2 ¬: 3		BU/3 L For M&	BU/3 connector, NO and NC outpu			

Setting-up Minimum mounting distances (mm) Mounted in a metal support Side by side Face to face Facing a metal object Ø8 e≥ 10 e≥30 e≥7.5 d≥24 h≥5 e ≥ 16 e ≥ 48 Ø 12 d≥36 h≥8 e ≥ 12 Ø 18 e ≥ 16 e ≥ 96 e ≥ 24 d ≥ 54 h ≥ 16 Ø 30 e ≥ 60 e ≥ 180 e ≥ 45 d≥90 h≥30



Inductive proximity sensors
XS range, general purpose
Cylindrical, quasi-flush mountable, increased range Three-wire DC, solid-state output



XS1N ••• 349

References	3				
Sensing distance (Sn) (mm)	Function	Output	Connection	Reference	Weight (kg)
Ø 12, threade	d M12 x 1				
4	NO	PNP	Pre-cabled (L = 2 m)	XS1N12PA349	0.070
			M12 connector	XS1N12PA349D	0.020
		NPN	Pre-cabled (L = 2 m)	XS1N12NA349	0.070
			M12 connector	XS1N12NA349D	0.020
	NC	PNP	Pre-cabled (L = 2 m)	XS1N12PB349	0.070
			M12 connector	XS1N12PB349D	0.020
Ø 18, threade	d M18 x 1				
10	NO	PNP	Pre-cabled (L = 2 m)	XS1N18PA349	0.100
			M12 connector	XS1N18PA349D	0.040
		NPN	Pre-cabled (L = 2 m)	XS1N18NA349	0.100
			M12 connector	XS1N18NA349D	0.040
	NC	PNP	Pre-cabled (L = 2 m)	XS1N18PB349	0.100
			M12 connector	XS1N18PB349D	0.040
Ø 30, threade	d M30 x 1.5				
20	NO	PNP	Pre-cabled (L = 2 m)	XS1N30PA349	0.160
			M12 connector	XS1N30PA349D	0.100
		NPN	Pre-cabled (L = 2 m)	XS1N30NA349	0.160
			M12 connector	XS1N30NA349D	0.100
	NC	PNP	Pre-cabled (L = 2 m)	XS1N30PB349	0.160
			M12 connector	XS1N30PB349D	0.100



XS1N••••349D



Accessories (1)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For further information, see page 120.


Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors XS range, general purpose

XS range, general purpose Cylindrical, quasi-flush mountable, increased range Three-wire DC, solid-state output

Sensor type			XS1 • • • • • 349D		XS1•••••349
Product certifications			cULus, CE, UKCA	cULus, C€, UKCA	
Connection			M12 connector		Pre-cabled, length: 2 m
Operating zone	Ø8	mm	02		
	Ø 12	mm	03.2		
	Ø 18	mm	08		
	Ø 30	mm	016		
Differential travel		%	115 of effective sen	sing distance (Sr)	
Degree of protection	Conforming to IEC 60529		IP 67		IP 68 (except Ø 8: IP 67)
	Conforming to DIN 40050		IP 69K for Ø 12 to Ø 3	30	
Storage temperature		°C	- 40+ 85		
Operating temperature		°C	- 25+ 70		
Materials	Case		Nickel plated brass		
	Cable		_		PvR 3 x 0.34 mm ² except Ø 8: 3 x 0.11 mm
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED, 4 viewing ports at 90° Yellow LED, annular		Yellow LED, annular
Rated supply voltage		٧	== 1224 with protection against reverse polarity		
Voltage limits (including ripple)		٧	 1036		
Insulation class					
Switching capacity		mA	≤ 200 with overload a	nd short-circuit prote	ection
Voltage drop, closed state		٧	≤2		
Current consumption, no-load		mA	≤ 10		
Maximum switching frequency	Ø 8 and Ø 12	Hz	2500		
	Ø 18	Hz	1000		
	Ø 30	Hz	500		
Delays	First-up	ms	≤5		
	Response	ms	≤ 0.2 for Ø 8 and Ø 12	$2, \le 0.3 \text{ for } \emptyset 18, \le 0.$	6 for Ø 30
	Recovery	ms	≤ 0.2 for Ø 8 and Ø 12	$2, \leq 0.7$ for Ø 18, ≤ 1 .	4 for Ø 30
Wiring schemes					
Connector	Pre-cabled	PNP	3-wire	NPN 3-wire	
M8 M12 4 3 1 1 3 3 4 4 3 3 4 4 4 4 4 4 4 4 4 4	BU: Blue BN: Brown BK: Black	BN/1 PNP	BK/4 (NO) BK/2 (NC)		+ 4 (NO)<br 2 (NC)</td

For M8 connector, NO and NC outputs on terminal 4





Dimensions

	Flus	Flush mountable in metal							
Sensor	Pre-c	Pre-cabled M8 connector			M12 conne	M12 connector			
	а	b	а	b	а	b			
Ø8	33	25	42	26	45	23			
Ø 12	35	25	_	_	50	30			
Ø 18	39	28	_	_	50	28			
Ø 30	43	32	_	_	55	32			

Inductive proximity sensors
XS range, general purpose
Miniature, cylindrical, quasi-flush mountable
Three-wire DC, solid-state output



XS604R1PAL2



XS504R1NAM08



XS604R1NBL2



XS505R1PAM08

Sensing distar (Sn) mm	nce Function	Output	Connection	Reference	Weight (kg)
Stainless ste	el case, qua	si-flush r	nountable		
1,5	NO	PNP	Pre-cabled (L = 2 m)	XS604R1PAL2	0.030
			M8 connector	XS604R1PAM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS604R1NAL2	0.030
			M8 connector	XS604R1NAM08	0.004
	NC	PNP	Pre-cabled (L = 2 m)	XS604R1PBL2	0.030
			M8 connector	XS604R1PBM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS604R1NBL2	0.030
			M8 connector	XS604R1NBM08	0.004
0,8	NO	PNP	Pre-cabled (L = 2 m)	XS504R1PAL2	0.030
			M8 connector	XS504R1PAM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS504R1NAL2	0.030
			M8 connector	XS504R1NAM08	0.004
	NC	PNP	Pre-cabled (L = 2 m)	XS504R1PBL2	0.030
			M8 connector	XS504R1PBM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS504R1NBL2	0.030
			M8 connector	XS504R1NBM08	0.004

Ø 5, threa	aded M5 x 0).5			
Sensing dist (Sn) mm	ance Function	Output	Connection	Reference	Weight (kg)
Stainless s	teel case, qua	si-flush ı	nountable		
1,5	NO	PNP	Pre-cabled (L = 2 m)	XS605R1PAL2	0.030
			Pre-cabled (L = 5 m)	XS605R1PAL5	0.030
			M8 connector	XS605R1PAM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS605R1NAL2	0.030
			M8 connector	XS605R1NAM08	0.004
	NC	PNP	Pre-cabled (L = 2 m)	XS605R1PBL2	0.030
			M8 connector	XS605R1PBM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS605R1NBL2	0.030
			M8 connector	XS605R1NBM08	0.004
0.8	NO	PNP	Pre-cabled (L = 2 m)	XS505R1PAL2	0.030
			M8 connector	XS505R1PAM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS505R1NAL2	0.030
			M8 connector	XS505R1NAM08	0.004
	NC	PNP	Pre-cabled (L = 2 m)	XS505R1PBL2	0.030
			M8 connector	XS505R1PBM08	0.004
		NPN	Pre-cabled (L = 2 m)	XS505R1NBL2	0.030
			M8 connector	XS505R1NBM08	0.004


Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range, general purpose Miniature, cylindrical, quasi-flush mountable Three-wire DC, solid-state output

Sensor type			XS•04•••••M08 XS•05•••••M08	XSe04eeeeeL2 XSe05eeeeeLe	
Product certifications			cULus, C€, UKCA	UL, C€, UKCA	
Connection (1)	Connector		M8	-	
	Pre-cabled Length	m	-	2 for XS•0•••••L2 5 for XS605•••••L5	
Operating zone	XS504	mm	00.65	·	
	XS505	mm	00.65		
	XS604	mm	01.21		
	XS605	mm	01.21		
Degree of protection	Conforming to IEC 60529		IP 67		
Storage temperature		°C	- 40+ 85		
Operating temperature		°C	- 25+ 70		
Materials Case			Stainless steel 303		
	Cable		PVC 3x0.149 mm²		
Vibration resistance			Conforming to IEC 60947-5-2		
Shock resistance			Conforming to IEC 60947-5-2		
Output state indication	LED		Yellow LED		
	Visibility		4 viewing ports at 90°	1 viewing port	
Rated supply voltage		V	 1224		
Voltage limits (including ri	pple)	V	 1030		
Insulation class			III		
Current consumption, no-	load	mA	≤ 10		
Switching capacity	3-wire PNP/NPN	mA	≤ 100 with overload and short-circuit protect	ion	
Voltage drop, closed state		V	≤1.5		
Maximum switching frequency	ency	kHz	5		
Delays	First-up	ms	50		


⁽¹⁾ Detection curves, see page 128



Setting-up Minimum mounting distances (mm) d4 d2 d3 Sensor d1 ≥ 0 (3) Ø 4 XS504 steel ≥ 2 (1) ≥ 3 (2) ≥4 ≥8 ≥ 2.4 ≥ 4 (2) Ø 4 XS604 steel ≥ 3 (1) ≥ 0 (3) ≥4 ≥8 ≥ 4.5 3 Sn d3 d2 Ø 5 **XS505** steel ≥5 ≥ 1 (2) ≥ 0 (3) ≥ 2.4 ≥ 0 (1) ≥5 Ø 5 **XS605** steel ≥ 2 (2) ≥ 1 *(1)* ≥ 0 (3) ≥5 ≥ 10 ≥ 4.5 (1) If mounting environment is ferro-magnetic metal, such as iron, cobalt, nickel, gadolinium, neodymium, etc. (2) If mounting environment is non ferro-magnetic metal, such as aluminium, copper, brass, gold, silver, titanium, etc.

(3) If mounting environment is non-metal, such as plastic, wood, etc.

Tightening torque



For Ø 5: A < 1.5 N.m.

Dillielisions	
	Sensor
	Ø4XS●04
b b	Ø 5 XS•05
a	

Sensor	Pre-cabled		M8 connector	M8 connector		
	а	b	a	b		
Ø4XS●04	30.2	-	38.4	-		
Ø 5 XS●05	30.2	26.5	38.4	22.1		

XS range, general purpose Miniature, cylindrical, flush mountable Three-wire DC, solid-state output



XS1L04 •• 310



XS1N05••311S



XS1N05••310

Ø 4 plain					
Sensing distance (Sn) mm	Function	Output	Connection (1)	Reference	Weight (kg)
Brass case, flu	sh mounta	able			
1	NO	PNP	Pre-cabled (L = 2 m)	XS1L04PA310	0,025
			M8 connector	XS1L04PA310S	0.010
		NPN	Pre-cabled (L = 2 m)	XS1L04NA310	0.025
			M8 connector	XS1L04NA310S	0.010
	NC	PNP	Pre-cabled (L = 2 m)	XS1L04PB310	0.025
			M8 connector	XS1L04PB310S	0.010
		NPN	Pre-cabled (L = 2 m)	XS1L04NB310	0.025
			M8 connector	XS1L04NB310S	0.010
Stainless steel	case, flus	h mounta	ble		
0,8	NO	PNP	Pre-cabled (L = 2 m)	XS1L04PA311	0,025
			M8 connector	XS1L04PA311S	0.010
		NPN	Pre-cabled (L = 2 m)	XS1L04NA311	0.025
			M8 connector	XS1L04NA311S	0.010
	NC	PNP	Pre-cabled (L = 2 m)	XS1L04PB311	0.025
			M8 connector	XS1L04PB311S	0.010
		NPN	Pre-cabled (L = 2 m)	XS1L04NB311	0.025
			M8 connector	XS1L04NB311S	0.010

Ø 5, threade	ed M5 x 0	.5			
Sensing distance (Sn) mm	Function	Output	Connection (1)	Reference	Weight (kg)
Brass case, flu	sh mounta	able			
1	NO	PNP	Pre-cabled (L = 2 m)	XS1N05PA310	0,030
		NPN	Pre-cabled (L = 2 m)	XS1N05NA310	0,030
	NC	PNP	Pre-cabled (L = 2 m)	XS1N05PB310	0,030
		NPN	Pre-cabled (L = 2 m)	XS1N05NB310	0,030
Stainless steel	case, flus	h mounta	able		
0.8	NO	PNP	Pre-cabled (L = 2 m)	XS1N05PA311	0.030
			M8 connector	XS1N05PA311S	0.015
		NPN	Pre-cabled (L = 2 m)	XS1N05NA311	0.030
			M8 connector	XS1N05NA311S	0.015
	NC	PNP	Pre-cabled (L = 2 m)	XS1N05PB311	0.030
			M8 connector	XS1N05PB311S	0.004
		NPN	Pre-cabled (L = 2 m)	XS1N05NB311	0.004
			M8 connector	XS1N05NB311S	0.015

⁽¹⁾ For a 5 m long cable add L1 to the reference; for a 10 m long cable add L2 to the reference. Example: XS1L04PA310 becomes XS1L04PA310L1 with a 5 m long cable.


Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range, general purpose Miniature, cylindrical, flush mountable Three-wire DC, solid-state output

Sensor type			XS1L04••••••S, XS1N05•••••S	XS1L04••••••, XS1N05••••••			
Product certifications			cULus, CE, UKCA				
Connection (1)	Connector		M8	_			
	Pre-cabled Length	m	-	2			
Operating zone	Ø 4 brass	mm	00.8				
	Ø 4 stainless steel	mm	00.6				
	Ø 5 brass	mm	00.8				
	Ø 5 stainless steel	mm	00.6	00.6			
Degree of protection	Conforming to IEC 60529		IP 67				
Storage temperature		°C	- 40+ 85				
Operating temperature		°C	-25+70				
Materials Case			Nickel plated brass or stainless steel 303				
Cable			PvR 3 x 0.11 mm ²				
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)				
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms				
Output state indication	LED		Yellow LED				
	Visibility		1 viewing port				
Rated supply voltage		٧	 524				
Voltage limits (including ri	ople)	٧	== 530				
Insulation class			0				
Current consumption, no-l	oad	mA	≤10				
Switching capacity	3-wire PNP/NPN	mA	≤ 100 with overload and short-circuit protection	on			
Voltage drop, closed state		٧	≤2				
Maximum switching freque	ency	kHz	5				
Delays	First-up	ms	≤5				
	Response	ms	≤0.1				
	Recovery	ms	≤ 0.1				

⁽¹⁾ Detection curves, see page 128



	e e	<u> </u>	тЮпОт		
Ø 4 XS1L04•••••	e≥2	e ≥ 12	e ≥ 3	d1 ≥ 4, h ≥ 0	
Ø 5 XS1N05•••••	e≥2	e ≥ 12	e ≥ 3	d1≥5, h≥0	

Tightening torque



Stainless steel A = 2.2 N.m.Brass A = 1.6 N.m

(values obtained with washers mounted)

Dimensions					
	Sensor	Pre-cabled		M8 connector	
		а	b	а	b
	Ø 4 XS1L04•••••	28	_	43	_
b b	Ø 5 XS1N05 •••••	28	24	43	24
a →					

XS range, basic sensors Cylindrical, standard range, flush and non flush mountable

Three-wire DC, solid-state output



Sensing distance (S	Function (n)	Output	Connection	Reference	Weight
mm					(kg)
	ded M8 x 1				
Three-wire	12-24 V, fl NO	ush mou	ntable Pre-cabled (L = 2 m)	XS108BLPAL2	0.035
	NO	FINE			
			Pre-cabled (L = 5 m)	XS108BLPAL5	0.10
			M8 connector	XS108BLPAM8	0.008
			M12 connector	XS108BLPAM12	0.01
		NPN	Pre-cabled (L = 2 m)	XS108BLNAL2	0.03
			M12 connector	XS108BLNAM12	0.01
Three-wire	12-24 V, n	on flush	mountable		
2.5	NO	PNP	Pre-cabled (L = 2 m)	XS208BLPAL2	0.03
			Pre-cabled (L = 5 m)	XS208BLPAL5	0.10
			M8 connector	XS208BLPAM8	0.008
			M12 connector	XS208BLPAM12	0.01
		NPN	Pre-cabled (L = 2 m)	XS208BLNAL2	0.03
Ø 12, thre	aded M12	c1			
	== 12-24 V, fl			V0440DI DAI 0	0.07
2	NO	PNP	Pre-cabled (L = 2 m)	XS112BLPAL2	0.070
			Pre-cabled (L = 5 m)	XS112BLPAL5	0.14
			M12 connector	XS112BLPAM12	0.01
		NPN	Pre-cabled (L = 2 m)	XS112BLNAL2	0.070
			M12 connector	XS112BLNAM12	0.01
	NC	PNP	Pre-cabled (L = 2 m)	XS112BLPBL2	0.070
			M12 connector	XS112BLPBM12	0.01
Three-wire	12-24 V, n	on flush	mountable		
ŀ	NO	PNP	Pre-cabled (L = 2 m)	XS212BLPAL2	0.070
			Pre-cabled (L = 5 m)	XS212BLPAL5	0.140
			M12 connector	XS212BLPAM12	0.01
		NPN	Pre-cabled (L = 2 m)	XS212BLNAL2	0.070
			Pre-cabled (L = 7 m)	XS212BLNAL7	0.18
			M12 connector	XS212BLNAM12	0.01
	NC	PNP	Pre-cabled (L = 2 m)	XS212BLPBL2	0.070
			Pre-cabled (L = 5 m)	XS212BLPBL5	0.140
		NPN	Pre-cabled (L = 2 m)	XS212BLNBL2	0.070

XS212BL••L•

XS212BL●●M12

XS range, basic sensors

Cylindrical, standard range, flush and non flush mountable

Three-wire DC, solid-state output, accessories











XS218BL••M12



XS218BL ...L


















Fixing access	ories (1)		
Description	For use with sensors	Reference	Weight kg
Fixing clamps	Ø 8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

Cabling accesso	ories (2)		
Description	Length of cable (m)	Reference	Weight kg
Pre-wired, straight, female connectors	5	XZCPV1141L5	0.210
M12 connectors, 4 pins PVC cable	10	XZCPV1141L10	0.390
re-wired, straight, female connectors	5	XZCPV0566L5	0.210
M8 connectors, 3 pins PVC cable	10	XZCPV0566L10	0.390

⁽¹⁾ See dimensions on page 83.

⁽²⁾ For other connection accessories, visit our website: www.telemecaniquesensors.com

Characteristics, schemes

Inductive proximity sensors

XS range, basic sensors Cylindrical, standard range, flush and non flush mountable Three-wire DC, solid-state output

Sensor type				XS1eeBLPeLe XS1eeBLNeLe	XS1eeBLPeMe XS1eeBLNeMe	XS2eeBLPeL XS2eeBLNeL	XS2eeBLPeMe XS2eeBLNeMe
Product certif	ications			cULus, UKCA, C€	ASTOODLING	AOZUEBLITUL	AOZOODEITONO
Connection		Pre-cabled		Length 2, 3 or 5 m, depending on model	_	Length 2, 5 or 7 m, depending on model	_
		Connector		-	M8 on Ø 8 M12 on Ø 8, Ø 12, Ø 18 and Ø 30	-	M8 on Ø 8 M12 on Ø 8, Ø 12 Ø 18 and Ø 30
Operating zor	ne (1)	Ø8	mm	01.2		02	
		Ø 12	mm	01.6		03.2	
		Ø 18	mm	04		06.4	
		Ø 30	mm	08		012	
Differential tra	avel		%	115 of effective sens	sing distance (Sr)		
Degree of pro	tection	Conforming to IEC 60529		IP 65 and IP 67			
Storage temp	erature		°C	- 40+ 85			
Operating ten	perature		°C	- 25+ 70			
Materials		Case		Nickel plated brass			
		Cable		PVC 3 x 0.14 mm ² except Ø 8: 3 x 0.11 mm ²	_	PVC 3 x 0.14 mm ² except Ø 8: 3 x 0.11 mm ²	_
Vibration resistance Conforming to IEC 60068-2-6				25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)			
Shock resistance Conforming to IEC 60068-2-27				50 gn, duration 11 ms			
Output state indication				Yellow LED, on rear	Yellow LED: 2 viewing ports at 180°	Yellow LED, on rear	Yellow LED: 2 viewing ports at 180°
Rated supply voltage				== 1224 with protec	tion against reverse po	olarity	
Voltage limits	(including ripple)		V	 1036			
Switching cap	acity		mA	≤ 200 with overload and short-circuit protection			
Voltage drop,	closed state		V	≤2			
Current consu	umption, no-load		mA	≤ 10			
Residual curr	ent, open state		mA	-			
Vlaximum swi	tching frequency	Ø 8	Hz	2500		2500	
		Ø 12	Hz	2500		1200	
		Ø 18	Hz	1200		500	
		Ø 30	Hz	500		300	
Delays	First-up		ms	≤ 15		≤ 15	
	Response	Ø8	ms	≤ 0.3		≤0.3	
		Ø 12	ms	≤ 0.1		≤ 0.1	
		Ø 18	ms	≤ 0.1		≤ 0.1	
		Ø 30	ms	≤ 0.1		≤0.2	
	Recovery	Ø8	ms	≤0.3		≤ 0.3	
	ŕ	Ø 12	ms	≤ 0.15		≤ 0.4	
		Ø 18	ms	≤ 0.3		≤1	
		Ø 30	ms	≤1		≤ 1.4	
Wiring so	chemes						
Connector		Pre-cabled	PNP			NPN	
M8 1 3	M12	BU: Blue BN: Brown BK: Black	BN/1 PNP BU/3	BK/4 (NO) BK/2 (NC)		BN/1	+ NO) NC)

For M8 connectors, NO and NC outputs on terminal 4

⁽¹⁾ Detection curves, see page 141.

XS range, basic sensors


Cylindrical, standard range, flush and non flush mountable

Three-wire DC, solid-state output

Minimum mounting distances (mm)

Sensors		Side by side	Face to face	Facing a metal object	Mounted in a metal support
Ø 8 flush mountable	XS108BL	e≥3	e ≥ 18	e ≥ 4,5	d ≥ 8 h ≥ 0
Ø 8 non flush mountable	XS208BL	e ≥ 10	e≥30	e ≥ 7,5	d≥24 h≥5
Ø 12 flush mountable	XS112BL	e ≥ 4	e ≥ 24	e ≥ 6	d≥12 h≥0
Ø 12 non flush mountable	XS212BL	e≥16	e ≥ 48	e ≥ 12	d≥36 h≥8
Ø 18 flush mountable	XS118BL	e≥10	e ≥ 60	e ≥ 15	d≥18 h≥0
Ø 18 non flush mountable	XS218BL	e≥16	e≥96	e ≥ 24	d≥54 h≥16
Ø 30 flush mountable	XS130BL	e≥20	e≥120	e ≥ 30	d≥30 h≥0
Ø 30 non flush mountable	XS230BL	e ≥ 60	e ≥ 180	e ≥ 45	d≥90 h≥30


Dimensions



		Flus	Flush mountable in metal							
Sensors		Pre-d (mm	cabled)	M8 c (mm	onnector)	M12 (mm	connector			
		а	b	а	b	а	b			
Ø8	XS108BL	42	33	50	34	61	40			
Ø 12	XS112BL	44	31		_	55	34			
Ø 18	XS118BL	53	41			64	43			
Ø 30	XS130BL	- 	44			68	47			

		Non	Non flush mountable in metal									
Sensors			Pre-cabled (mm)			M8 connector (mm)			M12 connector (mm)			
		а	b	С	а	b	С	а	b	С		
Ø8	XS208BL	42	29	4	50	32	4	61	36	4		
Ø 12	XS212BL	44	26	5		-	-	55	29	5		
Ø 18	XS218BL	53	33	8		-	-	64	35	8		
Ø 30	XS230BL	57	32	13		-	-	68	34	13		

Inductive proximity sensors
XS range, basic sensors
Cylindrical, increased range, flush mountable
Three-wire DC, solid-state output











Sensor	s, 3-wir	e 12	224 V		
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Ø 8, thread	ded M8 x 1				
2.5	NO	PNP	Pre-cabled (L = 2 m)	XS108BHPAL2	0.070
			M8 connector	XS108BHPAM8	0.030
			M12 connector	XS108BHPAM12	0.050
		NPN	Pre-cabled (L = 2 m)	XS108BHNAL2	0.070
			M8 connector	XS108BHNAM8	0.030
	N/C	PNP	Pre-cabled (L = 2 m)	XS108BHPBL2	0.070
			M8 connector	XS108BHPBM8	0.030
			M12 connector	XS108BHPBM12	0.050
Ø 12, threa	aded M12 x	:1			
4	NO	PNP	Pre-cabled (L = 2 m)	XS112BHPAL2	0.080
			Pre-cabled (L = 5 m)	XS112BHPAL5	0.150
			M12 connector	XS112BHPAM12	0.025
		NPN	Pre-cabled (L = 2 m)	XS112BHNAL2	0.080
			M12 connector	XS112BHNAM12	0.025
	N/C	PNP	Pre-cabled (L = 2 m)	XS112BHPBL2	0.080
			M12 connector	XS112BHPBM12	0.025
		NPN	Pre-cabled (L = 2 m)	XS112BHNBL2	0.080
			M12 connector	XS112BHNBM12	0.025
Ø 18, threa	aded M18 x	:1			
8	NO	PNP	Pre-cabled (L = 2 m)	XS118BHPAL2	0.105
			Pre-cabled (L = 5 m)	XS118BHPAL5	0.175
			M12 connector	XS118BHPAM12	0.035
		NPN	Pre-cabled (L = 2 m)	XS118BHNAL2	0.105
			M12 connector	XS118BHNAM12	0.035
	N/C	PNP	Pre-cabled (L = 2 m)	XS118BHPBL2	0.105
			M12 connector	XS118BHPBM12	0.035
		NPN	Pre-cabled (L = 2 m)	XS118BHNBL2	0.105
			M12 connector	XS118BHNBM12	0.035
Ø 30, threa	aded M30 x	1.5			
15	NO	PNP	Pre-cabled (L = 2 m)	XS130BHPAL2	0.165
			Pre-cabled (L = 5 m)	XS130BHPAL5	0.235
			M12 connector	XS130BHPAM12	0.075
		NPN	Pre-cabled (L = 2 m)	XS130BHNAL2	0.165
			M12 connector	XS130BHNAM12	0.075
	N/C	PNP	Pre-cabled (L = 2 m)	XS130BHPBL2	0.165
			M12 connector	XS130BHPBM12	0.075
		NPN	Pre-cabled (L = 2 m)	XS130BHNBL2	0.165
			M12 connector	XS130BHNBM12	0.075

Fixing accessories			
Description	For use with sensors	Reference	Weight (kg)
Fixing clamps	Ø 8	XSZB108	0.006
	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020
Connection accesso	ries (1)		
Description	Cable length m	Reference	Weight (kg)
Pre-wired, straight,	5	XZCPV1141L5	0.210
female connectors M12 connectors 4-pin, PVC cable	10	XZCPV1141L10	0.390
Pre-wired, straight,	5	XZCPV0566L5	0.210
female connectors M8 connectors 3-pin, PVC cable	10	XZCPV0566L10	0.390

(1) For other connection accessories, visit our website: www.telemecaniquesensors.com

Characteristics, connections, setting-up, dimensions

Inductive proximity sensors

XS range, basic sensors Cylindrical, increased range, flush mountable Three-wire DC, solid-state output

Sensor type			XS100BHP0L0 XS100BHN0L0	XS100BHP0M0 XS100BHN0M0			
Product certifications			cULus, UKCA, CE				
Connection	Pre-cabled		Cable length: 2 or 5 m, depending on model	-			
	Connector		-	M8 or M12 connector, depending on mode			
Operating zone (1)	Ø8	mm	02				
	Ø 12	mm	03.2				
	Ø 18	mm	06.4				
	Ø 30	mm	012				
Differential travel		%	115 of effective sensing distance (Sr)				
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67				
Storage temperature		°C	-40+85				
Operating temperature		°C	°C -25+70				
Materials	Case		Nickel plated brass				
Cable			PVC (number and c.s.a. of wires: 3 x 0.14 mm ²)				
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)				
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms				
Output state indication			Yellow LED, on rear	Yellow LED, 2 viewing ports at 180°			
Rated supply voltage		V	== 1224 with protection against reverse po	plarity			
Voltage limits (including ripple)		V	 1036				
Switching capacity		mA	≤ 200 with overload and short-circuit protect	ion			
Voltage drop, closed state		V	≤2				
Current consumption, no-load		mA	≤10				
Maximum switching frequency	Ø8	Hz	2500				
	Ø 12	Hz	950				
	Ø 18	Hz	700				
	Ø 30	Hz	200				
Delays	First-up	ms	≤15				
	Response	ms	≤0.3				
	Recovery	ms	≤0.3				
Connections							


M8



BU: Blue BN: Brown BK: Black

BN/1 PNP \Diamond





For M8 connectors, NO and NC outputs on terminal 4

Setting-up precautions

Minimum mounting distances (mm)










Sensors		Side by side	Face to face	Facing a metal object	Mounted in a metal support
Ø8	XS108BH	e≥5	e ≥ 30	e ≥ 8	_
Ø 12	XS112BH	e ≥ 8	e ≥ 50	e ≥ 12	_
Ø 18	XS118BH	e ≥ 16	e ≥ 100	e ≥ 25	_
Ø 30	XS130BH	e ≥ 30	e ≥ 180	e ≥ 30	h≥2

(1) See detection curves on page 139.



Fixing clamp dimensions XS2	ZB108, XSZ	ZBB112, XSZ	BB118	and XSZ	BB130			
38.3 ≥ Ø			а	a1	b	b1	b2	Ø
	Ø 8	XSZB108	19.9	14.5	14	12.5	7.5	8
25 12	Ø 12	XSZB112	21.9	14.5	16	15.5	8.5	12
(1) 3.5	Ø 18	XSZB118	26	15.7	22.3	20.1	11.5	18
	Ø 30	XSZB130	39	21.7	35.5	31	18.5	30
4 22 8	(1) 2 elong	ated holes Ø 4 x 8	mm					

Inductive proximity sensors XS range application

Adjustable range sensors
Cylindrical, flush mountable using teach mode (1)
Three-wire DC, solid-state output



Ø 12, threaded M12 x 1									
	Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)			
	5	NO	PNP	Remote M12 connector on 0.15 m flying lead	XS612B2PAL01M12	0.100			
		NC	PNP	Remote M12 connector	XS612B2PBL01M12	0.100			

Ø 18, threa	aded M1	18 x 1			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
9	NO	PNP	Remote M12 connector on 0.15 m flying lead	XS618B2PAL01M12	0.140
	NC	PNP	Remote M12 connector on 0.15 m flying lead	XS618B2PBL01M12	0.140

Ø 30, threaded M30 x 1.5								
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)			
18	NO	PNP	Remote M12 connector	XS630B2PAL01M12	0.220			



Accessories (2)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For further information on flush or non-flush mountable sensors using teach mode, see page 22. (2) For further information, see page 120.

Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range application Adjustable range sensors Cylindrical, flush mountable using teach mode Three-wire DC, solid-state output


Sensor type				XS6eeB2eeL01M12			
Product certifications				cULus, CE, UKCA			
Connection				Remote M12 connector on 0.15 m flying lead			
Sensing distance	Ø 12	Nominal sensing distance (Sn)	mm	05 non-flush mounted / 03.4 flush mounted			
and adjustment		Precision adjustment zone	mm	1.75 non-flush mounted / 1.73.4 flush mounted			
zone	Ø 18	Nominal sensing distance (Sn)	mm	09 non-flush mounted / 06 flush mounted			
		Precision adjustment zone	mm	39 non-flush mounted / 36 flush mounted			
	Ø 30	Nominal sensing distance (Sn)	mm	018 non-flush mounted / 011 flush mounted			
		Precision adjustment zone	mm	618 non-flush mounted / 611 flush mounted			
Differential travel			%	115 of effective sensing distance (Sr)			
Degree of protection Conforming to IEC 60529			IP 67				
Storage temperatur	е		°C	- 40+ 85			
Operating temperature		°C	-25+70				
Materials	Case			Nickel plated brass			
	Remote	control		PBT			
	Cable			PvR - Ø 4.2 mm			
Vibration resistance Conforming to IEC 60068-2-6			25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)				
Shock resistance Conforming to IEC 60068-2-27			50 gn, duration 11 ms				
Indicators	Output s	tate		Yellow LED			
	Supply o	n and teach mode		Green LED			
Rated supply voltag	je		٧	== 1224 with protection against reverse polarity			
Voltage limits (inclu	ding ripple	9)	٧	 1036			
Insulation class							
Switching capacity			mA	≤ 100 with overload and short-circuit protection			
Voltage drop, close	d state		٧	≤2			
Current consumpti	on, no-load	1	mA	≤10			
Maximum switching	g frequenc	у	Hz	1000			
Delays	First-up		ms	≤10			
	Respons	e	ms	≤ 0.3			
	Recover		ms	≤0.7			

Wiring schemes

Connector










Setting-up


Minimum mounting distances (mm)







Face to face						
flush mounted	not flush mounted					
e≥50	100					
e ≥ 100	200					
e ≥ 180	360					



Facing a metal object


Dimensions

XS6

Ø 12

Ø 18

Ø 30



(1) Teach mode button (2) LED

	Conn	ector (m	m)		
	а	b	С		
Ø 12	59	42	5		
Ø 18	64	44	8		
Ø 30	62.6	41	13		

Functions, principle, setting-up


Inductive proximity sensors


XS range application

Sensors for rotation monitoring, slip detection, shaft overload detection Cylindrical form

Example:

Coupling breakage monitoring





Metallic material

Functions

These self-contained rotation speed monitoring sensors have the special feature of incorporating, in the same case, the pulse sensing and processing electronics as well as the output switching amplifier that are required to establish an integrated rotation monitoring device.

The unit provides an economical solution for detecting slip, belt breakage, drive shaft shear and overloading, etc., in the following applications: conveyor belts, bucket elevators, Archemedian screws, grinders, crushers, pumps, centrifugal driers, mixers, etc.

Operating principle

The output signal of this type of sensor is processed by an impulse comparator incorporated in the sensor. The impulse frequency Fc generated by the moving part to be monitored is compared to the frequency Fr preset on the sensor. The output switching circuit of the sensor is in the closed state for Fc > Fr and the open state for Fc < Fr.

Sensors XSAV are particularly suitable for the detection of underspeed: when the speed of the moving part Fc falls below a preset threshold Fr, this causes the output circuit of the sensor to switch off

Note: Following power-up, the operational status of the sensor is subject to a delay of 9 seconds in order for the moving part being monitored to run-up to its nominal speed. During this time, the output of the sensor remains in the closed state.


Adjustment of frequency threshold

- Adjustment of sensor's frequency threshold: using potentiometer, 15 turns approximately.
- To increase the frequency threshold: turn the adjustment screw clockwise (+)
- To decrease the frequency threshold: turn the adjustment screw anti-clockwise (-).

1: Potentiometer	Diameter of sensor				
2: LED		а	b	С	
3: Metal target	M30	46 mm	30 mm	60 mm	

Potentiometer adjustment curves (for XSAV1ullet801, 2-wire \sim or \equiv sensors)

Low speed version (6...150 impulses/minute) High speed version (120...3000 impulses/minute)




Fixing nut tightening torque: < 50 N.m/442.53 lb-in

References, characteristics, dimensions, schemes

Inductive proximity sensors

XS range application Sensors for rotation monitoring, slip detection, shaft overload detection Cylindrical form

Flush mountable in metal





Lengths (mm): a = Overall b = Threaded section


a = 81 b = 67 $\emptyset = M30$


			DC	DC	AC/DC	AC/DC
Nominal sens	ing distance (Sn)		10 mm	10 mm	10 mm	10 mm
Adjustable fre	equency range		6150 impulses/min	1203000 impulses/min	6150 impulses/min	1203000 impulses/min
Reference	References					
3-wire ==	PNP/NC		XSAV11373	XSAV12373	_	_
2-wire	or ∼ / NC		_	_	XSAV11801	XSAV12801

Z-WII C	01 07140	
Weight (kg)		0.300

Characteristics						
Product certifications		cULus, CCC, C€, UKCA				
Connection		Pre-cabled, 3 x 0.34 mm ² , length 2 m (1)	Pre-cabled, 2 x 0.34 mm ² , length 2 m (1)			
Degree of protection conforming to IEC 60529		P 67				
Operating zone	mm)8				
Repeat accuracy	%	3 of Sr				
Differential travel	%	315 of Fr				
Operating temperature	°C	- 25+ 70				
Output state indication		Red LED				
Rated supply voltage	٧	== 1248 with protection against reverse polarity	~ 24240 (50/60 Hz) or 24210			
Voltage limits (including ripple)	٧	1058	∼ or 20264			
Insulation class						
Switching capacity	mA	≤ 200 with overload and short-circuit protection	∼5350 or 5200 (2)			
Voltage drop, closed state	٧	≤1.8	≤ 5.7			
Residual current, open state	mA	_	≤1.5			
Current consumption, no-load	mA	≤15	-			
Maximum switching frequency		6000 impulses/min (for XSAV11•••); 48,000 impulses/min (for XSAV12•••)				
"Run-up" delay following power-up		9 seconds ± 20 % + 1/Fr (3)				

Wiring schemes





⁽¹⁾ For a 5 m long cable add L05 to the reference, for a 10 m long cable add L10 to the reference. Example: XSAV11373 becomes XSAV11373L05 with a 5 m long cable.


⁽²⁾ These sensors do not incorporate overload or short-circuit protection and therefore, it is essential to connect a 0.4 A "quick-blow" fuse in series with the load, see page 120

⁽³⁾ For a sensor without a "run-up" delay following power-up, replace XSAV1 in the reference by XSAV0. Example: XSAV11801 becomes **XSAV01801** without a "run-up" delay. For a reduced "run-up" delay of 3 s, replace XSAV1 in the reference by XSAV3.

XS range application


Sensors for rotation monitoring, slip detection and shaft overload detection, with teach mode

Operating principle and applications



- These inductive proximity sensors are designed for monitoring rotational speed or the speed of the flow of objects to be protected or monitored.
- They operate on the principle of comparing a speed threshold preset by the operator against the instantaneous measurement of the speed of the moving object to be protected.
- They provide a simple, economical solution for detecting slip, belt breakage, coupling breakage and overload, etc.
- They are widely used in grinder/crusher, mixer, pump, centrifugal driver, conveyor belt, bucket elevator, Archimedean screw, etc. type applications.

Installation and setting-up



Setting-up and positioning the sensor

- In the positioning phase, the XS9 sensor can operate as a standard inductive sensor (Schneider Electric patent).
- Operation in inductive mode enables validation of reliable detection of all the moving objects to be monitored.
- Using this system, the positioning is therefore made 100 % reliable and can be checked at any time without altering the settings of the sensor.


≥3s Slow flash



- The normal or reference speed of the moving object (1) to be monitored is adjusted by simply pressing the teach mode button (2) and is then validated by the display LED.
- ☐ If in doubt, the sensor can be reset at any time to the factory settings.
- (1) To allow the moving object to reach its normal speed (machine inertia), the sensor holds its output closed for 9 seconds.
- (2) The sensor's default drop-out underspeed corresponds to the preset speed 30 %. Example: If the preset speed is 1000 rpm, the sensor drops out on underspeed when the speed of the moving object drops below $1000 - (1000 \times 0.3) = 700 \text{ rpm}$.
 - 20 %, 11 % and 6 % thresholds can be obtained by pressing the teach mode button.

Setting-up


Minimum mounting distances (mm)



Type XS9E XS9C

 $e \ge 40$


 $e \ge 60$



e ≥ 80

e ≥ 120

Dimensions XS9E, XS9C



Type	Α	В	С	D	E	F	
XS9E	14	26	13	8.8	20	3.5	
XS9C	14	40	15	9.8	33	4.5	

References, characteristics, schemes, accessories

Inductive proximity sensors

XS range application

Sensors for rotation monitoring, slip detection and shaft overload detection, with teach mode

Flush mountable in metal Sensor type






Nominal sensing distance (Sn)			10 mm		15 mm	
Adjustable frequency ra	nge		66000 impulses/min			
References						
3-wire	PNP/NC				_	
2-wire	or ∼ / NC		_	XS9E11RMBL01U20	XS9C11RMBL01U20	
Weight (kg)			0.040	0.040	0.060	
Characteristics						
Product certifications			cULus, C€, UKCA			
Connection			Remote M12 connector on 0.15 m flying lead	Remote 1/2"-20UNF connector	r on 0.15 m flying lead	
Operating zone		mm	08	08	012	
Degree of protection	Conforming to IEC 60529		IP 67			
Storage temperature		°C	- 40+ 85			
Operating temperature		°C	- 25+ 70			
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)			
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			
Indicators	Output state		Yellow LED			
	Supply on		Green LED			
Rated supply voltage		٧	1224			
Voltage limits (including	,	٧	 1036	∼ or === 20264		
Insulation class	===					
	$\overline{\sim}$		1			
Switching capacity		mA	≤ 100 (1)	∼ or 5100 (2)	5200, ∼ 5300(2)	
Voltage drop, closed sta	te	٧	≤2	≤2 ≤5.5		
Residual current, open s		mA	≤ 100	≤ 1.5		
Current consumption, n	o-load	mA	≤ 10	_		
Maximum switching free	luency		48,000 impulses/min			
"Run-up" delay followin	g power-up		9 seconds + 1/Fr			

Wiring schemes


Connector 1/2"-20UNF












Accessory (1)



Description	Reference
Remote control fixing clamp	XSZBPM12

0.015

(1) For accessories, see page 120.

Weight

⁽¹⁾ With overload and short-circuit protection. (2) It is essential to connect a 0.4 A "quick-blow" fuse in series with the load.


XS range application

Sensors with analogue output signal 0...10 V (1) or 4...20 mA

For position, displacement and deformation control/monitoring

Functions

Example: Sorting parts




These analogue output proximity sensors are solid-state sensors designed for monitoring displacement. They are not measuring sensors. They are suitable for use in many sectors, particularly for applications involving:


- deformation and displacement monitoring,
- vibration amplitude and frequency monitoring,
- control of dimensional tolerances,
- position control,
- concentricity or eccentricity monitoring.


Operating principle


The operating principle of the sensor is that of a damped oscillator. The degree of damping will depend on the distance of an object from the sensing face. The sensor will sense the distance and produce an output current with a value directly proportional to this distance.


Output curves 4..0.20 mA, 2-wire connection
















Output curves 0...10 V, 3-wire connection








Wiring schemes


2-wire connection



	Output current	Load impedance value
12 V	420 mA	R ≤ 8.2 Ω
24 V	420 mA	R ≤ 470 Ω

Ensure a minimum of 10 V between the + and the - (terminal 3) of the sensor.

3-wire connection



	Output current	Load impedance value	Output voltage	Load impedance value
24 V	010 mA	R ≤ 1500 Ω	010 V	R = 1000 Ω
48 V	010 mA	R ≤ 3300 Ω	010 V	R = 1000 Ω
				4)

Ensure a minimum of 5 V between the + and the sensor output (terminal 4).

(1) Voltage range only obtained with a load impedance of 1000 Ω .

References: pages 83 to 85

Characteristics: pages 83 to 85



XS range application

Sensors with analogue output signal 0...10 V (1) or 4...20 mA

For position, displacement and deformation control/monitoring

Sensor type		Flush mountable in metal	Non-flush mountable in metal			
b a	I					
Lengths: a = Overall b = Threaded section	mm	a = 50 b = 42	a = 50 b = 42	a = 54 b = 42		
		Metal case	Plastic case	Plastic case		
Nominal sensing distance (Sn)	mm	2	4	4		
References						
3-wire Output 010 V (2)		_	-	XS4P12AB110 (4)		
2-wire Output 420 mA (2)		XS1M12AB120 (3) (4)	XS4P12AB120 (4)	_		
Weight	kg	0.075	0.065	0.065		
Characteristics	ı		I			
Product certifications		cULus, C€, UKCA				
Connection		Pre-cabled, PvR 3 x 0.34 mm², length 2 m				
Degree of protection Conforming to IEC 60529		IP 67				
Operating zone	mm	0.22	0.44	0.44		
Repeat accuracy	%	±3				
Linearity error	mA	±2 ±1V				
Ambient air temperature	°C	For operation: - 25+70				
Rated supply voltage	٧	 1224	 1224	 2448		
Voltage limits (including ripple)	V	 1036	 1036	 1558		
Insulation class						
Output current drift %		≤ 10 (ambient temperature: - 25+ 70 °C)				
Current consumption, no-load	mA	4				
Maximum operating rate	Hz	1500				
-		(1) Voltage range only obtained with a loa	ad impedance of 1000 Ω .			

- (1) Voltage range only obtained with a load impedance of 1000 Ω . (2) Output current range Is, see page 82. (3) Add D at the end of reference for M12 connector version

- (4) For 5 m cable, add L1 at the end of the reference

Setting-up				
Minimum mounting distances (mm)	Side by side	Face to face	Facing a metal object	Mounted in a metal support
	e e	2 2	₽	d d
XS1M12AB120 flush mountable	e≥4	e≥24	e≥6	d≥12, h≥0
XS4P12AB110 non-flush mountable	e ≥ 16	e ≥ 48	e ≥ 12	d ≥ 36, h ≥ 8
XS4P12AB120 non-flush mountable	e ≥ 16	e ≥ 48	e ≥ 12	d≥36, h≥8
Fixing nut tightening torque	< 6 N.m (metal case), < 2 N.n	n (plastic case)		
Other versions	Please consult our Customer	Care Centre		

XS range application Sensors with analogue output signal 0...10 V (1) or 4...20 mA

Sensor type Flush mountable in metal Non-flush mountable in metal Lengths (mm): mm a = 53a = 41a = 41 a = Överall b = 44b = 26b = 26b = Threaded section c = 0c = 8c = 8c = For non-flush mountable sensors Metal case Plastic case Plastic case Nominal sensing distance (Sn) 5 8 8 mm References XS4P18AB110 (4) Output 0...10 V (2) 3-wire ---2-wire === Output 4...20 mA (2) XS1M18AB120 (3) (4) XS4P18AB120 (4) Weight 0.120 0.080 0.080 kg **Characteristics** Product certifications cULus, C€, UKCA Pre-cabled, PvR 3 x 0.34 mm², length 2 m Connection Degree of protection **IP 67** Conforming to IEC 60529 Operating zone mm 0.5...5 0.8...8 0.8...8 Repeat accuracy % ± 3 Linearity error mΑ ±1V Ambient air temperature °C For operation: - 25...+ 70 ٧12....2412....24 ... 24...48 Rated supply voltage Voltage limits (including ripple) ٧ --- 10...36 ... 10...36 --- 15...58 Insulation class ≤ 10 (ambient temperature: - 25...+ 70 °C) Output current drift % Current consumption, no-load mΑ 4 500 Maximum operating rate Ηz


- (1) Voltage range only obtained with a load impedance of 1000 Ω .
- (2) Output current range Is, see page 82. (3) Add D at the end of reference for M12 connector version
- (4) For 5 m cable, add L1 at the end of the reference


Setting-up


Minimum mounting distances (mm) Side by side Face to face


Facing a metal object

Mounted in a metal support









XS1M18AB120 flush mountable	e ≥ 10	e ≥ 60	e ≥ 15	d≥18, h≥0
XS4P18AB110 non-flush mountable	e ≥ 32	e ≥ 96	e ≥ 24	d≥54, h≥16
XS4P18AB120 non-flush mountable	e≥32	e≥96	e≥24	d≥54, h≥16

Fixing nut tightening torque

< 15 N.m (metal case), < 5 N.m (plastic case)

Other versions

Please consult our Customer Care Centre.

XS range application Sensors with analogue output signal 0...10 V (1) or 4...20 mA

Non-flush mountable in metal Flush mountable in metal Sensor type Lengths: $\mathbf{m}\mathbf{m}$ a = 50 a = Overall a = 53b = Threaded section b = 42 b = 32 b = 32 c = For non-flush mountable sensors c = 0c = 13 Plastic case Plastic case Metal case Nominal sensing distance (Sn) 10 15 15 mm References XS4P30AB110 3-wire ---Output 0...10 V (2) XS1M30AB120 (3) XS4P30AB120 2-wire ---Output 4...20 mA (2) Weight 0.200 0.100 0.100 kg **Characteristics Product certifications** cULus, C€, UKCA Connection Pre-cabled, PvR 3 x 0.34 mm², length 2 m Degree of protection Conforming to IEC 60529 IP 67 1...10 Operating zone 1.5...15 1.5...15 mm ± 3 Repeat accuracy % Linearity error ±2 ± 1 V mA °C For operation: - 25...+ 70 Ambient air temperature

(1) Voltage range only obtained with a load impedance of 1000 Ω .

....12....24

.... 10...36

---- 24...48

== 15...58

- (2) Output current range Is, see page 82.
- (3) Add D at the end of reference for M12 connector version

	()				
Setting-up					
Minimum mounting distances (mm)	Side by side	Face to face	Facing a metal object	Mounted in a metal support	
	e	€ +	₽ P	d →	
XS1M30AB120 flush mountable	e≥20	e ≥ 120	e ≥ 30	d≥30, h≥0	
XS4P30AB110 non-flush mountable	e ≥ 60	e ≥ 180	e ≥ 45	d≥90, h≥30	
XS4P30AB120 non-flush mountable	e≥60	e ≥ 180	e≥45	d≥90, h≥30	
Fixing nut tightening torque	< 40 N.m (metal case), < 20 N.m (plastic case)				
Other versions	Please consult our Customer Care Centre.				

Rated supply voltage

Insulation class
Output current drift

Voltage limits (including ripple)

Ambient temperature: - 25...+ 70 °C

Current consumption, no-load

Maximum operating rate

ν

٧

%

mA 4

Ηz

....12....24

--- 10...36

≤10

300

Functions, principle, curves, schemes

Inductive proximity sensors

XS range application

Sensors with analogue output signal 0...10 V (1) For position, displacement and deformation control/monitoring

Functions

These analogue output proximity sensors are solid-state sensors designed for monitoring displacement. They are not measuring sensors.

They are suitable for use in many sectors, particularly for applications involving:


- ☐ deformation and displacement monitoring,
- □ vibration amplitude and frequency monitoring,
- □ control of dimensional tolerances,
- □ position control,
- □ concentricity or eccentricity monitoring.

Operating principle


The operating principle of the sensor is that of a damped oscillator. The degree of damping will depend on the distance of an object from the sensing face. The sensor will sense the distance and produce an output current with a value directly proportional to this distance.

Output curves 0...10 V, 3-wire connection


XS9F




XS9E



XS9C



XS9D



Wiring schemes

Connector


M8

M12

Pre-cabled

BN: Brown BU: Blue BK: Black

3-wire connection



	Output current	Load impedance value	Output voltage	Load impedance value
24 V	010 mA	R ≤ 1400 Ω	010 V	$R = 1000 \Omega$

Note: Ensure a minimum of 5 V between the + (terminal 1) and the sensor output (terminal 4).

(1) Voltage range only obtained with a load impedance of 1000 Ω .

References, characteristics, dimensions, setting-up

Inductive proximity sensors

XS range application

Sensors with analogue output signal 0...10 V (1) For position, displacement and deformation control/monitoring

Flush mountable in metal










Nominal sensing distar	nce (Sn)	mm	10	15	
References					
3-wire 010 V	Pre-cabled (L = 2 m) (2)		XS9E111A1L2	XS9C111A1L2	
Weight		kg	0.075	0.095	
Characteristics					
Product certifications			cULus, CE, UKCA, ECOLAB		
Connection	Pre-cabled		PvR 3 x 0.34 mm ² , length 2 m for XS9•111A•L	2	
Operating zone		mm	110	215	
Degree of protection Conforming to IEC 60529	Pre-cabled 9		IP 68		
Storage temperature		°C	-40+85		
Operating temperature		°C	-25+70		
Materials			PBT case		
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			No		
Rated supply voltage		٧	 24		
Voltage limits (includin	g ripple)		 1536		
Insulation class					
Repeat accuracy		%	±3		
Linearity error		٧	±1		
Current consumption,	no-load	mA	≤ 4 with overload and short-circuit protection		
Maximum operating fre	equency	Hz	1000		
Output current drift		%	≤ 10 (throughout the operating temperature range)		
B					

Dimensions





Setting-up (Minimum mounting distances (mm))

Side by side Type XS9E XS9C


Type XS9E

XS9C









e ≥ 30 e ≥ 45

⁽²⁾ For a 5 m long cable replace L2 by L5, for a 10 m long cable replace L2 by L10. Example: XS9C111A1L2 becomes XS9C111A1L5 with a 5 m long cable.





⁽¹⁾ Voltage range only obtained with a load impedance of 1000 Ω .

Functions. principle, curves, schemes

Inductive proximity sensors

XS range application

Sensors with analogue output signal 4...20 mA For position, displacement and deformation control/monitoring

Functions

These analogue output proximity sensors are solid-state sensors designed for monitoring displacement. They are not measuring sensors.

They are suitable for use in many sectors, particularly for applications involving:

- □ deformation and displacement monitoring,
- □ vibration amplitude and frequency monitoring,
- □ control of dimensional tolerances,
- □ position control,
- □ concentricity or eccentricity monitoring.


Operating principle


The operating principle of the sensor is that of a damped oscillator. The degree of damping will depend on the distance of an object from the sensing face. The sensor will sense the distance and produce an output current with a value directly proportional to this distance.

Output curves 4...20 mA, 2-wire connection


Sensor - object distance (mm)

XS9F






XS9E




XS9C

Sn = 2...15 mm



XS9D

Sn = 5...40 mm



Wiring schemes


Connector

Pre-cabled



BN: Brown BU: Blue BK: Black

2-wire connection



	Output current	Load impedance value
12 V	420 mA	R ≤ 8.2 Ω
24 V	420 mA	R ≤ 470 Ω

Note: Ensure a minimum of 10 V between the + (terminal 1) and - (terminal 3) of the sensor.

References, characteristics, dimensions, setting-up

Inductive proximity sensors

XS range application

Sensors with analogue output signal 4...20 mA For position, displacement and deformation control/monitoring

Sensor type



Nominal sensing distance (Sn)

Flush mountable in metal



10

mm




15



40

References						
2-wire 	Pre-cabled (L = 2 m) (1)		XS9E111A2L2	XS9C111A2L2	XS9D111A2L2	
420 mA	Connector		-	-	XS9D111A2M12	
Weight	Pre-cabled (L = 2 m)	kg	0.075	0.095	0.340	
	Connector	kg	-	-	0.320	
Characteristics						
Product certifications			cULus, (€, UKCA, ECOLAB			
Connection	Pre-cabled		PvR 3 x 0.34 mm ² , length 2 m			
	Connector		-		M12	
Operating zone		mm	110	215	540	
Degree of protection	Pre-cabled		IP 68			
Conforming to IEC 6052	9 Connector		IP 67			
Storage temperature		°C	- 40+ 85			
Operating temperature	•		- 25+ 70			
Materials			PBT case			
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10) to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms			
Output state indication	1		No			
Rated supply voltage		٧	 1224			
Voltage limits (includin	g ripple)	V	 1036			
Insulation class						
Repeat accuracy		%	±3			
Linearity error		mA	±2			
Current consumption,	no-load	mA	≤ 4 with overload and short-circ	≤ 4 with overload and short-circuit protection		
Maximum operating fre	equency	Hz	1000		100	
Output current drift		%	≤ 10 (throughout the operating	temperature range)		
Dimensions		•				


Dimensions




Type	A (L2)	A (M12)	В	С	D	Ε	F	
XS9E	14	-	26	13	8.8	20	3.5	
XS9C	14	_	40	15	9.8	33	4.5	
XS9D	23	14	80	26	16	65	5.5	

Setting-up (Minimum mounting distances (mm))

Type XS9E XS9C XS9D





e ≥ 72 e ≥ 110 e ≥ 300

Facing a metal object

e ≥ 30 e ≥ 45 e ≥ 120

⁽¹⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Example: XS9E111A2L2 becomes XS9E111A2L5 with a 5 m long cable.

XS range application

Sensors with analogue output signal 0...10 V (1) or 4...20 mA. Plastic case, 40 x 40 mm front face 5-position turret head

Sensor type		Non-flush mountable in metal	
Dimensions	mm	40 x 40 x 70	40 x 40 x 117






Nominal sensing dista	nce (Sn)		mm	25		
References						
3-wire	010 V ou	itput (1)		XS9C2A2A1M12	-	
2-wire	420 mA	output		XS9C2A2A2M12	XS9C4A2A2P20 (2)	
				XS9C4eeeP20 sensors are available with an ISO M20 cable entry and can be supplied with a PG 13.5 (e.g. XS9C4A2A1G13) or a 1/2" NPT (e.g. XS9C4A2A2N12) cable entry: please consult our Customer Care Centre for more information.		
Weight			kg	0.149	0.244	
Characteristics						
Product certifications				cULus, C€, UKCA		
Conformity to standard	s			IEC 60947-5-2 and IEC 60947-5-7		
Connection				M12 connector (4-pin)	Screw terminals, clamping capacity 3 x 1.5 mm ² / 3 x 16 AWG	
Operating zone			mm	227		
Linearity error			%	<3		
Repeat accuracy			%	<3		
Output current drift			%	<5		
Degree of protection	Conforming to DIN 40050	IEC 60529 and		IP 65, IP 67 and IP 69K		
Temperature	Storage		°C	- 40+ 85		
	Operation (3)		°C	- 25+ 70		
Material		Case		PBT		
Vibration resistance	Conforming to	IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 1055 Hz)		
Shock resistance	Conforming to	IEC 60068-2-27		50 gn for 11 ms		
Indicators	Output state (a	llignment aid)		Yellow LED		
Rated supply voltage		420 mA	٧	== 1224 with protection against reverse polar	rity	
		010 V	٧	== 24 with protection against reverse polarity		
Voltage limits (includin	g ripple)	420 mA	٧	 1236		
		010 V	٧	== 1536		
Insulation class						
Current consumption,	no-load	3-wire ===	mA	< 4		
Delays		First-up	ms	< 7		
		Response	ms	< 6		
		Recovery	ms	< 6		

Analogue outputs 4-20 mA and 0-10 V

XS9C2A2A2M12 and XS9C4A2A2P20

Sn = 2...25 mm 22 20 18 16 14 12 10 8 6 4 2 Output current (mA) 0 2 4 6 8 10 12 14 16 18 20 22 24 26 28 30 Sensing distance (mm)

XS9C2A2A1M12



⁽¹⁾ Voltage range only obtained with a load impedance of 1000 Ω .

⁽²⁾ These sensors are supplied without a cable gland. An adaptable PG 13.5 cable gland is available (reference XSZPE13).
(3) Sensors are available for very low temperatures (suffix TF: - 40°C, + 70°C) or very high temperatures (suffix TT: - 25°C, + 85°C); please consult our Customer Care Centre.

XS range application

Sensors with analogue output signal 0...10 V (1) or 4...20 mA. Plastic case, 40 x 40 mm front face 5-position turret head

Setting-up precautions

Minimum mounting distances (mm)

Sensors non-flush mountable in metal



Side by side

Face to face


Facing a metal object

e ≥ 120

e ≥ 90

Wiring schemes


2-wire



Output current	Load impedance value
420 mA	R ≤ 82 Ω
420 mA	R ≤ 560 Ω
	420 mA

Ensure a minimum of 10 V between the + and the - (terminal 3) of the sensor.

3-wire




e ≥ 240


	Output current	Load impedance value	Output voltage	Load impedance value
12 V	010 mA	R ≤ 630 Ω	_	_
24 V	010 mA	R ≤ 1500 Ω	010 V	R = 1000 Ω

Ensure a minimum of 5 V between the + and the sensor output (terminal 4).

Dimensions


XS9C2A2A1M12 and XS9C2A2A2M12






Head positions

XS9C2A2A1M12 and XS9C2A2A2M12




XS9C4A2A2P20





XS9C4A2A2P20



screws: < 1.2 N.m / < 10.62 lb-in

(1) Voltage range only obtained with a load impedance of 1000 Ω .

References, schemes

Inductive proximity sensors


XS range application


Cylindrical, stainless steel 316L front face for food and beverage applications and harsh industrial environments. Three-wire DC, solid-state output





XS912•1PAM12





Ø 30 mm, threaded M30 x 1.5						
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)	
Three-wire 12-24V	, flush moເ	ıntable				
20	NO	PNP	M12	XS930S1PAM12	0.140	
Three-wire 12-24V	, non-flush	mountab	le			
40	NO	PNP	M12	XS930S4PAM12	0.145	



XS918•1PAM12



XS930•1PAM12





Accessories			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZBS12	0.090
	Ø 18	XUZA118	0.190
	Ø 30	XSZBS30	0.370





Connecting cables (PVC) (1)						
Description	Type	Length m	Reference	Weight (kg)		
Pre-wired M12 connectors	Straight	2	XZCPA1141L2	0.090		
		5	XZCPA1141L5	0.190		
Female, 4-pin Stainless steel		10	XZCPA1141L10	0.370		
clamping ring		2	XZCPA1241L2	0.090		
		5	XZCPA1241L5	0.190		
		10	XZCPA1241L10	0.370		

Wiring schemes	
M12 connector	PNP
4 3 1 2	O1 + O4(NO) + O3 - O3 - O4

(1) For further information, please consult our site www.telemecaniquesensors.com.

Characteristics, setting-up, dimensions

Inductive proximity sensors

XS range application Cylindrical, stainless steel 316L front face for food and beverage applications and harsh industrial environments. Three-wire DC, solid-state output

Characteristics						
Sensor type Flush			XS912S1PAM12	XS918S1PAM12	XS930S1PAM12	
	Non-flush		XS912S4PAM12	XS918S4PAM12	XS930S4PAM12	
Product certifications			cULus, C€, UKCA, ECOLAB	cULus, CE, UKCA, ECOLAB		
Connection	Connector		M12			
Operating zone	Flush	mm	04.8	08	016	
	Non-flush	mm	08	016	032	
Differential travel		%	115 (real sensing distance	Sr)		
Degree of protection	Conforming to IEC 60529		IP 68 (5 meters underwater f	or 1 month)		
	Conforming to DIN 40050		IP 69K			
Storage temperature		°C	-25+ 85 (-13185°F)			
Operating temperature		°C	-25+ 85 (-13185°F)			
Materials	Case		Stainless steel 316L			
Front face thickness		mm	mm 0.4 0.6 1.0			
Mechanical shock resistance	Conforming to IEC 62262		IK10			
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 1 mm (f =	25 gn, amplitude ± 1 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		30 gn, duration 11 ms			
Output state indication			Yellow LED, 4 viewing points at 90° (blinking from 0.8 Sr and Sr)			
Rated supply voltage		٧	== 1224 with protection ag	ainst reverse polarity		
Voltage limits (including ripple))	٧	 1030			
Insulation class						
Switching capacity		mA	≤ 200 with overload and sho	rt-circuit protection		
Voltage drop, closed state	<u> </u>	٧	≤2			
Current consumption, no-load		mA	≤10			
Maximum switching frequency	Flush	Hz	600	300	100	
	Non-flush	Hz	400	200	90	
Delays	First set-up	ms	40			
	Response	μs	0.06			
	Recovery	μs	15			

Setting-up

Minimum mounting distances in mm, flush version Side by side Face to face

Ø 12 e≥38 Ø 18 e≥42 Ø 30 e≥80











e ≥ 30

e≥60


e ≥ 120

Facing a metal object

Facing a metal object



d≥24 d ≥ 50 d≥90



Minimum mounting distances in mm, non-flush version

Side by side e ≥ 108

e ≥ 182

e≥270





Face to face








M30

1.3

0.9 0.35

0.7

d≥30 h ≥ 22 d≥60 h ≥ 34 d≥120 h ≥ 34




Dimensions

Ø 12

Ø 18

Ø 30



Lengths (mm): a = overall b = threaded c = for non-flush mountable sensors

	Flush s	ensor	
	M12	M18	M30
a (mm)	60	63.5	63.5
b (mm)	41	42	42
c (mm)	0	0	0

M18

1.2

8.0

0.5

0.9

Flush sensor

M12

1 1.3

0.85

0.5

Thickness 1 mm

Non-flush sensor					
M12	M18	M30			
60	63.5	63.5			
36	35	32			
5	7	10			

Reduction coefficient

Steel	
Aluminum	
Brass	
Cupper	
Stainless steel	

Steel Aluminum Brass Stainless steel

Flush-non mounted

	Thickness 2 mm
Flush mounted	
Steel	

M12	M18	M30
0.7	0.75	0.9
1.15	0.9	0.7
1.05	0.75	0.6
0.8	0.8	1.3

M12	M18	M30
1	1	1
1	1	1
1.4	1.35	1.2
0.8	0.9	0.9
(1)	0.3	(1)
0.66	0.6	0.25

(1) No detection.

Non-flush sensor


References

Inductive proximity sensors

XS range application

Food and beverage processing series Cylindrical, stainless steel, non-flush mountable Three-wire DC, solid-state output






(kg)


0.120

0.060

0.120

0.060







XS230SA • L2



Accessories (2)			
Description	For use with sensor (mm)	Reference	Weight (kg)
Stainless steel fixing bracket	Ø 12	XSZBS12	0.060
	Ø 18	XUZA118	0.045
	Ø 30	XSZBS30	0.080





Connecting cables				
Description	Туре	Length m	Reference	Weight (kg)
Pre-wired M12 connectors	Straight	2	XZCPA1141L2	0.090
Female, 4-pin, stainless steel clamping ring		5	XZCPA1141L5	0.210
		10	XZCPA1141L10	0.410
	Elbowed	2	XZCPA1241L2	0.090
		5 XZCPA1241L5	0.210	
		10	XZCPA1241L10	0.410
M12 jumper cable	Straight	2	XZCRA151140A2	0.095
Male, 3-pin, stainless steel clamping ring		5	XZCRA151140A5	0.200

For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Example: XS212SAPAL2 becomes XS212SAPAL5 with a 5 m long cable.
 For further information, see page 120.

Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range application Food and beverage processing series Cylindrical, stainless steel, non-flush mountable Three-wire DC, solid-state output

Sensor type			XS2eeSAeeM12	XS2eeSAeeL2
Product certifications/approvals			cULus, CE, UKCA	7.020007.0022
Connection Connector			M12	_
	Pre-cabled		_	Length: 2 m
Operating	Ø 12	mm	05.6	
zone	Ø 18	mm	09.6	
	Ø 30	mm	017.6	
Differential travel		%	115 of effective sensing distance (Sr)	
Degree of protection	Conforming to IEC 60529		IP 67	IP 68
	DIN 40050		IP 69K	
Storage temperature		°C	- 40+ 85 <i>(1)</i>	
Operating temperature		°C	- 25+ 85	
Materials Case			Stainless steel 316 L	
	Cable		-	Non-poisonous PVC, 3 x 0.34 mm ²
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)	
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms	
Output state indication			Yellow LED: 4 viewing ports at 90°	Yellow LED: annular
Rated supply voltage		٧	== 1224 with protection against revers	se polarity
Voltage limits (including	ripple)	٧	1036	
Insulation class			0	
Switching capacity		mA	≤ 200 with overload and short-circuit pro	otection
Voltage drop, closed sta	te	٧	≤2	
Current consumption, n	o-load	mA	≤ 10	
Maximum switching	XS212SA••••	Hz	2500	
frequency	XS218SA•••• and XS2L2••••	Hz	1000	
	XS230SA••••	Hz	500	
Delays	First-up	ms	≤ 10	
	Response	ms	≤ 0.2 Ø 12, ≤ 0.3 Ø 18, ≤ 0.6 Ø 30	
	Recovery	ms	≤ 0.2 Ø 12, ≤ 0.7 Ø 18, ≤ 1.4 Ø 30	

(1) + 100 °C for cleaning and sterilization phases whilst not in service.


Wiring schemes

Connector Pre-cabled PNP NPN BN/1 BN/1 + BK/4 (NO) BU: Blue PNP BK/4 (NO) NPN BN: Brown BU/3 \Diamond BK: Black


Ø 12

Ø 18


Setting-up




Minimum mounting distances (mm)



Side by side	
e ≥ 48	
e ≥ 72	
e ≥ 120	




Face to face	
e ≥ 84	
e ≥ 144	
e≥264	



Facing a metal object e ≥ 21 <u>e ≥ 36</u> e ≥ 66


XSZBS30

Dimensions



	Pre-ca	abled (mm)	Conn)		
XS2	а	b	а	b	С	
Ø 12	54.5	38	61	37	5	
Ø 18	60	40	70	42	8	
Ø 30	62.5	41	70	36	13	

XSZBS12



XUZA118

28	= = 50	38,10	7,92 2 Ø32,54 6,35
01 11 00 6.	15 1 20		60,33

Ø: 2 elongated holes Ø 4.8 x 12.7

References

Inductive proximity sensors
XS range application
Food and beverage processing series
Cylindrical, stainless steel, non-flush mountable Two-wire AC or DC







XS218SAMAU20

Ø 18, threade	d M18 x 1			
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
12	NO	Pre-cabled (L = 2 m) (1)	XS218SAMAL2	0.120
		1/2"-20UNF connector	XS218SAMAU20	0.060



XS230SAMeL2



XS230SAM•U20

Ø 30, threade	d M30 x 1.5			
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
22	NO	Pre-cabled (L = 2 m) (1)	XS230SAMAL2	0.205
		1/2"-20UNF connector	XS230SAMAU20	0.145

Connecting	cables			
Description	Туре	Length m	Reference	Weight (kg)
Pre-wired connectors 1/2"-20UNF 3-pin female, stainless steel clamping ring	Straight Elbowed	5	XZCPA1865L5	0.210
		10	XZCPA1865L10	0.410
		5	XZCPA1965L5	0.250
		10	XZCPA1965L10	0.485







Accessories			
Description	For use with sensors (mm)	Reference	Weight (kg)
Stainless steel fixing brackets	Ø 18	XUZA118	0.045
	Ø 30	XSZBS30	0.080

⁽¹⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Example: XS218SAMAL2 becomes XS218SAMAL5 with a 5 m long cable.

Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range application Food and beverage processing series Cylindrical, stainless steel, non-flush mountable Two-wire AC or DC


Sensor type			XS2eeSAMeU20	XS2eeSAMeL2	
Product certifications/a	pprovals		cULus, C€, UKCA		
Connection	Connector		1/2"-20UNF	_	
	Pre-cabled		_	Length: 2 m	
Operating zone	Ø 18	mm	09.6		
	Ø 30	mm	017.6		
Differential travel		%	115 of effective sensing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 67	IP 68	
	DIN 40050		IP 69K		
Storage temperature		°C	- 40+ 85 <i>(1)</i>		
Operating temperature		°C	- 25+ 85		
Materials	Case		Stainless steel 316 L		
	Cable		_	Non-poisonous PVC, 2 x 0.34 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED: 4 viewing ports at 90°	Yellow LED: annular	
Rated supply voltage		V	\sim or == 24240 (\sim 50/60 Hz)		
Voltage limits (including	ı ripple)	V	∼ or == 20264		
Insulation class			I	I	
Switching capacity		mA	∼ 5300 or == 5200 (2)		
Voltage drop, closed sta	te	V	≤ 5.5		
Residual current, open	state	mA	≤0.8		
Maximum switching	XS218SAM•••	Hz	\sim 25 or == 1000		
frequency	XS230SAM•••	Hz	\sim 25 or == 300		
Delays	First-up	ms	≤ 30		
	Response	ms	≤ 0.5		
	Recovery	ms	≤ 0.5 XS218SAM•••, ≤ 2 XS230SAM•	••	

^{(1) + 100 °}C for cleaning and sterilization phases whilst not in service.

Wiring schemes

Connector 1/2"-20UNF 1 AC/DC: 2 ↓ : 1 AC/DC: 3

Pre-cabled BU: Blue BN: Brown





2-wire ~ or ...


≟: on connector models only

Setting-up


Minimum mounting distances (mm)








XSZBS30



Side by side	Face to face
e ≥ 72	e ≥ 144
e ≥ 120	e ≥ 264

Facing a metal object
e ≥ 36


Dimensions





	Pre-cabled (mm)		Connector (mm)			
XS2	а	b	а	b	С	
Ø 18	60	40	72	44	8	
Ø 30	62.5	41	74	40	13	

XSZA118

Ø 18







Ø: 2 elongated holes Ø 7.14 x 29.36


⁽²⁾ It is essential to connect a 0.4 A "quick-blow" fuse in series with the load.

References

Inductive proximity sensors

XS range application Food and beverage processing series Cylindrical, plastic, non-flush mountable Three-wire DC, solid-state output







Ø 18, threade	ed M18	x 1			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
12	NO	PNP	Pre-cabled (L = 2 m) (1)	XS218AAPAL2	0.100
			M12 connector	XS218AAPAM12	0.040
		NPN	Pre-cabled (L = 2 m) (1)	XS218AANAL2	0.100
			M12 connector	XS218AANAM12	0.040



Ø 30, thread	ed M30	x 1.5			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
22	NO	PNP	Pre-cabled (L = 2 m) (1)	XS230AAPAL2	0.140
			M12 connector	XS230AAPAM12	0.080
		NPN	Pre-cabled (L = 2 m)	XS230AANAL2	0.140
			M12 connector	XS230AANAM12	0.080



Accessories (2)			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020





Connecting cables				
Description	Туре	Length m	Reference	Weight (kg)
Pre-wired M12 connectors Female, 4-pin, stainless steel clamping ring	Straight	2	XZCPA1141L2	0.090
		5	XZCPA1141L5	0.190
		10	XZCPA1141L10	0.370
	Elbowed	2	XZCPA1241L2	0.090
		5	XZCPA1241L5	0.190
		10	XZCPA1241L10	0.370
M12 jumper cable Male, 3-pin, stainless steel clamping ring	Straight	2	XZCRA151140A2	0.090
		5	XZCRA151140A5	0.190

⁽¹⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Example: XS212AAPAL2 becomes XS212AAPAL5 with a 5 m long cable. (2) For further information, see page 120.


Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors


XS range application
Food and beverage processing series
Cylindrical, plastic, non-flush mountable
Three-wire DC, solid-state output


Sensor type			XS2eeAAeeM12	XS2•eAA•eL2	
Product certifications/app	orovals		cULus, C€, UKCA	<u>'</u>	
Connection	Connector		M12	-	
	Pre-cabled		_	Length: 2 m	
Operating zone	Ø 12	mm	05.6	* -	
	Ø 18	mm	09.6		
	Ø 30	mm	017.6		
Differential travel		%	115 of effective sensing distant	ce (Sr)	
Degree of protection	Conforming to IEC 60529		IP 67	IP 68	
3 · · · · · · · · · · · · · · · · · · ·	DIN 40050		IP 69K	_	
Storage temperature		°C	- 40+ 85		
Operating temperature		°C	- 25+ 85		
Materials	Case		PPS		
	Cable		_	PvR and 3 x 0.34 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED: annular		
Rated supply voltage		٧	1248 for T - 25+ 85 °C		
Voltage limits (including ripple)		V	1058 for T - 25+ 85 °C		
Insulation class					
Switching capacity		mA	≤ 200 with overload and short-cir	cuit protection	
Voltage drop, closed state	9	V	≤2		
Current consumption, no	-load	mA	≤ 10		
Maximum switching	XS212AA••••	Hz	2500		
frequency	XS218AA••••	Hz	1000		
	XS230AA••••	Hz	500		
Delays	First-up	ms	≤ 10		
	Response	ms	≤ 0.2 Ø 12, ≤ 0.3 Ø 18, ≤ 0.6 Ø 30)	
	Recovery	ms	≤ 0.2 Ø 12, ≤ 0.7 Ø 18, ≤ 1.4 Ø 30)	
Wiring schemes					
Connector	Pre-cabled	PNP	NPN		
M12 4 (••)	BU: Blue BN: Brown BK: Black	BN/1 PNP	# BN/1 NPN	+ BK/4 (NO)	


Setting-up



Minimum mounting distances (mm)








Side by side	
e ≥ 48	
e ≥ 72	
e ≥ 120	

Face to	face	
e ≥ 84		
e ≥ 144		
e≥264		

Facing a metal object
e ≥ 21
e≥36
e ≥ 66

Dimensions



XS2

Ø 12 Ø 18 Ø 30

Pre-c		e-cabled (mm)		Connector (mm)	
XS2	а	b	а	b	
Ø 12	50	42	61	43	
Ø 18	60	51	70	52	
Ø 30	60	51	70	52	

References


Inductive proximity sensors

XS range application

Food and beverage processing series Cylindrical, plastic, non-flush mountable Two-wire AC or DC



 $XS2 \bullet \bullet AAM \bullet L2$





Ø 30, threaded	d M30 x 1.5			
Sensing distance (Sn) mm	Function	Connection	Reference	Weight (kg)
22	NO	Pre-cabled (L = 2 m) (1)	XS230AAMAL2	0.140
		1/2"-20UNF connector	XS230AAMAU20	0.080





Accessories	(2)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

Connecting cal	bles			
Description	Туре	Length m	Reference	Weight (kg)
Pre-wired connectors 1/2"-20UNF 3-pin female, stainless steel 316 L clamping ring	Straight	5	XZCPA1865L5	0.180
		10	XZCPA1865L10	0.350
	Elbowed	5	XZCPA1965L5	0.180
		10	XZCPA1965L10	0.350

⁽¹⁾ For a 5 m long cable replace L2 by L5; for a 10 m long cable replace L2 by L10. Example: XS218AAMAL2 becomes XS218AAMAL5 with a 5 m long cable. (2) For further information, see page 120.

Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range application Food and beverage processing series Cylindrical, plastic, non-flush mountable Two-wire AC or DC

Concertune			XS2eeAAMeU20	XS2eeAAMeL2	
Sensor type				X5200AAWOLZ	
Product certifications/a	· ·		cULus, C€, UKCA		
Connection	Connector		1/2"-20UNF		
	Pre-cabled		-	Length: 2 m	
Operating zone	Ø 18	mm	09.6		
	Ø 30	mm	017.6		
Differential travel		%	115 of effective sensing distance (Sr)		
Degree of protection	Conforming to IEC 60529		IP 67	IP 68	
	DIN 40050		IP 69K		
Storage temperature		°C	- 40+ 85		
Operating temperature		°C	- 25+ 85		
Materials	Case		PPS		
	Cable		-	PvR and 2 x 0.34 mm ²	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms		
Output state indication			Yellow LED: annular		
Rated supply voltage		٧	\sim or == 24240 (\sim 50/60 Hz)		
Voltage limits (including	ripple)	V	∼ or == 20264		
Insulation class			I	I	
Switching capacity		mA	~5300 or == 5200 (1)		
Voltage drop, closed sta	ite	V	≤ 5.5		
Residual current, open s	state	mA	≤ 0.8		
Maximum switching	XS218AAM•••	Hz	~ 25 or 1000		
frequency	XS230AAM•••	Hz	∼ 25 or 300		
Delays	First-up	ms	≤ 30		
•	Response	ms	≤ 0.5		
	Recovery	ms	≤ 0.5 XS218AAM•••, ≤ 2 XS230AAM••	•	

(1) It is essential to connect a 0.4 A "quick-blow" fuse in series with the load.

Wiring schemes

Connector


1/2"-20UNF



≂: 2 ≂: 3

Pre-cabled


BU: Blue BN: Brown




2-wire ∼ or ...

NO output

Setting-up



Ø 18 Ø 30




Minimum mounting distances (mm)

e≥72 e≥120



Face to face
e ≥ 144
e ≥ 264



e ≥ 36 e ≥ 66

Dimensions

XS2



XS2 Ø 18 Ø 30

(1) LED					
Pre-cab	Pre-cabled (mm)		Connector (mm)		
а	b	а	b		
60	51	70	52		
60	51	70	52		

References, schemes

Inductive proximity sensors

XS range application Cylindrical, stainless steel 303 front face for harsh industrial environments Three-wire DC, solid-state output













Ø 8 mm, threaded	1 x 8M t						
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)		
Three-wire 12-24V, flush mountable							
3	NO	PNP	M12	XS908R1PAM12	0.018		
Three-wire 12-24V ==, non-flush mountable							
6	NO	PNP	M12	XS908R4PAM12	0.018		

Ø 12 mm, thread	ed M12 x	1			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Three-wire 12-24V	່, flush moເ	untable			
6	NO	PNP	M12	XS912R1PAM12	0.024
Three-wire 12-24V	, non-flush	mountab	ole		
10	NO	PNP	M12	XS912R4PAM12	0.023

Ø 18 mm, thread	ed M18 x	1			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Three-wire 12-24V	, flush moເ	ıntable			
10	NO	PNP	M12	XS918R1PAM12	0.044

Three-wire 12-24V ==, non-flush mountable						
20	NO	PNP	M12	XS918R4PAM12	0.051	

Ø 30 mm, thread	ed M30 x	1.5			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Three-wire 12-24V	, flush mou	ıntable			
20	NO	PNP	M12	XS930R1PAM12	0.140
Three-wire 12-24V	, non-flush	mountab	le		
40	NO	PNP	M12	XS930R4PAM12	0.144

Connecting	cables (PUR) (1)		
Description	Туре	Length m	Reference	Weight (kg)
Pre-wired M12	Straight	2	XZCP1141L2	0.090
connectors		5	XZCP1141L5	0.190
Female, 4-pin Metal clamping		10	XZCP1141L10	0.370
	Elbowed	2	XZCP1241L2	0.090
		5	XZCP1241L5	0.190
		10	XZCP1241L10	0.370

Wiring schemes	
M12 connector	PNP
1 2	PNP 4(NO) +

(1) For further information, please consult our site www.telemecaniquesensors.com.

Characteristics, setting-up, dimensions

Inductive proximity sensors

XS range application Cylindrical, stainless steel 303 front face for harsh industrial environments Three-wire DC, solid-state output

Characteristics						
Sensor type	Flush		XS908R1PAM12	XS912R1PAM12	XS918R1PAM12	XS930R1PAM12
	Non-flush		XS908R4PAM12	XS912R4PAM12	XS918R4PAM12	XS930R4PAM12
Product certifications			cULus, C€, UKCA	•	•	•
Connection	Connector		M12			
Operating zone	Flush	mm	02.4	04.8	08	016
	Non-flush	mm	04.8	08	016	032
Differential travel		%	115 (real sensing	distance Sr)		
Degree of protection	Conforming to IEC 60529		IP 67	IP 68 (5 meters unde	erwater for 1 month)	
	Conforming to DIN 40050		IP 69K			
Storage temperature		°C	-25+ 70 (-13158°F)			
Operating temperature		°C	-25+ 70 (-13158°F)			
Materials	Case		Stainless steel, 303	grade		
Front face thickness		mm	0.25	0.4	0.6	1.0
Mechanical shock resistance	Conforming to IEC 62262		IK10			
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 1	mm (f = 10 to 55 Hz)		
Shock resistance	Conforming to IEC 60068-2-27		30 gn, duration 11 m	s		
Output state indication			Yellow LED, 4 viewin	ig points at 90° (blinkin	g from 0.8 Sr and Sr)	
Rated supply voltage		٧	== 1224 with prote	ction against reverse p	olarity	
Voltage limits (including ripple)		٧	 1030			
Insulation class						
Switching capacity		mA	≤ 200 with overload a	and short-circuit protec	tion	
Voltage drop, closed state		٧	≤2			
Current consumption, no-load		mΑ	≤10			
Maximum switching frequency	Flush	Hz	1000	600	300	100
	Non-flush	Hz	700	400	200	90
Delays	First set-up	ms	40			
	Response	μs	0.05	0.06		
	Recovery	μs	23	15		

Setting-up

Minimum mounting distances in mm, flush version

	Side by s	side
Ø 8	e ≥ 14	
Ø 12	e≥38	
Ø 18	e ≥ 42	
Ø 30	e ≥ 80	e e


Side by side

•	
-	
\Rightarrow	
\Rightarrow	
=	












d ≥ 12

d≥24

d ≥ 50

d≥90



Minimum mounting distances in mm, non-flush version

<i>v</i> 0	e > 52
Ø 12	e ≥ 108
Ø 18	e ≥ 182
Ø 30	e ≥ 270










Flush sonsor

Flush sensor



Mounted in a metal support

a = 20	n ≥ 15
d ≥ 30	h ≥ 22
d ≥ 60	h ≥ 34
d ≥ 120	h ≥ 34



M30


1.2

0.9

(1)

0.25

Dimensions



Lengths (mm): a = overall b = threaded c = for non-flush mountable sensors

	i iusi	i iusii seiisoi				
	M8	M12	M18	M30		
a (mm)	66	60	63.5	63.5		
b (mm)	46	41	42	42		
c (mm)	0	0	0	0		

Non-fl	ush sensor	•	
M8	M12	M18	M30
66	60	63.5	63.5
42	36	35	32
4	5	7	10

M18

1.35

0.9

Reduction coefficient

Steel	
Aluminum	
Brass	
Cupper	
Stainlass staal	

Non-flush mounted

Flush mounted
Steel
Aluminum
Brass
Stainless steel

	M8	M12	M18	M30
	1	1	1	1
	1	1	1	1
	1.35	1.3	1.2	1.3
	0.9	0.85	8.0	0.9
Thickness 1 mm	0.3	0.5	0.5	0.35
Thickness 2 mm	0.6	0.9	0.9	0.7

M8	M12	M18	M30
1	0.7	0.75	0.9
0.9	1.15	0.9	0.7
0.9	1.05	0.75	0.6
1	0.8	0.8	1.3

0.3	(1)	0.3	
0.9	0.66	0.6	

Non-flush sensor

M12

1.4

0.8

(1) No detection.

1 1.4

0.85

Inductive proximity sensors
XS range application
Flat sensor, flush mountable, increased range,
Switching capacity 300 mA 80 x 80 x 40 format, DIN rail mounting, solid-state output

Sensor type

Flush mountable in metal



Dimensions		mm	80 x 80 x 40
Nominal sensing distance (Sn)		mm	50 (not flush mounted: 42)
Reference			
2-wire (non polarised)	NO		XS7D1A3CAM12DIN
Weight		kg	0.374
Characteristics			
Product certifications			CE, UKCA
Degree of protection	Conforming to IEC 60529		IP 67
Temperature	Operating	°C	-25+70
	Storage	°C	- 40+ 85
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms
Connection			M12 connector
Operating zone		mm	040 (not flush mounted: 035)
Repeat accuracy		%	3 of Sr
Differential travel		%	115 of Sr
Output state indication			Yellow LED
Rated supply voltage		٧	1248 with protection against reverse polarity
Voltage limits (including r	ripple)	٧	1058
Insulation class			
Residual current, open s	state	mA	≤ 0.5
Switching capacity		mA	1.5300 with overload and short-circuit protection
Voltage drop, closed sta	te	٧	≤4.5
Maximum switching free	quency	Hz	100
Delays	First-up	ms	≤10
	Response	ms	€2
	Recovery	ms	≤5
<u> </u>	·		


Dimensions, setting-up, schemes

Inductive proximity sensors

XS range application

Flat sensor, flush mountable, increased range, Switching capacity 300 mA 80 x 80 x 40 format, DIN rail mounting, solid-state output

Dimensions XS7D1A3CAM12DIN



(1) Output LED

(2) For CHC type screws

Setting-up Minimum mounting distances (mm) Face to face Side by side Back to back Facing a metal object Flush mounted 450 140 90 150 Not flush mounted 450 180 180 150

Flush/non-flush conditions

In A37 steel




Sn	Su	Sn	Su	
42 mm	35 mm	50 mm	40 mm	

Wiring schemes

2-wire NO/M12 XS7D1A3CAM12DIN





References, schemes

Inductive proximity sensors
XS range application
Cylindrical, stainless steel 303 front face, for welding environments

Three-wire DC, solid-state output



Ø 12 mm, thread	ed M12 x	1			
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Three-wire 12-24V	, flush moເ	ıntable			
6	NO	PNP	M12	XS912RWPAM12	0.024



Ø 18 mm, threaded M18 x 1						
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)	
Three-wire 12-24V ==, flush mountable						
10	NO	PNP	M12	XS918RWPAM12	0.051	





Connecting cables (PUR) (1)						
Description	Туре	Length m	Reference	Weight (kg)		
Pre-wired M12 connectors Female, 4-pin Metal clamping ring	Straight	2	XZCP1141L2	0.090		
		5	XZCP1141L5	0.190		
		10	XZCP1141L10	0.370		
	Elbowed	2	XZCP1241L2	0.090		
		5	XZCP1241L5	0.190		
		10	XZCP1241L10	0.370		

Wiring schemes	
M12 connector	PNP
1 2	9NP 04(NO) + 03 - 03 - 03

(1) For further information, please consult our site www.telemecaniquesensors.com.

Characteristics, setting-up, dimensions

Inductive proximity sensors

XS range application

Cylindrical, stainless steel 303 front face, for welding environments

Three-wire DC, solid-state output

Characteristics				
Sensor type	Flush		XS912RWPAM12	XS918RWPAM12
Product certifications			cULus, C€, UKCA	
Connection	Connector		M12	
Operating zone		mm	04.8	08
Differential travel		%	115 (real sensing distance Sr)	
Degree of protection	Conforming to IEC 60529		IP 68 (5 meters underwater for 1 month)	
	Conforming to DIN 40050		IP 69K	
Storage temperature	<u> </u>	°C	-25+ 70 (-13158°F)	
Operating temperature		°C	-25+ 70 (-13158°F)	
Materials	Case		Stainless steel, 303 grade	
Front face thickness		mm	0.4	0.6
Mechanical shock resistance	Conforming to IEC 62262		IK10	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 1 mm (f = 10 to 55 Hz)	
Shock resistance	Conforming to IEC 60068-2-27		30 gn, duration 11 ms	
Output state indication			Yellow LED, 4 viewing points at 90° (blinking from 0.8 Sr and Sr)	
Rated supply voltage		٧	== 1224 with protection against reverse po	olarity
Voltage limits (including ripple)		٧	 1030	
Insultation class				
Switching capacity		mA	≤ 200 with overload and short-circuit protect	ion
Voltage drop, closed state		٧	≤2	
Current consumption, no-load	<u> </u>	mA	≤10	
Maximum switching frequency	<u> </u>	Hz	15	
Delays	First set-up	ms	80	
	Response	μs	100	
	Recovery	μs	15	

Setting-up

Minimum mounting distances in mm, flush version

Side by side Face to face

Facing a metal object

Mounted in a metal support

 $\frac{\emptyset 12}{\emptyset 18} \quad \frac{e \geqslant 38}{e \geqslant 42}$



 $\frac{e \ge 30}{e \ge 40}$




e≥20 e≥30



 $\frac{d \ge 24}{d \ge 50}$



Dimensions



	i iudii delidoi			
	M12	M18		
a (mm)	60	63.5		
b (mm)	41	42		
c (mm)	0	0		

Flush sensor

Reduction coefficient

Non-flush mounted

Steel	
Aluminum	
Brass	
Cupper	
Stainless steel	

	M12	M18	
	1	1	
	1	1	
	1.3	1.2	
	0.85	0.8	
Thickness 1 mm	0.5	0.5	
Thickness 2 mm	0.9	0.9	

Flush sensor

Flush mounted	
Steel	
Aluminum	
Brass	
Stainless steel	

M12	M18	
0.7	0.75	
1.15	0.9	
1.05	0.75	
0.8	0.8	

XS range application

Factor 1 sensors for ferrous or non-ferrous material detection and welding applications. Plastic case, 40 x 40 mm front face. 5-position turret head

Flush mountable in metal Sensor type 40 x 40 x 117 **Dimensions** 40 x 40 x 70







Nominal sensing distance (Sn)	mm	20	
References				
4-wire	PNP NO+NC		XS9C2A1PCM12	
	NPN NO+NC		XS9C2A1NCM12	-
			XS9C4•••P20 sensors are available with an with a Pg 13.5 (e.g. XS9C4A1PCG13) or a 1/please consult our Customer Care Centre for	2" NPT (e.g. XS9C4A1PCN12) cable entry:
Weight		kg	0.110	0.220
Characteristics				
Product certifications			cULus, CE, UKCA	
Conformity to standards			IEC 60947-5-2	
Connection			M12 connector (4-pin)	Screw terminals, clamping capacity 4 x 1.5 mm ² / 4 x 16 AWG
Operating zone		mm	016	
Differential travel		%	315 of Sr	
Repeat accuracy		%	< 3	
Immunity to magnetic fields	5		< 250 mTesla	
Degree of protection	Conforming to IEC 60529 and DIN 40050		IP 65, IP 67 and IP 69K	
Temperature	Storage	°C	-40+ 85	
Operation (2)		°C	- 25+ 70	
Material			Case: PBT	
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 1055 Hz)	
Shock resistance	Conforming to IEC 60068-2-27		50 gn for 11 ms	
Indicators			Output state: yellow LED. Supply on: green L	
Rated supply voltage	4-wire	٧	== 1224 with protection against reverse pol	arity
Voltage limits (including ripple)	4-wire	V	 1036	
Insulation class				
Current consumption, no-load	4-wire	mA	<30	
Switching capacity	4-wire ===	mA	4 < 200 with protection against overload and short-circuit	
Voltage drop, closed state	4-wire ===	٧	<2	
Maximum switching frequency	4-wire	Hz	z 250	
Delays	First-up	ms	< 15	
	Response m		< 2.5	
Recovery ms		ms	< 2.5	

Setting-up

Sensing distance correction factor

1.20 0.80 0.60 0.20 0.00 SS 303 SS 304 SS 316 Fe360






- (1) These sensors are supplied without a cable gland. A suitable Pg 13.5 cable gland is available (reference XSZPE13).
- (2) Sensors are available for very low temperatures (suffix TF: 40°C, + 70°C) or very high temperatures (suffix TT: 25°C, + 85°C); please consult our Customer Care Centre

Setting-up (continued), schemes, dimensions


Inductive proximity sensors

XS range application

Factor 1 sensors for ferrous or non-ferrous material detection and welding applications. Plastic case, 40 x 40 mm front face. 5 position turret head



(1) 2 elongated holes Ø 5.3 x 7 mm. Tightening torque of cover fixing screws and clamp screws: < 1.2 N.m/< 10.62 lb-in.



References, characteristics, schemes, dimensions

Inductive proximity sensors
XS range application
Selective detection of ferrous and non-ferrous materials
Cylindrical type, solid-state output

Sensor type Flush mountable Stainless steel case



	mm	T _a
Nominal sensing distance (Sn)		5
References		
3-wire, ferrous version PNP Insensitive to non ferrous materials	NO	XS1M18PAS40D
3-wire, non ferrous version PNP Insensitive to ferrous materials	NO	XS1M18PAS20D
Weight	kg	0.060
Characteristics		
Product certifications		cULus, CE, UKCA
Connection		M12 connector
Degree of protection conforming to IEC 6052	9	IP 67
Operating zone	mm	04
Operating temperature		-25+70
Output state indication		Yellow LED, 4 viewing ports at 90°
Rated supply voltage		1224 with protection against reverse polarity
Voltage limits (including ripple)	V	 1038
Insulation class		
Switching capacity		0200 mA with overload and short-circuit protection
Voltage drop, closed state	V	≤2.6
Residual current, open state		-
Current consumption, no-load		≤15
Maximum switching frequency		1000
Delays First-up	ms	≤10
Response	ms	≤0.3
Recovery	ms	≤0.7

XS range application

Selective detection of ferrous and non-ferrous materials Cylindrical type, solid-state output

Wiring schemes **Dimensions** M12 connector 3-wire --- PNP b (mm) PNP 51.5 Setting-up Minimum mounting distances (mm) Side by side Face to face Facing a metal object Mounted in a metal support XS1M18 e ≥ 10 e ≥ 60 e ≥ 15 d ≥ 18, h ≥ 0 (ferrous metal)

d ≥ 18, h ≥ 5 (non ferrous

metal)

References

Inductive proximity sensors

XS range, Fail Safe Cylindrical, metal, flush mountable Standard sensing distance Four-wire DC, solid-state NO + NC output, SIL2, PLd, cat 2



XS512BSPD●●



XS518BSPD•



XS530BSPD●●

Sensors, 4-wire, brass case, flush mountable					
Sensing distance (Sn) mm	Function	Output	Connection	Reference	Weight (kg)
Ø 12, thread	ded M12 x 1				
2	NO + NC	PNP	Pre-cabled (L = 2 m)	XS512BSPDL2	0.070
			M12 connector	XS512BSPDM12	0.020
Ø 18, thread	ded M18 x 1				
5	NO + NC	PNP	Pre-cabled (L = 2 m)	XS518BSPDL2	0.100
			M12 connector	XS518BSPDM12	0.040
Ø 30, thread	ded M30 x 1	.5			
10 N	NO + NC	PNP	Pre-cabled (L = 2 m)	XS530BSPDL2	0.160
			M12 connector	XS530BSPDM12	0.100



Accessories			
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

Characteristics, schemes, setting-up, dimensions


Inductive proximity sensors

XS range, Fail Safe Cylindrical, metal, flush mountable Standard sensing distance Four-wire DC, solid-state NO + NC output, SIL2, PLd, cat 2

Sensor type			XS5eeBSPDM12	XS5eeBSPDL2
Product certifications			cULus, C€, UKCA, E2	cULus, C€, UKCA, E2
Conformity to safety standards	Ø 12, Ø 18 and Ø 30		IEC 60947-5-2 IEC 60947-5-3 EN/IEC 61508: SIL 2 EN/ISO 13849-1: PL =d IEC 62061: SILcl2	
Reliability data	Ø 12, Ø 18 and Ø 30		MTTFd = 2422 years, PFHd = 47.1 10 ⁻⁹ 1/h, SFF > 98.9 %, DC > 96 % (with a safety controller)	
Connection			M12 connector	Pre-cabled, length: 2m
Operating zone (Sao/Sar)	Ø 12 flush mountable	mm	0.41.6/2.8	
	Ø 18 flush mountable	mm	1.54/7	
	Ø 30 flush mountable	mm	4.98.1/13.9	
Differential travel		%	115 of effective sensing distance (Sr)	
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67	IP 65 and IP 68
	Conforming to DIN 40050		IP 69K	
Storage temperature		°C	- 40+ 85	
Operating temperature		°C	-40+70	
Materials Case/Sensing face			Nickel plated brass/PPS	
	Cable			PVC 4 x 0.22 mm ² (Ø 12, Ø 18 and Ø 3
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)	
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms	
Output state indication			Yellow LED, 4 viewing ports at 90°	
Rated supply voltage		٧	== 1224 with protection against reverse p	olarity
Voltage limits (including ripple)		٧	 1036	 1036
Insulation class				
Switching capacity		mA	≤ 200 with overload and short-circuit protection	
Voltage drop, closed state		٧	≤2	
Current consumption, no-load		mA	≤10	
Maximum switching frequency	Ø 12	Hz	85	
	Ø 18	Hz	85	
	Ø 30	Hz	85	
Delays	First-up	ms	≤10	
	Response	ms	≤5.7	
	Recovery	ms	≤5.7	
Wiring schemes				
M12 connector	Pre-cabled	PNP	4-wire	
4 3	BU: Blue BN: Brown BK: Black	BN/1	BK/4 (NO) +	



WH: White



Setting-up

Sensor	
Ø 12 flush mountable	XS512
Ø 18 flush mountable	XS518
Ø 30 flush mountable	XS530


Minimum mounting distances (mm)

e ≥ 10

e ≥ 20

Side by side e ≥ 4

i ace to	iace	
тиАпАтт е	: тАпАт	e ≥ 24
		e ≥ 60
		e ≥ 120




-	
e ≥ 6	
e ≥ 15	
e ≥ 30	

Mounted in a metal support d≥12h≥0 d ≥ 18 h ≥ 0

d ≥ 30 h ≥ 0

Dimensions



Flush m	ountable	in metal
---------	----------	----------

Sensor		
Ø 12 brass	XS512	
Ø 18 brass	XS518	
Ø 30 brass	XS530	

Pre-cabled	(mm)
а	b
37	25
41	29
45	33

M12 connector (mm)				
а	b			
50	31			
51	28			
54	33			

References


Inductive proximity sensors

XS range, Fail Safe
Cylindrical, metal, flush mountable
Increased range

Four-wire DC, solid-state NO + NC output, SIL2, PLd, cat 2









Accessories ((1)		
Description	For use with sensors (mm)	Reference	Weight (kg)
Fixing clamps	Ø 12	XSZB112	0.006
	Ø 18	XSZB118	0.010
	Ø 30	XSZB130	0.020

⁽¹⁾ For further information, see page 120.

Characteristics, schemes, setting-up, dimensions

Inductive proximity sensors

XS range, Fail Safe
Cylindrical, metal, flush mountable
Increased range
Four-wire DC, solid-state NO + NC output, SIL2, PLd, cat 2

Characteristics			VOA DODDIMAG	VOA BODDLO
Sensor type			XS1●●B3PDM12	XS1●●B3PDL2
Product certifications	Ø 12, 18 and 30		cULus, C€, UKCA, E2	
Conformity to safety standards	Ø 12, Ø 18 and Ø 30		IEC 60947-5-2 IEC 60947-5-3 EN/IEC 61508: SIL 2 EN/ISO 13849-1: PL =d IEC 62061: SILcl2	
Reliability data	Ø 12, Ø 18 and Ø 30		MTTFd = 2422 years, PFHd = 47.1 10 ^{.9} 1/h, SFF > 98.9 %, DC > 96 % (with a safety controller)	
Connection			M12 connector	Pre-cabled, length 2 m
Operating zone (Sao/Sar) Ø 12		mm	1.23.2/5.6	
	Ø 18	mm	36.5/11.1	
	Ø 30	mm	5.812.2/20.9	
Differential travel		%	115 of effective sensing distance (Sr)	
Degree of protection	Conforming to IEC 60529		IP 65 and IP 67	IP 65 and IP 68
	Conforming to DIN 40050		IP 69K	-
Storage temperature		°C	-40+85	
Operating temperature		°C	-40+70	
Materials	Case		Nickel plated brass	
	Sensing face		PPS	
	Cable		_	PVC 4 x 0.22 mm ²
Vibration resistance	Conforming to IEC 60068-2-6		25 gn, amplitude ± 2 mm (f = 10 to 55 Hz)	
Shock resistance	Conforming to IEC 60068-2-27		50 gn, duration 11 ms	
Output state indication			Yellow LED, 4 viewing ports at 90°	Yellow LED, annular
Rated supply voltage		٧	=== 1224 with protection against reverse polarity	
Voltage limits (including ripple)		٧	 936	
Insulation class			III	
Switching capacity		mA	≤ 200 with overload and short-circuit protection	
Voltage drop, closed state		٧	≤2	
Current consumption, no-load		mΑ	≤10	
Maximum switching frequency	Ø 12	Hz	85	
	Ø 18	Hz	85	
	Ø 30	Hz	85	
Delays	First-up	ms	≤10	
	Response	ms	≤ 5.7	
	Recovery	ms	≤ 5.7	

Wiring schemes M12 connector

Pre-cabled



BU: Blue BN: Brown BK: Black WH: White

Setting-up

Minimum mounting distances (mm)







PNP 4	-wire	
BN/1	□ BK/4 (NO)	+
PNP	WH/2 (NC)	

Sensors	Side by side	Face to face	Facing a metal object
Ø 12	e ≥ 8	e ≥ 50	e ≥ 12
Ø 18	e ≥ 16	e ≥ 100	e ≥ 25
Ø 30	e ≥ 30	e ≥ 180	e ≥ 45

Dimensions (3) b a

	Pre-cable	Pre-cabled (mm)		ctor (mm)
Sensors	а	b	а	b
Ø 12	37	25	50	31
Ø 18	41	29	51	28
Ø 30	45	33	54	33

(3) LED.

References, Characteristics,

Inductive proximity sensors

XS range, Fail Safe Cubic case, 40 x 40 x 70 mm, M12 connector 5-position turret head Four-wire DC, solid-state NO + NC output, SIL2, PLd, cat 2

Sensor type Flush mountable in metal Non-flush mountable in metal




Nominal sensing distance (Sn)		mm	20	40		
References						
4-wire	PNP	NO+NC		XS8C2A1PDM12	XS8C2A4PDM12	
Weight			kg	0.149	0.149	
Characteristics						
Operating zone (Sao/Sar)			mm	8.316.2/27.8	18.432.4/55.7	
Product certifications				cULus, C€, UKCA, TÜV (4-wire), E2 (3-wire and	d 4-wire)	
Conformity to standards				IEC 60947-5-2		
Conformity to safety stand	lards (1)			IEC 60947-5-3 EN 62061 (2005): SILci2		
comorning to surety stance	iui us (1)			EN 61508 (2010): SIL 2, EN ISO 13849 (2008): PL d		
Reliability data (1)				MTTFd = 2422 years,		
• , ,				PFHd = 7.4 10 ⁻⁸ 1/h,		
				SFF > 98.9 %, DC > 96 % (with a safety controller)		
Connection				M12 connector		
Differential travel			%	315 of Sr		
Degree of protection	Conforming t			IP 65, IP 67 and IP 69K		
Temperature	Storage		°C - 40+ 85			
	Operation (3))	°C	- 40+ 70		
Material	Case			PBT		
Vibration resistance	Conforming t 60068-2-6			25 gn, amplitude ± 2 mm (f = 1055 Hz)		
Shock resistance	Conforming t 60068-2-27			50 gn for 11 ms		
Indicators	Output state			Yellow LED		
	Power on			Green LED		
Rated supply voltage		4-wire ===	٧	1248 with protection against reverse polarity		
Voltage limits (including ri	pple)	4-wire ===	٧	1058		
Insulation class						
Current consumption, no-	load	4-wire ===	mA	< 15		
Switching capacity		4-wire ===	mA	< 200 with overload and short-circuit protection		
Voltage drop, closed state		4-wire ===	٧	V <2		
Maximum switching frequency	Flush mount			40		
	Non-flush mo	ountable	Hz == 30			
Delays	First-up		ms	Flush mountable: ≤ 12. Non-flush mountable: ≤	14	
	Response		ms	Flush mountable: ≤ 10. Non-flush mountable: ≤	12.5	
	Recovery		ms	Flush mountable: ≤ 10. Non-flush mountable: ≤	12.5	
(4) OII O				4-4	(alama and a same a sa	

⁽¹⁾ SIL 2 protection can only be obtained by connecting both outputs to a safety PLC. Please consult our website: www.telemecaniquesensors.com.

XS range, Fail Safe Cubic case, 40 x 40 x 70 mm, M12 connector 5-position turret head Four-wire DC, solid-state NO + NC output, SIL2, PLd, cat 2

Setting-up precautions

Minimum mounting distances (mm)




	Side by side	Face to face	Facing a metal object
XS8C2A1●●	e ≥ 80	e ≥ 160	e ≥ 60
XS8C2A4ee	e ≥ 160	e ≥ 320	e ≥ 120

Wiring schemes

4-wire ---, NO + NC outputs

Sensors flush mountable in metal Sensors non-flush mountable in metal




M12 connector




+ V:	1
NC:	2
- V:	3
NO:	4


Accessory references				
Description	Туре	Length	Reference	Weight
		m		(kg)
Pre-wired M12 connectors	Straight	2	XZCP1141L2	0.090
Female, 4-pin, zinc die-cast, nickel plated		5	XZCP1141L5	0.190
clamping ring		10	XZCP1141L10	0.370
	Elbowed	2	XZCP1241L2	0.090
		5	XZCP1241L5	0.190
		10	XZCP1241L10	0.370

Dimensions
















Example SIL 2 wiring scheme (with XPSMC safety PLC)



 $\boldsymbol{\mathsf{SFF}}$ (Safe Failure Fraction): 98,9 %DC (Diagnosis Coverage): 96 %

Inductive proximity sensors XS range, Fail Safe


Plastic case, 40 x 40 x 117 mm, plug-in

Sensor type			Flush mountable in metal	Non-flush mountable in metal		
Nominal sensing distance	e (Sn)	mm	20	40		
References						
4-wire 	PNP NO+NC		XS8C4A1PDP20	XS8C4A4PDP20		
Weight		kg	0.244	0.244		
		Ţ	Note: These sensors have an M20 cable e 13.5 cable entry (e.g. XS8C4A4PDG13) or XS8C4A1PDN12). Please consult our Customer Care Centre.			
Characteristics						
Operating zone (Sao/Sar)		mm	8.316.2/27.8	18.432.4/55.7		
Product certifications			cULus, C€, UKCA, TÜV, E2			
Conformity to standards			IEC 60947-5-2 IEC 60947-5-3			
Conformity to safety standards (1)			EN 62061 (2005): SILcl2, EN 61508 (2010): SIL 2, EN ISO 13849 (2008): PL d			
Reliability data (1)			MTTFd = 2422 years, PFHd = 7.4 10-8 1/h, SFF > 98.9 %, DC > 96 % (with a safety controller)			
Connection			Screw terminals, clamping capacity: 2 or 4 x 1.5 mm2 / 2 or 4 x 16 AWG (3)			
Differential travel		%	315 of Sr			
Degree of protection	Conforming to IEC 60529 and DIN 40050		IP 65, IP 67 and IP 69K			
Temperature	Storage	°C	- 40+ 85			
Mark to 1	Operation	°C	-40+70			
Material Vibration resistance	Conforming to IEC 60069 2.6	+	Case: PBT			
	Conforming to IEC 60068-2-6	+	25 gn, amplitude ± 2 mm (f = 1055 Hz)			
Shock resistance Indicators	Conforming to IEC 60068-2-27 Output state	+	50 gn for 11 ms Yellow LED			
malcators	Power on	+	Green LED			
Rated supply voltage	4-wire	V	1248 with protection against reverse pola	arity		
Voltage limits (including ripple)	4-wire	٧	1058			
Insulation class						
Current consumption, no-load	4-wire	mA	< 15			
Switching capacity	4-wire ===	mA	< 200 mA with overload and short-circuit pro	otection		
Voltage drop, closed state	4-wire	٧	< 2			
Maximum switching frequ	ency	Hz	Flush mountable: == 40 Non-flush mountable: == 30			
Delays	First-up	ms	Flush mountable: ≤ 12. Non-flush mountab	le: ≤ 14.		
	Response	ms	Flush mountable: ≤ 10. Non-flush mountab	le: ≤ 12.5.		
	Recovery	ms	Flush mountable: ≤ 10. Non-flush mountab	le: ≤ 12.5.		

⁽¹⁾ SIL 2 protection can only be obtained by connecting both outputs to a safety PLC. Please consult our website www.telemecaniquesensors.com.

XS range, Fail Safe Plastic case, 40 x 40 x 117 mm, plug-in


Setting-up precautions Minimum mounting distances (mm)




		Side by side	Face to face	Facing a metal object
Sensors flush mountable in metal	XS8C4A1●●	e ≥ 80	e ≥ 160	e ≥ 60
Sensors non-flush mountable in metal	XS8C4A4••	e ≥ 160	e ≥ 320	e ≥ 120

Wiring schemes


NO + NC outputs



Dimensions




Head positions



(1) 2 elongated holes Ø 5.3 x 7 cm.

Tightening torque of cover fixing screws and clamp screws: < 1.2 N.m/< 10.62 lb-in

Example SIL 2 wiring scheme (with XPSMC safety PLC)



Inductive proximity sensors XS range Accessories



XSZBE10



XSZBC10



XSZBD10



XX 545_CPFUR	
XSZB1●●	

Description	xing accessories For use with sensor		Unit reference	Weight
Description	Type			
Replacement bracket	XS●E Replaces: XS7T2, XS8T2, XSE	-	XSZBE10	0.060
	XSeC Replaces: XS7T4, XS7C40, XS8T4, XS8C40 and XSC	-	XSZBC10	0.110
	XS●D (for XSD) (1)	_	XSZBD10	0.065
Fixing clamps	XS1, XS2, XS4, XS5, XS6	8 (M8 x 1)	XSZB108	0.006
	XS1, XS2, XS4, XS5,	12 (M12 x 1)	XSZB112	0.006
	XS6	18 (M18 x 1)	XSZB118	0.010
		30 (M30 x 1.5)	XSZB130	0.020
Set of 2 metal fixing nut	s, XS1, XS2, XS5, XS6	12 (M12 x 1)	XSZE112	0.015
nickel plated		18 (M18 x 1)	XSZE118	0.020
		30 (M30 x 1.5)	XSZE130	0.050



XSCZ01




Description	For use with sensor	For use with sensor		
	Туре	Diameter (mm)	(kg)
Cable sleeve adaptor	XS●, XT●	12 (M12 x 1)	XSZP112	0.005
(CNOMO type)		18 (M18 x 1)	XSZP118	0.005
		30 (M30 x 1.5)	XSZP130	0.010
Outer cover (IP 68)	XT7, XS7, XS8 and XS (C format)	9 –	XSCZ01	0.100

Fuses (for unprote	ected 2-wire ==-/~ sensors)			
Description	Туре	Sold in lots of	Unit reference	Weight (kg)
Cartridge fuses 5 x 20	0.4 A "quick-blow"	10	XUZE04	0.001
	0.63 A "quick-blow"	10	XUZE06	0.001
	0.8 A "quick-blow"	10	XUZE08	0.001


⁽¹⁾ Depth adjustment shim for converting 80 x 80 x 26 mm format to 80 x 80 x 40 mm format. Also enables clipping onto 35 mm omega rail.

XS range Accessories


XSZBE10




XSZBC10



XSZBD10 (for mounting on XSeDeeee)



XSZB108, XSZB112, XSZB118, XSZB130, XSZB165



(1) 2 elongated holes 4 x 8 mm.

	<u>-</u>			B130	39	21.7	35.5	31	18.5	30	
(4)			_3,5								
(1)		a1	_								
/		~ · · ~									

B112

B118

XSZ a a1 b


26

21.9 14.5 16

b1 b2


15.5 8.5 12 15.7 22.3 20.1 11.5 18

XSZP112, XSZP118, XSZP130



XSZ	h	Ød1	Ø d2	
P112	7	12	16,8	
P118	6,2	18	23	
P130	6.2	30	34.4	

XSCZ01




(1) 13P cable gland

XS range

Cylindrical, standard range sensors

Cylindrical type sensors

Flush mountable in metal



Sensor (mm)	Standard steel target (mm)	Operating zone (mm)
Ø 4	5 x 5 x 1	00.8
Ø 5	5 x 5 x 1	00.8
Ø 6.5	8 x 8 x 1	01.2
Ø8	8 x 8 x 1	01.2
Ø 12	12 x 12 x 1	01.6


- pick-up points
- drop-out points (object approaching from the side)
 4 (plain) XS1 and Ø 5 (M5 x 0.5) XS1
- 2 Ø 6.5 (plain) XS1 and Ø 8 (M8 x 1) XS5
- 3 Ø 12 (M12 x 1) XS5

		5	Sensing di	stance (n	nm)		
			15				
		2	10		2		
				1			
			8 1 5	1	****		
		11					
mm-15	-10	0 -7,5 -5	5 -2,5	0 2,5	5 7,5	10	15 mm

Sensor (mm)	Standard steel target (mm)	Operating zone (mm)	
Ø 18	18 x 18 x 1	04	
Ø 30	30 x 30 x 1	08	


- pick-up points
- --- drop-out points (object approaching from the side) 1 \varnothing 18 (M18 x 1) XS5 2 \varnothing 30 (M30 x 1.5) XS5

Non flush mountable in metal



Sensor (mm)	Standard steel target (mm)	Operating zone (mm)	
Ø 12	12 x 12 x 1	03.2	


- pick-up points
- drop-out points (object approaching from the side)
- 1 Ø 12 (M12 x 1) XS4



Sensor (mm)	Standard steel target (mm)	Operating zone (mm)
Ø 18	24 x 24 x 1	06.4
Ø 30	45 x 45 x 1	012

- pick-up points
- ---- drop-out points (object approaching from the side)
 1 Ø 18 (M18 x 1) XS4
- 2 Ø 30 (M30 x 1.5) XS4

Quasi-flush mountable in m	netal
----------------------------	-------



Sensor (mm)	Standard steel target (mm)	Operating zone (mm)
Ø 4	4 x 4 x 1	00.65
Ø 5	5 x 5 x 1	0 0.65

- 1 Ø 4
- 2 Ø 5


XS range

Cylindrical, standard range, basic sensors

Cylindrical type basic sensors

Ø8 sensors


Flush mountable in metal



Standard steel target (mm): 8 x 8 x 1 Operating zone (mm): 0...1.2

Ø 12 sensors


Flush mountable in metal



Standard steel target (mm): 12 x 12 x 1 Operating zone (mm): 0...1.6

Ø 18 sensors


Flush mountable in metal



Standard steel target (mm): 18 x 18 x 1


Operating zone (mm): 0...4 Ø 30 sensors

Flush mountable in metal




Standard steel target (mm): 30 x 30 x 1 Operating zone (mm): 0...8

Non flush mountable in metal




Standard steel target (mm): 8 x 8 x 1 Operating zone (mm): 0...2

Non flush mountable in metal




Standard steel target (mm): 12 x 12 x 1 Operating zone (mm): 0...3.2

Non flush mountable in metal



Standard steel target (mm): 24 x 24 x 1 Operating zone (mm): 0...6.4

Non flush mountable in metal




Standard steel target (mm): 45 x 45 x 1 Operating zone (mm): 0...12

pick-up points

--- drop-out points (object approaching from the side)

XS range


Cylindrical, increased range sensors



pick-up points

--- drop-out points (object approaching from the side)

XS range Cylindrical increased range, basic sensors



8 mm

2

Standard metal target (mm): 45 x 45 x 1

Operating zone (mm): 0...12

10

 $20\,mm$

Operating zone (mm): 0...6.4

Standard metal target (mm): 24 x 24 x 1


drop-out points (object approaching from the side)

XS range

Cubic, flat or rectangular sensors, standard range

Cubic, flat or rectangular type sensors


Flush mountable in metal



Sensor	Standard steel target (mm)	Operating zone (mm)	
XS7J1A1	5 x 5 x 1	02	

pick-up points


--- drop-out points (object approaching from the side)



Sensor	Standard steel target (mm)	Operating zone (mm)	
XS7F1A1	5 x 5 x 1	04	

pick-up points


---- drop-out points (object approaching from the side)



Sensor	Standard steel target (mm)	Operating zone (mm)
XS7E1A1	8 x 8 x 1	08

pick-up points


--- drop-out points (object approaching from the side)



Sensor	Standard steel target (mm)	Operating zone (mm)
XS7C1A1 XS7C2A1	18 x 18 x 1	012

pick-up points

---- drop-out points (object approaching from the side)




Sensor	Standard steel target (mm)	Operating zone (mm)
S7D1A1	30 x 30 x 1	032

pick-up points

- - - drop-out points (object approaching from the side)

XS range

Cubic or rectangular sensors, increased range



Old sensor	New XS sensor	Old sensor	New XS sensor	Old sensor	New XS sensor
Cylindrical type, DC		XS1L06NA340S	XS506B1NAM8	XS1M08NB370D	XS508BLNBM
Diameter 4 mm		XS1L06NB340	XS506B1NBL2	XS1M08PA370	XS508BLPAL2
(S1		XS1L06NB340S	XS506B1NBM8	XS1M08PA370D	XS508BLPAM1
(S1L04NA310	XS604R1NAL2	XS1L06PA340	XS506B1PAL2	XS1M08PA370L1	XS508BLPAL5
(S1L04NA310S	XS604R1NAM08	XS1L06PA340L1	XS506B1PAL5	XS1M08PA370L2	XS508BLPAL1
(S1L04NB310	XS604R1NBL2	XS1L06PA340D	XS506B1PAM12	XS1M08PA370LD	XS508BLPAM12
		XS1L06PA340S	XS506B1PAM8	XS1M08PA370S	XS508BLPAM1
(S1L04NB310S	XS604R1NBM08	XS1L06PB340	XS506B1PBL2	XS1M08PB370	XS508BLPBL2
(S1L04PA310	XS604R1PAL2	XS1L06PB340L1	XS506B1PBL5	XS1M08PB370D	XS508BLPBM
(S1L04PA310S	XS604R1PAM08	XS1L 06PB340S	XS506B1PBM8	XS1M08PB370L1	XS508BLPBL5
(S1L04PB310	XS604R1PBL2			XS1M08PB370L2	XS508BLPBL1
(S1L04PB310S	XS604R1PBM08				
		XS1L06NA349	XS106B3NAL2		
		XS1L06NA349S	XS106B3NAM8	XS1N08NA340	XS508B1NAL2
(S1L04NA311	XS504R1NAL2	XS1L06NB349	XS106B3NBL2	XS1N08NA340D	XS508B1NAM1
(S1L04NA311S	XS504R1NAM08	XS1L06NB349S	XS106B3NBM8	XS1N08NA340L1	XS508B1NAL5
	XS504R1NBL2	XS1L06PA349	XS106B3PAL2	XS1N08NA340L2	XS508B1NAL10
(S1L04NB311		XS1L06PA349L1	XS106B3PAL5	XS1N08NA340S	XS508B1NAM8
(S1L04NB311S	XS504R1NBM08	XS1L06PA349D	XS106B3PAM12	XS1N08NB340	XS508B1NBL2
(S1L04PA311	XS504R1PAL2	XS1L06PA349S	XS106B3PAM8	XS1N08NB340D	XS508B1NBM1
(S1L04PA311S	XS504R1PAM08	XS1L06PB349	XS106B3PBL2	XS1N08NB340S	XS508B1NBM8
S1L04PB311	XS504R1PBL2	XS1L06PB349L1	XS106B3PBL5	XS1N08PA340	XS508B1PAL2
S1L04PB311S	XS504R1PBM08	XS1L06PB349S	XS106B3PBM8	XS1N08PA340D	XS508B1PAM1
		X672007 B0700	ACTOODOL DING		
				XS1N08PA340L1	XS508B1PAL5
iameter 5 mm		Dit0		XS1N08PA340L2	XS508B1PAL10
		Diameter 8 mm		XS1N08PA340LD	XS508B1PAM1
(S1		XS1	VC400DI NALO	XS1N08PA340S	XS508B1PAM8
(S1N05NA310	XS605R1NAL2	XS1D08NA140	XS108BLNAL2	XS1N08PB340	XS508B1PBL2
(S1N05NA310S	XS605R1NAM08	XS1D08NA140D	XS108BLNAM12	XS1N08PB340D	XS508B1PBM1
(S1N05NB310	XS605R1NBL2	XS1D08PA140	XS108BLPAL2	XS1N08PB340L1	XS508B1PBL5
(S1N05NB310S	XS605R1NBM08	XS1D08PA140D	XS108BLPAM12	XS1N08PB340L2	XS508B1PBL10
S1N05PA310	XS605R1PAL2	XS1D08PA140L1	XS108BLPAL5	XS1N08PB340S	XS508B1PBM8
(S1N05PA310L1	XS605R1PAL5			XS1N08NA349	XS108B3NAL2
(S1N05PA310S	XS605R1PAM08	V041400D 4040	VCENODADAL O	XS1N08NA349L1	XS108B3NAL2
(S1N05PB310	XS605R1PBL2	XS1M08DA210	XS508B1DAL2	XS1N08NA349D	XS108B3NAM
(S1N05PB310S	XS605R1PBM08	XS1M08DA210D	XS508B1DAM12	XS1N08NA349D XS1N08NA349S	XS108B3NAM
		XS1M08DA210L1	XS508B1DAL5	XS1N08NB349	XS108B3NBL2
		XS1M08DA210L2	XS508B1DAL10		
(0.11)0511.5	V0=0===	XS1M08DA210LD	XS508B1DAL08M12	XS1N08NB349L1 YS1N08NB349D	XS108B3NBL5
(S1N05NA311	XS505R1NAL2	XS1M08DB210	XS508B1DBL2	XS1N08NB349D	XS108B3NBM
(S1N05NA311S	XS505R1NAM08	XS1M08DB210D	XS508B1DBM12	XS1N08NB349S	XS108B3NBM
(S1N05NB311	XS505R1NBL2	XS1M08DB210L1	XS508B1DBL5	XS1N08PA349	XS108B3PAL2
(S1N05NB311S	XS505R1NBM08	XS1M08DB210LD	XS508B1DBM12 (1)	XS1N08PA349L1	XS108B3PAL5
S1N05PA311	XS505R1PAL2			XS1N08PA349D	XS108B3PAM
S1N05PA311S	XS505R1PAM08			XS1N08PA349S	XS108B3PAM
(S1N05PB311	XS505R1PBL2	XS1M08DA214D	XS508B1CAM12	XS1N08PB349	XS108B3PBL2
		XS1M08DA214LD	XS508B1CAL08M12	XS1N08PB349L1	XS108B3PBL5
(S1N05PB311S	XS505R1PBM08			XS1N08PB349D	XS108B3PBM
				XS1N08PB349S	XS108B3PBM
		XS1M08NA370	XS508BLNAL2		
Diameter 6.5 mm		XS1M08NA370D	XS508BLNAM12		
(S1		XS1M08NA370L1	XS508BLNAL5		
(S1L06NA340	XS506B1NAL2	XS1M08NB370	XS508BLNBL2		

⁽¹⁾ For the new sensor an integral M12 connector replaces the remote M12 connector on a 0.80 m flying lead.
(2) For the new sensor an M12 connector replaces the M8 connector.
(3) For the new sensor, the metal case replaces the plastic case.

Inductive proximity sensors

Old sensor	New XS sensor	Old sensor	New XS sensor	Old sensor	New XS sensor
Cylindrical type, DC ((continued)	XS1M12NA370L1	XS512BLNAL5	XS2M12NA370D	XS612B1NAM12
KS2		XS1M12NA370L2	XS512BLNAL10	XS2M12NA370L1	XS612B1NAL5
XS2M08NA340	XS608B1NAL2	XS1M12NA370S	XS612B1NAM12 (2)	XS2M12NA370L2	XS612B1NAL10
XS2N08NA340	XS108B3NAL2	XS1M12NB370	XS512BLNBL2	XS2M12NB370	XS612B1NBL2
XS2N08NA340D	XS108B3NAM12	XS1M12NB370D	XS512BLNBM12	XS2M12NB370D	XS612B1NBM12
XS2N08NA340L1	XS108B3NAL5	XS1M12PA370	XS512BLPAL2	XS2M12PA370	XS612B1PAL2
XS2N08NA340L2	XS108B3NAL10	XS1M12PA370D	XS512BLPAM12	XS2M12PA370D	XS612B1PAM12
XS2N08NA340S	XS108B3NAM8	XS1M12PA370L1	XS512BLPAL5	XS2M12PA370L1	XS612B1PAL5
XS2N08NB340	XS108B3NBL2	XS1M12PA370L2	XS512BLPAL10	XS2M12PA370L2	XS612B1PAL10
XS2N08NB340D	XS108B3NBM12	XS1M12PA370LA	XS612B1PAL08U78	XS2M12PA370LA	XS612B1PAL08U78
XS2N08NB340S	XS108B3NBM8	XS1M12PA370LD	XS612B1PAL08M12	XS2M12PA370LD	XS612B1PAL08M12
XS2N08PA340	XS108B3PAL2	XS1M12PB370	XS512BLPBL2	XS2M12PB370	XS612B1PBL2
XS2N08PA340D	XS108B3PAM12	XS1M12PB370D	XS512BLPBM12	XS2M12PB370D	XS612B1PBM12
XS2N08PA340L1	XS108B3PAL5	XS1M12PB370L1	XS512BLPBL5	XS2M12PB370L1	XS612B1PBL5
XS2N08PA340L2	XS108B3PAL10	XS1M12PB370L2	XS512BLPBL10	XS2M12PB370S	XS612B1PBM12 (2)
XS2N08PA340S	XS108B3PAM8	XS1M12PB370LD	XS612B1PAM12 (1)		(-)
XS2N08PB340	XS108B3PBL2		()	XS2N12NA340	XS112B3NAL2
XS2N08PB340D	XS108B3PBM12			XS2N12NA340D	XS112B3NAM12
XS2N08PB340S	XS108B3PBM8	XS1N12NA340	XS512B1NAL2	XS2N12NA340L1	XS112B3NAL5
		XS1N12NA340D	XS512B1NAM12	XS2N12NA340L2	XS112B3NAL10
XS3		XS1N12NA340L1	XS512B1NAL5	XS2N12NB340	XS112B3NBL2
XS3P08NA340	XS508B1NAL2 (3)	XS1N12NA340L2	XS512B1NAL10	XS2N12NB340D	XS112B3NBM12
XS3P08NA340D	XS508B1NAM12 (3)	XS1N12NB340	XS512B1NBL2	XS2N12NC410L1	XS2N12NC410D
KS3P08NA340L1	XS508B1NAL5 (3)	XS1N12NB340D	XS512B1NBM12	XOZIVIZIVOTIOLI	+ XZCPV1141L5
XS3P08PA340	XS508B1PAL2 (3)	XS1N12NC410L2	XS1N12NC410D	XS2N12PA340	XS112B3PAL2
KS3P08PA340D	XS508B1PAM12 (3)	XOTIVIZIVO+TOLZ	+ XZCPV1141L10	XS2N12PA340D	XS112B3PAM12
	. ,	XS1N12PA340	XS512B1PAL2	XS2N12PA340L1	XS112B3PAL5
XS3P08PA340L1	XS508B1PAL5 (3)	XS1N12PA340D	XS512B1PAM12	XS2N12PA340L2	XS112B3PAL10
VC2D00NA270	VCEOCRI NALO (2)	XS1N12PA340L1	XS512B1PAL5	XS2N12PC410	XS112B3PCL2
XS3P08NA370	XS508BLNAL2 (3)	XS1N12PA340L2	XS512B1PAL10	XS2N12PC410D	XS112B3PCM12
XS3P08NA370L1	XS508BLNAL5 (3)	XS1N12PA340LD	XS512B1PAM12 (1)	XS2N12PC410L1	XS112B3PCM12
XS3P08PA370	XS508BLPAL2 (3)	XS1N12PA340S	XS512B1PAM12 (2)		+ XZCPV1141L5
XS3P08PA370L1	XS508BLPAL5 (3)	XS1N12PB340	XS512B1PBL2	XS2N12PC410L2	XS112B3PCM12
		XS1N12PB340D	XS512B1PBM12		+ XZCPV1141L10
Diameter 12 mm		XS1N12PB340L1	XS512B1PBL5	XS2N12PB340	XS112B3PBL2
XS1				XS2N12PB340D	XS112B3PBM12
XS1M12DA210	XS512B1DAL2	XS1M12PA349D	XS612B1PAM12	XS2N12PB340L1	XS112B3PBL5
XS1M12DA210D	XS512B1DAM12	XS1N12NA349	XS112B3NAL2		
XS1M12DA210L1	XS512B1DAL5	XS1N12NA349L1	XS112B3NAL5	XS3	
XS1M12DA210L2	XS512B1DAL10	XS1N12NA349L1 XS1N12NA349D	XS112B3NAM12	XS3P12NA340	XS512B1NAL2 (3)
XS1M12DA210LA	XS512B1DAL08U78	XS1N12NA349D XS1N12NB349	XS112B3NBL2	XS3P12NA340D	XS512B1NAM12 (3)
XS1M12DA210LD	XS512B1DAL08M12			XS3P12NA340L1	XS512B1NAL5 (3)
XS1M12DB210	XS512B1DBL2	XS1N12NB349L1	XS112B3NBL5	XS3P12PA340	XS512B1PAL2 (3)
XS1M12DB210D	XS512B1DBM12	XS1N12NB349D	XS112B3NBM12	XS3P12PA340D	XS512B1PAM12 (3)
XS1M12DB210L1	XS512B1DBL5	XS1N12PA349	XS112B3PAL2	XS3P12PA340L1	XS512B1PAL5 (3)
XS1M12DB210L2	XS512B1DBL10	XS1N12PA349L1	XS112B3PAL5		
XS1M12DB210LD	XS512B1DBL08M12	XS1N12PA349D	XS112B3PAM12	XS3P12NA370	XS512BLNAL2 (3)
		XS1N12PB349	XS112B3PBL2	XS3P12NA370L1	XS512BLNAL5 (3)
XS1M12DA214D	XS512B1CAM12	XS1N12PB349L1	XS112B3PBL5	XS3P12PA370	XS512BLPAL2 (3)
XS1M12DA214LD	XS512B1CAL08M12	XS1N12PB349D	XS112B3PBM12	XS3P12PA370L1	XS512BLPAL5 (3)
XS1M12NA370	XS512BLNAL2			XS4	

⁽¹⁾ For the new sensor an integral M12 connector replaces the remote M12 connector on a 0.80 m flying lead.
(2) For the new sensor an M12 connector replaces the M8 connector.
(3) For the new sensor, the metal case replaces the plastic case.

Inductive proximity sensors

Old sensor	New XS sensor	Old sensor	New XS sensor	Old sensor	New XS sensor
Cylindrical type, DC	(continued)	XS1		XS2M18NB370	XS618B1NBL2
Diameter 18 mm		XS1M18PB370D	XS518BLPBM12		
XS1		XS1M18PB370L1	XS518BLPBL5	XS2M18NB370B	XS618B1NBL01B (4)
XS1M18DA210	XS518B1DAL2	XS1M18PB370L2	XS518BLPBL10	XS2M18NB370C	XS618B1NBL01C (4)
XS1M18DA210B	XS518B1DAL01B (4)	XS1M18PB370C	XS618B1PBL01C (4)	XS2M18NB370D	XS618B1NBM12
XS1M18DA210C	XS518B1DAL01C (4)			XS2M18NB370L1	XS618B1NBL5
XS1M18DA210D	XS518B1DAM12			XS2M18NB370L2	XS618B1NBL10
XS1M18DA210G	XS518B1DAL01G (4)	XS1N18NA340	XS518B1NAL2	XS2M18PA370	XS618B1PAL2
XS1M18DA210L1	XS518B1DAL5	XS1N18NA340D	XS518B1NAM12	XS2M18PA370A	XS618B1PAL01U78 (4
XS1M18DA210L2	XS518B1DAL10	XS1N18NA340L1	XS518B1NAL5	XS2M18PA370B	XS618B1PAL01B (4)
XS1M18DA210LD	XS518B1DAL08M12	XS1N18NA340L2	XS518B1NAL10	XS2M18PA370C	XS618B1PAL01C (4)
XS1M18DB210	XS518B1DBL2	XS1N18NB340	XS518B1NBL2	XS2M18PA370D	XS618B1PAM12
XS1M18DB210B	XS518B1DBL01B (4)	XS1N18NB340D	XS518B1NBM12	XS2M18PA370G	XS618B1PAL01G (4)
XS1M18DB210D	XS518B1DBM12	XS1N18NB340L2	XS518B1NBL10	XS2M18PA370LA	XS618B1PAL08U78 (4
XS1M18DB210LD	XS518B1DBL08M12	XS1N18NC410L1	XS1N18NC410D	XS2M18PA370L1	XS618B1PAL5
			+ XZCPV1141L5	XS2M18PA370L2	XS618B1PAL10
		XS1N18PA340	XS518B1PAL2	XS2M18PB370	XS618B1PBL2
XS1M18DA214D	XS518B1CAM12	XS1N18PA340D	XS518B1PAM12	XS2M18PB370A	XS618B1PBL01U78 (
XS1M18DA214LD	XS518B1CAL08M12	XS1N18PA340L1	XS518B1PAL5	XS2M18PB370B	XS618B1PBL01B (4)
NO TIMPODALET TED	AGG TOD TO ALCOMITE	XS1N18PA340L2	XS518B1PAL10	XS2M18PB370C	XS618B1PBL01C (4)
		XS1N18PB340	XS518B1PBL2	XS2M18PB370D	XS618B1PBM12
XS1M18NA370	XS518BLNAL2	XS1N18PB340D	XS518B1PBM12	XS2M18PB370L1	XS618B1PBL5
XS1M18NA370A	XS618B1NAL01U78 (4)	XS1N18PB340L2	XS518B1PBL10	XS2M18PB370L2	XS618B1PBL10
XS1M18NA370A	XS618B1NAL01B (4)			A SZIWITOF BSTOLZ	AGGIODIFDEIG
XS1M18NA370C	XS618B1NAL01C (4)				
	. ,				
XS1M18NA370D	XS518BLNAM12				
XS1M18NA370L1	XS518BLNAL5	XS2		Y00	
XS1M18NA370L2	XS518BLNAL10	XS2N18NA340	XS118B3NAL2	XS3	V0540B4NALQ (0)
XS1M18NB370	XS518BLNBL2	XS2N18NA340D	XS118B3NAM12	XS3P18NA340	XS518B1NAL2 (3)
XS1M18NB370B	XS618B1NBL01B (4)	XS2N18NA340L1	XS118B3NAL5	XS3P18NA340D	XS518B1NAM12 (3)
XS1M18NB370C	XS618B1NBL01C (4)	XS2N18NA340L2	XS118B3NAL10	XS3P18NA340L1	XS518B1NAL5 (3)
XS1M18NB370D	XS518BLNBM12	XS2N18NB340	XS118B3NBL2	XS3P18PA340	XS518B1PAL2 (3)
XS1M18NB370L1	XS518BLNBL5	XS2N18NC410L2	XS2N18NC410D	XS3P18PA340D	XS518B1PAM12 (3)
XS1M18NB370L2	XS518BLNBL10	7.02.77077077022	+ XZCPV1141L10	XS3P18PA340L1	XS518B1PAL5 (3)
XS1M18PA370	XS518BLPAL2	XS2N18PC410	XS118B3PCL2	XS3P18NA370	XS518BLNAL2 (3)
XS1M18PA370A	XS618B1PAL01U78 (4)	XS2N18PC410D	XS118B3PCM12	XS3P18NA370L1	XS518BLNAL5 (3)
XS1M18PA370B	XS618B1PAL01B (4)	XS2N18PC410L1	XS118B3PCM12	XS3P18PA370	XS518BLPAL2 (3)
XS1M18PA370C	XS618B1PAL01C (4)		+ XZCPV1141L5	XS3P18PA370L1	XS518BLPAL5 (3)
XS1M18PA370D	XS518BLPAM12	XS2N18NB340D	XS118B3NBM12	XS3P18PA370L2	XS518BLPAL10 (3)
XS1M18PA370G	XS618B1PAL01G (4)	XS2N18PA340	XS118B3PAL2		
XS1M18PA370DTQ	XS518BLPAM12TQ	XS2N18PA340D	XS118B3PAM12		
XS1M18PA370G	XS618B1PAL01G (4)	XS2N18PA340L1	XS118B3PAL5		
XS1M18PA370L1	XS518BLPAL5	XS2N18PA340L2	XS118B3PAL10	XS4	
XS1M18PA370L2	XS518BLPAL10	XS2N18PB340	XS118B3PBL2	XS4P18NA370B	XS4P18NA370L01B (
XS1M18PA370LA	XS618B1PAL08U78	XS2N18PB340D	XS118B3PBM12	XS4P18NB370B	XS4P18NB370L01B (
XS1M18PA370LD	XS518BLPAM12 (1)	XS2M18NA370	XS618B1NAL2	XS4P18PA370B	XS4P18PA370L01B (4
XS1M18PA370DTQ	XS518BLPAM12TQ	XS2M18NA370A	XS618B1NAL01U78 (4)	XS4P18PB370B	XS4P18PB370L01B (
XS1M18PA370TF	XS518BLPAL2TF	XS2M18NA370B	XS618B1NAL01B (4)	XS4P18PC410L1	XS4P18PC410D
XS1M18PB370	XS518BLPBL2	XS2M18NA370C	XS618B1NAL01C (4)		+ XZCPV1141L5
XS1M18PB370A	XS618B1PBL01U78 (4)	XS2M18NA370D	XS618B1NAM12		
V0.4440DD070D	XS618B1PBL01B (4)	XS2M18NA370L1	XS618B1NAL5		
XS1M18PB370B					

⁽¹⁾ For the new sensor an integral M12 connector replaces the remote M12 connector on a 0.80 m flying lead.
(3) For the new sensor, the metal case replaces the plastic case.
(4) For the new sensor, connectors A, B, C and G on 0.1 m flying lead replace integral connectors A, B, C and G.

Inductive proximity sensors

Old sensor	New XS sensor	Old sensor	New XS sensor	Old sensor	New XS sensor
Cylindrical type, DC	(continued)	XS1N30NA340	XS530B1NAL2	XS2M30PA370G	XS630B1PAL01G (4)
Diameter 30 mm		XS1N30NA340D	XS530B1NAM12	XS2M30PA370L1	XS630B1PAL5
XS1		XS1N30NA340L1	XS530B1NAL5	XS2M30PA370L2	XS630B1PAL10
XS1M30DA210	XS530B1DAL2	XS1N30NA340L2	XS530B1NAL10	XS2M30PB370	XS630B1PBL2
XS1M30DA210B	XS530B1DAL01B (4)	XS1N30NB340	XS530B1NBL2	XS2M30PB370B	XS630B1PBL01B (4)
XS1M30DA210C	XS530B1DAL01C (4)	XS1N30NB340D	XS530B1NBM12	XS2M30PB370C	XS630B1PBL01C (4)
XS1M30DA210D	XS530B1DAM12	XS1N30PA340	XS530B1PAL2	XS2M30PB370D	XS630B1PBM12
XS1M30DA210G	XS530B1DAL01G (4)	XS1N30PA340D	XS530B1PAM12	XS2M30PB370G	XS630B1PBL01G (4)
XS1M30DA210L1	XS530B1DAL5	XS1N30PA340L1	XS530B1PAL5	XS2M30PB370L1	XS630B1PBL5
XS1M30DA210L2	XS530B1DAL10	XS1N30PA340L2	XS530B1PAL10	XS2M30PB370L2	XS630B1PBL10
XS1M30DA210LD	XS530B1DAL08M12	XS1N30PB340	XS530B1PBL2		
XS1M30DB210	XS530B1DBL2	XS1N30PB340D	XS530B1PBM12		
XS1M30DB210B	XS530B1DBL01B (4)				
XS1M30DB210D	XS530B1DBM12				
XS1M30DB210LD	XS530B1DBM12 (1)	XS2			
		XS2N30NA340	XS130B3NAL2		
		XS2N30NA340D	XS130B3NAM12	XS3	
XS1M30DA214D	XS530B1CAM12	XS2N30NA340L1	XS130B3NAL5	XS3P30NA340	XS530B1NAL2 (3)
XS1M30DA214D XS1M30DA214LD	XS530B1CAM12 XS530B1CAL08M12	XS2N30NA340L1 XS2N30NA340L2	XS130B3NAL5 XS130B3NAL10	XS3P30NA340 XS3P30NA340D	XS530B1NAL2 (3) XS530B1NAM12 (3)
KS TMISUDA 2 T4LD	X3330BTCALUOWITZ		XS130B3NBL10 XS130B3NBL2		. ,
		XS2N30NB340		XS3P30NA340L1	XS530B1NAL5 (3)
VO41400D4040D	VOCCOPARAMAC (5)	XS2N30NC410L1	XS2N30NC410D + XZCPV1141L5	XS3P30PA340	XS530B1PAL2 (3)
KS1M30PA349D	XS630B1PAM12 (5)	XS2N30PC410	XS130B3PCL2	XS3P30PA340D	XS530B1PAM12 (3)
		XS2N30PC410D	XS130B3PCM12	XS3P30PA340L1	XS530B1PAL5 (3)
KS1M30NA370	XS530BLNAL2	XS2N30PC410L1	XS130B3PCM12 + XZCPV1141L5	XS3P30PA340L2	XS530B1PAL10 (3)
KS1M30NA370B	XS630B1NAL01B (4)	XS2N30NB340D	XS130B3NBM12	XS3P30PA370	XS530BLPAL2 (3)
XS1M30NA370C	XS630B1NAL01C (4)	XS2N30PA340	XS130B3PAL2	XS3P30PA370L1	XS530BLPAL5 (3)
XS1M30NA370D	XS530BLNAM12	XS2N30PA340D		XS3P30PA370L2	XS530BLPAL10 (3)
XS1M30NA370L1	XS530BLNAL5	XS2N30PA340L1	XS130B3PAM12	XS3P30NA370	XS530BLNAL2 (3)
XS1M30NA370L2	XS530BLNAL10		XS130B3PAL5	XS3P30NA370L1	XS530BLNAL5 (3)
XS1M30NB370	XS530BLNBL2	XS2N30PA340L2	XS130B3PAL10		
XS1M30NB370B	XS630B1NBL01B (4)	XS2N30PB340	XS130B3PBL2		
XS1M30NB370C	XS630B1NBL01C (4)	XS2N30PB340D	XS130B3PBM12		
XS1M30NB370D	XS530BLNBM12				
XS1M30NB370L1	XS530BLNBL5	V001400	V0000 411		
XS1M30NB370L2	XS530BLNBL10	XS2M30NA370	XS630B1NAL2		
XS1M30PA370	XS530BLPAL2	XS2M30NA370B	XS630B1NAL01B (4)	XS4	
XS1M30PA370A	XS630B1PAL01U78 (4)	XS2M30NA370C	XS630B1NAL01C (4)	XS4P30NA370B	XS4P30NA370L01B (4
XS1M30PA370B	XS630B1PAL01B (4)	XS2M30NA370D	XS630B1NAM12	XS4P30NB370B	XS4P30NB370L01B (4
XS1M30PA370C	XS630B1PAL01C (4)	XS2M30NA370L1	XS630B1NAL5	XS4P30NC410L2	XS4P30NC410D
XS1M30PA370D	XS530BLPAM12	XS2M30NA370L2	XS630B1NAL10		+ XZCPV1141L10
KS1M30PA370G	XS630B1PAL01G (4)	XS2M30NB370	XS630B1NBL2	XS4P30PA370B	XS4P30PA370L01B (4
XS1M30PA370L1	XS530BLPAL5	XS2M30NB370B	XS630B1NBL01B (4)	XS4P30PB370B	XS4P30PB370L01B (4
KS1M30PA370L2	XS530BLPAL10	XS2M30NB370C	XS630B1NBL01C (4)	XS4P30PC410L1	XS4P30PC410D
XS1M30PA370L2 XS1M30PB370	XS530BLPBL2	XS2M30NB370D	XS630B1NBM12		+ XZCPV1141L5
		XS2M30NB370L1	XS630B1NBL5	XS4P30PC410L2	XS4P30PC410D + XZCPV1141L10
XS1M30PB370B	XS630B1PBL01B (4)	XS2M30NB370L2	XS630B1NBL10	T.	+ XZCPV1141L10
XS1M30PB370C	XS630B1PBL01C (4)	XS2M30PA370	XS630B1PAL2		
XS1M30PB370D	XS530BLPBM12	XS2M30PA370A	XS630B1PAL01U78 (4)		
XS1M30PB370G	XS630B1PBL01G (4)	XS2M30PA370B	XS630B1PAL01B (4)		
XS1M30PB370L1	XS530BLPBL5	XS2M30PA370C	XS630B1PAL01C (4)		
XS1M30PB370L2	XS530BLPBL10	XS2M30PA370D	XS630B1PAM12		

⁽¹⁾ For the new sensor an integral M12 connector replaces the remote M12 connector on a 0.80 m flying lead.
(3) For the new sensor, the metal case replaces the plastic case.
(4) For the new sensor, connectors A, B, C and G on 0.1 m flying lead replace integral connectors A, B, C and G.
(5) For the new sensor, Sn = 15 mm instead of 20 mm.

Inductive proximity sensors

Old sensor	New XS sensor	Old sensor	New XS sensor	Old sensor	New XS sensor		
Cylindrical type, AC or	r DC	Diameter 18 mm (contin	nued)	Diameter 30 mm (contin	Diameter 30 mm (continued)		
Diameter 12 mm		XS1		XS1M30MB230C	XS630B1MBL01C (4)		
XS1		XS1M18MA239A	XS1M18MA239L01A (4)	XS1M30MB230G	XS630B1MBL01G (4)		
XS1M12MA230	XS512B1MAL2	XS1M18MA239K	XS618B1MAU20 (5)	XS1M30MB230K	XS530B1MBU20		
XS1M12MA230K	XS512B1MAU20			XS1M30MB230L1	XS530B1MBL5		
XS1M12MA230L1	XS512B1MAL5	XS2		XS1M30MB230L2	XS530B1MBL10		
XS1M12MA230L2	XS512B1MAL10	XS2M18MA230	XS618B1MAL2				
XS1M12MB230	XS512B1MBL2	XS2M18MA230A	XS618B1MAL01U78 (4)	XS1M30MA239	XS630B1MAL2 (5)		
XS1M12MB230K	XS512B1MBU20	XS2M18MA230B	XS618B1MAL01B (4)	XS1M30MA239A	XS1M30MA239L01A (4)		
XS1M12MB230L1	XS512B1MBL5	XS2M18MA230C	XS618B1MAL01C (4)				
XS1M12MB230L2	XS512B1MBL10	XS2M18MA230G	XS618B1MAL01G (4)				
		XS2M18MA230K	XS618B1MAU20	XS2			
XS1M12MA239	XS612B1MAL2	XS2M18MA230L1	XS618B1MAL5	XS2M30MA230	XS630B1MAL2		
XS1M12MA239K	XS612B1MAU20	XS2M18MA230L2	XS618B1MAL10	XS2M30MA230A	XS630B1MAL01U78 (4)		
		XS2M18MB230	XS618B1MBL2	XS2M30MA230B	XS630B1MAL01B (4)		
XS2		XS2M18MB230A	XS618B1MBL01U78 (4)	XS2M30MA230C	XS630B1MAL01C (4)		
XS2M12MA230	XS612B1MAL2	XS2M18MB230B	XS618B1MBL01B (4)	XS2M30MA230G	XS630B1MAL01G (4)		
XS2M12MA230K	XS612B1MAU20	XS2M18MB230C	XS618B1MBL01C (4)	XS2M30MA230K	XS630B1MAU20		
XS2M12MA230L1	XS612B1MAL5	XS2M18MB230G	XS618B1MBL01G (4)	XS2M30MA230L1	XS630B1MAL5		
XS2M12MA230L2	XS612B1MAL10	XS2M18MB230K	XS618B1MBU20	XS2M30MA230L2	XS630B1MAL10		
XS2M12MB230	XS612B1MBL2	XS2M18MB230L1	XS618B1MBL5	XS2M30MB230	XS630B1MBL2		
XS2M12MB230K	XS612B1MBU20	XS2M18MB230L2	XS618B1MBL10	XS2M30MB230A	XS630B1MBL01U78 (4)		
XS2M12MB230L1	XS612B1MBL5			XS2M30MB230B	XS630B1MBL01B (4)		
XS2M12MB230L2	XS612B1MBL10	XS3		XS2M30MB230C	XS630B1MBL01C (4)		
7.02.M.12.M.220012	7,001,201,110	XS3P18MA230	XS618B1MAL2 (3)	XS2M30MB230G	XS630B1MBL01G (4)		
XS3		XS3P18MA230K	XS618B1MAU20 (3)	XS2M30MB230K	XS630B1MBU20		
XS3P12MA230	XS612B1MAL2 (3)	XS3P18MA230L1	XS618B1MAL5 (3)	XS2M30MB230L1	XS630B1MBL5		
XS3P12MA230K	XS612B1MAU20 (3)	XS3P18MA230L2	XS618B1MAL10 (3)	XS2M30MB230L2	XS630B1MBL10		
XS3P12MA230L1	XS612B1MAL5 (3)	XS3P18MB230	XS618B1MBL2 (3)				
XS3P12MA230L2	XS612B1MAL10 (3)	XS3P18MB230A	XS618B1MBU20 (3)	XS3			
XS3P12MB230	XS612B1MBL2 (3)	XS3P18MB230K	XS618B1MBU20 (3)	XS3P30MA230	XS630B1MAL2 (3)		
XS3P12MB230K	XS612B1MBU20 (3)	XS3P18MB230L1	XS618B1MBL5 (3)	XS3P30MA230K	XS630B1MAU20 (3)		
XS3P12MB230L1	XS612B1MBL5 (3)		1,00	XS3P30MA230L1	XS630B1MAL5 (3)		
XOOF TEMBEOOLT	X0012511115120 (0)	XS4		XS3P30MA230L2	XS630B1MAL10 (3)		
Diameter 18 mm		XS4P18MA230B	XS4P18MA230L01B (4)	XS3P30MB230	XS630B1MBL2 (3)		
XS1		XS4P18MA230C	XS4P18MA230L01C (4)	XS3P30MB230K	XS630B1MBU20 (3)		
XS1M18MA230	XS518B1MAL2	XS4P18MA230G	XS4P18MA230L01G (4)	XS3P30MB230L1	XS630B1MBL5 (3)		
XS1M18MA230A	XS618B1MAL01U78 (4)	XS4P18MB230B	XS4P18MB230L01B (4)				
XS1M18MA230B	XS618B1MAL01B (4)	XS4P18MB230C	XS4P18MB230L01C (4)				
XS1M18MA230C	XS618B1MAL01C (4)	7.6 7622666	70 H 10HH2202010 (1)	XS4			
XS1M18MA230G	XS618B1MAL01G (4)	Diameter 30 mm		XS4P30MA230B	XS4P30MA230L01B (4)		
XS1M18MA230K	XS518B1MAU20	XS1		XS4P30MA230C	XS4P30MA230L01C (4)		
XS1M18MA230L1	XS518B1MAU5	XS1M30MA230	XS530B1MAL2	XS4P30MA230G	XS4P30MA230L01G (4)		
XS1M18MA230L1 XS1M18MA230L2	XS518B1MAL10	XS1M30MA230A	XS630B1MAL01U78 (4)	XS4P30MB230B	XS4P30MB230L01B (4)		
XS1M18MB230 XS1M18MB230	XS518B1MBL2	XS1M30MA230B	XS630B1MAL01B (4)	XS4P30MB230C	XS4P30MB230L01C (4)		
XS1M18MB230A	XS618B1MBL01U78 (4)	XS1M30MA230C	XS630B1MAL01C (4)	NO II GOMBEGGO	XO41 COMBECCEO (1)		
XS1M18MB230A XS1M18MB230B	XS618B1MBL01B (4)	XS1M30MA230G	XS630B1MAL01G (4)				
	. ,	XS1M30MA230K	XS530B1MAU20				
XS1M18MB230C	XS618B1MBL01C (4)	XS1M30MA230L1	XS530B1MAL5				
XS1M18MB230G XS1M18MB230K	XS618B1MBL01G (4)	XS1M30MA230L1 XS1M30MA230L2	XS530B1MAL10				
XS1M18MB230K	XS518B1MBU20	XS1M30MB230 XS1M30MB230	XS530B1MBL2				
XS1M18MB230L1	XS518B1MBL5	XS1M30MB230A	XS630B1MBL01U78 (4)				
XS1M18MB230L2	XS518B1MBL10						

⁽³⁾ For the new sensor, the metal case replaces the plastic case.
(4) For the new sensor, connectors A, B, C and G on 0.1 m flying lead replace integral connectors A, B, C and G.
(5) For the new sensor, Sn = 8 mm instead of 10 mm.

Inductive proximity sensors

Old sensor	New XS sensor	Old sensor	New XS sensor
Block type		40 x 40 x 70 mm and 40 x	40 x 117 mm (continued)
40 x 40 x 70 mm and 40 x	40 x 117 mm	XS8	
XS7		XS8C40DA210	XS8C4A1DPG13
XS7C40DA210	XS7C4A1DPG13	XS8C40DA210H29	XS8C4A1DPP20
XS7C40DA210A	XS7C4A1DPU78	XS8C40DA214D	XS8C4A1DPM12
XS7C40DA210D	XS7C4A1DPM12	XS8C40DP210	XS8C4A1DPG13
XS7C40DA210H29	XS7C4A1DPP20	XS8C40DP210H29	XS8C4A1DPP20
XS7C40DA210H7	XS7C4A1DPN12	XS8C40DP210H7	XS8C4A1DPN12
XS7C40DA214D	XS7C4A1DPM12	XS8C40FP260	XS8C4A1MPG13
XS7C40DP210	XS7C4A1DPG13	XS8C40FP260H29	XS8C4A1MPP20
XS7C40DP210H29	XS7C4A1DPP20	XS8C40FP260H7	XS8C4A1MPN12
XS7C40DP210H7	XS7C4A1DPN12	XS8C40MP230	XS8C4A1MPG13
XS7C40FP260	XS7C4A1MPG13	XS8C40MP230H29	XS8C4A1MPP20
XS7C40FP260A	XS7C4A1MPU78	XS8C40MP230H7	XS8C4A1MPN12
XS7C40FP260H29	XS7C4A1MPP20	XS8C40NC440	XS8C4A1NCG13
XS7C40FP260H7	XS7C4A1MPN12	XS8C40NC440H29	XS8C4A1NCP20
XS7C40KPM40	XS9C4A1PCG13	XS8C40NC449	XS8C4A4NCG13
XS7C40KPM40H29	XS9C4A1PCP20	XS8C40NC449H29	XS8C4A4NCP20
XS7C40KPM40H7	XS9C4A1PCN12	XS8C40NC449H7	XS8C4A4NCN12
XS7C40MP230	XS7C4A1MPG13	XS8C40PC440	XS8C4A1PCG13
XS7C40MP230A	XS7C4A1MPU78	XS8C40PC440D	XS8C4A1PCM12
XS7C40MP230H29	XS7C4A1MPP20	XS8C40PC440H29	XS8C4A1PCP20
XS7C40MP230H7	XS7C4A1MPN12	XS8C40PC440H7	XS8C4A1PCN12
XS7C40NC440	XS8C4A1NCG13	XS8C40PC449	XS8C4A4PCG13
XS7C40NC440D	XS8C4A1NCM12	XS8C40PC449D	XS8C4A4PCM12
XS7C40NC440H29	XS8C4A1NCP20	XS8C40PC449H29	XS8C4A4PCP20
XS7C40NC440H7	XS8C4A1NCN12	XS8C40PC449H7	XS8C4A4PCN12
XS7C40NC449	XS8C4A1NCG13	XS8T4NC440	XS8C2A1NCM12 + XZCP1141L2
XS7C40NC449H29	XS8C4A1NCP20	XS8T4NC440LD01	XS8C2A1NCM12
XS7C40NC449H7	XS8C4A1NCN12	XS8T4PC440	XS8C2A1PCM12
XS7C40PC440	XS8C4A1PCG13	X3014F 0440	+ XZCP1141L2
XS7C40PC440D	XS8C4A1PCM12	XS8T4PC440L1	XS8C2A1PCM12
XS7C40PC440H29	XS8C4A1PCP20		+ XZCP1141L5
XS7C40PC440H7	XS8C4A1PCN12	XS8T4PC440L2	XS8C2A1PCM12 + XZCP1141L10
XS7C40PC449	XS8C4A1PCG13	V0074D04404D	
XS7C40PC449D	XS8C4A1PCM12	XS8T4PC440LD	XS8C2A1PCM12
XS7C40PC449H29	XS8C4A1PCP20	XS8T4PC440LD01	XS8C2A1PCM12
XS7C40PC449H7	XS8C4A1PCN12	40 x 40 x 117 mm	
XS7T4DA210	XS7C2A1DAM12 + XZCP1141L2	XSCH	
XS7T4DA214LD	XS8C2A1CAM12	XSCH203629	XS9C4A2A2G13
XS7T4DA2T4LD XS7T4DA2T4LD01	XS8C2A1CAM12	XSCH203629H7	XS9C4A2A2N12
XS7T4DA2T4LD0T XS7T4DA2T4LD01W	XS8C2A1CAM12	XSCH207629	XS9C4A2A1G13
NOT I TUNK I TLUUT IV	+ XSZPKC2	XSCH207629H7	XS9C4A2A1N12
XS7T4DA214LDW	XS8C2A1CAM12 +XSZPKC2		
XS7T4NC440	XS8C2A1NCM12 + XZCP1141L2		
XS7T4NC440LD	XS8C2A1NCM12		
XS7T4NC440LD01	XS8C2A1NCM12		
XS7T4PC440	XS8C2A1PCM12 + XZCP1141L2		
XS7T4PC440LD	XS8C2A1PCM12		

Inductive proximity sensors XS range Product reference index

X		XS1N12PC410D	62	XS4P18KP340D	68	XS7E1A1PAL2	52	XS8D1A1PAL2	54
XS1L04NA310	76	XS1N18NA349	72	XS4P18MA230	70	XS7E1A1PAM8	52	XS8D1A1PAM12	54
XS1L04NA310S	76	XS1N18NA349D	72	XS4P18MA230K	70	XS7E1A1PBL01M12	52	XS8D1A1PBL2	54
XS1L04NA311	76	XS1N18PA349	72	XS4P18MB230	70	XS7E1A1PBL2	52	XS8D1A1PBM12	54
XS1L04NA311S	76	XS1N18PA349D	72	XS4P18MB230K	70	XS7E1A1PBM8	52	XS8E1A1MAL01U20	54
XS1L04NB310	76	XS1N18PB349	72	XS4P18NA340	70	XS7F1A1DAL2	50	XS8E1A1MAL2	54
XS1L04NB310S	76	XS1N18PB349D	72	XS4P18NA370	70	XS7F1A1DBL01M8	50	XS8E1A1MBL01U20	54
XS1L04NB311	76	XS1N18PC410	63	XS4P18PA340	70	XS7F1A1DBL2	50	XS8E1A1MBL2	54
XS1L04NB311S	76	XS1N18PC410D	63	XS4P18PA370	70	XS7F1A1NAL2	50	XS8E1A1NAL2	54
XS1L04PA310	76	XS1N30NA349	72	XS4P18PB340	70	XS7F1A1NBL2	50	XS8E1A1NBL2	54
XS1L04PA310S	76	XS1N30NA349D	72	XS4P18PB370	70	XS7F1A1PAL01M8	50	XS8E1A1NBM8	54
XS1L04PA311	76	XS1N30PA349	72	XS4P18PC410	63	XS7F1A1PAL2	50	XS8E1A1PAL01M12	54
XS1L04PA311S	76	XS1N30PA349D	72	XS4P18PC410D	63	XS7F1A1PBL01M8	50	XS8E1A1PAL2	54
XS1L04PB310	76	XS1N30PB349	72	XS4P30AB110	93	XS7F1A1PBL2	50	XS8E1A1PAM8	54
XS1L04PB310S	76	XS1N30PB349D	72	XS4P30AB120	93	XS7J1A1DAL2	50	XS8E1A1PBL2	54
XS1L04PB311	76	XS1N30PC410	63	XS4P30KP340	68	XS7J1A1NAL01M8	50	XS8E1A1PBM8	54
XS1L04PB311S	76	XS1N30PC410D	63	XS4P30KP340D	68	XS7J1A1NAL2	50	XS9C2A1NCM12	116
XS1L06PC410	62	XS2M08PC410	62	XS4P30MA230	70	XS7J1A1NBL2	50	XS9C2A1PCM12	116
XS1M08PC410	62	XS2M08PC410D	62	XS4P30MA230K	70	XS7J1A1PAL01M8	50	XS9C2A2A1M12	98
XS1M08PC410D	62	XS2M12KP340	68	XS4P30MB230	70	XS7J1A1PAL2	50	XS9C2A2A1M12	98
XS1M12AB120	91	XS2M12KP340D	68	XS4P30MB230K	70	XS7J1A1PBL01M8	50	XS9C4A1PCP20	116
XS1M12KP340	68	XS2M18KP340D		XS4P30NA340	70	XS7J1A1PBL01M6 XS7J1A1PBL2	50	XS9C4A1PCP20 XS9C4A2A2P20	98
			68	XS4P30NA340 XS4P30PA340	70		54		89
XS1M12KP340D XS1M18AB120	68	XS2M18KP340D	68	XS4P30PA370	70	XS8C1A1MAL01U20 XS8C1A1MAL2	54	XS9C11RMBL01U20 XS9C111A1L2	95
	92 68	XS2M18MA250	60		70		54		95
XS1M18KP340 XS1M18KP340D	68	XS2M18MA250K	60	XS4P30PB340		XS8C1A1MBL01U20		XS9C111A2L2	
		XS2M18MB250	60	XS4P30PB370	70 63	XS8C1A1MBL2	54	XS9D111A2L2 XS9D111A2M12	97
XS1M18MA250	60	XS2M18MB250K	60	XS4P30PC410		XS8C1A1NAL2	54		
XS1M18MA250K	60	XS2M30KP340	68	XS4P30PC410D	63	XS8C1A1PAL01M12	54	XS9E11RMBL01U20	89
XS1M18MB250	60	XS2M30KP340D	68	XS7C1A1DAL2	52	XS8C1A1PAL2	54	XS9E11RPBL01M12	
XS1M18MB250K	60	XS2M30MA250	60	XS7C1A1DAM8	52	XS8C1A1PAM8	54	XS9E111A1L2	95
XS1M18PAS20D	118	XS2M30MA250K	60	XS7C1A1DBL01M12	52	XS8C1A1PBL2	54	XS9E111A2L2	97
XS1M18PAS40D	118	XS2M30MB250	60	XS7C1A1NBL2	52	XS8C1A1PBM8	54	XS106B3PAL2	36
XS1M30AB120	93	XS2M30MB250K	60	XS7C1A1NBM8	52	XS8C2A1DAM12	56	XS106B3PAM8	36
XS1M30KP340	68	XS2N12PC140	62	XS7C1A1PAL01M12	52	XS8C2A1MAU20	56	XS106B3PAM12	36
XS1M30KP340D	68	XS4P08MA230	70	XS7C1A1PAL2	52	XS8C2A1MBU20	56	XS106B3PBL2	36
XS1M30MA250	60	XS4P08MB230	70	XS7C1A1PAM8	52	XS8C2A1NCM12	56	XS106B3PBM8	36
XS1M30MA250K	60	XS4P08NA340	70	XS7C1A1PBL2	52	XS8C2A1PCM12	56	XS108B3NAL2	36
XS1M30MB250	60	XS4P08NB340	70	XS7C1A1PBM8	52	XS8C2A1PDM12	124	XS108B3NAM8	36
XS1M30MB250K	60	XS4P08PA340	70	XS7C2A1DAM12	56	XS8C2A4CAM12	56	XS108B3NAM12	36
XS1N05NA310	76	XS4P08PB340	70	XS7C2A1DBM12	56	XS8C2A4DAM12	56	XS108B3NBM8	36
XS1N05NA311	76	XS4P08PC410	62	XS7C2A1NAM12	56	XS8C2A4MAU20	56	XS108B3PAL2	36
XS1N05NA311S	76	XS4P12AB110	91	XS7C2A1NBM12	56	XS8C2A4MBU20	56	XS108B3PAM8	36
XS1N05NB310	76	XS4P12AB120	91	XS7C2A1PAM12	56	XS8C2A4NCM12	56	XS108B3PAM12	36
XS1N05NB311	76	XS4P12KP340	68	XS7C2A1PBM12	56	XS8C2A4PCM12	56	XS108B3PBL2	36
XS1N05NB311S	76	XS4P12KP340D	68	XS7C4A1DPP20	58	XS8C2A4PDM12	124	XS108B3PBM8	36
XS1N05PA310	76	XS4P12MA230	70	XS7C4A1MPP20	58	XS8C4A1DPP20	58	XS108B3PBM12	36
XS1N05PA311	76	XS4P12MA230K	70	XS7D1A1DAL2	52	XS8C4A1MPP20	58	XS108BHNAL2	82
XS1N05PA311S	76	XS4P12MB230	70	XS7D1A1DAM12	52	XS8C4A1NCP20	58	XS108BHNAM8	82
XS1N05PB310	76	XS4P12NA340	70	XS7D1A1DBL2	52	XS8C4A1PCP20	58	XS108BHPAL2	82
XS1N05PB311	76	XS4P12NA370	70	XS7D1A1NAL2	52	XS8C4A4DPP20	58	XS108BHPAM8	82
XS1N05PB311S	76	XS4P12NB340	70	XS7D1A1PAL2	52	XS8C4A4MPP20	58	XS108BHPAM12	82
XS1N12NA349	72	XS4P12PA340	70	XS7D1A1PAM12	52	XS8C4A4NCP20	58	XS108BHPBL2	82
XS1N12NA349D	72	XS4P12PA370	70	XS7D1A1PBM12	52	XS8C4A4PCM12	58	XS108BHPBM8	82
XS1N12NC410	62	XS4P12PB340	70	XS7D1A3CAM12DIN	112	XS8C4A4PCP20	58	XS108BHPBM12	82
XS1N12NC410D	62	XS4P12PB370	70	XS7E1A1CAL01M12	52	XS8C4A4PDP20	126	XS108BLNAL2	78
XS1N12PA349	72	XS4P12PC410	62	XS7E1A1DAL01M12	52	XS8D1A1MAL2	54	XS108BLNAM12	78
XS1N12PA349D	72	XS4P12PC410D	62	XS7E1A1DAL2	52	XS8D1A1MAU20	54	XS108BLPAL2	78
XS1N12PB349	72	XS4P18AB110	92	XS7E1A1NAL2	52	XS8D1A1MBL2	54	XS108BLPAL5	78
XS1N12PB349D	72	XS4P18AB120	92	XS7E1A1NBL2	52	XS8D1A1MBU20	54	XS108BLPAM8	78
XS1N12PC410	62	XS4P18KP340	68	XS7E1A1PAL01M12	52	XS8D1A1NAL2	54	XS108BLPAM12	78

Inductive proximity sensors XS range Product reference index

XS112B3NAL2	36	XS130B3PCM12	66	XS218BLNAM12	79	XS508B1PAL2	26	XS530B1DBL2	31
XS112B3NAM12	36	XS130B3PDL2	122	XS218BLNBL2	79	XS508B1PAM8	26	XS530B1MAL2	34
XS112B3PAL2	36	XS130B3PDM12	122	XS218BLPAL2	79	XS508B1PAM12	26	XS530B1MAU20	34
XS112B3PAM12	36	XS130BHNAL2	82	XS218BLPAL5	79	XS508B1PBL2	26	XS530B1MBL2	34
XS112B3PBL2	36	XS130BHNAM12	82	XS218BLPAM12	79	XS508B1PBM8	26	XS530B1NAL2	26
XS112B3PBM12	36	XS130BHNBL2	82	XS218BLPBL2	79	XS508B1PBM12	26	XS530B1NAM12	26
XS112B3PCL2	66	XS130BHNBM12	82	XS218SAMAL2	104	XS508BLNBM12	27	XS530B1PAL2	26
XS112B3PCM12	66	XS130BHPAL2	82	XS218SAMAU20	104	XS508BLPAL2	27	XS530B1PAM12	26
XS112B3PDL2	122	XS130BHPAL5	82	XS218SANAL2	102	XS508BLPAM12	27	XS530B1PBL2	26
XS112B3PDM12	122	XS130BHPAM12	82	XS218SANAM12	102	XS508BLPBM12	27	XS530B1PBM12	26
XS112BHNAL2	82	XS130BHPBL2	82	XS218SAPAL2	102	XS508BSCBL2	30	XS530BLPAL2	27
XS112BHNAM12	82	XS130BHPBM12	82	XS218SAPAM12	102	XS512B1CAL08M12	31	XS530BLPAM12	27
XS112BHNBL2	82	XS130BLNAL2	79	XS230AAMAL2	108	XS512B1CAM12	31	XS530BLPBL2	27
XS112BHNBM12	82	XS130BLPAL2	79	XS230AAMAU20	108	XS512B1DAL2	31	XS530BSCAM12	30
XS112BHPAL2	82	XS130BLPAM12	79	XS230AANAL2	106	XS512B1DAM12	31	XS530BSPDL2	120
XS112BHPAL5	82	XS130BLPBL2	79	XS230AANAM12	106	XS512B1DBL2	31	XS530BSPDM12	120
XS112BHPAM12	82	XS130BLPBM12	79	XS230AAPAL2	106	XS512B1MAL2	34	XS604R1NAL2	74
XS112BHPBL2	82	XS208BLNAL2	78	XS230AAPAM12	106	XS512B1MAU20	34	XS604R1NAM08	74
XS112BHPBM12	82	XS208BLPAL2	78	XS230AAPAW12 XS230BLNAL2	79	XS512B1MBL2	34	XS604R1NBL2	74
XS112BLNAL2	78	XS208BLPAL5	78	XS230BLNAM12	79	XS512B1MBU20	34	XS604R1NBM08	74
XS112BLNAM12	78	XS208BLPAM8	78	XS230BLNAW12 XS230BLPAL2	79	XS512B1NAL2	26	XS604R1PAL2	74
XS112BLPAL2	78	XS208BLPAM12	78	XS230BLPAL5	79	XS512B1NAM12	26	XS604R1PAM08	74
XS112BLPAL5	78	XS212AANAL2	106	XS230BLPAU3 XS230BLPAM12		XS512B1PAL2	26	XS604R1PBL2	74
	78				79	XS512B1PAM12			74
XS112BLPAM12	78	XS212AANAM12	106	XS230BLPBL2	104		26 26	XS604R1PBM08	74
XS112BLPBL2		XS212AAPAL2		XS230SAMAL2		XS512B1PBL2		XS605R1NAL2	
XS112BLPBM12	78	XS212AAPAM12	106	XS230SAMAU20	104	XS512B1PBM12	26	XS605R1NAM08	74
XS118B3NAL2	37	XS212B4NAL2	46	XS230SANAL2	102	XS512BLPAL2	27	XS605R1NBL2	74 74
XS118B3NAM12	37	XS212B4NAM12	46	XS230SANAM12	102	XS512BLPAM12	27	XS605R1NBM08	
XS118B3PAL2	37	XS212B4NBL2	46	XS230SAPAL2	102	XS512BLPBL2	27	XS605R1PAL2	74
XS118B3PAM12	37	XS212B4PAL2	46	XS230SAPAM12	102	XS512BSDAM12	30	XS605R1PAL5	74
XS118B3PBL2	37	XS212B4PAL5	46	XS504R1NAL2	74	XS512BSPDL2	120	XS605R1PAM08	74
XS118B3PBM12	37	XS212B4PAM12	46	XS504R1NAM08	74	XS512BSPDM12	120	XS605R1PBL2	74
XS118B3PCL2	66	XS212B4PBL2	46	XS504R1NBL2	74	XS518B1CAL08M12	31	XS605R1PBM08	74
XS118B3PCM12	66	XS212B4PBM12	46	XS504R1NBM08	74	XS518B1CAM12	31	XS606B1DBL2	40
XS118B3PDL2	122	XS212BLNAL2	78	XS504R1PAL2	74	XS518B1DAL01C	31	XS606B3CAL2	40
XS118B3PDM12	122	XS212BLNAL7	78	XS504R1PAM08	74	XS518B1DAL2	31	XS606B3CBL2	40
XS118BHNAL2	82	XS212BLNAM12	78	XS504R1PBL2	74	XS518B1DAM12	31	XS608B1DAL2	40
XS118BHNAM12	82	XS212BLNBL2	78	XS504R1PBM08	74	XS518B1DBL2	31	XS608B1DAM12	40
XS118BHNBL2	82	XS212BLPAL2	78	XS505R1NAL2	74	XS518B1DBM12	31	XS608B1DBL2	40
XS118BHNBM12	82	XS212BLPAL5	78	XS505R1NAM08	74	XS518B1MAL2	34	XS608B1NAL2	38
XS118BHPAL2	82	XS212BLPAM12	78	XS505R1NBL2	74	XS518B1MAU20	34	XS608B1NAM8	38
XS118BHPAL5	82	XS212BLPBL2	78	XS505R1NBM08	74	XS518B1MBL2	34	XS608B1NAM12	38
XS118BHPAM12	82	XS212BLPBL5	78	XS505R1PAL2	74	XS518B1MBU20	34	XS608B1NBL2	38
XS118BHPBL2	82	XS212SANAL2	102	XS505R1PAM08	74	XS518B1NAL2	26	XS608B1NBM8	38
XS118BHPBM12	82	XS212SANAM12	102	XS505R1PBL2	74	XS518B1NAM12	26	XS608B1PAL2	38
XS118BLNAL2	79	XS212SAPAL2	102	XS505R1PBM08	74	XS518B1PAL2	26	XS608B1PAM8	38
XS118BLNAL5	79	XS212SAPAM12	102	XS506B1NAL2	26	XS518B1PAM12	26	XS608B1PAM12	38
XS118BLNAM12	79	XS218AAMAL2	108	XS506B1NAM8	26	XS518B1PBL2	26	XS608B1PBL2	38
XS118BLPAL2	79	XS218AAMAU20	108	XS506B1NBL2	26	XS518B1PBM12	26	XS608B1PBM8	38
XS118BLPAL5	79	XS218AANAL2	106	XS506B1NBM8	26	XS518BLNAL2	27	XS608B1PBM12	38
XS118BLPAM12	79	XS218AANAM12	106	XS506B1PAL2	26	XS518BLPAL2	27	XS608B1PCL2	66
XS118BLPBL2	79	XS218AAPAL2	106	XS506B1PAM8	26	XS518BLPAM12	27	XS608B1PCM12	66
XS118BLPBM12	79	XS218AAPAM12	106	XS506B1PAM12	26	XS518BLPBL2	27	XS608B3CAL2	40
XS130B3NAL2	37	XS218B4NAL2	46	XS506B1PBL2	26	XS518BLPBM12	27	XS608B4NAL2	44
XS130B3NAM12	37	XS218B4NAM12	46	XS506B1PBM8	26	XS518BSDAM12	30	XS608B4NAM8	44
XS130B3PAL2	37	XS218B4PAL2	46	XS508B1CAL08M12	31	XS518BSPDL2	120	XS608B4NAM12	44
XS130B3PAM12	37	XS218B4PAM12	46	XS508B1DAL2	31	XS518BSPDM12	120	XS608B4NBL2	44
XS130B3PBL2	37	XS218B4PBL2	46	XS508B1DAM12	31	XS530B1CAM12	31	XS608B4NBM8	44
XS130B3PBM12	37	XS218B4PBM12	46	XS508B1NAL2	26	XS530B1DAL2	31	XS608B4NBM12	44
 	٠.								

YAGEO & | ® Telemecanique Sensors

XS618B4MAU20 XS618B4MBL2 XS618B4MBU20 XS618B4NAL2 XS618B4NAM12 XS618B4NBL2 XS618B4PAL2 XS618B4PAM12 XS618B4PBL2 XS618B4PBM12 XS630B1DAL2 XS630B1DAM12 XS630B1DBM12 XS630B1MAL01B XS630B1MAL01C XS630B1MAL01U78 XS630B1MAL2 XS630B1MAU20 XS630B1MBL01B XS630B1MBL2 XS630B1MBU20 XS630B1NAL2 XS630B1NAM12 XS630B1NBL2 XS630B1PAL01C XS630B1PAL2 XS630B1PAM12 XS630B1PBL2 XS630B1PBM12 XS630B2PAL01M12 XS630B3DAL2 XS630B3DAM12 XS630B4MAL2 XS630B4MAU20 XS630B4MBL2 XS630B5NAL2 XS630B5PAL2 XS630B5PAM12 XS630B5PBM12 XS908R1PAM12 XS908R4PAM12 XS912R1PAM12 XS912R4PAM12 XS912RWPAM12 XS912S1PAM12 XS912S4PAM12 XS918R1PAM12 XS918R4PAM12 XS918RWPAM12 XS918S1PAM12 XS918S4PAM12 XS930R1PAM12

Inductive proximity sensors

XS range

Product reference index

V0000D4D4M0	
XS608B4PAM8	44
XS608B4PAM12 XS608B4PBL2	44
XS608B4PBM8	44
XS608B4PBM12	44
XS612B1DAL2	40
XS612B1DAM12	40
XS612B1DBM12	40
XS612B1MAL2	42
XS612B1MAU20	42
XS612B1MBL2	42
XS612B1MBU20	42
XS612B1NAL2	38
XS612B1NAM12	38
XS612B1NBL2	38
XS612B1NBM12	38
XS612B1PAL2	38
XS612B1PAM12	38
XS612B1PBL2	38
XS612B1PBM12	38
XS612B2PAL01M12	84
XS612B2PBL01M12	84
XS612B3DAL2	40
XS612B3DAM12	40
XS612B3DBL2	40
XS612B3DBM12	40
XS612B4NAL2	44
XS612B4NAM12	44
XS612B4NBL2	44
XS612B4PAL2	44
XS612B4PAM12	44
XS612B4PBL2	44
XS612B4PBM12	44
XS618B1DAL2	40
XS618B1DAM12	40
XS618B1DBL2	40
XS618B1DBM12	40
XS618B1MAL01B	42
XS618B1MAL01C	42
XS618B1MAL01U78	42
XS618B1MAL2	42
XS618B1MAU20	42
XS618B1MBL2	42
XS618B1MBU20	42
XS618B1NAL2	38
XS618B1NAM12	38
XS618B1NBL2	38
XS618B1NBM12	38
XS618B1PAL01C	38
XS618B1PAL2	38
XS618B1PAM12	38
XS618B1PBL2	38
XS618B1PBM12	38
	84
XS618B2PAL01M12	
XS618B2PBL01M12	84
XS618B2PBL01M12 XS618B3DAL2	40
XS618B2PBL01M12 XS618B3DAL2 XS618B3DAM12	40
XS618B2PBL01M12 XS618B3DAL2 XS618B3DAM12 XS618B3DBL2	40
XS618B2PBL01M12 XS618B3DAL2 XS618B3DAM12	40

48)
48	>
48	_
44	,
44	>
44	>
44)
44	5
44)
40	
40	
42	
42	
42	
42	
42 42	
42	5
42	_
38	
38	
38	
38	
38	
38	
38	
84	
40	
40	
48	
48	
48)
44	
44	
44	
110	
111	
110 111	
110 111	
110	
111	
114 115	
100	
101 100	
101	
110 111	
110	
111 114	-
115	
100 101	
100	
101	
110 111	

XS930R4PAM12	110
XS930S1PAM12	111 100
XS930S4PAM12	101
A393034FAW12	100
XSAV11373	87
XSAV11801	87
XSAV12373	87
XSAV12801	87
XSCZ01	128
XSZB108	26 27 30 31 37 38 40 44 63 66 79 82 128
XSZB112	26 27 30 31 34 37 38 40 42 44 46 63 66 68 72 79 82 84 106 120 122 128
XSZB118	26 27 30 31 37 38 40 42 44 46 48 60 63 66 68 72 79 82 84 106 108 120 122

V07D400	
XSZB130	26 27
	30
	31
	34 37
	38
	40
	42 44
	48
	60
	63 66
	68
	72
	79 82
	84
	106
	108 120
	122
	128
XSZB165	26 27
	37
	40
XSZBC10	128
XSZBD10	128
XSZBE10	128
XSZBPM12	89
XSZBS12	100
XSZBS30	102
X32B330	102
	104
XSZE112	128
XSZE118	128
XSZE130	128
XSZP112	128
XSZP118	128
XSZP130	128
XSZPSC2	117
XUZA118	100
	102
XUZE04	104
XUZE06	128
XUZE08	128
XZCP1141L2	57
XZCP1141L2	57 110
	114
V=05////	125
XZCP1141L5	57 110
	114
	125
XZCP1141L10	57 110
	114
	125
XZCP1241L2	57
	110 114
	125
XZCP1241L5	57
	110 111
	114 125
XZCP1241L10	57
	110
	114 125
XZCP1865L5	57
XZCP1865L10	57
-	

XZCP1965L5	57
XZCP1965L10	57
XZCPA1141L2	100 102
	108
XZCPA1141L5	100
	102
V70D4444444	106
XZCPA1141L10	100 102
	106
XZCPA1241L2	100
	102
XZCPA1241L5	106
AZCFA1Z41L3	102
	106
XZCPA1241L10	100
	102 106
XZCPA1865L5	104
XZCPA1865L5	108
XZCPA1865L10	104
XZCPA1865L10	108
XZCPA1965L5	104
XZCPA1965L5	108
XZCPA1965L10	104
XZCPA1965L10	108
XZCPV0566L5	79
XZCPV0566L10	82
AZCPVUS66L1U	79 82
XZCPV1141L5	79
	82
XZCPV1141L10	79
XZCRA151140A2	82 102
ALUKA 13114UAZ	102
XZCRA151140A5	102
	106

www.telemecaniquesensors.com

The information provided in this catalogue contains description of products sold by TMSS France, its subsidiaries and other affiliated companies ('Offer') with technical specifications and technical characteristics of the performance of the corresponding Offer.

The content of this document is subject to revision at any time without notice due to continued progress in methodology, design and manufacturing.

To the extent permitted by applicable law, no responsibility or liability is assumed by TMSS France, its subsidiaries and other affiliated companies for any type of damage arising out of or in connexion with (a) informational content of this catalogue not conforming with or exceeding the technical specifications, or (b) any error contained in this catalogue, or (c) any use, decision, act or omission made or taken on the basis of or in reliance on any information contained or referred to in this catalogue.

NEITHER TMSS FRANCE, ITS SUBSIDIARIES, NOR ITS OTHER AFFILIATES, AS THE CASE MAYBE, MAKE NO WARRANTY OR REPRESENTATION OF ANY KIND, WHETHER EXPRESS OR IMPLIED, AS TO WHETHER THIS CATALOGUE OR ANY INFORMATION CONTAINED THEREIN SUCH AS PRODUCTS WILL MEET REQUIREMENTS, EXPECTATIONS OR PURPOSE OF ANY PERSON MAKING USE THEREOF.

Telemecanique™ Sensors is a trademark of Schneider Electric Industries SAS used under license by TMSS France. Any other brands or trademarks referred to in this catalogue are property of TMSS France or, as the case may be, of its subsidiaries or other affiliated companies. All other brands are trademarks of their respective owners. This catalogue and its content are protected under applicable copyright laws and provided for informative use only.

No part of this catalogue may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of TMSS France. Copyright, intellectual, and all other proprietary rights in the content of this catalogue (including but not limited to audio, video, text, and photographs) rests with TMSS France, its subsidiaries, and other affiliated companies or its licensors. All rights in such content not expressly granted herein are reserved. No rights of any kind are licensed or assigned or shall otherwise pass to persons accessing this information.

As standards, specifications and design change from time to time, please ask for confirmation of the information given in this publication.

©2025, TMSS France, All Rights Reserved.

TMSS France SAS
Share capital: 366 931 214 €
Tour Eqho, 2 avenue Gambetta
92400 Courbevoie – France

908 125 255 RCS Nanterre