

## STRADELLA-8-HV-HB-W

~85° wide beam for industrial applications.  
Variant with improved creepage distance for  
high voltage circuit designs.

## SPECIFICATION:

|                |             |
|----------------|-------------|
| Dimensions     | 49.5 x 49.5 |
| Height         | 7.1 mm      |
| Fastening      | pin, screw  |
| ROHS compliant | yes ⓘ       |




## MATERIALS:

| Component           | Type       | Material | Colour | Finish | Length (mm) |
|---------------------|------------|----------|--------|--------|-------------|
| STRADELLA-8-HV-HB-W | Multi-lens | PMMA     | clear  |        |             |

## ORDERING INFORMATION:

| Component                                                    | Qty in box | MOQ | MPQ | Box weight (kg) |
|--------------------------------------------------------------|------------|-----|-----|-----------------|
| C15985_STRADELLA-8-HV-HB-W<br>» Box size: 480 x 280 x 300 mm | 800        | 160 | 160 | 6.0             |





See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)

#### OPTICAL RESULTS (MEASURED):





LED JB3030 HE B Class  
 FWHM / FWTM 92.0° / 133.0°  
 Efficiency 97 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files





LED XD16  
 FWHM / FWTM 104.0° / 146.0°  
 Efficiency 94 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED XT-E  
 FWHM / FWTM 92.0° / 141.0°  
 Efficiency 94 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:





Light distribution files

#### OPTICAL RESULTS (MEASURED):

##### inventronics


|                      |                             |
|----------------------|-----------------------------|
| LED                  | PL-BRICK HP 3x8 Stradella-8 |
| FWHM / FWTM          | 90.0° / 131.0°              |
| Efficiency           | 97 %                        |
| Peak intensity       | 0.5 cd/lm                   |
| LEDs/each optic      | 1                           |
| Light colour/type    | White                       |
| Required components: |                             |



Light distribution files

##### LUMINUS



|                      |                |
|----------------------|----------------|
| LED                  | SST-10-B130    |
| FWHM / FWTM          | 99.0° / 137.0° |
| Efficiency           | 95 %           |
| Peak intensity       | 0.4 cd/lm      |
| LEDs/each optic      | 1              |
| Light colour/type    | Deep Red       |
| Required components: |                |



Light distribution files

##### NICHIA

|                      |                 |
|----------------------|-----------------|
| LED                  | NF2W585AR       |
| FWHM / FWTM          | 102.0° / 142.0° |
| Efficiency           | 94 %            |
| Peak intensity       | 0.4 cd/lm       |
| LEDs/each optic      | 1               |
| Light colour/type    | White           |
| Required components: |                 |




Light distribution files



#### OPTICAL RESULTS (MEASURED):

**OSRAM**  
Opto Semiconductors



LED OSCONIQ S 3030 (QSLR31)  
FWHM / FWTM 92.0° / 132.0°  
Efficiency 94 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

**PHILIPS**



LED Fortimo FastFlex LED 4x8up PR G5  
FWHM / FWTM 90.0° / 131.0°  
Efficiency 94 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

**SAMSUNG**

LED LH151B  
FWHM / FWTM 96.0° / 139.0°  
Efficiency 95 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:





Light distribution files

#### OPTICAL RESULTS (MEASURED):





LED: SEOUL DC 3030C  
 FWHM / FWTM: 92.0° / 132.0°  
 Efficiency: 94 %  
 Peak intensity: 0.5 cd/lm  
 LEDs/each optic: 1  
 Light colour/type: White  
 Required components:



Light distribution files





LED: Z5M3  
 FWHM / FWTM: 96.0° / 139.0°  
 Efficiency: 94 %  
 Peak intensity: 0.4 cd/lm  
 LEDs/each optic: 1  
 Light colour/type: White  
 Required components:



Light distribution files



LED: Z5M4  
 FWHM / FWTM: 94.0° / 126.0°  
 Efficiency: 98 %  
 Peak intensity: 0.5 cd/lm  
 LEDs/each optic: 1  
 Light colour/type: White  
 Required components:



Light distribution files

## OPTICAL RESULTS (MEASURED):



SEOUL SEMICONDUCTOR


|                      |                 |
|----------------------|-----------------|
| LED                  | Z8Y19           |
| FWHM / FWTM          | 100.0° / 142.0° |
| Efficiency           | 94 %            |
| Peak intensity       | 0.4 cd/lm       |
| LEDs/each optic      | 1               |
| Light colour/type    | White           |
| Required components: |                 |

[Light distribution files](#)

#### OPTICAL RESULTS (SIMULATED):




LED XP-G2 HE  
 FWHM / FWTM 92.0° / 132.0°  
 Efficiency 94 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED XP-G3  
 FWHM / FWTM 96.0° / 138.0°  
 Efficiency 94 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED XP-G3  
 FWHM / FWTM 94.0° / 141.0°  
 Efficiency 91 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:

Light distribution files

### OPTICAL RESULTS (SIMULATED):



|                      |                |
|----------------------|----------------|
| LED                  | XT-E           |
| FWHM / FWTM          | 87.0° / 141.0° |
| Efficiency           | 92 %           |
| Peak intensity       | 0.5 cd/lm      |
| LEDs/each optic      | 1              |
| Light colour/type    | White          |
| Required components: |                |

[Light distribution files](#)



|                      |                            |
|----------------------|----------------------------|
| LED                  | LUXEON 3030 2D (Round LES) |
| FWHM / FWTM          | 87.0° / 130.0°             |
| Efficiency           | 94 %                       |
| Peak intensity       | 0.5 cd/lm                  |
| LEDs/each optic      | 1                          |
| Light colour/type    | White                      |
| Required components: |                            |

[Light distribution files](#)




|                      |                 |
|----------------------|-----------------|
| LED                  | LUXEON 3535L HE |
| FWHM / FWTM          | 80.0° / 131.0°  |
| Efficiency           | 94 %            |
| Peak intensity       | 0.5 cd/lm       |
| LEDs/each optic      | 1               |
| Light colour/type    | White           |
| Required components: |                 |

[Light distribution files](#)

#### OPTICAL RESULTS (SIMULATED):




LED LUXEON CZ  
 FWHM / FWTM 52.0° / 122.0°  
 Efficiency 96 %  
 Peak intensity 0.7 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED LUXEON CZ  
 FWHM / FWTM 93.0° / 136.0°  
 Efficiency 97 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED LUXEON HR30  
 FWHM / FWTM 82.0° / 130.0°  
 Efficiency 93 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:

Light distribution files



#### OPTICAL RESULTS (SIMULATED):




|                      |                |
|----------------------|----------------|
| LED                  | LUXEON TX      |
| FWHM / FWTM          | 84.0° / 139.0° |
| Efficiency           | 92 %           |
| Peak intensity       | 0.5 cd/lm      |
| LEDs/each optic      | 1              |
| Light colour/type    | White          |
| Required components: |                |

Light distribution files



|                      |                       |
|----------------------|-----------------------|
| LED                  | SST-20 Gen2           |
| FWHM / FWTM          | 95.0 + 96.0° / 134.0° |
| Efficiency           | 87 %                  |
| Peak intensity       | 0.4 cd/lm             |
| LEDs/each optic      | 1                     |
| Light colour/type    | White                 |
| Required components: |                       |


Protective plate, glass




Light distribution files



|                      |                |
|----------------------|----------------|
| LED                  | SST-20 Gen2    |
| FWHM / FWTM          | 96.0° / 136.0° |
| Efficiency           | 96 %           |
| Peak intensity       | 0.4 cd/lm      |
| LEDs/each optic      | 1              |
| Light colour/type    | White          |
| Required components: |                |



Simulated from photometric data




Light distribution files

#### OPTICAL RESULTS (SIMULATED):



LED NVSW519A  
 FWHM / FWTM 93.0° / 130.0°  
 Efficiency 89 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files



LED NVSxx19B/NVSxx19C  
 FWHM / FWTM 95.0° / 134.0°  
 Efficiency 91 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



LED OSCONIQ C 2424 Gen1  
 FWHM / FWTM 92.0° / 134.0°  
 Efficiency 97 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files


#### OPTICAL RESULTS (SIMULATED):

**OSRAM**  
Opto Semiconductors

LED OSCONIQ C 3030  
FWHM / FWTM 90.0° / 132.0°  
Efficiency 87 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:

Protective plate, glass


Light distribution files



**OSRAM**  
Opto Semiconductors

LED OSCONIQ C 3030  
FWHM / FWTM 90.0° / 134.0°  
Efficiency 97 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:


Light distribution files



**OSRAM**  
Opto Semiconductors

LED OSCONIQ P 3030  
FWHM / FWTM 82.0° / 132.0°  
Efficiency 97 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:


Light distribution files



#### OPTICAL RESULTS (SIMULATED):

**OSRAM**  
Opto Semiconductors


LED OSLON Pure 1414  
FWHM / FWTM 92.0° / 133.0 + 134.0°  
Efficiency 97 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

**OSRAM**  
Opto Semiconductors


LED OSLON Square CSSRM2/CSSRM3  
FWHM / FWTM 89.0° / 134.0°  
Efficiency 96 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

**OSRAM**  
Opto Semiconductors

LED OSLON SSL 80  
FWHM / FWTM 66.0° / 128.0°  
Efficiency 95 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour/type Red  
Required components:




Light distribution files

#### OPTICAL RESULTS (SIMULATED):

**OSRAM**  
Opto Semiconductors


LED OSLON SSL 80  
FWHM / FWTM 62.0° / 124.0°  
Efficiency 96 %  
Peak intensity 0.8 cd/lm  
LEDs/each optic 1  
Light colour/type Blue  
Required components:



Light distribution files

**OSRAM**  
Opto Semiconductors


LED OSLON SSL 80  
FWHM / FWTM 66.0° / 104.0°  
Efficiency 97 %  
Peak intensity 0.8 cd/lm  
LEDs/each optic 1  
Light colour/type True Green  
Required components:



Light distribution files

**OSRAM**  
Opto Semiconductors

LED SFH 4715AS  
FWHM / FWTM 71.0° / 109.0°  
Efficiency 96 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour/type IR  
Required components:




Light distribution files

#### OPTICAL RESULTS (SIMULATED):

#### SAMSUNG


LED LH181A  
 FWHM / FWTM 97.0° / 143.0°  
 Efficiency 94 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

#### SAMSUNG



LED LH181B  
 FWHM / FWTM 89.0° / 135.0°  
 Efficiency 94 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED Z5M3-E1  
 FWHM / FWTM 88.0° / 123.0 + 122.0°  
 Efficiency 97 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files

#### OPTICAL RESULTS (SIMULATED):




LED Z5M4-E1  
 FWHM / FWTM 90.0° / 126.0°  
 Efficiency 97 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files




LED Z5M4-E2  
 FWHM / FWTM 88.0° / 126.0°  
 Efficiency 97 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED Z8Y22T  
 FWHM / FWTM 90.0° / 137.0°  
 Efficiency 94 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



### GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

### MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 7  
FI-24100 SALO  
Finland

#### LEDiL Inc.

228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

#### Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

#### Local sales and technical support

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

#### Shipping locations

Poznan, Poland  
Hong Kong, China

#### Distribution Partners

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)