

## STRADA-2X2R-T2

IESNA Type II (medium) beam applicable for pedestrian and road lighting from low poles.

### SPECIFICATION:

Dimensions	50.0 x 50.0
Height	11.4 mm
Fastening	pin, screw
ROHS compliant	yes 




### MATERIALS:

Component	Type	Material	Colour	Finish	Coating
STRADA-2X2R-T2	Reflector	PC	metal		HMDS

### ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C19761_STRADA-2X2R-T2	504	504	28	5.6
» Box size: 480 x 280 x 300 mm				



See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)


### OPTICAL RESULTS (SIMULATED):



**LED** J Series 5050B 6V K Class  
**FWHM / FWTM** Asymmetric  
**Efficiency** 89 %  
**Peak intensity** 0.7 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**


Protective plate, glass

Light distribution files




**LED** J Series 5050B 6V K Class  
**FWHM / FWTM** Asymmetric  
**Efficiency** 92 %  
**Peak intensity** 0.7 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**

Protective plate, glass



**LED** J Series 5050B 6V K Class  
**FWHM / FWTM** Asymmetric  
**Efficiency** 97 %  
**Peak intensity** 0.8 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**




Light distribution files

### OPTICAL RESULTS (SIMULATED):




LED	J Series 5050C 6V E Class
FWHM / FWTM	Asymmetric
Efficiency	97 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files



LED	J Series 5050C 6V E Class
FWHM / FWTM	Asymmetric
Efficiency	89 %
Peak intensity	0.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Protective plate, glass

Light distribution files



LED	XP-G3
FWHM / FWTM	Asymmetric
Efficiency	95 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

### OPTICAL RESULTS (SIMULATED):



LED XP-G4  
 FWHM / FWTM Asymmetric  
 Efficiency 98 %  
 Peak intensity 1.1 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files



LED XP-G4  
 FWHM / FWTM Asymmetric  
 Efficiency 89 %  
 Peak intensity 0.8 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Protective plate, glass



Light distribution files



LED XP-L2  
 FWHM / FWTM Asymmetric  
 Efficiency 96 %  
 Peak intensity 0.9 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files

### OPTICAL RESULTS (SIMULATED):



LED XP-L2  
 FWHM / FWTM Asymmetric  
 Efficiency 86 %  
 Peak intensity 0.7 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:

Protective plate, glass




Light distribution files



LED LUXEON 5050 HE  
 FWHM / FWTM Asymmetric  
 Efficiency 89 %  
 Peak intensity 0.7 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:


Protective plate, glass



Light distribution files



LED LUXEON 5050 HE  
 FWHM / FWTM Asymmetric  
 Efficiency 97 %  
 Peak intensity 0.9 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files

## OPTICAL RESULTS (SIMULATED):



**LED** LUXEON 5050 HE Plus  
**FWHM / FWTM** Asymmetric  
**Efficiency** 97 %  
**Peak intensity** 0.8 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**




Light distribution files



**LED** LUXEON 5050 HE Plus  
**FWHM / FWTM** Asymmetric  
**Efficiency** 89 %  
**Peak intensity** 0.7 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**

Protective plate, glass




Light distribution files



**LED** LUXEON 5050 Square LES  
**FWHM / FWTM** Asymmetric  
**Efficiency** 93 %  
**Peak intensity** 0.8 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**

Protective plate, glass




Light distribution files

## OPTICAL RESULTS (SIMULATED):




LED LUXEON 7070  
 FWHM / FWTM Asymmetric  
 Efficiency 92 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:

Protective plate, glass



LED LUXEON 7070  
 FWHM / FWTM Asymmetric  
 Efficiency 97 %  
 Peak intensity 0.7 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files



LED LUXEON 7070  
 FWHM / FWTM Asymmetric  
 Efficiency 88 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:

Protective plate, glass

Light distribution files




### OPTICAL RESULTS (SIMULATED):



**LED** LUXEON XR-5050 SQR (L213-xxxx008MRH001)  
**FWHM / FWTM** Asymmetric  
**Efficiency** 93 %  
**Peak intensity** 0.8 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**

Protective plate, glass




Light distribution files



**LED** NVSW219F  
**FWHM / FWTM** Asymmetric  
**Efficiency** 86 %  
**Peak intensity** 0.7 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**

Protective plate, glass




Light distribution files



**LED** Duris S8  
**FWHM / FWTM** Asymmetric  
**Efficiency** 92 %  
**Peak intensity** 0.7 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**

Protective plate, glass



Light distribution files


### OPTICAL RESULTS (SIMULATED):

**OSRAM**  
Opto Semiconductors

LED OSCONIQ P 3737 (2W version)  
FWHM / FWTM Asymmetric  
Efficiency 89 %  
Peak intensity 0.8 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:


Protective plate, glass

Light distribution files



**OSRAM**  
Opto Semiconductors

LED OSCONIQ P 3737 (2W version)  
FWHM / FWTM Asymmetric  
Efficiency 97 %  
Peak intensity 1.1 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

**OSRAM**  
Opto Semiconductors

LED OSCONIQ P 3737 (3W version)  
FWHM / FWTM Asymmetric  
Efficiency 88 %  
Peak intensity 0.8 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:

Protective plate, glass



Light distribution files



### OPTICAL RESULTS (SIMULATED):

**OSRAM**  
Opto Semiconductors

LED OSCONIQ P 3737 (3W version)  
FWHM / FWTM Asymmetric  
Efficiency 97 %  
Peak intensity 1 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

**OSRAM**  
Opto Semiconductors

LED OSCONIQ S 5050 (Q9LR32)  
FWHM / FWTM Asymmetric  
Efficiency 85 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:


Protective plate, glass



Light distribution files

**OSRAM**  
Opto Semiconductors

LED OSCONIQ S 5050 (Q9LR32)  
FWHM / FWTM Asymmetric  
Efficiency 94 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

### OPTICAL RESULTS (SIMULATED):

**OSRAM**

Opto Semiconductors

LED OSCONIQ S 5050 (Q9LR35)  
FWHM / FWTM Asymmetric  
Efficiency 97 %  
Peak intensity 0.9 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

**OSRAM**

Opto Semiconductors

LED OSCONIQ S 5050 (Q9LR35)  
FWHM / FWTM Asymmetric  
Efficiency 89 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:

Protective plate, glass




Light distribution files

**OSRAM**

Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3  
FWHM / FWTM Asymmetric  
Efficiency 87 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:

Protective plate, glass




Light distribution files

### OPTICAL RESULTS (SIMULATED):

**OSRAM**  
Opto Semiconductors


LED OSLON Square CSSRM2/CSSRM3  
FWHM / FWTM Asymmetric  
Efficiency 97 %  
Peak intensity 0.9 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

**PHILIPS**

LED Fortimo FastFlex LED 2x8 DA (U)HE  
FWHM / FWTM Asymmetric  
Efficiency 85 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Protective plate, glass

Light distribution files

**PHILIPS**

LED Fortimo FastFlex LED 2x8 DA G5  
FWHM / FWTM Asymmetric  
Efficiency 87 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Protective plate, glass

Light distribution files

### OPTICAL RESULTS (SIMULATED):

#### PHILIPS


LED Fortimo FastFlex LED 2x8 DA G5  
 FWHM / FWTM Asymmetric  
 Efficiency 97 %  
 Peak intensity 0.9 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

  
 SEOUL SEMICONDUCTOR

LED SEOUL DC 5050 6V  
 FWHM / FWTM Asymmetric  
 Efficiency 89 %  
 Peak intensity 0.7 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:





Protective plate, glass

Light distribution files

  
 SEOUL SEMICONDUCTOR

LED SEOUL DC 5050 6V  
 FWHM / FWTM Asymmetric  
 Efficiency 97 %  
 Peak intensity 0.8 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files


## OPTICAL RESULTS (SIMULATED):

### TRIDONIC

LED RLE 2x8 6000lm HP HE EXC3 OTD  
FWHM / FWTM Asymmetric  
Efficiency 90 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:

Protective plate, glass

Light distribution files



## GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

## MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

## PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

**LEDiL Oy**  
Joensuunkatu 7  
FI-24100 SALO  
Finland

**LEDiL Inc.**  
228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

**Ledil Optics Technology  
(Shenzhen) Co., Ltd.**  
# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

**Local sales and technical  
support**  
[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

**Shipping locations**  
Poznan, Poland  
Hong Kong, China

**Distribution Partners**  
[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)