



Security cameras and video doorbells




Building Automation



Littelfuse®

Expertise Applied | Answers Delivered

Smart homes are equipped with intelligent technologies for convenient and energy-efficient living



IoT devices protect, control, and sense to improve safety, reliability, convenience, and energy efficiency of buildings



Expertise Applied | Answers Delivered

Security cameras are a fast-growing market

Market Trends and Drivers

An estimated 120 million units of **non-residential security cameras** are installed each year globally, and this is expected to increase at a CAGR of 11%


Growth in Asia is driven by government initiatives to improve public safety and security. **Growth in the Americas** is driven by retail and commercial use

Global **residential security camera** unit shipments are expected to grow from 54 million units in 2018 to 120 million units in 2023 at a CAGR of 17%

Wired and wireless cameras are expected to maintain the majority of the shipment volume. The **video doorbell** segment is expected to show the largest growth over the next three years

Cameras with thermal imaging functionality to detect body temperature will show significant growth driven by the COVID-19 pandemic

Projected increase in security camera installation from 2018 to 2023



Sources: 1. [Global Video Surveillance Market](#) (Markets and Markets, Apr 2020)
2. [Security Cameras Market](#) (Transparency Market Research, 2016)

Littelfuse solutions for wired security cameras

Memory

- Diode array



Motor drive

- Solid state relay



DC power input

- Fuse, PPTC
- TVS diode



Power over ethernet

- Fuse, PPTC
- Diode array



Power adapter


- Fuse
- MOV
- TVS diode





Click on the product series in the table below for more info

Wired security camera functional block diagram



	Technology	Series
1	Fuse	875 , 807 , 373
	MOV	TMOV* , LA , UltraMOV
	TVS diode	P6KE , P6SMB
2a	Fuse, PPTC	461 , 449 , picoSMD
	TVS diode	5.0SMDJ
2b	Fuse, PPTC	461 , 449 , picoSMD
	Diode array	SRV05-4HTG , SP0504SHTG
3	Diode array	SP1006
4	Solid state relay	CPC1560 , CPC1561B


* TMOV is the recommended solution to comply with the new IEC 62368-1 standard



Benefits of Littelfuse products for wired cameras

	Technology	Function in application	Product series	Benefits	Features
1	Fuse	Protects power stage from overcurrent events	875 , 807 , 373	Reduces customer qualification time by complying with third-party safety standards such as UL/IEC	Third-party compliance (UL/IEC); low internal resistance; shock safe; vibration resistant
	MOV	Protects power unit from voltage transients and lightning	TMOV , LA , UltraMOV	Reduces customer qualification time by complying with third-party safety standards such as UL/IEC	High energy absorption capability: 40–530 J (2 ms)
	TVS diode	Protects power unit from voltage transients	P6KE , P6SMB	Improves system reliability by protecting downstream parts from transients on power lines	600 W peak pulse capability; glass passivated chip junction; compatible with lead-free solder reflow temperature profile
2a	Fuse	Protects the power stage from overcurrent events	461 , 449 , picoSMD	Reduces customer qualification time by complying with UL/IEC; compact design	Surface mountable; resettable option; compatible with the lead-free solder process per IEC standards
	TVS Diode	Protects sensitive electronic parts in power stage from voltage transients	5.0SMDJ	Improves system reliability by clamping the voltage at safe levels during transients	5000 W peak pulse capability; compatible with high temperature soldering; fast response time (< 1.0 ps)
2b	Fuse, PPTC	Protects the power stage from overcurrent events	461 , 449 , picoSMD	Reduces customer qualification time by complying with UL/IEC; compact design	Surface mountable; resettable option; compatible with the lead-free solder process per IEC standards
	Diode array	Protects sensitive electronic parts from voltage transients	SRV05-4HTG , SP0504SHTG	Compact package with multi-rail protection; retains high-speed signal reliability	Multiple rail-to-rail protections; low leakage current; low capacitance of 1 pF (TYP) per I/O
3	Diode array	Protects memory card from user-induced ESD event	SP1006	Enables compact design; low power loss	Industry's smallest footprint available (0201); low leakage current
4	Solid state relay	Optically-isolated switch to drive motor	CPC1560 , CPC1561B	Robust operation with integrated protection in case of motor stalling	Integrated current limit, thermal shutdown; bounce-free switching; fast turn-on


Littelfuse solutions for wired doorbell cameras





Click on the product series in the table below for more info

Wired doorbell camera functional block diagram



	Technology	Series
1a	Fuse	443, 449
	Solid state relay	PLB190
	TVS diode	4.0SMDJ24A
1b*	Fuse, PPTC	469, 449, 1206L450SL
	TVS diode	SMBJ
	MLV	MLA
	NTC	KC
2	Diode array	SP1006
3**	Solid state relay	LCB710
4	Diode array	SP1006
5***	Polymer ESD suppressor	PGB10603, PGB10402

* In some applications, micro-USB port is provided for charging removable Li-Ion batteries. The rechargeable battery is built in and gets power from the main power stage

** This is found in European markets where SSR is used to cut off vampire power and as an energy harvester switch to transfer power to the image sensor only a few times an hour, as per privacy regulations

*** This is recommended for compact designs where clearance between the antenna and the casing is < 2 mm



Click on the product series in the table below for more info

Benefits of Littelfuse products for doorbell cameras

	Technology	Function in application	Product series	Benefits	Features
1a	Fuse	Protects the power stage from overcurrent events	443, 449	Reduces customer qualification time by complying with UL/IEC; compact design; avoids nuisance trips	Surface mountable; compatible with the lead-free solder process; wide range of current ratings; time lag fuse
	Solid state relay	Optically-isolated switch	PLB190	Improves system reliability; enables compact design	5000 Vrms input/output isolation; no EMI/RFI generation; arc-free with no snubbing circuits
	TVS diode	Protects sensitive electronic parts from voltage transients	4.0SMDJ24A	Improves system reliability by clamping the voltage at safe levels during transients	4000 W peak pulse capability; lead-free solder reflow temperature profile compatible
1b	Fuse	Protects from high discharge currents due to external shorts	469, 449	Reduces customer qualification time by complying with UL/IEC; compact design	Surface mountable; wide range of current ratings available; compatible with the lead-free solder process, per IEC standards
	TVS diode	Protects sensitive electronic parts from voltage transients	SMBJ	Enables compact design; improves system reliability by protecting downstream parts through clamping the voltage at safe levels during transients on power lines	600 W peak pulse power capability; excellent clamping capability; fast response time: typically less than 1.0 ps
	MLV	ESD protection for data lines	MLA	Fast clamping response; rigid performance under high temperatures	Bidirectional clamping; low form factor; wide operational temperature range
	NTC	Temperature monitoring of battery pack during charging & discharging cycles	KC	Provides accurate temperature reading for enabling safe device operation	Kynar insulated lead wires, small form factor, fast thermal response
2	Diode array	Protects memory card from user-induced ESD events	SP1006	Enables compact design; low power loss	Industry's smallest footprint available (0201); low leakage current
3	Solid state relay	Optically-isolated switch functions as a dual-purpose switch between chime and camera	LCB710	Enables OEMs to meet European privacy regulation; enables compact design; low power loss and potential energy harvesting	Normally closed switch; no EMI/RFI generation; arc-free with no snubbing circuits
4	Diode array	Protects memory card from user-induced ESD events	SP1006	Enables compact design; low power loss	Industry's smallest footprint available (0201); low leakage current
5	Polymer ESD suppressor	Protects the Wi-Fi chipset from user-induced ESD events	PGB10603 , PGB10402	Enables compact design and low clearance between antenna and casing; retains RF signal integrity; improves system reliability	Ultra-low capacitance; compact form factor; low leakage current; fast response time



Littelfuse solutions for wireless security cameras

Wireless interface

- Polymer ESD suppressor



Memory

- Diode array



Charging port

- PPTC
- MLV
- Temperature indicator



Power adapter


- Fuse
- MOV
- TVS diode
- Temperature indicator





Click on the product series in the table below for more info

Wireless security camera functional block diagram



	Technology	Series
1	Fuse	875 , 807 , 373
	MOV	C-III , LA , UltraMOV
	TVS diode	P6KE , P6SMB
	Temperature indicator**	setP™
2	PPTC	0805L , nanoSMD , picoSMD
	MLV	MLA
	Temperature indicator**	setP™
3	Diode array	SP1006
4*	Polymer ESD suppressor	PGB10603 , PGB10402

* This is recommended for compact designs where clearance between the antenna and the casing is < 2 mm

** The setP™ solution is recommended for USB type C port protection.



Click on the product series in the table below for more info


Benefits of Littelfuse products for wireless cameras

	Technology	Function in application	Product series	Benefits	Features
1	Fuse	Protects power stage from overcurrent	875 , 807 , 373	Reduces customer qualification time by complying with third-party safety standards such as UL/IEC	Third-party compliance (UL/IEC); low internal resistance; shock safe; vibration resistant
	MOV	Protects power unit from voltage transients and lightning	C-III , LA , UltraMOV	Reduces customer qualification time by complying with third-party safety standards such as UL/IEC	High energy absorption capability: 40–530J (2ms)
	TVS diode	Protects power unit from voltage transients	P6KE , P6SMB	Improves system reliability by protecting downstream parts from transients on power lines	600 W peak pulse capability; glass passivated chip junction; compatible with lead-free solder reflow temperature profile
	Temperature indicator	Protects USB-C plugs and receptacles from overheating	setP™	Auto resets after fault is removed; allows for compact design	Resettable; low resistance; compact design
2	PPTC	Protects the power stage from overcurrent events	0805L , nanoSMD , picoSMD	Auto resets after fault is removed; allows for compact design	Resettable; low resistance; compact design
	MLV	ESD protection for data lines	MLA	Fast clamping response; rigid performance under high temperatures	Bidirectional clamping; low form factor; wide operational temperature range
	Temperature indicator	Protects USB-C plugs and receptacles from overheating	setP™	Auto resets after fault is removed; allows for compact design	Resettable; low resistance; compact design
3	Diode array	Protects memory card from user-induced ESD events	SP1006	Enables compact design; low power loss	Industry's smallest footprint available (0201); low leakage current
4	Polymer ESD suppressor	Protects the Wi-Fi chipset from user-induced ESD events	PGB10603 , PGB10402	Enables compact design and low clearance between antenna and casing; retains RF signal integrity; improves system reliability	Ultra-low capacitance; compact form factor; low leakage current; fast response time

Select safety standards for surveillance cameras

Standard	Title	General scope	Littelfuse Technology	Region
IEC 62368-1	Audio/video, information and communication technology equipment – Part 1: safety requirements	This part of IEC 62368 is a product safety standard that classifies energy sources; prescribes safeguards against those energy sources; provides guidance on the application of, and requirements for, those safeguards	Fuse, MOV	Global
IEC 62311-2	Secondary cells and batteries containing alkaline or other non-acid electrolytes	Safety requirements for portable sealed secondary lithium cells, and for batteries made from them, for use in portable applications - Part 2: Lithium systems	Fuse, PPTC	Global

Thermal scanning using security cameras to monitor body temperature post **COVID-19**



Click on images to open the catalog

Circuit Protection Selection Guide

Sensor Selection Guide

Industrial Fuses Catalog

Power Semiconductor Selection Guide

Integrated Circuits Catalog

Power Relay & Control Catalog


Littelfuse Capability Brochure

IXYS
A Littelfuse Technology


IXYS Integrated Circuits Product Catalog 2018 - 2019
High Voltage, Analog & Mixed Signal ICs, Optically Isolated Devices

PROTECT CONTROL SENSE

Local resources supporting our global customers



Partner for tomorrow's electronic systems





Expertise Applied | Answers Delivered



Littelfuse.com

This document is provided by Littelfuse, Inc. ("Littelfuse") for informational and guideline purposes only. Littelfuse assumes no liability for errors or omissions in this document or for any of the information contained herein. Information is provided on an "as is" and "with all faults" basis for evaluation purposes only. Applications described are for illustrative purposes only and Littelfuse makes no representation that such applications will be suitable for the customer's specific use without further testing or modification. Littelfuse expressly disclaims all warranties, whether express, implied, or statutory, including but not limited to the implied warranties of merchantability and fitness for a particular purpose and non-infringement. It is the customer's sole responsibility to determine suitability for a particular system or use based on their own performance criteria, conditions, specific application, compatibility with other parts, and environmental conditions. Customers must independently provide appropriate design and operating safeguards to minimize any risks associated with their applications and products. Read complete Disclaimer Notice at littelfuse.com/disclaimer-electronics.