

FSUSB30

Low-Power, Two-Port, High-Speed USB 2.0 (480Mbps) Switch

Features

- ? Low On Capacitance: 3.7pF (Typical)
- ? Low On Resistance: 6.5Ω (Typical)
- ? Low Power Consumption: 1μA (Maximum)
 - 10μA Maximum I_{CC}T over an Expanded Control Voltage Range (V_{IN} = 2.6V, V_{CC} = 4.3V)
- ? Wide -3dB Bandwidth, >720MHz
- ? 8kV ESD Protection
- ? Power-Off Protection when V_{CC} = 0V; D+/D- Pins can Tolerate up to 5.5V
- ? Packaged in:
 - 10-lead MicroPak™ (1.6 x 2.1mm)
 - 10-lead MSOP
 - 10-lead UMLP (1.4 x 1.8mm)

Applications

- ? Cell phone, PDA, Digital Camera, and Notebook LCD Monitor, TV, and Set-top Box

Related Application Notes

- ? *AN-6022 Using the FSUSB30 / FSUSB31 to Comply with USB 2.0 Fault Condition Requirements*

Description

The FSUSB30 is a low-power, two-port, high-speed USB 2.0 switch. Configured as a double-pole double-throw (DPDT) switch, it is optimized for switching between two high-speed (480Mbps) sources or a Hi-Speed and Full-Speed (12Mbps) source. The FSUSB30 is compatible with the requirements of USB2.0 and features an extremely low on capacitance (C_{ON}) of 3.7pF. The wide bandwidth of this device (720MHz), exceeds the bandwidth needed to pass the third harmonic, resulting in signals with minimum edge and phase distortion. Superior channel-to-channel crosstalk minimizes interference.

The FSUSB30 contains special circuitry on the D+/D- pins which allows the device to withstand an overvoltage condition when powered off. This device is also designed to minimize current consumption even when the control voltage applied to the S pin, is lower than the supply voltage (V_{CC}). This feature is especially valuable to ultra-portable applications such as cell phones, allowing for direct interface with the general purpose I/Os of the baseband processor. Other applications include switching and connector sharing in portable cell phones, PDAs, digital cameras, printers, and notebook computers.

Ordering Information

| Order Number | Package Number | Product Code Top Mark | Package Description |
|--------------|----------------|-----------------------|---|
| FSUSB30L10X | MAC010A | FJ | 10-Lead MicroPak, 1.6 x 2.1mm |
| FSUSB30MUX | MUA10A | FSUSB30 | 10-Lead Molded Small Outline Package (MSOP), JEDEC MO-187, 3.0mm Wide |
| FSUSB30UMX | MLP010A | GJ | 10-Lead, Quad, Ultrathin, MLP (UMLP) 1.4 x 1.8mm |





Figure 1. Typical Application


MicroPak™ is a trademark of Fairchild Semiconductor Corporation.

Connection Diagrams


Pad Assignments for MicroPak




Pad Assignments for DQFN




Pin Assignment for MSOP



Pad Assignments for μ MLP



Analog Symbol



Pin Descriptions

| Pin Name | Description |
|----------------------|-------------------|
| \overline{OE} | Bus Switch Enable |
| S | Select Input |
| D+, D-, HSDn+, HSDn- | Data Ports |
| NC | No Connect |

Truth Table

| S | \overline{OE} | Function |
|------|-----------------|----------------------------|
| X | HIGH | Disconnect |
| LOW | LOW | D+, D- = HSD1 _n |
| HIGH | LOW | D+, D- = HSD2 _n |

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

| Symbol | Parameter | Minimum | Maximum | Unit | |
|-------------|----------------------------------|-------------------------|----------|----------|----|
| V_{CC} | Supply Voltage | -0.5 | +5.5 | V | |
| V_{CNTRL} | DC Input Voltage ⁽¹⁾ | -0.5 | V_{CC} | V | |
| V_{SW} | DC Switch Voltage ⁽¹⁾ | HSDnX | 0.5 | V_{CC} | V |
| | | D+,D- when $V_{CC} > 0$ | 0.5 | V_{CC} | V |
| | | D+,D- when $V_{CC} = 0$ | -0.50 | V_{CC} | V |
| I_{IK} | DC Input Diode Current | -50 | | mA | |
| I_{OUT} | DC Output Current | | 50 | mA | |
| T_{STG} | Storage Temperature | -65 | +150 | °C | |
| ESD | Human Body Model | All Pins | | 8 | kV |
| | | I/O to GND | | 8 | kV |

Note:

1. The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.⁽²⁾

| Symbol | Parameter | Minimum | Maximum | Unit |
|---------------|---------------------------------|---------|----------|------|
| V_{CC} | Supply Voltage | 3.0 | 4.3 | V |
| V_{IN} | Control Input Voltage | 0 | V_{CC} | V |
| V_{SW} | Switch Input Voltage | 0 | V_{CC} | V |
| T_A | Operating Temperature | -40 | +85 | °C |
| θ_{JA} | Thermal Resistance, 10 MicroPak | | 250 | °C/W |

Note:

2. Control input must be held HIGH or LOW and it must not float.

DC Electrical Characteristics

All typical values are at 25°C unless otherwise specified.

| Symbol | Parameter | Conditions | V _{CC} (V) | T _A = -40°C to +85°C | | | Unit |
|--------------------------|---|---|---------------------|---------------------------------|------|------|------|
| | | | | Min. | Typ. | Max. | |
| V _{IK} | Clamp Diode Voltage | I _{IN} = -18mA | 3.0 | | | -1.2 | V |
| V _{IH} | Input Voltage HIGH | | 3.0 to 3.6 | 1.3 | | | V |
| | | | 4.3 | 1.7 | | | V |
| V _{IL} | Input Voltage LOW | | 3.0 to 3.6 | | | 0.5 | V |
| | | | 4.3 | | | 0.7 | V |
| I _{IN} | Control Input Leakage | V _{SW} = 0.0V to V _{CC} | 4.3 | -1.0 | | 1.0 | μA |
| I _{OZ} | OFF State Leakage | 0 ≤ D _n , HSD1 _n , HSD2 _n ≤ V _{CC} | 4.3 | -2.0 | | 2.0 | μA |
| I _{OFF} | Power OFF Leakage Current (D+, D-) | V _{SW} = 0V to 4.3V, V _{CC} = 0V | 0 | -2.0 | | 2.0 | μA |
| R _{ON} | Switch On Resistance ⁽³⁾ | V _{SW} = 0.4V, I _{ON} = -8mA V _{SW} = 0V, I _O = 30mA at 25°C | 3.0 | | 6.5 | 10.0 | Ω |
| | | | 3.6 | | | 7.0 | Ω |
| ΔR _{ON} | Delta R _{ON} ⁽⁴⁾ | V _{SW} = 0.4V, I _{ON} = -8mA | 3.0 | | 0.35 | | Ω |
| R _{ON} Flatness | R _{ON} Flatness ⁽³⁾ | V _{SW} = 0.0V - 1.0V, I _{ON} = -8mA | 3.0 | | 2.0 | | Ω |
| I _{CC} | Quiescent Supply Current | V _{CNTRL} = 0.0V or V _{CC} , I _{OUT} = 0 | 4.3 | | | 1.0 | μA |
| I _{CCT} | Increase in I _{CC} Current per Control Voltage | V _{CNTRL} (control input) = 2.6V | 4.3 | | | 10.0 | μA |

Notes:

- Measured by the voltage drop between D_n, HSD1_n, HSD2_n pins at the indicated current through the switch. On resistance is determined by the lower of the voltage on the two ports.
- Guaranteed by characterization.

AC Electrical Characteristics

All typical values are for V_{CC} = 3.3V at 25°C unless otherwise specified.

| Symbol | Parameter | Conditions | V _{CC} (V) | T _A = -40°C to +85°C | | | Unit | Figure Number |
|------------------|----------------------------------|---|---------------------|---------------------------------|------|------|------|----------------------|
| | | | | Min. | Typ. | Max. | | |
| t _{ON} | Turn-On Time S, OE to Output | HD1 _n , HD2 _n = 0.8V, R _L = 50Ω, C _L = 5pF | 3.0 to 3.6 | | 13 | 30 | ns | Figure 9 |
| t _{OFF} | Turn-Off Time S, OE to Output | HD1 _n , HD2 _n = 0.8V, R _L = 50Ω, C _L = 5pF | 3.0 to 3.6 | | 12 | 25 | ns | Figure 9 |
| t _{PD} | Propagation Delay ⁽⁴⁾ | R _L = 50Ω, C _L = 5pF | 3.3 | | 0.25 | | ns | Figure 7 Figure 8 |
| t _{BMM} | Break-Before-Make | R _L = 50Ω, C _L = 5pF, V _{IN} = 0.8V | 3.0 to 3.6 | 2.0 | | 6.5 | ns | Figure 10 |
| O _{IRR} | Off Isolation (Non-Adjacent) | f = 240MHz, R _T = 50Ω | 3.0 to 3.6 | | -30 | | dB | Figure 13 |
| Xtalk | Non-Adjacent Channel Crosstalk | R _T = 50Ω, f = 240MHz | 3.0 to 3.6 | | -45 | | dB | Figure 14 |
| BW | -3dB Bandwidth | R _T = 50Ω, C _L = 0pF | 3.0 to 3.6 | | 720 | | MHz | Figure 12 |
| | | R _T = 50Ω, C _L = 5pF | | | 550 | | | |

USB Hi-Speed Related AC Electrical Characteristics

| Symbol | Parameter | Conditions | V _{CC} (V) | T _A = -40°C to +85°C | | | Units | Figure Number |
|--------------------|--|--|---------------------|---------------------------------|------|------|-------|-----------------------|
| | | | | Min. | Typ. | Max. | | |
| t _{SK(O)} | Channel-to-Channel Skew ⁽⁵⁾ | R _L = 50Ω, C _L = 5pF | 3.0 to 3.6 | | 50 | | ps | Figure 7 Figure 11 |
| t _{SK(P)} | Skew of Opposite Transitions of the Same Output ⁽⁵⁾ | R _L = 50Ω, C _L = 5pF | 3.0 to 3.6 | | 20 | | ps | Figure 7 Figure 11 |
| t _J | Total Jitter ⁽⁵⁾ | R _L = 50Ω, C _L = 5pF, t _R = t _F = 500ps at 480 Mbps (PRBS = 2 ¹⁵ - 1) | 3.0 to 3.6 | | 200 | | ps | |

Note:

5. Guaranteed by characterization.

Capacitance

| Symbol | Parameter | Conditions | T _A = -40°C to +85°C | | | Units | Figure Number |
|------------------|---|---|---------------------------------|------|------|-------|---------------|
| | | | Min. | Typ. | Max. | | |
| C _{IN} | Control Pin Input Capacitance | V _{CC} = 0V | | 1.5 | | pF | Figure 16 |
| C _{ON} | D1 _n , D2 _n , Dn On Capacitance | V _{CC} = 3.3, \overline{OE} = 0V | | 3.7 | | pF | Figure 15 |
| C _{OFF} | D1 _n , D2 _n Off Capacitance | V _{CC} and \overline{OE} = 3.3 | | 2.5 | | pF | Figure 16 |

Typical Characteristics




Figure 2. Gain vs. Frequency




Figure 3. Off Isolation




Figure 4. Crosstalk

Test Diagrams






Figure 5. On Resistance



Each switch port is tested separately.

Figure 6. Off Leakage



R_L , R_S , and C_L are functions of the application environment (see AC Electrical tables for specific values).

C_L includes test fixture and stray capacitance.

Figure 7. AC Test Circuit Load




Figure 8. Switch Propagation Delay Waveforms







Figure 9. Turn-On / Turn-Off Waveform






Figure 13. Channel Off Isolation




Figure 14. Non-Adjacent Channel-to-Channel Crosstalk




Figure 15. Channel On Capacitance




Figure 16. Channel Off Capacitance

Application Guidance: Meeting USB 2.0 Vbus Short Requirements

In section 7.1.1 of the USB 2.0 specification, it notes that USB devices must be able to withstand a Vbus short to D+ or D- when the USB devices is either powered off or powered on. The FSUSB30 can be successfully configured to meet both these requirements.

Power-Off Protection

For a Vbus short circuit, the switch is expected to withstand such a condition for at least 24 hours. The FSUSB30 has specially designed circuitry which prevents unintended signal bleed through as well as guaranteed system reliability during a power-down, over-voltage condition. The protection has been added to the common pins (D+, D-).

Power-On Protection

The USB 2.0 specification also notes that the USB device should be capable of withstanding a Vbus short during transmission of data. Fairchild recommends adding a 100Ω series resistor between the switch VCC pin and supply rail to protect against this case. This modification works by limiting current flow back into the V_{CC} rail during the over-voltage event so current remains within the safe operating range. In this application, the switch passes the full 5.25V input signal through to the selected output, while maintaining specified off isolation on the un-selected pins.




Figure 17. Adding 100Ω resistor in series with the V_{CC} supply allows the FSUSB30 to withstand a Vbus short when powered up

For more information, see Applications Note *AN-6022 Using the FSUSB30 to Comply with USB 2.0 Fault Condition Requirements* at www.fairchildsemi.com


Tape and Reel Specifications

Tape Format for DQFN

| Package Designator | Tape Section | Number Cavities | Cavity Status | Cover Tape Status |
|--------------------|--------------------|-----------------|---------------|-------------------|
| BQX | Leader (Start End) | 125 (typ) | Empty | Sealed |
| | Carrier | 2500/3000 | Filled | Sealed |
| | Trailer (Hub End) | 75 (typ) | Empty | Sealed |

Tape Dimensions

Dimensions are in millimeters unless otherwise specified.



DIMENSIONS ARE IN MILLIMETERS


NOTES: unless otherwise specified

1. Cumulative pitch for feeding holes and cavities (chip pockets) not to exceed 0.008[0.20] over 10 pitch span.
2. Smallest allowable bending radius.
3. Thru hole inside cavity is centered within cavity.
4. Tolerance is ±0.002[0.05] for these dimensions on all 12mm tapes.
5. A_o and B_o measured on a plane 0.120[0.30] above the bottom of the pocket.
6. K_o measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
7. Pocket position relative to sprocket hole measured as true position of pocket. Not pocket hole.
8. Controlling dimension is millimeter. Dimension in inches rounded.



Reel Dimensions for DQFN


Dimensions are in inches (millimeters) unless otherwise specified.



| Tape Size | A | B | C | D | N | W1 | W2 |
|-----------|---------------|-----------------|------------------|------------------|----------------|-----------------|-----------------|
| (12mm) | 13.0 (330) | 0.059 (1.50) | 0.512 (13.00) | 0.795 (20.20) | 7.008 (178) | 0.488 (12.4) | 0.724 (18.4) |

Tape Dimensions for MSOP

Dimensions are in inches (millimeters) unless otherwise specified.




Notes:

1. All dimensions are in millimeters.
2. Measured from centerline of sprocket hole to centerline of pocket.
3. Cumulative tolerance of ten sprocket holes is ±0.20mm.
4. Other material available.

Reel Dimensions for MSOP

Dimensions are in inches (millimeters) unless otherwise specified.



| Tape Size | A | B | C | D | N | W1 | W2 | W3 |
|-----------|-------------|----------------|---------------|-----------------|----------------|-----------------|-----------------|-----------------------------|
| (12mm) | 13 (330) | 0.059 (1.5) | 0.512 (13) | 0.795 (20.2) | 7.008 (178) | 0.448 (12.4) | 0.724 (18.4) | 0.468-0.606 (11.9 -15.4) |

Physical Dimensions




Figure 17. 10-Lead MicroPak, 1.6 x 2.1mm

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:
<http://www.fairchildsemi.com/packaging/>

Physical Dimensions




Figure 18. 10-Lead Molded Small Outline Package (MSOP), JEDEC MO-187, 3.0mm Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

<http://www.fairchildsemi.com/packaging/>

Physical Dimensions




Figure 19. 10-Lead, Quad, Ultrathin Molded Leadless Package (UMLP), 1.4 x 1.8mm

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:
<http://www.fairchildsemi.com/packaging/>.



TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

- | | | | |
|--------------------------|--|---------------------------------------|------------------|
| 2Cool™ | FPS™ | | Sync-Lock™ |
| AccuPower™ | F-PFS™ | PowerTrench® | SYSTEM GENERAL® |
| AX-CAP®* | FRFET® | PowerXS™ | TinyBoost™ |
| BitSiC™ | Global Power Resource™ | Programmable Active Droop™ | TinyBuck™ |
| Build it Now™ | GreenBridge™ | QFET® | TinyCalc™ |
| CorePLUS™ | Green FPS™ | QS™ | TinyLogic® |
| CorePOWER™ | Green FPS™ e-Series™ | Quiet Series™ | TINYOPTO™ |
| CROSSVOLT™ | Gmax™ | RapidConfigure™ | TinyPower™ |
| CTL™ | GTO™ | | TinyPWM™ |
| Current Transfer Logic™ | IntelliMAX™ | Saving our world, 1mW/W/kW at a time™ | TinyWire™ |
| DEUXPEED® | ISOPLANAR™ | SignalWise™ | TranSiC™ |
| Dual Cool™ | Making Small Speakers Sound Louder and Better™ | SmartMax™ | TriFault Detect™ |
| EcoSPARK® | MegaBuck™ | SMART START™ | TRUECURRENT®* |
| EfficientMax™ | MICROCOUPLER™ | Solutions for Your Success™ | µSerDes™ |
| ESBC™ | MicroFET™ | SPM® | |
| | MicroPak™ | STEALTH™ | UHC® |
| Fairchild® | MicroPak2™ | SuperFET® | Ultra FRFET™ |
| Fairchild Semiconductor® | MillerDrive™ | SuperSOT™-3 | UniFET™ |
| FACT Quiet Series™ | MotionMax™ | SuperSOT™-6 | VCX™ |
| FACT™ | mWSaver™ | SuperSOT™-8 | VisualMax™ |
| FAST™ | OptoHiT™ | SupreMOS® | VoltagePlus™ |
| FastvCore™ | OPTOLOGIC® | SyncFET™ | XS™ |
| FETBench™ | OPTOPLANAR® | | |

* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms

| Datasheet Identification | Product Status | Definition |
|--------------------------|-----------------------|---|
| Advance Information | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice. |
| Preliminary | First Production | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design. |
| Obsolete | Not In Production | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only. |

Rev. I64

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fairchild Semiconductor:](#)

[FSUSB30L10X](#) [FSUSB30MUX](#) [FSUSB30UMX](#)