


XLamp® XP-G4 LEDs



PRODUCT DESCRIPTION

XLamp® XP-G4 LEDs are are the fourth generation of Cree LED's standard-setting XP-G product family, featuring both best-in-class efficacy and optical performance. New features in this generation include a higher maximum drive current of 3000 mA and an optimized optical profile that maximizes on-axis light output.

With the same mechanical dimensions as XP-G3, the XP-G4 is an easy upgrade path for many high-power LED designs. XP-G4 provides higher maximum current and lower thermal resistance than competing high-power LEDs, enabling new levels of output and reliability for many lighting applications.

XLamp XP-G4 LEDs are optimized for a wide range of directional lighting applications where light control and long lifetime are critical, including outdoor, indoor premium, architectural, portable and entertainment.

FEATURES

- Available in no CRI minimum white, 70-, 80- and 90-CRI white
- ANSI-compatible chromaticity bins
- Broadcast color option at 5700 K provides maximum performance for TV events that require extremely high TLCI
- 3-step and 5-step options
- · Binned at 85 °C
- Maximum drive current: 3000 mA
- · Low thermal resistance: 1.3 °C/W
- Wide viewing angle: 120°
- Unlimited floor life at ≤ 30 °C/85% RH
- Reflow solderable JEDEC J-STD-020C
- Electrically neutral thermal path
- · RoHS and REACH compliant
- UL® recognized component (E349212)





TABLE OF CONTENTS

Characteristics
Flux Characteristics
Flux Characteristics - Broadcast Order Codes and Bins
Relative Spectral Power Distribution
Relative Flux vs. Junction Temperature
Electrical Characteristics
Relative Luminous Flux vs. Current
Relative Chromaticity vs. Current and Temperature20
Typical Spatial Distribution
Thermal Design
Performance Groups - Luminous Flux
Performance Groups - Chromaticity
Cree LED's Standard Cool White Kits Plotted on ANSI Standard Chromaticity Regions
Cree LED's Standard Warm and Neutral White Kits Plotted on ANSI Standard Chromaticity Regions2
Cree LED's EasyWhite® White Kits Plotted on ANSI Standard Chromaticity Regions2
Cree LED's Standard Chromaticity Kits
Bin and Order Code Formats
Reflow Soldering Characteristics
Notes
Mechanical Dimensions
Tape and Reel
Packaging3



CHARACTERISTICS

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point	°C/W		1.3	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-1.3	
ESD withstand voltage (HBM per Mil-Std-883D)			Class 3B	
DC forward current	mA			3000
Reverse voltage	V			5
Forward voltage (@ 700 mA, 85 °C)	V		2.8	3.3
Forward voltage (@ 1000 mA, 85 °C)	V		2.92	
Forward voltage (@ 2000 mA, 85 °C)	V		3.14	
Forward voltage (@ 3000 mA, 85 °C)	V		3.32	
CRI R9 (70 CRI minimum)		-40		
CRI R9 (80 CRI minimum)		0		
CRI R9 (90 CRI minimum)		50		
LED junction temperature	°C			150

Note:

♦ Thermal resistance measurement was performed per the JEDEC JESD51-14 standard. See the Thermal Resistance Measurement application note for more details.



FLUX CHARACTERISTICS - T_J = 85 °C

The following table provides order codes for XLamp XP-G4 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 31). For definitions of the chromaticity kits, please see the Cree LED's Standard Chromaticity Kits section (page 30).

Chro	maticity	Minimu	m Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		C5	340	371	XPGEWT-01-0000- 000000QDT	XPGEWT-01-0000- 00000BQDT		
		C4	330	360	XPGEWT-01-0000- 000000PDT	XPGEWT-01-0000- 00000BPDT		
DT	7000 K	C3	320	349	XPGEWT-01-0000- 000000NDT	XPGEWT-01-0000- 00000BNDT	XPGEWT-01-0000- 00000HNDT	
		C2	310	338		XPGEWT-01-0000- 00000BMDT	XPGEWT-01-0000- 00000HMDT	
		C1	300	327			XPGEWT-01-0000- 00000HLDT	
		C5	340	371		XPGEWT-01-0000- 00000BQE0		
	>6500 K	C4	330	360		XPGEWT-01-0000- 00000BPE0		
E0		C3	320	349		XPGEWT-01-0000- 00000BNE0		
		C2	310	338			XPGEWT-01-0000- 00000HME0	
		C1	300	327			XPGEWT-01-0000- 00000HLE0	
		D1	350	382	XPGEWT-01-0000- 000000RE1	XPGEWT-01-0000- 00000BRE1		
		C5	340	371	XPGEWT-01-0000- 000000QE1	XPGEWT-01-0000- 00000BQE1		
E1	6500 K	C4	330	360	XPGEWT-01-0000- 000000PE1	XPGEWT-01-0000- 00000BPE1		
EI	0300 K	C3	320	349			XPGEWT-01-0000- 00000HNE1	
		C2	310	338			XPGEWT-01-0000- 00000HME1	
		C1	300	327			XPGEWT-01-0000- 00000HLE1	

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimum Luminous Flux (lm) @ 700 mA				Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum		
	6000 K	D1	350	382	XPGEWT-01-0000- 000000RDV	XPGEWT-01-0000- 00000BRDV				
		C5	340	371	XPGEWT-01-0000- 000000QDV	XPGEWT-01-0000- 00000BQDV				
DV		C4	330	360	XPGEWT-01-0000- 000000PDV	XPGEWT-01-0000- 00000BPDV				
DV	6000 K	C3	320	349			XPGEWT-01-0000- 00000HNDV			
		C2	310	338			XPGEWT-01-0000- 00000HMDV			
		C1	300	327			XPGEWT-01-0000- 00000HLDV			
		D1	350	382	XPGEWT-01-0000- 000000R50	XPGEWT-01-0000- 00000BR50				
		C5	340	371	XPGEWT-01-0000- 000000Q50	XPGEWT-01-0000- 00000BQ50				
50	6000 K	C4	330	360	XPGEWT-01-0000- 000000P50	XPGEWT-01-0000- 00000BP50				
30		C3	320	349			XPGEWT-01-0000- 00000HN50			
		C2	310	338			XPGEWT-01-0000- 00000HM50			
		C1	300	327			XPGEWT-01-0000- 00000HL50			
		D1	350	382		XPGEWT-01-0000- 00000BR2E				
		C5	340	371		XPGEWT-01-0000- 00000BQ2E				
		C4	330	360		XPGEWT-01-0000- 00000BP2E				
		C3	320	349			XPGEWT-01-0000- 00000HN2E			
2E	5700 K	C2	310	338			XPGEWT-01-0000- 00000HM2E			
		C1	300	327			XPGEWT-01-0000- 00000HL2E			
		B5	290	316						
		B4	280	305				XPGEWT-01-0000- 00000UJ2E		
		В3	270	294				XPGEWT-01-0000- 00000UH2E		

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimur	m Luminous @ 700 mA	Flux (lm)		Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum		
		D1	350	382	XPGEWT-01-0000- 000000RE2	XPGEWT-01-0000- 00000BRE2				
		C5	340	371	XPGEWT-01-0000- 000000QE2	XPGEWT-01-0000- 00000BQE2				
		C4	330	360	XPGEWT-01-0000- 000000PE2	XPGEWT-01-0000- 00000BPE2				
		C3	320	349		XPGEWT-01-0000- 00000BNE2	XPGEWT-01-0000- 00000HNE2			
E2	5700 K	C2	310	338			XPGEWT-01-0000- 00000HME2			
		C1	300	327			XPGEWT-01-0000- 00000HLE2			
		B5	290	316						
		B4	280	305				XPGEWT-01-0000- 00000UJE2		
		В3	270	294				XPGEWT-01-0000- 00000UHE2		
		D2	360	393		XPGEWT-01-0000- 00000BS3E				
		D1	350	382		XPGEWT-01-0000- 00000BR3E				
		C5	340	371		XPGEWT-01-0000- 00000BQ3E				
		C4	330	360		XPGEWT-01-0000- 00000BP3E				
3E	5000 K	C3	320	349			XPGEWT-01-0000- 00000HN3E			
		C2	310	338			XPGEWT-01-0000- 00000HM3E			
		C1	300	327			XPGEWT-01-0000- 00000HL3E			
		B5	290	316						
		B4	280	305				XPGEWT-01-0000- 00000UJ3E		
		В3	270	294				XPGEWT-01-0000- 00000UH3E		

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimum Luminous Flux (lm) @ 700 mA				Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum		
		D2	360	393	XPGEWT-01-0000- 000000SE3	XPGEWT-01-0000- 00000BSE3				
		D1	350	382	XPGEWT-01-0000- 000000RE3	XPGEWT-01-0000- 00000BRE3				
		C5	340	371	XPGEWT-01-0000- 000000QE3	XPGEWT-01-0000- 00000BQE3				
		C4	330	360	XPGEWT-01-0000- 000000PE3	XPGEWT-01-0000- 00000BPE3				
E3	5000 K	C3	320	349			XPGEWT-01-0000- 00000HNE3			
		C2	310	338			XPGEWT-01-0000- 00000HME3			
		C1	300	327			XPGEWT-01-0000- 00000HLE3			
		В5	290	316						
		B4	280	305				XPGEWT-01-0000- 00000UJE3		
		В3	270	294				XPGEWT-01-0000- 00000UHE3		
		D1	350	382	XPGEWT-01-0000- 000000RF4	XPGEWT-01-0000- 00000BRF4				
		C5	340	371	XPGEWT-01-0000- 000000QF4	XPGEWT-01-0000- 00000BQF4				
		C4	330	360	XPGEWT-01-0000- 000000PF4	XPGEWT-01-0000- 00000BPF4				
		C3	320	349			XPGEWT-01-0000- 00000HNF4			
F4	4750 K	C2	310	338			XPGEWT-01-0000- 00000HMF4			
		C1	300	327			XPGEWT-01-0000- 00000HLF4			
		В5	290	316						
		B4	280	305						
		В3	270	294				XPGEWT-01-0000- 00000UHF4		
		B2	260	284				XPGEWT-01-0000- 00000UGF4		

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimur	m Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		D1	350	382		XPGEWT-01-0000- 00000BR4E		
		C5	340	371		XPGEWT-01-0000- 00000BQ4E		
		C4	330	360		XPGEWT-01-0000- 00000BP4E		
		C3	320	349			XPGEWT-01-0000- 00000HN4E	
4E	4500K	C2	310	338			XPGEWT-01-0000- 00000HM4E	
		C1	300	327			XPGEWT-01-0000- 00000HL4E	
		В5	290	316				
		B4	280	305				
		В3	270	294				XPGEWT-01-0000- 00000UH4E
		B2	260	284				XPGEWT-01-0000- 00000UG4E
		D1	350	382	XPGEWT-01-0000- 000000RE4	XPGEWT-01-0000- 00000BRE4		
		C5	340	371	XPGEWT-01-0000- 000000QE4	XPGEWT-01-0000- 00000BQE4		
		C4	330	360	XPGEWT-01-0000- 000000PE4	XPGEWT-01-0000- 00000BPE4		
		C3	320	349			XPGEWT-01-0000- 00000HNE4	
E4	4500 K	C2	310	338			XPGEWT-01-0000- 00000HME4	
		C1	300	327			XPGEWT-01-0000- 00000HLE4	
		В5	290	316				
		B4	280	305				
		В3	270	294				XPGEWT-01-0000- 00000UHE4
		B2	260	284				XPGEWT-01-0000- 00000UGE4

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimu	m Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		D1	350	382	XPGEWT-01-0000- 000000RF5	XPGEWT-01-0000- 00000BRF5		
		C5	340	371	XPGEWT-01-0000- 000000QF5	XPGEWT-01-0000- 00000BQF5		
		C4	330	360	XPGEWT-01-0000- 000000PF5	XPGEWT-01-0000- 00000BPF5		
		C3	320	349			XPGEWT-01-0000- 00000HNF5	
F5	4200 K	C2	310	338			XPGEWT-01-0000- 00000HMF5	
		C1	300	327			XPGEWT-01-0000- 00000HLF5	
		B5	290	316				
		B4	280	305				
		В3	270	294				XPGEWT-01-0000- 00000UHF5
		B2	260	284				XPGEWT-01-0000- 00000UGF5
		D1	350	382		XPGEWT-01-0000- 00000BR5E		
		C5	340	371		XPGEWT-01-0000- 00000BQ5E		
		C4	330	360		XPGEWT-01-0000- 00000BP5E		
		C3	320	349			XPGEWT-01-0000- 00000HN5E	
5E	4000 K	C2	310	338			XPGEWT-01-0000- 00000HM5E	
		C1	300	327			XPGEWT-01-0000- 00000HL5E	
		B5	290	316				
		B4	280	305				
		В3	270	294				XPGEWT-01-0000- 00000UH5E
		B2	260	284				XPGEWT-01-0000- 00000UG5E

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimu	m Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		D1	350	382	XPGEWT-01-0000- 000000RE5	XPGEWT-01-0000- 00000BRE5		
		C5	340	371	XPGEWT-01-0000- 000000QE5	XPGEWT-01-0000- 00000BQE5		
		C4	330	360	XPGEWT-01-0000- 000000PE5	XPGEWT-01-0000- 00000BPE5		
		C3	320	349			XPGEWT-01-0000- 00000HNE5	
E5	4000 K	C2	310	338			XPGEWT-01-0000- 00000HME5	
		C1	300	327			XPGEWT-01-0000- 00000HLE5	
		B5	290	316				
		B4	280	305				
		В3	270	294				XPGEWT-01-0000- 00000UHE5
		B2	260	284				XPGEWT-01-0000- 00000UGE5
		C5	340	371	XPGEWT-01-0000- 000000QF6	XPGEWT-01-0000- 00000BQF6		
		C4	330	360	XPGEWT-01-0000- 000000PF6	XPGEWT-01-0000- 00000BPF6		
		C3	320	349	XPGEWT-01-0000- 000000NF6	XPGEWT-01-0000- 00000BNF6		
		C2	310	338			XPGEWT-01-0000- 00000HMF6	
F6	3700 K	C1	300	327			XPGEWT-01-0000- 00000HLF6	
		B5	290	316			XPGEWT-01-0000- 00000HKF6	
		B4	280	305				
		В3	270	294				
		B2	260	284				XPGEWT-01-0000- 00000UGF6
		B1	250	273				XPGEWT-01-0000- 00000UFF6

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimur	m Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		C5	340	371		XPGEWT-01-0000- 00000BQ6E		
		C4	330	360		XPGEWT-01-0000- 00000BP6E		
		C3	320	349		XPGEWT-01-0000- 00000BN6E		
		C2	310	338			XPGEWT-01-0000- 00000HM6E	
6E	3500 K	C1	300	327			XPGEWT-01-0000- 00000HL6E	
		B5	290	316			XPGEWT-01-0000- 00000HK6E	
		B4	280	305				
		В3	270	294				
		B2	260	284				XPGEWT-01-0000- 00000UG6E
		B1	250	273				XPGEWT-01-0000- 00000UF6E
6G	3500 K	B2	260	284				XPGEWT-01-0000- 00000UG6G
OG	3300 K	B1	250	273				XPGEWT-01-0000- 00000UF6G
		C5	340	371	XPGEWT-01-0000- 000000QE6	XPGEWT-01-0000- 00000BQE6		
		C4	330	360	XPGEWT-01-0000- 000000PE6	XPGEWT-01-0000- 00000BPE6		
		C3	320	349	XPGEWT-01-0000- 000000NE6	XPGEWT-01-0000- 00000BNE6		
		C2	310	338			XPGEWT-01-0000- 00000HME6	
E6	3500 K	C1	300	327			XPGEWT-01-0000- 00000HLE6	
		B5	290	316			XPGEWT-01-0000- 00000HKE6	
		В4	280	305				
		В3	270	294				
		B2	260	284				XPGEWT-01-0000- 00000UGE6
		B1	250	273				XPGEWT-01-0000- 00000UFE6

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



FLUX CHARACTERISTICS (T_J = 85 °C) - CONTINUED

Chro	Chromaticity Minimum Luminous Flux (Im) @ 700 mA		Flux (lm)	Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		C5	340	371	XPGEWT-01-0000- 000000QF7	XPGEWT-01-0000- 00000BQF7		
		C4	330	360	XPGEWT-01-0000- 000000PF7	XPGEWT-01-0000- 00000BPF7		
		C3	320	349	XPGEWT-01-0000- 000000NF7	XPGEWT-01-0000- 00000BNF7		
		C2	310	338				
		C1	300	327			XPGEWT-01-0000- 00000HLF7	
F7	3200K	B5	290	316			XPGEWT-01-0000- 00000HKF7	
		B4	280	305			XPGEWT-01-0000- 00000HJF7	
		В3	270	294				
		B2	260	284				
		B1	250	273				XPGEWT-01-0000- 00000UFF7
		A5	240	262				XPGEWT-01-0000- 00000UEF7
		A4	230	251				XPGEWT-01-0000- 00000UDF7

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimur	m Luminous @ 700 mA	Flux (lm)		Order Codes				
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum		
		C5	340	371		XPGEWT-01-0000- 00000BQ7E				
		C4	330	360		XPGEWT-01-0000- 00000BP7E				
		C3	320	349		XPGEWT-01-0000- 00000BN7E				
		C2	310	338						
		C1	300	327			XPGEWT-01-0000- 00000HL7E			
7E	3000 K	B5	290	316			XPGEWT-01-0000- 00000HK7E			
	0000 K	B4	280	305			XPGEWT-01-0000- 00000HJ7E			
		В3	270	294						
		B2	260	284						
		B1	250	273				XPGEWT-01-0000- 00000UF7E		
		A5	240	262				XPGEWT-01-0000- 00000UE7E		
		A4	230	251				XPGEWT-01-0000- 00000UD7E		
		B1	250	273				XPGEWT-01-0000- 00000UF7G		
7G	3000 K	A5	240	262				XPGEWT-01-0000- 00000UE7G		
		A4	230	251				XPGEWT-01-0000- 00000UD7G		

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimur	n Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		C5	340	371	XPGEWT-01-0000- 000000QE7	XPGEWT-01-0000- 00000BQE7		
		C4	330	360	XPGEWT-01-0000- 000000PE7	XPGEWT-01-0000- 00000BPE7		
		C3	320	349	XPGEWT-01-0000- 000000NE7	XPGEWT-01-0000- 00000BNE7		
		C2	310	338				
		C1	300	327			XPGEWT-01-0000- 00000HLE7	
E7	3000 K	В5	290	316			XPGEWT-01-0000- 00000HKE7	
		B4	280	305			XPGEWT-01-0000- 00000HJE7	
		В3	270	294				
		B2	260	284				
		B1	250	273				XPGEWT-01-0000- 00000UFE7
		A5	240	262				XPGEWT-01-0000- 00000UEE7
		A4	230	251				XPGEWT-01-0000- 00000UDE7
		C3	320	349	XPGEWT-01-0000- 000000NF8	XPGEWT-01-0000- 00000BNF8		
		C2	310	338	XPGEWT-01-0000- 000000MF8	XPGEWT-01-0000- 00000BMF8		
		C1	300	327	XPGEWT-01-0000- 000000LF8	XPGEWT-01-0000- 00000BLF8	XPGEWT-01-0000- 00000HLF8	
		В5	290	316			XPGEWT-01-0000- 00000HKF8	
F8	2850 K	B4	280	305			XPGEWT-01-0000- 00000HJF8	
	200010	В3	270	294				
		B2	260	284				
		B1	250	273				
		A5	240	262				
		A4	230	251				XPGEWT-01-0000- 00000UDF8
		А3	220	240				XPGEWT-01-0000- 00000UCF8

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- Flux values @ 25 °C are calculated and for reference only.



Chro	maticity	Minimu	m Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (lm) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		C3	320	349		XPGEWT-01-0000- 00000BN8E		
		C2	310	338		XPGEWT-01-0000- 00000BM8E		
		C1	300	327		XPGEWT-01-0000- 00000BL8E	XPGEWT-01-0000- 00000HL8E	
		B5	290	316			XPGEWT-01-0000- 00000HK8E	
8E	2700 K	B4	280	305			XPGEWT-01-0000- 00000HJ8E	
OL	270010	В3	270	294				
		B2	260	284				
		B1	250	273				
		A5	240	262				
		A4	230	251				XPGEWT-01-0000- 00000UD8E
		А3	220	240				XPGEWT-01-0000- 00000UC8E
0.0	2700 K	A4	230	251				XPGEWT-01-0000- 00000UD8G
8G	2700 K	А3	220	240				XPGEWT-01-0000- 00000UC8G
		C3	320	349	XPGEWT-01-0000- 000000NE8	XPGEWT-01-0000- 00000BNE8		
		C2	310	338	XPGEWT-01-0000- 000000ME8	XPGEWT-01-0000- 00000BME8		
		C1	300	327	XPGEWT-01-0000- 000000LE8	XPGEWT-01-0000- 00000BLE8	XPGEWT-01-0000- 00000HLE8	
		B5	290	316			XPGEWT-01-0000- 00000HKE8	
E8	2700K	B4	280	305			XPGEWT-01-0000- 00000HJE8	
		В3	270	294				
		B2	260	284				
		B1	250	273				
		A5	240	262				
		A4	230	251				XPGEWT-01-0000- 00000UDE8
		A3	220	240				XPGEWT-01-0000- 00000UCE8

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



FLUX CHARACTERISTICS (T_J = 85 °C) - CONTINUED

Chro	maticity	Minimu	m Luminous @ 700 mA	Flux (lm)		Order	Codes	
Kit	сст	Code	Flux (Im) @ 85 °C	Flux (lm) @25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
		B4	280	305	XPGEWT-01-0000- 000000JEA	XPGEWT-01-0000- 00000BJEA		
EA	2200 K	В3	270	294	XPGEWT-01-0000- 000000HEA	XPGEWT-01-0000- 00000BHEA		
EA	2200 K	B2	260	284	XPGEWT-01-0000- 000000GEA	XPGEWT-01-0000- 00000BGEA		
		B1	250	273	XPGEWT-01-0000- 000000FEA	XPGEWT-01-0000- 00000BFEA		
		В4	280	305		XPGEWT-01-0000- 00000BJAE		
AE	2200 K	В3	270	294		XPGEWT-01-0000- 00000BHAE		
AE	2200 K	B2	260	284		XPGEWT-01-0000- 00000BGAE		
		B1	250	273		XPGEWT-01-0000- 00000BFAE		
		A5	240	262	XPGEWT-01-0000- 000000EBE	XPGEWT-01-0000- 00000BEBE		
BE	1800 K	A4	230	251	XPGEWT-01-0000- 000000DBE	XPGEWT-01-0000- 00000BDBE		
		А3	220	240	XPGEWT-01-0000- 000000CBE	XPGEWT-01-0000- 00000BCBE		

- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.



FLUX CHARACTERISTICS - BROADCAST ORDER CODES AND BINS (T_J = 85 °C)


The following table provides order codes for XLamp XP-G4 Broadcast LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 31). For definitions of the chromaticity kits, please see the Standard Chromaticity Kits section (page 30).

Chrom	aticity	Minimum Luminous Flux (lm) @ 700 mA			Order Codes				
Kit	сст	Flux Bin	Flux Bin		90 CRI Minimum 90 TLCI Minimum	95 CRI Minimum 95 TLCI Minimum			
		В4	280	305	XPGEWT-01-0000-0T000UJE2				
EO	5700 V	В3	270	294	XPGEWT-01-0000-0T000UHE2	XPGEWT-01-0000-0T000ZHE2			
EZ	E2 5700 K	B2	260	284	XPGEWT-01-0000-0T000UGE2	XPGEWT-01-0000-0T000ZGE2			
		B1	250	273		XPGEWT-01-0000-0T000ZFE2			


- TLCI refers to the European Broadcast Union's Television Lighting Consistency Index 2012, which aids broadcasters in assessing the
 colorimetric quality of lighting in their production environment. Cree LED maintains a tolerance of ±2 on TLCI measurements. See the Measurements
 section (page 33).
- Cree LED maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI. See the Measurements section (page 33).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- Flux values @ 25 °C are calculated and for reference only.



RELATIVE SPECTRAL POWER DISTRIBUTION




RELATIVE FLUX VS. JUNCTION TEMPERATURE ($I_F = 700 \text{ mA}$)






ELECTRICAL CHARACTERISTICS (T_J = 85 °C)




RELATIVE LUMINOUS FLUX VS. CURRENT (T $_{\rm J}$ = 85 °C)






RELATIVE CHROMATICITY VS. CURRENT AND TEMPERATURE


Data shown is representative of typical XP-G4 70 CRI performance.








TYPICAL SPATIAL DISTRIBUTION



THERMAL DESIGN

The maximum forward current is determined by the thermal resistance between the LED junction and ambient. It is crucial for the end product to be designed in a manner that minimizes the thermal resistance from the solder point to ambient in order to optimize lamp life and optical characteristics.





PERFORMANCE GROUPS - LUMINOUS FLUX

XLamp XP-G4 LEDs are tested for luminous flux and placed into one of the following luminous-flux groups.

Group Code	Minimum Luminous Flux (lm) @ 700 mA	Maximum Luminous Flux (lm) @ 700 mA
А3	220	230
A4	230	240
A5	240	250
B1	250	260
B2	260	270
В3	270	280
В4	280	290
В5	290	300
C1	300	310
C2	310	320
C3	320	330
C4	330	340
C5	340	350
D1	350	360
D2	360	370
D3	370	380



PERFORMANCE GROUPS - CHROMATICITY

Region	x	у	Region	x	у	Region	х	у	Region	x	у
	0.2950	0.2970		0.2920	0.3060		0.2984	0.3133		0.2984	0.3133
	0.2920	0.3060	0.5	0.2895	0.3135		0.2962	0.3220	0.5	0.3048	0.3207
0A	0.2984	0.3133	0B	0.2962	0.3220	0C	0.3028	0.3304	0D	0.3068	0.3113
	0.3009	0.3042		0.2984	0.3133		0.3048	0.3207		0.3009	0.3042
	0.2980	0.2880		0.2895	0.3135		0.2962	0.3220		0.3037	0.2937
OD	0.2950	0.2970	00	0.2870	0.3210	OT	0.2937	0.3312	011	0.3009	0.3042
0R	0.3009	0.3042	0S	0.2937	0.3312	OT	0.3005	0.3415	0U	0.3068	0.3113
	0.3037	0.2937		0.2962	0.3220		0.3028	0.3304		0.3093	0.2993
	0.3048	0.3207		0.3028	0.3304		0.3115	0.3391		0.3130	0.3290
1.4	0.3130	0.3290	10	0.3115	0.3391	10	0.3205	0.3481	10	0.3213	0.3373
1A	0.3144	0.3186	1B	0.3130	0.3290	1C	0.3213	0.3373	1D	0.3221	0.3261
	0.3068	0.3113		0.3048	0.3207		0.3130	0.3290		0.3144	0.3186
	0.3068	0.3113		0.3005	0.3415		0.3099	0.3509		0.3144	0.3186
10	0.3144	0.3186	10	0.3099	0.3509	1.	0.3196	0.3602	111	0.3221	0.3261
1R	0.3161	0.3059	1S	0.3115	0.3391	1T	0.3205	0.3481	1U	0.3231	0.3120
	0.3093	0.2993		0.3028	0.3304		0.3115	0.3391		0.3161	0.3059
	0.3215	0.3350		0.3207	0.3462		0.3290	0.3538		0.3290	0.3417
2A	0.3290	0.3417	2P	0.3290	0.3538	2C	0.3376	0.3616	30	0.3371	0.3490
ZA	0.3290	0.3300	2B	0.3290	0.3417	20	0.3371	0.3490	2D	0.3366	0.3369
	0.3222	0.3243		0.3215	0.3350		0.3290	0.3417		0.3290	0.3300
	0.3222	0.3243		0.3196	0.3602		0.3290	0.3690		0.3290	0.3300
2R	0.3290	0.3300	20	0.3290	0.3690	ОТ	0.3381	0.3762	211	0.3366	0.3369
ZK	0.3290	0.3180	2S	0.3290	0.3538	2T	0.3376	0.3616	2U	0.3361	0.3245
	0.3231	0.3120		0.3207	0.3462		0.3290	0.3538		0.3290	0.3180
	0.3371	0.3490		0.3376	0.3616		0.3463	0.3687		0.3451	0.3554
3A	0.3451	0.3554	3B	0.3463	0.3687	3C	0.3551	0.3760	3D	0.3533	0.3620
SA	0.3440	0.3427	30	0.3451	0.3554	30	0.3533	0.3620	30	0.3515	0.3487
	0.3366	0.3369		0.3371	0.3490		0.3451	0.3554		0.3440	0.3427
	0.3530	0.3597		0.3548	0.3736		0.3641	0.3804		0.3615	0.3659
40	0.3615	0.3659	/D	0.3641	0.3804	40	0.3736	0.3874	40	0.3702	0.3722
4A	0.3590	0.3521	4B 0.3615	0.3659	4C	0.3702	0.3722	4D	0.3670	0.3578	
	0.3512	0.3465		0.3530	0.3597		0.3615	0.3659		0.3590	0.3521
	0.3670	0.3578		0.3686	0.3649		0.3744	0.3685		0.3726	0.3612
5A1	0.3686	0.3649	542	0.3702	0.3722	5.4.2	0.3763	0.3760	5.4	0.3744	0.3685
SAT	0.3744	0.3685	5A2 0.3	0.3763	0.3760	5A3	0.3825	0.3798	5A4	0.3804	0.3721
	0.3726	0.3612		0.3744	0.3685		0.3804	0.3721		0.3783	0.3646



PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	x	у									
	0.3702	0.3722		0.3719	0.3797		0.3782	0.3837		0.3763	0.3760
ED1	0.3719	0.3797	ED0	0.3736	0.3874	ED0	0.3802	0.3916	ED 4	0.3782	0.3837
5B1	0.3782	0.3837	5B2	0.3802	0.3916	5B3	0.3869	0.3958	5B4	0.3847	0.3877
	0.3763	0.3760		0.3782	0.3837		0.3847	0.3877		0.3825	0.3798
	0.3825	0.3798		0.3847	0.3877		0.3912	0.3917		0.3887	0.3836
FO1	0.3847	0.3877	F.00	0.3869	0.3958	5C3	0.3937	0.4001	5C4	0.3912	0.3917
5C1	0.3912	0.3917	5C2	0.3937	0.4001	503	0.4006	0.4044	504	0.3978	0.3958
	0.3887	0.3836		0.3912	0.3917		0.3978	0.3958		0.3950	0.3875
	0.3783	0.3646		0.3804	0.3721		0.3863	0.3758		0.3840	0.3681
5D1	0.3804	0.3721	5D2	0.3825	0.3798	ED2	0.3887	0.3836	5D4	0.3863	0.3758
ועכ	0.3863	0.3758	302	0.3887	0.3836	5D3	0.3950	0.3875	304	0.3924	0.3794
	0.3840	0.3681		0.3863	0.3758		0.3924	0.3794		0.3898	0.3716
	0.3889	0.3690		0.3915	0.3768		0.3981	0.3800		0.3953	0.3720
6.4.1	0.3915	0.3768	6 4 0	0.3941	0.3848	6 4 2	0.4010	0.3882	6 / /	0.3981	0.3800
6A1	0.3981	0.3800	6A2	0.4010	0.3882	6A3	0.4080	0.3916	6A4	0.4048	0.3832
	0.3953	0.3720		0.3981	0.3800		0.4048	0.3832		0.4017	0.3751
	0.3941	0.3848		0.3968	0.3930		0.4040	0.3966		0.4010	0.3882
CD1	0.3968	0.3930	CD0	0.3996	0.4015	6B3	0.4071	0.4052	604	0.4040	0.3966
6B1	0.4040	0.3966	6B2	0.4071	0.4052		0.4146	0.4089	6B4	0.4113	0.4001
	0.4010	0.3882		0.4040	0.3966		0.4113	0.4001		0.4080	0.3916
	0.4080	0.3916		0.4113	0.4001		0.4186	0.4037		0.4150	0.3950
601	0.4113	0.4001	600	0.4146	0.4089	600	0.4222	0.4127	604	0.4186	0.4037
6C1	0.4186	0.4037	6C2	0.4222	0.4127	6C3	0.4299	0.4165	6C4	0.4259	0.4073
	0.4150	0.3950		0.4186	0.4037		0.4259	0.4073		0.4221	0.3984
	0.4017	0.3751		0.4048	0.3832		0.4116	0.3865		0.4082	0.3782
CD1	0.4048	0.3832	600	0.4080	0.3916	(D2	0.4150	0.3950	604	0.4116	0.3865
6D1	0.4116	0.3865	6D2	0.4150	0.3950	6D3	0.4221	0.3984	6D4	0.4183	0.3898
	0.4082	0.3782		0.4116	0.3865		0.4183	0.3898		0.4147	0.3814
	0.4147	0.3814		0.4183	0.3898		0.4242	0.3919		0.4203	0.3833
7.4.1	0.4183	0.3898	740	0.4221	0.3984	740	0.4281	0.4006	7.4.4	0.4242	0.3919
7A1	0.4242	0.3919	7A2	0.4281	0.4006	7A3	0.4342	0.4028	7A4	0.4300	0.3939
	0.4203	0.3833		0.4242	0.3919		0.4300	0.3939		0.4259	0.3853
	0.4221	0.3984		0.4259	0.4073		0.4322	0.4096		0.4281	0.4006
704	0.4259	0.4073	700	0.4299	0.4165	700	0.4364	0.4188	70.4	0.4322	0.4096
7B1	0.4322	0.4096	7B2	0.4364	0.4188	7B3	0.4430	0.4212	7B4	0.4385	0.4119
	0.4281	0.4006		0.4322	0.4096		0.4385	0.4119		0.4342	0.4028



PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	x	у									
	0.4342	0.4028		0.4385	0.4119		0.4449	0.4141		0.4403	0.4049
701	0.4385	0.4119	700	0.4430	0.4212	700	0.4496	0.4236	704	0.4449	0.4141
7C1	0.4449	0.4141	7C2	0.4496	0.4236	7C3	0.4562	0.4260	7C4	0.4513	0.4164
	0.4403	0.4049		0.4449	0.4141		0.4513	0.4164		0.4465	0.4071
	0.4259	0.3853		0.4300	0.3939		0.4359	0.3960		0.4316	0.3873
7D1	0.4300	0.3939	7D2	0.4342	0.4028	7D3	0.4403	0.4049	7D4	0.4359	0.3960
701	0.4359	0.3960	702	0.4403	0.4049	703	0.4465	0.4071	704	0.4418	0.3981
	0.4316	0.3873		0.4359	0.3960		0.4418	0.3981		0.4373	0.3893
	0.4373	0.3893		0.4418	0.3981		0.4475	0.3994		0.4428	0.3906
8A1	0.4418	0.3981	8A2	0.4465	0.4071	8A3	0.4523	0.4085	8A4	0.4475	0.3994
δΑΙ	0.4475	0.3994	8AZ	0.4523	0.4085	6A3	0.4582	0.4099	6A4	0.4532	0.4008
	0.4428	0.3906		0.4475	0.3994		0.4532	0.4008		0.4483	0.3919
	0.4465	0.4071		0.4513	0.4164		0.4573	0.4178		0.4523	0.4085
8B1	0.4513	0.4164	8B2	0.4562	0.4260	8B3	0.4624	0.4274	8B4	0.4573	0.4178
ODI	0.4573	0.4178	8BZ	0.4624	0.4274	003	0.4687	0.4289	0D4	0.4634	0.4193
	0.4523	0.4085		0.4573	0.4178		0.4634	0.4193		0.4582	0.4099
	0.4582	0.4099		0.4634	0.4193		0.4695	0.4207		0.4641	0.4112
8C1	0.4634	0.4193	8C2	0.4687	0.4289	8C3	0.4750	0.4304	8C4	0.4695	0.4207
001	0.4695	0.4207	002	0.4750	0.4304		0.4813	0.4319	004	0.4756	0.4221
	0.4641	0.4112		0.4695	0.4207		0.4756	0.4221		0.4700	0.4126
	0.4483	0.3919		0.4532	0.4008		0.4589	0.4021		0.4538	0.3931
8D1	0.4532	0.4008	8D2	0.4582	0.4099	8D3	0.4641	0.4112	8D4	0.4589	0.4021
ועס	0.4589	0.4021	802	0.4641	0.4112	803	0.4700	0.4126	8D4	0.4646	0.4034
	0.4538	0.3931		0.4589	0.4021		0.4646	0.4034		0.4593	0.3944
	0.4822	0.3973		0.4884	0.4067		0.4942	0.4066		0.4879	0.3972
AA1	0.4884	0.4067	AA2	0.4946	0.4162	AA3	0.5006	0.4160	AA4	0.4942	0.4066
AAT	0.4942	0.4066	AAZ	0.5006	0.4160	AA3	0.5066	0.4158	AA4	0.5001	0.4064
	0.4879	0.3972		0.4942	0.4066		0.5001	0.4064		0.4936	0.3970
	0.4946	0.4162		0.5008	0.4256		0.5069	0.4254		0.5006	0.4160
A D1	0.5008	0.4256	A DO	0.5070	0.4350	A DO	0.5133	0.4348	A D 4	0.5069	0.4254
AB1	0.5069	0.4254	AB2	0.5133	0.4348	AB3	0.5196	0.4346	AB4	0.5131	0.4252
	0.5006	0.4160		0.5069	0.4254		0.5131	0.4252		0.5066	0.4158
	0.5066	0.4158		0.5131	0.4252		0.5192	0.4250		0.5126	0.4156
401	0.5131	0.4252	400	0.5196	0.4346	400	0.5258	0.4343	A.C.4	0.5192	0.4250
AC1	0.5192	0.4250	AC2	0.5258	0.4343	AC3	0.5321	0.4341	AC4	0.5253	0.4248
	0.5126	0.4156		0.5192	0.4250		0.5253	0.4248		0.5186	0.4154



PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	х	у									
	0.4936	0.3970	AD2	0.5001	0.4064	AD3	0.5059	0.4062		0.4993	0.3969
A D 1	0.5001	0.4064		0.5066	0.4158		0.5126	0.4156	A.D.4	0.5059	0.4062
AD1	0.5059	0.4062		0.5126	0.4156		0.5186	0.4154	AD4	0.5118	0.4061
	0.4993	0.3969		0.5059	0.4062		0.5118	0.4061		0.5050	0.3967


XLamp XP-G4 LEDs are tested for chromaticity and placed into one of the regions defined by the following bounding coordinates.

	EasyWhite Color Temperatures - 3-Step Ellipse									
Bin Code	сст	Center Point x y		Major Axis	Minor Axis	Rotation Angle (°)				
Bill Code	CCI			а	b					
6G	3500 K	0.4073	0.3917	0.00927	0.00414	54.0				
7G	3000 K	0.4338	0.4030	0.00834	0.00408	53.2				
8G	2700 K	0.4577	0.4099	0.00834	0.00420	48.5				

		EasyWhi	te Color Temperatu	res – 5-Step Ellipse		
Bin Code	сст	Cente	Point	Major Axis	Minor Axis	Rotation Angle
Bill Code	661	х	у	a	b	(°)
2E	5700 K	0.3287	0.3417	0.01230	0.00600	72.0
3E	5000 K	0.3447	0.3553	0.01400	0.00520	65.0
4E	4500 K	0.3611	0.3658	0.01420	0.00550	61.5
5E	4000 K	0.3818	0.3797	0.01565	0.00670	53.7
6E	3500 K	0.4073	0.3917	0.01545	0.00690	54.0
7E	3000 K	0.4338	0.4030	0.01390	0.00680	53.2
8E	2700 K	0.4577	0.4099	0.01350	0.00700	48.5
AE	2200 K	0.5066	0.4158	0.01633	0.00800	45.5
BE	1800 K	0.5492	0.4082	0.00683	0.01546	40.0




CREE LED'S STANDARD COOL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS






CREE LED'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS






CREE LED'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS - CONTINUED



CREE LED'S EASYWHITE® WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS





CREE LED'S STANDARD CHROMATICITY KITS


The following table provides the chromaticity bins associated with chromaticity kits.


Color	ССТ	Kit	Chromaticity Bins
	7000 K	DT	0A, 0B, 0C, 0D, 0R, 0S, 0T, 0U, 1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U
	>6500 K	E0	0A, 0B, 0C, 0D
	6500 K	E1	1A, 1B, 1C, 1D
Cool White	6000 K	DV	1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U, 2A, 2B, 2C, 2D, 2R, 2S, 2T, 2U
	6200 K	50	1A, 1B, 1C, 1D, 2A, 2B, 2C, 2D
	5700 K	E2	2A, 2B, 2C, 2D
	5700 K	2E	57E
	5000 K	3E	50E
	5000 K	E3	3A, 3B, 3C, 3D
	4750 K	F4	3C, 3D, 4A, 4B
Neutral	4500 K	4E	45E
White	4500 K	E4	4A, 4B, 4C, 4D
	4250 K	F5	4C, 4D, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4
	4000 K	5E	40E
	4000 K	E5	5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4
	3750 K	F6	5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4
	3500 K	6E	35E, 35G
	3500 K	6G	35G
	3500 K	E6	6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4
	3250 K	F7	6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4, 7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4
	3000 K	7E	30E, 30G
	3000 K	7G	30G
Warm White	3000 K	E7	7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4, 7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4
	2850 K	F8	7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4, 8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4
	2700 K	8E	27E, 27G
	2700 K	8G	27G
	2700 K	E8	8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4, 8C1, 8C2, 8C3, 8C4, 8D1, 8D2, 8D3, 8D4
	2200 K	EA	AA1, AA2, AA3, AA4, AB1, AB2, AB3, AB4, AC1, AC2, AC3, AC4, AD1, AD2, AD3, AD4
	2200 K	AE	22E
	1800 K	BE	18E



BIN AND ORDER CODE FORMATS

XP-G4 bin codes and order codes are configured in the following manner:








REFLOW SOLDERING CHARACTERISTICS

In testing, Cree LED has found XLamp XP-G4 LEDs to be compatible with JEDEC J-STD-020C, with the exception of the peak temperature requirements listed in the table below. As a general guideline, Cree LED recommends that users follow the recommended soldering profile provided by the manufacturer of the solder paste used, and therefore it is the lamp or luminaire manufacturer's responsibility to determine applicable soldering requirements.

Note that this general guideline may not apply to all PCB designs and configurations of reflow soldering equipment.



Profile Feature	Lead-Free Solder
Average Ramp-Up Rate (Ts _{max} to T _p)	1.2 °C/second
Preheat: Temperature Min (Ts _{min})	120 °C
Preheat: Temperature Max (Ts _{max})	170 °C
Preheat: Time (ts _{min} to ts _{max})	65-150 seconds
Time Maintained Above: Temperature (T _L)	217 °C
Time Maintained Above: Time (t_L)	45-90 seconds
Peak/Classification Temperature (Tp)	235 - 245 °C
Time Within 5 °C of Actual Peak Temperature (tp)	20-40 seconds
Ramp-Down Rate	1 - 6 °C/second
Time 25 °C to Peak Temperature	4 minutes max.

Note: All temperatures refer to topside of the package, measured on the package body surface.



NOTES

Measurements

The luminous flux, radiant power, chromaticity, forward voltage and CRI measurements in this document are binning specifications only and solely represent product measurements as of the date of shipment. These measurements will change over time based on a number of factors that are not within Cree LED's control and are not intended or provided as operational specifications for the products. Calculated values are provided for informational purposes only and are not intended or provided as specifications.

Pre-Release Qualification Testing

Please read the LED Reliability Overview for details of the qualification process Cree LED applies to ensure long-term reliability for XLamp LEDs and details of Cree LED's pre-release qualification testing for XLamp LEDs. Cree LED did not perform Room Temperature Operating Life (RTOL) testing on the XP-G4 LED.

Lumen Maintenance

Cree LED now uses standardized IES LM-80-08 and TM-21-11 methods for collecting long-term data and extrapolating LED lumen maintenance. For information on the specific LM-80 data sets available for this LED, refer to the public LM-80 results document.

Please read the Long-Term Lumen Maintenance application note for more details on Cree LED's lumen maintenance testing and forecasting. Please read the Thermal Management application note for details on how thermal design, ambient temperature, and drive current affect the LED junction temperature.

Moisture Sensitivity

Cree LED recommends keeping XLamp LEDs in the provided, resealable moisture-barrier packaging (MBP) until immediately prior to soldering. Unopened MBPs that contain XLamp LEDs do not need special storage for moisture sensitivity.

Once the MBP is opened, XLamp XP-G4 LEDs may be stored as MSL 1 per JEDEC J-STD-033, meaning they have unlimited floor life in conditions of \leq 30 °C/85% relative humidity (RH). Regardless of the storage condition, Cree LED recommends sealing any unsoldered LEDs in the original MBP.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree LED representative or from the Product Ecology section of the Cree LED website.

REACH Compliance

REACH substances of very high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Cree LED representative to insure you get the most up-to-date REACH Declaration. REACH banned substance information (REACH Article 67) is also available upon request.



NOTES - CONTINUED

UL® Recognized Component

This product meets the requirements to be considered a UL Recognized Component with Level 4 enclosure consideration. The LED package or a portion thereof has been investigated as a fire and electrical enclosure per ANSI/UL 8750.

Vision Advisory


WARNING: Do not look at an exposed lamp in operation. Eye injury can result. For more information about LEDs and eye safety, please refer to the LED Eye Safety application note.




MECHANICAL DIMENSIONS (T $_{\rm A}$ = 25 °C)

Thermal vias, if present, are not shown on these drawings.


All measurements are ±.13 mm unless otherwise indicated.








MECHANICAL DIMENSIONS (T_A = 25 °C) - CONTINUED



Recommended PCB Footprint



Recommended Stencil Openings*

- Cree LED recommends using thermal pad kickouts to maximize component thermal performance.
- Cree LED recommends using white solder mask material to minimize system optical loss.
- * This stencil has been tested and optimized for the avoidance of voiding when using ALPHA® LUMET® P30 Maxrel solder paste. For other solder pastes, a "window pane" design for the thermal pad stencil may result in a lower voiding percentage. Contact your local Cree LED Field Applications Engineer for consultation regarding your specific application.




TAPE AND REEL

All Cree LED carrier tapes conform to EIA-481D, Automated Component Handling Systems Standard.


All dimensions in mm.


All measurements are ±.15 mm unless otherwise indicated.






TAPE AND REEL - CONTINUED







PACKAGING



Code, Quantity, Reel ID

