

GRF2584

High Gain Low Noise Amplifier 3 to 9 GHz

PRELIMINARY DATA SHEET

FEATURES

- Gain Levels Up to 36.5 dB
- Noise Figure Levels as Low as 1 dB
- Excellent Linearity Performance
- Supports Tuning Over Wide Bands
- 2.7 to 6 V Supply Voltage
- Flexible Biasing Provides Latitude for Linearity Optimization
- 50 mA Native Mode Quiescent Current Consumption
- 50 Ω Single-Ended Input and Output Impedances
- RoHS Compliant

Reference: 5 V / 50 mA / 3.6 GHz

- Gain: 36.5 dB
- OP1dB: 17 dB
- OIP3: 30 dBm
- Evaluation Board NF: 1 dB

Reference: 5 V / 50 mA / 5.9 GHz

- Gain: 32.5 dB
- OP1dB: 17 dBm
- OIP3: 30 dBm
- Evaluation Board NF: 1.1 dB

Reference: 5 V / 50 mA / 8.0 GHz

- Gain: 26 dB
- OP1dB: 13 dBm
- OIP3: 28 dBm
- Evaluation Board NF: 1.4 dB

APPLICATIONS


- 5G n48, n77, n78 & n79 Massive MIMO Base Stations
- Automotive V2X Band n47 Front Ends and Compensators
- High-Performance RF Infrastructure

DESCRIPTION


The GRF2584 is a two-stage GaAs pHEMT low noise amplifier targeting high-performance wireless infrastructure applications. The device can be tuned to operate over narrow or wide bandwidths over a range of 3 to 9 GHz while delivering up to 36 dB of gain and noise figures as low as 1 dB.

For optimal efficiency and linearity, the amplifier was designed to operate with a single 5 V supply voltage while using only 50 mA of quiescent current. Supply voltages ranging from 2.7 to 6 V are also supported. Similarly, I_{DDQ} can be increased beyond the native biasing point for enhanced linearity performance.

BLOCK DIAGRAM



 **ORDERING INFORMATION**
Buy it Now



Pin Out (Top View)

Pin Assignments

Pin	Name	Description	Note
1	VEN2	2nd Stage Enable	$VEN2 \leq 0.2$ disables the second stage. VEN2 and external series resistor controls the second stage I_{DDQ} when VEN2 is high.
2	VEN1	1st Stage Enable	$VEN1 \leq 0.2$ disables the first stage. VEN1 and external series resistor control the first stage I_{DDQ} when VEN1 is high.
3	RFIN	RF Input	Internally matched 50 Ω . An external DC blocking cap must be used.
4	RFOUT/VDD2	RF Output/2nd Stage Bias	Internally matched 50 Ω . V_{DD} must be applied through a choke to this pin.
5	NC	No Connect	No internal connection. This pin can be left unconnected, or be connected to the ground (recommended). Use a via as close to the pin as possible if grounded.
6	VDD1	1st Stage Bias	Pull up to V_{DD} through the inductor and use bypass capacitors as close to the pin as possible. In addition to supplying the first stage of the device with a DC voltage, there is also an RF signal present.
PKG BASE	GND	Ground	Provides DC and RF ground for amplifiers, as well as thermal heat sink. In order to match the devices rated performance, it is strongly recommended to use multiple 8 mil vias beneath the package for optimal RF and thermal performance. Refer to evaluation board top layer graphic on schematic page.

Absolute Ratings

Parameter	Symbol	Min.	Max.	Unit
Supply Voltage	V_{DD}	0	6	V
RF Input Power: Load VSWR < 2:1, V_{DD} < 6 V.	$P_{IN\ MAX}$		27	dBm
Operating Temperature (Package Heat Sink)	$T_{PKG\ BASE}$	-40	115	°C
Maximum Channel Temperature (MTTF > 10 ⁶ Hours)	T_{MAX}		TBD	°C
Maximum Dissipated Power	$P_{DISS\ MAX}$		TBD	W

Electrostatic Discharge

Charged Device Model	CDM	TBD		V
Human Body Model	HBM	TBD		V

Storage

Storage Temperature	T_{STG}	-65	150	°C
Moisture Sensitivity Level			1	--



Caution! ESD Sensitive Device.

Exceeding Absolute Maximum Rating conditions may cause permanent damage.

Note: For additional information, please refer to [Manufacturing Note MN-001 - Packaging and Manufacturing Information](#).



All Guerrilla RF products are provided in RoHS compliant lead (Pb)-free packaging. For additional information, please refer to the [Certificate of RoHS Compliance](#).

Recommended Operating Conditions

Parameter	Symbol	Specification			Unit	Condition
		Min.	Typ.	Max.		
Supply Voltage	V_{DD}	4.75	5	6	V	
Operating Temperature Range	$T_{PKG\ BASE}$	-40		115	°C	
RF Frequency Range (note 1)	F_{RF}	3.3		4.2	GHz	3.75 GHz tuning set (5G Bands n48, n77, n78)
		4.4		5		4.7 GHz tuning set (5G Band n79)
		5.855		5.925		5.9 GHz tuning set (Automotive V2X Band n47)
		5.925		7.125		6.525 GHz tuning set (5G Bands n96, n102, n104)
RFIN Port Impedance	Z_{RFIN}		50		Ω	Single ended, with respective matching elements from each tuning set.
RFOUT Port Impedance	Z_{RFOUT}		50		Ω	Single ended, with respective matching elements from each tuning set.

Note 1: Operation outside of these ranges is possible but with degraded performance of some parameters. Contact the GRF applications team for guidance on selecting the specific matching components for each tuning set.

Nominal Operating Parameters - General

Parameter	Symbol	Specification			Unit	Condition
		Min.	Typ.	Max.		
Test Frequency	F_{TEST}		5.9		GHz	
Logic Input Low	V_{IL}	0		0.2	V	VEN1 & VEN2
Logic Input High	V_{IH}	TBD	3.9	V_{DD}	V	VEN1 & VEN2
Turn On (Rise) Time	t_{ON}		TBD		ns	VEN1 & VEN2 Low to High
Turn Off (Fall) Time	t_{OFF}		TBD		ns	VEN1 & VEN2 High to Low
VBIAS	V_{BIAS}		5.0		V	VBIAS1 & VBIAS2
Supply Quiescent Current	I_{DDQ}		50		mA	IBIAS1 & IBIAS2, $R_{BIAS} = TBD$, $R_{BIAS2} = TBD$
Enable Current	I_{EN}		1.4		mA	IEN1 + IEN2. $V_{DD} = High$, VEN1 & VEN2 = High
Disabled Mode						
Standby Current	I_{STBY}		350		μA	$V_{DD} = 5 V$, VEN1 & VEN2 = LOW
Thermal Data						
Thermal Resistance (Infrared Scan)	Θ_{JC}		TBD		$^{\circ}C/W$	On standard evaluation board
Channel Temperature @ 115 $^{\circ}C$ Reference (Package Heat Sink)	$T_{CHANNEL}$		TBD		$^{\circ}C$	$V_{DD} = 5 V$, $I_{DDQ} = 47 mA$, $P_{DISS} = TBD mW$, No RF (note 2)

Note 2: MTTF > 10⁶ hours for $T_{CHANNEL} \leq 170^{\circ}C$.

Nominal Operating Parameters - RF

The following conditions apply unless noted otherwise: typical application schematic using the 5.7 to 6.2 GHz tuning set, $V_{EN1} = V_{EN2} = 5\text{ V}$, $R_{BIAS1} = \text{TBD } \Omega$ and $R_{BIAS2} = \text{TBD } \Omega$, $V_{DD} = 5\text{ V}$, $50\text{ } \Omega$ system impedance, $P_{OUT} = 0\text{ dBm}$, $F_{TEST} = 5.9\text{ GHz}$, $T_{PKG\text{ BASE}} = 25\text{ }^{\circ}\text{C}$. Evaluation board losses are included within the specifications.


Parameter	Symbol	Specification			Unit	Condition
		Min.	Typ.	Max.		
Gain	S21		32.5		dB	$F_{RF} = 5.89\text{ GHz}$
Gain Flatness	S21 _{FLAT}		0.02		dB	$F_{RF} = 5.855\text{ to }5.925\text{ GHz}$
Gain Variation Over Temp	S21 _{TEMP}		+0.8/-1.9		dB	$T_{PKG\text{ BASE}} = -40\text{ to }115\text{ }^{\circ}\text{C}$, referenced to $T_{PKG\text{ BASE}} = 25\text{ }^{\circ}\text{C}$.
Standby Mode Gain	S21 _{STBY}		TBD		dB	$V_{EN1} \text{ \& } V_{EN2} = \text{LOW}$
Input Return Loss	S11		< -9		dB	$F_{RF} = 5.855\text{ to }5.925\text{ GHz}$
Output Return Loss	S22		< -13		dB	$F_{RF} = 5.855\text{ to }5.925\text{ GHz}$
Reverse Isolation	S12		38		dB	$F_{RF} = 5.855\text{ to }5.925\text{ GHz}$
De-Embedded Noise Figure	NF		0.95		dB	
Eval Board Noise Figure			1.1			
Output 3rd Order Intercept Point	OIP3		30		dBm	0 dBm P_{OUT} per tone at 2 MHz Spacing.
Output 1dB Compression Power	OP1dB		17		dBm	

GRF2584 Typical Operating Curves: 5.7 to 6.2 GHz Tune


Truth Table

Mode	Pin Logic	
	VEN1	VEN2
Device ON	HIGH	HIGH
Standby (Device OFF)	LOW	LOW

S-Parameters




GRF2584 Typical Operating Curves: Stability Mu Factor (10 MHz to 20 GHz)




Note: Mu factor ≥ 1.0 implies unconditional stability

GRF2584 Typical Operating Curves: Noise Figure (5.7 to 6.2 GHz Tune)




GRF2584 Typical Operating Curves: 5.7 to 6.2 GHz Tune

GRF2584 Gain vs Pout at Frequency = 5900 MHz




GRF2584 Gain vs Frequency at Pin = -25 dBm




GRF2584 Typical Operating Curves: 5.7 to 6.2 GHz Tune

GRF2584 OP1dB vs Frequency




GRF2584 OIP3 vs Frequency at Pout (per tone) = 0 dBm





GRF2584 Typical Operating Curves: 5.7 to 6.2 GHz Tune

GRF2584 Noise Figure vs Frequency




GRF2584 IddTot vs Pout at Frequency = 5900 MHz





Standard Test Schematic








GRF2584 Evaluation Board Assembly Diagram

GRF2584 Evaluation Board Assembly Diagram Reference (5.7 to 6.2 GHz Tune)


Component	Type	Manufacturer	Family	Value	Package	Substitution
C1	Capacitor	Murata	GJM	100 pF	0402	ok
M2	Resistor	Various	5%	4.75 k Ω	0402	ok
M3	Capacitor	Murata	GJM	0.6 pF	0402	ok
M4	Resistor	Various	5%	2 k Ω	0402	ok
M7	Capacitor	Murata	GRM	0.1 μ F	0201	ok
M8	Resistor	Various	5%	3 Ω	0402	ok
M9	Resistor (jumper)	Various	5%	0 Ω	0402	ok
M10	Inductor	Murata	LQG	5.1 nH	0402	ok
M12	Capacitor	Murata	GJM	20 pF	0402	ok
M13	Capacitor	Murata	GJM	20 pF	0402	ok
M14	Capacitor	Murata	GJM	0.2 pF	0402	ok
Evaluation Board	DFN6-15-47-A					

GRF2584 Bias Resistor Selection Curves





DFN 6 1.5x1.5mm Package Dimensions



DFN 6 1.5x1.5mm Suggested PCB Footprint (Top View)


Package Marking Diagram




Line 1: "Y" = YEAR (single digit). "WW" = WORK WEEK the Device was assembled.
Line 2: "XXXX" = Device Part Number.

Tape and Reel Information

Guerrilla RF's tape and reel specification complies with Electronics Industries Association (EIA) standards for "Embossed Carrier Tape of Surface Mount Components for Automatic Handling" (reference EIA-481). Devices are loaded with pins down into the carrier pocket with protective cover tape and reeled onto a plastic reel. Each reel is packaged in a cardboard box. There are product labels on the reel, the protective ESD bag, and the outside surface of the box. For the latest reel specifications and package information (including units/reel), please visit [Package Manufacturing Information](#) | [Guerrilla RF](#) (guerrilla-rf.com).



Tape and Reel Packaging with Reel Diameter Noted (D)



Carrier Tape Width (W), Pitch (P), Feed Direction and Pin 1 Quadrant Information



Revision History

Revision Date	Description of Change
December 21, 2023	Preliminary Data Sheet - Initial Release.



Data Sheet Classifications

Data Sheet Status	Notes
Advance	S-parameter and NF data based on EM simulations for the fully packaged device using foundry-supplied transistor S-parameters. Linearity estimates based on device size, bias condition and experience with related devices.
Preliminary	All data based on evaluation board measurements taken within the Guerrilla RF Applications Lab. Any MIN/MAX limits represented within the data sheet are based solely on <i>estimated</i> part-to-part variations and process spreads. All parametric values are subject to change pending the collection of additional data.
Release Ø	All data based on measurements taken with <i>production-released</i> material. TYP values are based on a combination of ATE and bench-level measurements, with MIN/MAX limits defined using <i>modelled estimates</i> that account for part-to-part variations and expected process spreads. Although unlikely, future refinements to the TYP/MIN/MAX values may be in order as multiple lots are processed through the factory.
Release A-Z	All data based on measurements taken with production-released material <i>derived from multiple lots which have been fabricated over an extended period of time</i> . MIN/MAX limits may be refined over previous releases as more statistically significant data is collected to account for process spreads.

Information in this data sheet is specific to the Guerrilla RF, Inc. ("Guerrilla RF") product identified.

This data sheet, including the information contained in it, is provided by Guerrilla RF as a service to its customers and may be used for informational purposes only by the customer. Guerrilla RF assumes no responsibility for errors or omissions on this data sheet or the information contained herein. Information provided is believed to be accurate and reliable, however, no responsibility is assumed by Guerrilla RF for its use, nor for any infringement of patents, or other rights of third parties, resulting from its use. Guerrilla RF assumes no liability for any data sheet, data sheet information, materials, products, product information, or other information provided hereunder, including the sale, distribution, reproduction or use of Guerrilla RF products, information or materials.

No license, whether express, implied, by estoppel, by implication or otherwise granted by this data sheet for any intellectual property of Guerrilla RF, or any third party, including without limitation, patents, patent rights, copyrights, trademarks, and trade secrets. All rights are reserved by Guerrilla RF.

All information herein, products, product information, data sheets, and data sheet information are subject to change and availability without notice. Guerrilla RF reserves the right to change component circuitry, recommended application circuitry and specifications at any time without prior notice. Guerrilla RF may further change its data sheet, product information, documentation, products, services, specifications or product descriptions at any time, without notice. Guerrilla RF makes no commitment to update any materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

GUERRILLA RF INFORMATION, PRODUCTS, PRODUCT INFORMATION, DATA SHEETS AND DATA SHEET INFORMATION ARE PROVIDED "AS IS" AND WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. GUERRILLA RF DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. GUERRILLA RF SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Customers are solely responsible for their use of Guerrilla RF products in the Customer's products and applications or in ways which deviate from Guerrilla RF's published specifications, either intentionally or as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Guerrilla RF assumes no liability or responsibility for applications assistance, customer product design, or damage to any equipment resulting from the use of Guerrilla RF products outside of stated published specifications or parameters.