

AS5132

Programmable Magnetic Rotary Encoder

AS5132-AB-v1.0

Adapterboard

OPERATION MANUAL

1 General Description

The AS5132 is a contactless magnetic rotary encoder for accurate angular measurement over a full turn of 360 degrees. It is a system-on-chip, combining integrated Hall elements, analog frontend and digital signal processing in a single device.

To measure the angle, only a simple two-pole magnet, rotating over the center of the chip is required.

The absolute angle measurement provides instant indication of the magnet's angular position with a resolution of $8.5 \text{ bit} = 360 \text{ positions}$ per revolution. This digital data is available as serial output over the interface and as a pulse width modulated (PWM) signal.

An additional U,V,W output can be used for a block commutation for

a brushless DC motor. An incremental signal is available as an option.

In addition to the angle information, the strength of the magnetic field

is also available as a 5-bit code.

A software programmable (OTP) zero position simplifies assembly as the zero position. The magnet does not need to be mechanically aligned.


To optimize the torque characteristic at a certain speed the AS5132 has the option to use a static or dynamic pre-commutation

2 The AS5132 Adapter board

2.1 Board description

The AS5132 adapter board is a simple circuit allowing test and evaluation of the AS5132 rotary encoder quickly without building a test fixture or PCB. The PCB requires 5V power supply and GND connection. To program the device or read out the absolute position of the magnet via SSI a software is mandatory. COM/INC PIN is needed to select UVW Output or ABIndex. To use the static or dynamic pre-commutation a programming on the device is mandatory.

Figure 1: AS5132 Adapterboard



2.2 Mounting the AS5132 adapter board





Figure 2: AS5050 adapter board mounting and dimension

A diametral magnet must be placed over on under the AS5132 encoder, and should be placed centered in y direction and 4.1mm with respect to PIN1 in x direction. Tolerance of 0.5mm.



The airgap between the magnet and the encoder casing should be maintained in the range 0.5mm-2mm (magnet related). The magnet holder must not be ferromagnetic. Materials as brass, copper, aluminum, stainless steel are the best choices to make this part

3 AS5132 and adapter board pinout




Figure 3: AS5132 adapter board connectors and encoder pinout

Pin# Board	Pin# AS5132	Symbol Board	Type	Description
J1 - 1	6	GND	Supply	Supply ground
J1 - 2	15	DIO	Bi-directional digital	Data I/O for serial interface (VDDP)
J1 - 3	17	CLK	Digital input/Schmitt-Trigger	Clock input for serial interface (VDDP)
J1 - 4	16	CSN	Digital input/Schmitt-Trigger	Chip select input (active low) (VDDP)
J1 - 5	15	VDDP	Supply	Supply Voltage for the selected pins
J1 - 6	16	5V	Supply	Positive supply voltage
J1 - 7	5	PROG	Supply	SPI Clock Schmitt trigger
J2 -1	6	GND	Supply	Supply ground
J2 -2	7	U_A	Digital output	Communication output or incremental output
J2 -3	4	V_B	Digital output	Communication output or incremental output
J2 -4	3	W_I	Digital output	Communication output or incremental output
J2 -5	9	C/I	Digital input/Schmitt-Trigger	Selection of the output
J2 -6	18	DIR	Digital input/Schmitt-Trigger	Input signal for the pre commutation at start-up
J2 -7	20	PWM/	Digital Output	PWM Output

Table 1: Pin description

4 AS5132 adapter board hardware

4.1 AS5132-AB-1.0 schematics




Figure 4: AS5132-AB-1.0 adapterboard schematics

4.2 AS5132-AB-1.0 PCB layout




Figure 5: AS5132-AB-1.0 adapter board layout

Table of contents

1	General Description.....	1
2	The AS5132 Adapter board.....	1
2.1	Board description.....	1
2.2	Mounting the AS5132 adapter board.....	2
3	AS5132 and adapter board pinout.....	3
4	AS5132 adapter board hardware	4
4.1	AS5132-AB-1.0 schematics.....	4
4.2	AS5132-AB-1.0 PCB layout.....	4
	Table of contents.....	5
	Copyrights.....	6
	Disclaimer.....	6
	Contact Information	6

Copyrights

Copyright © 1997-2010, austriamicrosystems AG, Schloss Premstaetten, 8141 Unterpremstaetten, Austria-Europe. Trademarks Registered ®. All rights reserved. The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner. All products and companies mentioned are trademarks or registered trademarks of their respective companies.

Disclaimer

Devices sold by austriamicrosystems AG are covered by the warranty and patent indemnification provisions appearing in its Term of Sale. austriamicrosystems AG makes no warranty, express, statutory, implied, or by description regarding the information set forth herein or regarding the freedom of the described devices from patent infringement. austriamicrosystems AG reserves the right to change specifications and prices at any time and without notice. Therefore, prior to designing this product into a system, it is necessary to check with austriamicrosystems AG for current information. This product is intended for use in normal commercial applications. Applications requiring extended temperature range, unusual environmental requirements, or high reliability applications, such as military, medical life-support or lifesustaining equipment are specifically not recommended without additional processing by austriamicrosystems AG for each application.

The information furnished here by austriamicrosystems AG is believed to be correct and accurate. However, austriamicrosystems AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data herein. No obligation or liability to recipient or any third party shall arise or flow out of austriamicrosystems AG rendering of technical or other services.

Contact Information

Headquarters

austriamicrosystems AG
A-8141 Schloss Premstaetten, Austria
Tel: +43 (0) 3136 500 0
Fax: +43 (0) 3136 525 01

For Sales Offices, Distributors and Representatives, please visit:

<http://www.austriamicrosystems.com>