CY3280-SRM UNIVERSAL CAPSENSE[®] RADIAL SLIDER MODULE KIT QUICK START GUIDE



 Insert the kit DVD in the CD/DVD drive.
 Install the kit content, PSoC[®] DesignerTM, and PSoC Programmer.

Note The hardware prerequisites for this kit are any CY3280 Universal CapSense Controller (UCC) board, such as the latest CY3280-20x66 DVK, and MiniProg1.

	88	CONNEC	TIDISCONNECT	
PortSelection MINProg1/33AFA0541316 Device Family 24c34 W		Programmer (Usite) JNA Programming Parameters <u>Fin Parts</u> C155ath/02_Me/Work02_Previous Quarters/07_03110bridge/Firmware/USBts/0300		
		Distantiniti MHTH-og INDAFASAI 310 Distantinitia Addit 0 m 0 of Distantinitia Addit 0 m 0 of Andidatatan 0 m 0 of Distantinitia Addit 0 m 0 of Distantinitia Addit Programma Characteristics Distantinitia Distantinitia Distantinitia Distantinitia Programma Characteristics Distantinitia Distantinitia Distantinitia Distantinitia Distantini Distontinitia Distantinitia Distantinitia Distantinitia		
				Clack Spred: 32MHz M Status Execution Time: Execution Time:
CY9C24894-24LTX	2	Bandr	0 13 4 0 28 4 0 184	Voltage: NA
Successfully to MINIProg1/83.	Connec IFA0541	ted 316 MINI Versi	on 1.79	

1. Connect MiniProg1 to the CY3280-20x34 UCC board's ISSP connector (J3). Connect it to your PC using a USB cable.

2. Open PSoC Programmer and click File > File Load. Browse and load the

CY3280_SRM_20x34.hex file*.

- 3. Click Connect; connect MiniProg1 to PC.
- 4. Click Program button to program the device.
- 5. Click Toggle button to power the board.

* Note This file is located at: <Install directory>\ Cypress\CY3280-SRM\<version>\

Firmware\20x34 CSA\PD project 1\

CY3280_SRM_20x34\CY3280_SRM_20x34.hex



 Connect the CY3280-SRM board to the CY3280-20x34 UCC board's P2 connector.
 In the CY3280-20x34 board, place the jumper on header J1 to short pins 2 and 3.
 In the CY3280-SRM board, place the jumper on header J2 to short pins 2 and 3.



1. Touch and move the radial slider on the CY3280-SRM module board. The corresponding LEDs on the CY3280-SRM board light up.

2. Touch a button. The corresponding LED on the CY3280-SRM module board lights up.

3. You can touch multiple buttons at the same time. The radial slider and buttons can be used at the same time.

CY3280-SRM UNIVERSAL CAPSENSE[®] RADIAL SLIDER MODULE KIT QUICK START GUIDE



CY3280-SRM Kit Details

Notes

- For more details on code examples, refer to the PDF file along with the project in the Firmware folder (for example, *Readme_SRM_21x34_CSD PD1.pdf*) in the following directory: <Install directory>\Cypress\CY3280-SRM\<version>\Firmware\21x34_CSD\PD project 1.
- CY3280-SRM can be used with any of the following UCCs:
 - 1. CY3280- 20x66
 - 2. CY3280- 24x94
 - 3. CY3280- 21x34 (ordering part number is CY3280-BK1)

For the latest information about this kit, visit www.cypress.com/go/CY3280-SRM



© 2009-2018 Cypress Semiconductor Corporation. All rights reserved. All trademarks or registered trademarks referenced herein are the properties of their respective owners. Doc #: 001-51791 Rev. *F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cypress Semiconductor: CY3280-SRM