INFRASOLID

Highest accuracy · Highest selectivity

Gas Filter Cell

for best optical measurement of gases




Key features

- Elimination of cross-sensitivities to interfering gases in optical gas analysis.
- **Adjustment of measuring instruments** and gas analyzers.
- Soldered, high-quality CaF₂ window. Leakage tested!
- Filling tube enables self-filling with desired gas and sealing.
- Broad range of applications from UV to far infrared spectral range.

Hermetic gas filter cells are gas-filled cylinders and are used to block out specific frequency bands of interfering gases in optical gas analysis.

Additionally, the cells can be filled with reference gases of certain gas concentrations to be used for calibration of gas analysis systems, e.g. adjusting laser wavelengths to specific gas absorption bands.

For a very high long-term stability our gold-plated gas filter cells are hermetically sealed. The high transmissivity is achieved by soldered CaF₂ windows.



ENVIRONMENTAL MONITORING



H₂O VAPOR FILTER




MEDICAL GAS ANALYSIS



SYSTEM CALIBRATION


Example application

NDIR measurement of CO with Gas Filter Cell filled with CO₂ for elimination of cross sensitivities and highest selectivity (e.g. for emission monitoring)



Data sheet

Optical specifications




Main specifications

Parameter	GFC-12	GFC-35	GFC-100
Length*	12 mm	35 mm	100 mm
Temperature range	-25+85 °C	-25+85 °C	-25+85 °C
Window	2 x soldered CaF2	2 x soldered CaF2	2 x soldered CaF2
Material	Gold plated brass	Gold plated brass	Gold plated brass
Transmissivity	85% up to 8 μm	85% up to 8 μm	85% up to 8 μm

^{*} Other lengths on request.

Technical drawing



Are you looking for IR emitters, detailed technical specifications or would you like to have an individual development?

Visit our website and feel free to contact us!

www.infrasolid.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Innovative Sensor Technology:

GFC-35 GFC-100-G GFC-100 GFC-12 GFC-35-G