≥ ШО

HF series

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



35T.HF.2432

DISTINCTIVE FEATURES

One, two or three axis
Analog outputs
CAN bus J1939 and CANopen options
USB 2.0 HID interface options
Connectorized housing



ENVIRONMENTAL SPECIFICATIONS

- Operating Temperature: -40 °C to +85 °C (-40 °F to +185 °F)
- Storage Temperature: -40 °C to +85 °C (-40 °F to +185 °F)
- Above Panel Sealing: Up to IP67 (subject to final specifications)
- EMC Immunity Level (V/M): EN61000-4-3
- EMC Emissions Level: EN61000-6-3:2001
- ESD: EN61000-4-3 Level 2 (±4 kv contact, ± 6 kv air)
- Output linearity: ±200 mV
- Dual output interlinearity (X/Y): ±400 mV
- Dual output interlinearity (Z): ±600 mV



SENSOR SPECIFICATIONS

- Sensor: Hall effect, single or dual
- Supply Voltage Range: 5 VDC ±0.01 VDC
- Supply Current: 40 mA typical / 50 mA max (3 axis)
- Reverse Polarity Max: -10 VDC
- Transient Overvoltage Max: 16 VDC
- Ratiometric Output Voltage: see output options
- Output Current: 8 mA
- Output Load: 1 K ohm min
- Output Impedance: 2Ω



MATERIALS

- Shaft: Stainless Steel
- Boot: Silicone
- Handles: Glass filled nylon*
- Body: Glass filled nylon

The company reserves the right to change specifications without notice.





Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



TERMINATION (ANALOG OUTPUTS ONLY)

- The HF series (Output options 0-11) features a **Hirose DF11-12DP-2DS9 (24)** header (male receptacle) (Fig 1)
- The mating harness is not included but may be specified at the time of order. Contact your APEM sales representative. This optional harness features a Hirose DF11-12DS-2C connector (female socket)(Fig. 2) to individual stripped and tinned wire leads.
- Header specifications: 12 position, 2mm pitch dual row (2x6) pin header
- Wire harness specifications: 22AWG Teflon, 25cm multiconductor with heat shrink. Hirose **DF11-12DS-2C** to stripped and tinned wire leads



Fig. 1 Hirose DF11-12DP-2DS9(24) header



Fig. 2
Mating wire harness fitted with
Hirose DF11-12DS-2C connector

* Most handles, dependent upon configurations

JOYSTICK HEADER - HIROSE DF11-12DP-2DS9 (24) PINOUT (FIG 1)

PIN 2	PIN 4	PIN 6	PIN 8	PIN 10	PIN 12
RED	BLUE	YELLOW	GREEN	WHITE	
BLACK	BLU/WHT	YEL/BLK	GRN/BLK	ORANGE	VIOLET
PIN 1	PIN 3	PIN 5	PIN 7	PIN 9	PIN 11

MATING WIRE HARNESS COLOR DEFINITION (FIG 2)

HIROSE DF11-12DS-2C CONNECTOR PIN #	WIRE COLOR	JOYSTICK FUNCTION
1	Black	Ground
2	Red	Supply power
3	Blue / white	X axis (dual output)
4	Blue	X axis
5	Yellow / black	Y axis (dual output)
6	Yellow	Y axis
7	Green / black	Z axis (dual output)
8	Green	Z axis
9	Orange	Button one
10	White	Button common
11	Violet	Button two
12		



MECHANICAL SPECIFICATIONS

X/Y AXIS

- Break Out Force: 1.3 N (0.3 lbf)
- Operating Force: 2.8 N (0.63 lbf)
- Expected Mechanical Life: 5 million lifecycles
- Lever Action: Single spring, omnidirectional
- Deflection Angle:

Limiter plate	Cardinal axis (±)	Diagonal axis (±)
Square / Diamond	13.5°	20
Circular	15.8°	n/a
Slot X	15.8°	n/a
Slot Y	15.8°	n/a
Cross	15.8°	n/a

Z AXIS

- Break Out Torque: 0.09 Nm (0.80 lbf in)
- Operating Torque: 0.121 Nm (1.07 lbf in)
- Degrees of rotation: 60° (30° from center)
- Expected Mechanical Life: 5 million lifecycles
- Handle Action: Spring centering

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



GENERAL MOUNTING OPTIONS


DROP-IN MOUNT REAR MOUNT 4-40 x 9/16 * 4-40 x 3/8 * Phil Panhead Phil Panhead 23.83 Brass insert Brass insert (0.938)30.05 4 places 4 places (1.183)V

* = Recommended maximum torque: 0.1 - 0.125 Nm evenly per screw (18 oz-in).




PANEL CUT-OUT

DROP-IN MOUNT




REAR MOUNT




Not available for option 55 handles

CLAMPING RING



AXIS ORIENTATION



NOTES:

- For DROP-IN mounting, panel thickness can be 1.17 mm to 3.17 mm (0.046 in to 0.125 in).
- For REAR MOUNT, the maximum panel thickness is 1.6 mm (0.063 in).
- $\rm \acute{A}$ panel thickness of 1/16» (1.6 mm/0.063 in) was considered for all below panel depth values.
- The below panel depth is extended by 7.11 mm (0.28 in) with the USB, Cursor Emulation, Voltage Regulator options.

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



CAN J1939 INTERFACE SPECIFICATION

The HF Series joystick can be configured with a maximum of three axis and two buttons. All axis and button data are delivered on a CAN 2.0B compliant physical interface. Two additional signals allow configuration of the controller Source Address. Controller messages are delivered per the SAE J1939-71 message protocol.

CAN 2.0B INTERFACE PARAMETERS

• Baud rate: 250 kbps

• Transmission repetition rate: 50ms

• BJMI/EJMI interval time: 20ms

• Terminating resistor: No

(available by special request to factory)

CAN MESSAGE PROTOCOL

- Primary Axis and button data on Basic Joystick Message 1 (BJM1):
- Priority: 3
- Base PGN: 0xFDD6
- Source address: 0x16
- Data field: 8 bytes
- Z-Axis data on Extended Joystick Message 1 (EJMI):
- Priority: 3
- Base PGN: 0xFDD7
- Source address: 0x16
- Data field: 8 bytes

CAN MESSAGE ADDRESSES

Alternate source addresses may be selected by gounding combinations of the blue and/or orange wires. For further information, please see TERMINATION on page 6.

CAN SOURCE ADDRESS	ORANGE WIRE	BLUE WIRE
0x16 (default)	OPEN	OPEN
0x26	OPEN	Grounded
0x36	Grounded	OPEN
0x46	Grounded	Grounded

BJM1 DATA FIELD STRUCTURE:

START POSITION (BYTE/BIT)	LENGTH (BITS)	FUNCTION
1/1	2	Primary X-axis neutral position status
1/3	2	Primary X-axis left position status
1/5	2	Primary X-axis right position status
1/7 to 2/8	10	Primary X-axis position data
3/1	2	Primary Y-axis neutral position status
3/3	2	Primary Y-axis down position status
3/5	2	Primary Y-axis up position status
3/7 to 4/8	10	Primary Y-axis position data
6/5	2	Button 2 status
6/7	2	Button 1 status

EJM1 DATA FIELD STRUCTURE:

START POSITION (BYTE/BIT)	LENGTH (BITS)	FUNCTION	
5/1	2	Primary Z-axis neutral position status	
5/3	2	Primary Z-axis counter-clockwise position status	
5/5	2	Primary Z-axis clockwise position status	
5/7 TO 6/8	10	Primary Z-axis position data	

CUSTOM CAN BUS J1939 FIRMWARE*

- Baud rate: 125 kbps, 500 kbps, 1Mbps (250 kbps default)
- Custom CAN addresses
- Custom CAN bus output

^{*} Custom CAN bus firmware available upon request.

A P E M

HF series

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



CANOPEN INTERFACE SPECIFICATION

CANOPEN INTERFACE PARAMETERS*

• Baud rate: 250 kbps

• Node ID: 20h

• Buttons: 1A0H (180H + NODE ID)

• Analog (axis) outputs: 2A0h (280h + Node ID)

• Heartbeat (500ms): 720h (700h + Node ID)

• Axis resolution: 8 bit

• Network Management: Auto start enabled

CANOPEN NODE ID SELECTION

Alternate NODE IDs may be selected by gounding the blue and/or orange wires. For further information, please see TERMINATION on page 6.

NODE ID SELECT	ORANGE WIRE	BLUE WIRE
20H (default)	OPEN	OPEN
21H	OPEN	Grounded
22H	Grounded	OPEN
23H	Grounded	Grounded

CANOPEN BUTTON OUTPUT CONFIGURATION

BUTTON STATUS IS TRANSMITTED IN THE ONE BYTE DATA FIELD OF FRAMES WITH AN IDENTIFIER OF 1A0 (DEFAULT)			
Identifier Byte 0			
1A0	Buttons (2:0)		

CANOPEN ANALOG OUTPUT CONFIGURATION

EIGHT BIT ANALOG DATA IS TRANSMITTED IN THE THREE BYTE DATA FIELD OF FRAMES WITH AN IDENTIFIER OF 2A0 (DEFAULT)				
Identifier Byte 0 Byte 1 Byte 2				
2A0	A_IN0 (7:0)	A_IN1 (7:0)	A_IN2 (7:0)	

CUSTOM CANOPEN FIRMWARE*

- Baud rate: 125 kbps, 500 kbps, 1Mbps (250 kbps default)
- Custom Node IDs (default 20 hexadecimal)
- 10-bit axis resolution
- 12-bit axis resolution
- Signed resolution
- Custom CANopen output



CANOPEN LSS INTERFACE SPECIFICATION

The CANopen LSS interface option follows the CiA305 and CiA401 standards for CAN in automation. The node ID, baud rate and additional configurations can be set and stored in the EEPROM by Service Data Object. The default settings are as follows:



CANOPEN LSS INTERFACE SPECIFICATION

CANOPEN INTERFACE PARAMETERS*

• Baud rate: 250 kbps

• Node ID: 20h (default)

• Buttons: 1A0H (180H + NODE ID)

• Analog (axis) outputs: 2A0h (280h + Node ID)

• Heartbeat (500ms): 720h (700h + Node ID)

• Axis resolution: 10-bit

• Network Management: Auto start enabled

CANOPEN LSS BUTTON OUTPUT CONFIGURATION

BUTTON STATUS IS TRANSMITTED IN THE ONE BYTE DATA FIELD OF FRAMES WITH AN IDENTIFIER OF 1A0 (DEFAULT)		
Identifier Byte 0		
1A0	Buttons (2:0)	

CANOPEN LSS ANALOG OUTPUT CONFIGURATION

TEN BIT ANALOG DATA IS TRANSMITTED IN THE SIX BYTE DATA FIELD OF FRAMES WITH AN IDENTIFIER OF 2A0 (DEFAULT)				
Identifier Byte 0 Byte 1 Byte 2				
2A0	A_IN0 (7:0)	A_IN0 (9:8)	A_IN1 (7:0)	
Identifier	Byte 3	Byte 4	Byte 5	
2A0 A_IN1 (9:8) A_IN2 (7:0) A_IN2 (9:8)				

^{*} Custom CAN bus firmware available upon request.

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



TERMINATION (CAN OUTPUTS ONLY)

- HF series joysticks configured with CAN outputs (Output options 2C and 3C only) feature a JST B6B-PH-S(LF)(SN) header (male receptacle) (Fig 1) and are supplied with a mating wire harness (Fig 2)
- Header specifications: JST B6B-PH-S(LF)(SN) 6 position, 2mm pitch, single row header (Fig 1)
- Mating wire harness specifications: Six conductor, 22 AWG, 56 cm PTFE, JST PHR-6 to stripped and tinned wire leads (Fig 2)



HEADER PINOUT AND MATING WIRE HARNESS COLOR DEFINITION

	MATING WIRE HARNESS		
JST B6B-PH- S(LF)(SN) HEADER PIN #	CAN BUS FUNCTION	CANOPEN FUNCTION	WIRE COLOR
1	Supply power (7 to 35 VDC)	Supply power (7 to 35 VDC)	Red
2	Ground	Ground	Black
3	ID select MSB	Node ID select MSB	Orange
4	ID select LSB	Node ID select LSB	Blue
5	CAN Hi	CAN Hi	Green
6	CAN Lo	CAN Lo	White




CANOPEN LSS INTERFACE SPECIFICATIONS


The CANopen LSS interface option follows the CiA305 and CiA401 standards for CAN in automation. The node ID, baud rate and additional configurations can be set and stored in the EEPROM by Service Data Object. The default settings are as follows:


SETTINGS	DEFAULT CONFIGURATION
Baud rate	250 kbits/s
Node ID	20h
Analog (axis) outputs	2A0h (280h + Node ID)
Buttons	1A0h (180h + Node ID)
Heartbeat (500ms)	720h (700h + Node ID)
Axis Resolution	Unsigned 10-bit



CAN BUS SPECIFICATIONS







^{*} Custom CAN bus firmware available upon request.

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



USB SPECIFICATIONS

• Supply Voltage Range: 5.00 VDC

• Maximum current: 70 mA

• USB version: 2.0

USB GAME CONTROLLER

Featuring USB 2.0 HID compliant interface, APEM's USB joysticks are recognized as standard HID "game controller" devices. Adhering to the HID specification, APEM's USB joysticks are plugand-play with most versions of Windows. Joystick button and axis assignments are dependent upon the controlled application.

Features

- USB 2.0 HID compliant "game controller" device
- · Easy to install and operate
- Functions determined by controlled application
- 12-bit (0 to 4095) axis resolution

Termination (supplied cable)

- USB Male Type A Connector (198 cm)
- (72" +/-1") overmolded cabled Mini B to Male Type A USB connector (option 0U)
- (84" +/-1") overmolded cable Male Type A USB connector (option 2U)

USB CURSOR EMULATION

The Cursor Emulation option converts multi-axis joystick output into a mouse or cursor control device. The Cursor Emulation option is ideal for vehicle applications subjected to dirt and high vibration which makes operating a traditional cursor control device difficult. Cursor simulation is only compatible with Window OS.

Features

• HID compliant "mouse" device

Button Function

- B1: Left Mouse Click
- B2: Right Mouse Click

Termination (supplied cable)

- USB Male Type A Connector (185 cm):
 - (72" +/-1") overmolded cabled Mini B to Male Type A USB connector

SUPPORTED OPERATING SYSTEMS: USB GAME CONTROLLER AND CURSOR EMULATION

Windows Operating System

- Windows 7
- Windows 8.1
- Windows 10

Linux Operating System

APEM's USB joysticks are compatible with Linux, although system compatibility is not guaranteed. The user is responsible for verifying specific Linux OS compatibility.

Custom Firmware

Custom configurations and firmware is available upon request. Available options include:

- 8-bit axis resolution
- 10-bit axis resolution
- · Signed bit axis resolution
- Custom USB product name

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



VOLTAGE REGULATOR SPECIFICATIONS

The Voltage Regulator allows APEM's Hall effect joysticks to operate with a range of supply voltages..

Voltage Regulator - Unipolar

- Supply Voltage Range: 8-35 VDC
- Output Voltage Range: see output options
- Maximum Current: 90 mA

Voltage Regulator - Bipolar

- Supply Voltage Range: 11-35 VDC
- Output Voltage Range: ±10 VDC
- Maximum Current: 90 mA

Termination (flying leads)

• 28 AWG 20.32 cm (8.0") ±1.54 cm (1") PTFE


WIRE DEFINITION)

WIRE COLOR	JOYSTICK FUNCTION
Black	Ground
Red	Supply power
Blue / white	X axis (dual output)
Blue	X axis
Yellow / black	Y axis (dual output)
Yellow	Y axis
Green / black	Z axis (dual output)
Green	Z axis
Orange	Button one
White	Button common
Violet	Button two

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology

(£3)

BUILD YOUR PART NUMBER



- 1 Output voltage is ratiometric to supple voltage.
- 2 Cable length is $6" \pm 1"$ fside of joystick to Male Type A USB connector.
- 3 Cable length is 84" ±1" from bottom of joystick to Male Type A USB connector.
- 4 Requires operating voltage 7V ≥ 35V.
- 5 Requires operating voltage $11V \ge 35V$.
- 6 Operating voltage: 7 35VDC.
- 7 L "locked" limiter plate is only recommended for handles with a rotational third / Z axis. Handles (33 56)
- 8 Optional mating wire harnesses may be selected for option options 0-11. Termination is included for output options 0U, 2U, 1J, 0V, BV, 2C, 3C, 4C.
- 9 R restricts or locks the Z axis function on handles 33-56. This option prevents the handle from rotating.

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology

HANDLE 10




HANDLE 11





HANDLE 27





25.40 (1.00)

41.15

(1.62)

φ.

35.56

(1.40)

Proportional multi-axis fingertip controllers • non-contacting Hall effect technology








HANDLE 46





Proportional multi-axis fingertip controllers • non-contacting Hall effect technology








HANDLE 52







Proportional multi-axis fingertip controllers • non-contacting Hall effect technology



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apem:

HFX36S10 HF10R11 HFX22S10 HFX11S10 HFX33S10 HF44S10 HF45S10U HF45R10 HFX33R13 HF10S11 HF45S12 HF22Y12 HF10S10 HF10P10 HFX44S10 HFX45S10 HFX10S10 HFX245S10 HF22Y10 HF33Y10 HF45S11 HF27Y11 HF22R10 HF11S10U HF46Y10 HF11P10 HF44Y10 HF33P10 HF27R11 HF22R10U HF22S10U HF11Y10 HF27S10U HF27P10 HF44R10 HF11S11 HF46S10 HF11X10 HF45Y10 HF44S12 HF45S40U HF46S411 HF45S40 HF11R11 HF11R10 HF45R41 HF27Y10 HF45P12 HF22Y10U HF46S41 HF45S41J HF10Y40 HF22S10 HF22X10U HF11R10U HF27Y12 HF33R10 HF45R10U HF11P11 HF45P10 HF44P10 HF10Y10 HF44R11 HF44S11 HF11R15 HF44R12 HF46S10U HF22P10 HF44R10U HF33S11 HF10S10U HF46P10 HF44R40V HF45W11 HF46R10U HF3396 HF3395 HF55S10 HF52S10 HF3397 HF46R10 HF55Y10 HF11Y11 HF22R40U HF55S11 HF44P10U HF50S10 HF51S10 HF22S12 HF50W18 HF46S110 HF27R111 HF11X41 HF11Z11 HF52S40U HF55Z10U