


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



**NOTES, UNLESS OTHERWISE SPECIFIED:**

**OCTT TOOL USE:**

This tool is intended to be used to terminate Panduit OptiCam connectors. The tool emits a laser beam, which, when used in conjunction with patch cord (sold separately), creates a glow effect from the connector which aides in proper connector termination.

Contact Panduit Corp. for a list of available replacement and additional parts for OptiCam connector products.

Complies with IEC 60825-1 Ed. 2 (2007). Complies with FDA performance standards for laser products except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007.

**TECHNICAL SPECIFICATIONS:**

Recommended use: With available patch cords only

Laser Diode type: Laser Light.-CLASS 1M LASER PRODUCT

Power Supply: 2 type AAA - 1.5 volt Alkaline batteries

Battery Life: Approx. 15 hours of continuous use

Operating temperature: 0° C to 40° C

Overall Dimensions: 2.0" H x 1.8" W x 6.7" L  
(52mm H x 47mm W x 172mm L)  
All dimensions are for reference only.

Weight: 4.7 oz (133 g) without batteries

FILE LOCATION: TEAMCENTER

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

**OCTT\*OptiCam Termination Tool  
Customer Drawing**

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.x) ± — (.xxx) ± —  
(.xx) ± — ANGLES ± —

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN IN  
INCHES, THIRD ANGLE  
PROJECTION.

DRAWN BY:  
BLR

MATL:

SCALE

DATE:  
3-31-05

----

DRAWING NO.

**FG24922B01**

DWG  
**B**  
SIZE

CHK'D:  
ABJ

|  |  |  |  |  |  |  |  |  |  |                                                                                                           |  |  |  |
|--|--|--|--|--|--|--|--|--|--|-----------------------------------------------------------------------------------------------------------|--|--|--|
|  |  |  |  |  |  |  |  |  |  | <b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS                                                                |  |  |  |
|  |  |  |  |  |  |  |  |  |  | <b>OCTT*OptiCam Termination Tool<br/>Customer Drawing</b>                                                 |  |  |  |
|  |  |  |  |  |  |  |  |  |  | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.x) ± — (.xxx) ± —<br>(.xx) ± — ANGLES ± — |  |  |  |
|  |  |  |  |  |  |  |  |  |  | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN IN<br>INCHES, THIRD ANGLE<br>PROJECTION.          |  |  |  |
|  |  |  |  |  |  |  |  |  |  | DRAWN BY:<br>BLR                                                                                          |  |  |  |
|  |  |  |  |  |  |  |  |  |  | MATL:<br>----                                                                                             |  |  |  |
|  |  |  |  |  |  |  |  |  |  | SCALE<br><b>NONE</b>                                                                                      |  |  |  |
|  |  |  |  |  |  |  |  |  |  | DATE:<br>3-31-05                                                                                          |  |  |  |
|  |  |  |  |  |  |  |  |  |  | CHK'D:<br>ABJ                                                                                             |  |  |  |
|  |  |  |  |  |  |  |  |  |  | DRAWING NO.<br><b>FG24922B01</b>                                                                          |  |  |  |
|  |  |  |  |  |  |  |  |  |  | DWG<br><b>B</b><br>SIZE                                                                                   |  |  |  |

|     |         |     |       |                              |      |     |      |     |  |  |  |  |  |
|-----|---------|-----|-------|------------------------------|------|-----|------|-----|--|--|--|--|--|
|     |         |     |       |                              |      |     |      |     |  |  |  |  |  |
|     |         |     |       |                              |      |     |      |     |  |  |  |  |  |
|     |         |     |       |                              |      |     |      |     |  |  |  |  |  |
| 03  | 3-19-15 | BLR | LWA   | UPD COMPLIANCE TEXT & LABELS | 4804 | --  | ABJ  |     |  |  |  |  |  |
| 02  | 8-04-11 | BLR | MABH  | UPD TOP VIEW GRAPHIC         | 4413 | --  | ABJ  |     |  |  |  |  |  |
| 01  | 4-14-05 | BLR | ABJ   | UPDATE BOTH LABELS           | 4152 | --  | DLWE |     |  |  |  |  |  |
| 00  | 3-31-05 | BLR | ABJ   | RELEASED                     | 4152 | --  | DLWE |     |  |  |  |  |  |
| REV | DATE    | BY  | CHK'D | DESCRIPTION                  | ECN  | - R | CUST | SUP |  |  |  |  |  |

Complies with FDA performance  
standards for laser products except  
for deviations pursuant to  
Laser Notice No. 50,  
dated June 24, 2007.

COMPLIANCE LABEL

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

OCTT