

## Insert label - EMT (40X17)R - 0817293

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter range: 16 ... 35 mm, lettering field size: 40 x 17 mm, Number of individual labels: 2300

### Your advantages

- ✓ EMT ... insert labels for labeling various marking collars
- ✓ Thanks to their special shape, EMT ... insert labels remain securely inside the collar once inserted
- ✓ Quick and inexpensive marking with THERMOMARK ... roll printers from PHOENIX CONTACT
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ Marking service: Phoenix Contact can custom-mark all EMT ... markers according to your requirements



### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 046356 124188 |
| GTIN         | 4046356124188                                                                                           |

### Technical data

#### Dimensions

|                |                 |
|----------------|-----------------|
| Length (b)     | 17 mm           |
| Width (a)      | 40 mm           |
| Cable diameter | 16 mm ... 35 mm |

#### Ambient conditions

|                                 |                                |
|---------------------------------|--------------------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C              |
| Recommended storage conditions  | 23 °C / 50 % relative humidity |

#### General

|            |                                |
|------------|--------------------------------|
| Color      | white                          |
| Components | free from silicone and halogen |
| Material   | Polyester                      |

## Insert label - EMT (40X17)R - 0817293

### Technical data

#### General

|                                                                     |                              |
|---------------------------------------------------------------------|------------------------------|
| RoHS compliant                                                      | Yes                          |
| Wipe resistance                                                     | DIN EN 61010-1 (VDE 0411-1)  |
| Number of individual labels                                         | 2300                         |
| Number of individual labels per row                                 | 2                            |
| Printability                                                        | Thermal transfer             |
| Device                                                              | 5146477 THERMOMARK ROLL      |
|                                                                     | 5145274 THERMOMARK X1.1      |
|                                                                     | 5146231 THERMOMARK X1.2      |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02         |
| Result                                                              | Test passed                  |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03 |
| Test duration                                                       | 96 h                         |
| Result of weather resistance test                                   | Test passed                  |
| Salt spray test specification                                       | DIN EN ISO 9227:2012-09      |
| Test duration                                                       | 96 h                         |
| Salt spray testing result                                           | Test passed                  |
| Alternating condensation climate with SO2 test specification        | DIN 50018:2013-05            |
| Climate level                                                       | AHT 1.0 S                    |
| Cycles                                                              | 2                            |
| Condensation test result                                            | Test passed                  |
| Foil strength                                                       | 175 µm                       |
| Marking mounting type                                               | insert                       |

#### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149129 |
| eCl@ss 8.0    | 27400401 |
| eCl@ss 9.0    | 27400629 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
|----------|----------|

## Insert label - EMT (40X17)R - 0817293

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

### Accessories

#### Accessories

##### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0817293