
820M1-6000-TRAY ~ ACTIVE

MEAS | MEAS 820 TE Internal #: 20007180-01 TE Internal Description: 820M1-6000 Single Axis, 6000g, Tray 820M1 Single Axis SMT Accelerometers View on TE.com >



Sensors > Vibration Sensors > Embedded Accelerometers > 820M1 Single Axis SMT Accelerometers



Acceleration Range (±): 6000 g Frequency Response: 2 to 10000 Hz Overall Acceleration Range (±): 6000 g Accelerometer Type: 3-Wire Voltage Number of Axes: 1

Features

Product Type Features

Accelerometer Type

Embedded Accelerometer Sensor Type

Electrical Characteristics

3-Wire Voltage

AC Response Embedded Accelerometers

Excitation Voltage	2.8 – 5.5 VDC
Full Scale Output Voltage	±1.25 VDC
Signal Characteristics	
Frequency Response	2 to 10000 Hz
Body Features	
Material	Ceramic
Weight	1 g[.04 oz]
Number of Axes	1
Mechanical Attachment	
Embedded Accelerometer Mounting Type	Solder
Usage Conditions	
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
Other	
Nonlinearity	±1 %FSO

820M1-6000 Single Axis, 6000g, Tray



Acceleration Range (±)	6000 g
Overall Acceleration Range (±)	6000 g
Sensitivity	.21 mV/g
Sensitivity Range	.21 mV/g

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




820M1-6000 Single Axis, 6000g, Tray



Also in the Series MEAS 820 Image: Measure of the series Measure of the series Image: Measure of the series Measure of the series Image: Measure of the series Measure of the series Image: Measure of the series Measure of the series Image: Measure of the series Measure of the series Image: Measure of the series Measure of the series

Customers Also Bought









Documents

CAD Files

3D PDF

3D

Customer View Model ENG_CVM_CVM_20007180-01_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_20007180-01_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_20007180-01_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

C For support call+1 800 522 6752

820M1-6000-TRAY

820M1-6000 Single Axis, 6000g, Tray



MODEL 820M1 ACCELEROMETER

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity: 20007180-01