



# QSFP28/56 and zQSFP+ Interconnects

TE Connectivity's (TE) Quad Small Form-Factor Pluggable (QSFP28/56) and z-Quad Small Form-Factor Pluggable Plus (zQSFP+) interconnects offer increased data rates of 28 Gbps NRZ and 56 Gbps PAM-4 in an industry standard, scalable design that allows for backwards compatibility with QSFP+ cables and transceivers, providing a simple upgrade path from 10 Gbps to 28 Gbps and 56 Gbps. The complete portfolio of interconnects deliver a large range of simple and customizable design options to meet most customer requirements. TE's zQSFP+ interconnects are dual sourced with Molex, LLC.

## Key Features

- Data transfer rates of 28 Gbps NRZ and 56 Gbps PAM-4
- Supports Ethernet and InfiniBand (IB) Enhanced Data Rate (EDR) requirements
- Supports single, dual and quad channel implementations

## Applications

- Network interface
- Switches
- Servers
- Routers
- Wireless Base Stations
- Test and Measurement Equipment

## Key Benefits


- Superior signal integrity and EMI protection through 56 Gbps
- Industry standard interface
- Backwards compatible with QSFP+ cables and transceivers
- Comprehensive product portfolio

## Applications By Protocol

- 50, 100 and 200 Gigabit Ethernet
- 100 Gbps InfiniBand (IB) Enhanced Data Rate (EDR) requirements
- 128G Fibre Channel
- 25G/50G Consortium
- 28G NRZ and 56G PAM-4

### Enhanced QSFP28/56 and zQSFP+ Cages

#### EMI Enhanced



Reference base part number 2170709 on page 7


#### Lower Assembly Insertion Force

Help increase assembly throughput by providing a 55% reduction in force needed to insert the line card into the front bezel. The reduction in insertion force makes assembly easier, faster, and reduces the risk for damage which can lead to reduced EMI performance.

#### Improved EMI Performance

EMI sealing enhancements on these new cages provide 10 dB EMI performance improvement over current QSFP28 products.

#### Thermally Enhanced



Reference base part numbers 2299940, 2299870, 2299924, 2321666 and 2321630 on page 7

#### Lower Port Cooling


Internal riding heatsink in the separator plate area provides enhanced cooling to the lower ports and a 12-15°C improvement over standard stacked zQSFP+ cages.

#### Optimized Airflow

External riding heatsinks on the upper port are optimized for airflow direction (also available without heatsinks).

Air vent holes allow for air to pass through and exit out the sides and rear of the cage.

#### Intel Omni-Path Architecture



Reference part numbers 2227670-7, 2300281-1, 2170704-1 and 1551920-2 on page 7

#### Designed for Intel Omni-Path Architecture

These QSFP28/56 and zQSFP+ 2x2 and 1x2 cages are specifically designed for Intel Omni-Path Architecture (OPA) switch architectures, and 1x1 QSFP28/56 cages for OPA NIC cards. Designing with these cages allows access to proven technology to support high performance applications.

#### Stacked Belly-to-Belly



Reference base part numbers 2314790, 2308171 and 2315050 on page 7

#### High Density

Certain stacked cages can be used in belly-to-belly applications to support high density 2RU+ box designs and switch designs using next-gen 48 and 64 silicon ports.

#### Low Cost

Using a stacked belly-to-belly design enables single PCB architecture versus two PCBs per line card, saving significant system costs.


### 1xN QSFP28/56 Mechanical Options

#### Bezel Mount


- Behind bezel cages use a gasket applied by the customer to the cage or bezel sheet metal
- EMI spring versions and gasket versions share the same PCB footprint and bezel cutout
- TE offers low insertion force EMI springs to assist in assembly of high density products



Through Bezel with EMI Springs



Through Bezel with EMI Gasket



Behind Bezel (customer applies gasket)



Single



Dual



Quad

#### Lightpipe Options

- TE offers 1, 2 or 4 lightpipe options per port
- Standard lightpipes are designed to support up to 1.00mm height 0805 style LEDs
- Lightpipes are shipped with an organizer to prevent optical cross-talk

#### Heat Sink Styles

- TE offers SAN, LAN and Networking height heatsinks
- Custom heatsinks are available upon request
- Height is max height of assembly from surface of PCB




PCI (13.7mm height)




SAN (16.0mm height)




NET (23.0mm height)



2 rear EONs



1 rear EONs



0 rear EON's


#### Rear EONs

- Rear pins are used to improve EMI grounding and cage retention to the PCB
- TE offers all styles outlined in the SFF-8662 footprint
- Rear EONs will be dependent upon the customer's routing preference and technical specifications

### 2xN zQSFP+ Mechanical Options

#### Bezel Mount


- Through bezel assemblies with EMI springs or EMI gaskets are available
- Custom gasketing options are available upon request




Through Bezel with EMI Springs



Through Bezel with EMI Gasket



Single (per port)




Dual (per port)

#### Lightpipe Options


- TE offers zero, single and dual lightpipe options per port
- For higher lightpipe counts, the customer may add lightpipes underneath their PCB to indicate lower port activity
- The thermal footprint design offers 4x lightpipes assembled above the cage
- Lightpipes are designed to support up to 0.80mm height 0805 style LEDs

#### Rear EONs

- Rear pins are used to improve EMI grounding and cage retention to the PCB
- TE offers zero or three rear pins per port column
- Rear EONs will be dependent upon the customer's routing preference and technical specifications



3 rear EONs



0 rear EONs

## Part Number Detail

### Cages

| Base Part Number | Ports | Cage Applications | EMI Suppression | Lightpipes Applied Per Port |      |      | Heat Sinks | Applied |     |
|------------------|-------|-------------------|-----------------|-----------------------------|------|------|------------|---------|-----|
|                  |       |                   |                 | Single                      | Dual | Quad |            | PCI     | SAN |
| 2170754          | 1x1   | Through Bezel     | EMI Gasket      | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170705          | 1x1   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170773          | 1x1   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | No         | No      | No  |
| 2170753          | 1x1   | Through Bezel     | EMI Gasket      | No                          | No   | No   | Yes        | Yes     | Yes |
| 2170752          | 1x1   | Through Bezel     | EMI Gasket      | No                          | No   | No   | No         | No      | No  |
| 2170704          | 1x1   | Through Bezel     | EMI Springs     | No                          | No   | No   | Yes        | Yes     | Yes |
| 2170703          | 1x1   | Through Bezel     | EMI Springs     | No                          | No   | No   | No         | No      | No  |
| 1551892          | 1x1   | Behind Bezel      | C               | No                          | No   | No   | Yes        | Yes     | Yes |
| 1551891          | 1x1   | Behind Bezel      | C               | No                          | No   | No   | No         | No      | No  |
| 2170814          | 1x2   | Through Bezel     | EMI Gasket      | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170813          | 1x2   | Through Bezel     | EMI Gasket      | Yes                         | Yes  | Yes  | No         | No      | No  |
| 2170808          | 1x2   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170807          | 1x2   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | No         | No      | No  |
| 2170812          | 1x2   | Through Bezel     | EMI Gasket      | No                          | No   | No   | Yes        | Yes     | Yes |
| 2170811          | 1x2   | Through Bezel     | EMI Gasket      | No                          | No   | No   | No         | No      | No  |
| 2170806          | 1x2   | Through Bezel     | EMI Springs     | No                          | No   | No   | Yes        | Yes     | Yes |
| 2170805          | 1x2   | Through Bezel     | EMI Springs     | No                          | No   | No   | No         | No      | No  |
| 2227103          | 1x2   | Behind Bezel      | C               | Yes                         | Yes  | No   | Yes        | Yes     | Yes |
| 2227103          | 1x2   | Behind Bezel      | C               | No                          | No   | No   | Yes        | Yes     | Yes |
| 2227104          | 1x2   | Behind Bezel      | C               | No                          | No   | No   | Open Top   |         |     |
| 2170769          | 1x3   | Through Bezel     | EMI Gasket      | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170740          | 1x3   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170739          | 1x3   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | No         | No      | No  |
| 2170768          | 1x3   | Through Bezel     | EMI Gasket      | No                          | No   | No   | Yes        | Yes     | Yes |
| 2170767          | 1x3   | Through Bezel     | EMI Gasket      | No                          | No   | No   | No         | No      | No  |
| 2170738          | 1x3   | Through Bezel     | EMI Springs     | No                          | No   | No   | Yes        | Yes     | Yes |
| 2170737          | 1x3   | Through Bezel     | EMI Springs     | No                          | No   | No   | No         | No      | No  |
| 2173239          | 1x3   | Behind Bezel      | C               | No                          | No   | No   | Yes        | Yes     | Yes |
| 2173238          | 1x3   | Behind Bezel      | C               | No                          | No   | No   | Open Top   |         |     |
| 2170785          | 1x4   | Through Bezel     | EMI Gasket      | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170784          | 1x4   | Through Bezel     | EMI Gasket      | Yes                         | Yes  | Yes  | No         | No      | No  |
| 2170747          | 1x4   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | Yes        | Yes     | Yes |
| 2170746          | 1x4   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | No         | No      | No  |

Part Number 1551920-2: zQSFP+ Surface Mount Connector for use with all 1xN QSFP28/56 cages

#### Notes:

C = Customer Applied Gasket  
 1xN cages: require a SMT connector to complete the assembly  
 2xN cages: connectors and cages come as one integrated assembly  
 All cages use EMI Plug 1888810-2

## Cages (con't)

| Base Part Number | Ports | Cage Applications | EMI Suppression | Lightpipes Applied Per Port |      |      | Heat Sinks             | Applied |     |
|------------------|-------|-------------------|-----------------|-----------------------------|------|------|------------------------|---------|-----|
|                  |       |                   |                 | Single                      | Dual | Quad |                        | PCI     | SAN |
| 2170783          | 1x4   | Through Bezel     | EMI Gasket      | No                          | No   | No   | Yes                    | Yes     | Yes |
| 2170782          | 1x4   | Through Bezel     | EMI Gasket      | No                          | No   | No   | No                     | No      | No  |
| 2170745          | 1x4   | Through Bezel     | EMI Springs     | No                          | No   | No   | Yes                    | Yes     | Yes |
| 2170744          | 1x4   | Through Bezel     | EMI Springs     | No                          | No   | No   | No                     | No      | No  |
| 2227249          | 1x4   | Behind Bezel      | C               | No                          | No   | No   | Yes                    | Yes     | Yes |
| 2227250          | 1x4   | Behind Bezel      | C               | No                          | No   | No   | Open Top               |         |     |
| 2315050          | 1x2   | Behind Bezel      | EMI Springs     | No                          | No   | Yes  | No                     | No      | No  |
| 2170790          | 1x4   | Through Bezel     | EMI Springs     | No                          | No   | Yes  | Custom Height          |         |     |
| 2299940          | 2x1   | Through Bezel     | EMI Springs     | Yes                         | Yes  | No   | Custom Height          |         |     |
| 2321666          | 2x1   | Through Bezel     | EMI Springs     | Yes                         | Yes  | No   | Single Piece Press Fit |         |     |
| 2299870          | 2x2   | Through Bezel     | EMI Springs     | Yes                         | Yes  | No   | Custom Height          |         |     |
| 2321630          | 2x2   | Through Bezel     | EMI Springs     | Yes                         | Yes  | No   | Single Piece Press Fit |         |     |
| 2299924          | 2x3   | Through Bezel     | EMI Springs     | Yes                         | Yes  | No   | Custom Height          |         |     |
| 2227670          | 2x2   | Belly-to-Belly    | EMI Springs     | No                          | No   | No   | No                     | No      | No  |
| 2300281          | 1x2   | Belly-to-Belly    | EMI Springs     | No                          | No   | No   | No                     | No      | No  |
| 2314790          | 2x1   | Belly-to-Belly    | EMI Springs     | Yes                         | Yes  | Yes  | No                     | No      | No  |
| 2308171          | 2x2   | Belly-to-Belly    | EMI Springs     | Yes                         | Yes  | Yes  | No                     | No      | No  |
| 2170708          | 1x6   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | Yes                    | Yes     | Yes |
| 2170734          | 1x6   | Through Bezel     | EMI Springs     | Yes                         | Yes  | Yes  | No                     | No      | No  |
| 2170707          | 1x6   | Through Bezel     | EMI Springs     | No                          | No   | No   | Yes                    | Yes     | Yes |
| 2170706          | 1x6   | Through Bezel     | EMI Springs     | No                          | No   | No   | No                     | No      | No  |
| 2334626-1        | 1x6   | Behind Bezel      | C               | No                          | No   | No   | No                     | No      | Yes |
| 2334626-2        | 1x6   | Behind Bezel      | C               | No                          | No   | No   | No                     | No      | Yes |
| 2198373          | 2x1   | Through Bezel     | EMI Gasket      | 0/1                         |      |      | No                     | No      | No  |
| 2227224          | 2x1   | Through Bezel     | EMI Gasket      | 0/1                         |      |      | No                     | No      | No  |
| 2287054          | 2x1   | Through Bezel     | EMI Gasket      | 2                           |      |      | No                     | No      | No  |
| 2227666          | 2x1   | Through Bezel     | EMI Springs     | 0/1                         |      |      | No                     | No      | No  |
| 2227669          | 2x1   | Through Bezel     | EMI Springs     | 0/1                         |      |      | No                     | No      | No  |
| 2227669          | 2x1   | Through Bezel     | EMI Springs     | 2                           |      |      | No                     | No      | No  |
| 2170608          | 2x1   | Through Bezel     | EMI Gasket      | 2**                         |      |      | Thermal Footprint      |         |     |
| 2214593          | 2x2   | Through Bezel     | EMI Gasket      | 0/1                         |      |      | No                     | No      | No  |
| 2227225          | 2x2   | Through Bezel     | EMI Gasket      | 0/1                         |      |      | No                     | No      | No  |
| 2287054          | 2x2   | Through Bezel     | EMI Gasket      | 2                           |      |      | No                     | No      | No  |
| 2227667          | 2x2   | Through Bezel     | EMI Springs     | 0/1                         |      |      | No                     | No      | No  |
| 2227670          | 2x2   | Through Bezel     | EMI Springs     | 0/1                         |      |      | No                     | No      | No  |
| 2289129          | 2x2   | Through Bezel     | EMI Springs     | 2                           |      |      | No                     | No      | No  |
| 2214565          | 2x3   | Through Bezel     | EMI Gasket      | 0/1                         |      |      | No                     | No      | No  |
| 2227226          | 2x3   | Through Bezel     | EMI Gasket      | 0/1                         |      |      | No                     | No      | No  |
| 2287054          | 2x3   | Through Bezel     | EMI Gasket      | 2                           |      |      | No                     | No      | No  |
| 2227668          | 2x3   | Through Bezel     | EMI Springs     | 0/1                         |      |      | No                     | No      | No  |
| 2227671          | 2x3   | Through Bezel     | EMI Springs     | 0/1                         |      |      | No                     | No      | No  |
| 2227671          | 2x3   | Through Bezel     | EMI Springs     | 2                           |      |      | No                     | No      | No  |
| 2170610          | 2x3   | Through Bezel     | EMI Gasket      | 1/2**                       |      |      | Thermal Footprint      |         |     |

Part Number 1551920-2: zQSFP+ Surface Mount Connector for use with all 1xN QSFP28/56 cages

### Notes:

C = Customer Applied Gasket  
 1xN cages: require a SMT connector to complete the assembly  
 2xN cages: connectors and cages come as one integrated assembly  
 All cages use EMI Plug 1888810-2

### Accessories

| Type                    | Description                                                 | Part Number(s)        |
|-------------------------|-------------------------------------------------------------|-----------------------|
| Surface Mount Connector | zQSFP+ SMT connector (For use with all 1xN QSFP28/56 cages) | 1551920-2             |
| Behind Bezel            | 1x1 Heat Sink Clip                                          | 2007304-5             |
|                         | 1xN Heat Sink Clip                                          | 2227644-3, -4, -6     |
|                         | 1x1 Single Lightpipe                                        | 2173481-1             |
|                         | 1xN Single Lightpipe                                        | 2173482-1, -2, -3, -7 |
| Through Bezel           | 1x1 Heats Sink Clip                                         | 2007304-5             |
|                         | 1xN Heat Sink Clip                                          | 2227644-3, -4, -6     |
|                         | 1x1 Single Lightpipe                                        | 2170720-1             |
|                         | 1x1 Dual Lightpipe                                          | 2170762-1             |
|                         | 1x1 Quad Lightpipe                                          | 2170777-1             |
|                         | 1xN Single Lightpipe                                        | 2170720-1             |
|                         | 1xN Dual Lightpipe                                          | 2170761-1             |
|                         | 1xN Quad Lightpipe                                          | 2170762-1             |

### Specifications

#### 1xN QSFP28/56 cages and zQSFP+ SMT connector

- Cage and Connector Product Spec: 108-19428
- zQSFP+ SMT Connector Application Spec: 114-32022
- QSFP28/56 Cage Assembly Applications Spec: 114-32023

#### 2xN Stacked zQSFP+

- Product Spec: 108-60102
- Application Spec: 114-60015

### Direct Attach Copper Cable Assemblies

TE's QSFP28 and QSFP56 passive copper cable assemblies feature eight differential copper pairs, providing four data transmission channels at speeds up to 28 Gbps NRZ and 56 Gbps PAM-4, and meet 100G Ethernet, 200G Ethernet and Infiniband Enhanced Data Rate (EDR) requirements.

Offered in a broad range of wire gauges – from 32AWG up to 26AWG – this 100G copper cable assembly features low insertion loss and low cross talk. This next generation cable assembly shares the same mating interface with QSFP+ and QSFP28 form factors, making it backward compatible with existing QSFP ports. QSFP28 and QSFP56 form factors can be used with current 40G, 100G and 200G applications with substantial signal integrity margin.



### Features and Benefits

- Compatible with IEEE 802.3cd, IEEE 802.3bj, IEEE 802.3by and InfiniBand EDR
- Optimized construction to minimize insertion loss and cross talk
- Customized 360° cable braid termination limits EMI radiation
- Compatible with all existing QSFP connectors and cages
- Pull-to-release slide latch design
- 32AWG up to 26AWG
- Straight and breakout assembly configurations available
- Customizable EEPROM mapping for cable signature
- RoHS compliant
- Low smoke zero halogen options available by request
- Contact your TE Representative for customized lengths

## Part Number Detail

### QSFP28 Cable Assemblies

| Base Part Number | Description                        | AWG | Dash to Length (meters) |    |     |    |     |    |     |    |     |     |
|------------------|------------------------------------|-----|-------------------------|----|-----|----|-----|----|-----|----|-----|-----|
|                  |                                    |     | 0.5                     | 1  | 1.5 | 2  | 2.5 | 3  | 3.5 | 4  | 4.5 | 5   |
| 2336313          | QSFP28 to QSFP28 Straight Assembly | 32  | -1                      | -2 | -3  | -4 |     |    |     |    |     |     |
| 2333393          |                                    | 30  | -1                      | -3 | -4  | -5 | -6  | -7 |     |    |     |     |
| 2333841          |                                    | 28  | -1                      | -2 | -3  | -4 | -5  | -6 | -7  | -8 |     |     |
| 2333842          |                                    | 26  | -1                      | -2 | -3  | -4 | -5  | -6 | -7  | -8 | -9  | -10 |
| 2340655          | QSFP28 to 2xQSFP28 Breakout Cable  | 32  | -1                      | -2 | -3  | -4 |     |    |     |    |     |     |
| 2333801          |                                    | 30  | -1                      | -2 | -3  | -4 | -5  | -6 |     |    |     |     |
| 2333843          |                                    | 28  | -1                      | -2 | -3  | -4 | -5  | -6 | -7  | -8 |     |     |
| 2333844          |                                    | 26  | -1                      | -2 | -3  | -4 | -5  | -6 | -7  | -8 | -9  | -10 |
| 2340654          | QSFP28 to 4xSFP28 Breakout Cable   | 32  | -1                      | -2 | -3  | -4 |     |    |     |    |     |     |
| 2334236          |                                    | 30  | -1                      | -2 | -3  | -4 |     |    |     |    |     |     |
| 2334877          |                                    | 28  | -1                      | -2 | -3  | -4 | -5  | -6 | -7  | -8 |     |     |
| 2334878          |                                    | 26  | -1                      | -2 | -3  | -4 | -5  | -6 | -7  | -8 | -9  | -10 |

### QSFP56 Cable Assemblies

| Base Part Number | Description                           | AWG | Dash to Length (meters) |     |     |     |     |     |
|------------------|---------------------------------------|-----|-------------------------|-----|-----|-----|-----|-----|
|                  |                                       |     | 0.5                     | 1   | 1.5 | 2   | 2.5 | 3   |
| 2336313          | QSFP56 to QSFP56<br>Straight Assembly | 32  | -41                     | -42 | -43 |     |     |     |
| 2333393          |                                       | 30  | -41                     | -43 | -44 | -45 |     |     |
| 2333841          |                                       | 28  | -41                     | -42 | -43 | -44 | -45 |     |
| 2333841          |                                       | 26  | -41                     | -42 | -43 | -44 | -45 | -46 |
| 2340655          | QSFP56 to 2xQSFP56<br>Breakout Cable  | 32  | -41                     | -42 | -43 |     |     |     |
| 2333801          |                                       | 30  | -41                     | -42 | -43 | -44 |     |     |
| 2333843          |                                       | 28  | -41                     | -42 | -43 | -44 | -45 |     |
| 2333844          |                                       | 26  | -41                     | -42 | -43 | -44 | -45 | -46 |
| 2340654          | QSFP28 to 4xSFP56<br>Breakout Cable   | 32  | -41                     | -42 | -43 |     |     |     |
| 2334236          |                                       | 30  | -41                     | -42 | -43 | -44 |     |     |
| 2334877          |                                       | 28  | -41                     | -42 | -43 | -44 | -45 |     |
| 2334878          |                                       | 26  | -41                     | -42 | -43 | -44 | -45 | -46 |

### Frequently Asked Questions

#### What data rates do QSFP28/56 and zQSFP+ support?

These products provide four data transmission channels at speeds up to 28 Gbps NRZ and 56 Gbps PAM-4 per channel.

#### Is TE's footprint compatible with other suppliers?

TE's 1xN QSFP28/56 cages are designed to SFF-8663 and are industry standard. TE's zQSFP+ SMT connector and 2xN assemblies are dual sourced with Molex, LLC.

#### Are heat sinks available?

Yes, TE offers a generous portfolio of heat sink heights and styles, as well as custom heat sinks upon request.

#### Is application tooling required?

Single port cage assemblies require only flat-rock tooling, while 1xN and stacked assemblies normally require specific application tooling.

### For More Information

#### TE Technical Support Center

|                   |                    |
|-------------------|--------------------|
| USA:              | 1.800.522.6752     |
| Canada:           | 1.905.475.6222     |
| Mexico:           | 52.0.55.1106.0800  |
| Latin/S. America: | 54.0.11.4733.2200  |
| Germany:          | 49.0.6251.133.1999 |
| UK:               | 44.0.800.267666    |
| France:           | 33.0.1.3420.8686   |
| Netherlands:      | 31.0.73.6246.999   |
| China:            | 86.0.400.820.6015  |

[te.com/products/qsfp](https://te.com/products/qsfp)

© 2019 TE Connectivity Ltd. family of companies. All Rights Reserved.

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks.  
zQSFP+ is a part of the ZXP\* family of connectors and uses ZXP technology. ZXP is a trademark of Molex, LLC.

5-1773463-0 DND 05/2019

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2227226-2](#)